



## Rugged Stainless Steel Pressure Transducers Featuring Microfused Technology (Cont.)

Operating Pressure Range PSIG	Voltage Supply (VDC)	Digi-Key Part No.	Price Each		Measurement Specialties Part No.
			1	10	
500	5	MSP3501P2-ND	75.55	63.30	2000260
1000		MSP3102P2-ND	75.55	63.30	2000046
2500		MSP3252P2-ND	75.55	63.30	2000223
5000		MSP3502P2-ND	75.55	63.30	2000099
10000		MSP3103P2-ND	75.55	63.30	2000158
<b>1V - 5V Output - Fixed 3 Wire Supply Current 10mA Maximum 1/4" NPT, 2 Foot Cable</b>					
100	10 - 32	MSP3101P3-ND	79.75	66.82	2000133
250		MSP3251P3-ND	79.75	66.82	2000204
500		MSP3501P3-ND	79.75	66.82	2000262
1000		MSP3102P3-ND	79.75	66.82	2000048
2500		MSP3252P3-ND	79.75	66.82	2000226
5000	10 - 32	MSP3502P3-ND	79.75	66.82	2000100
10000		MSP3103P3-ND	79.75	66.82	2000159
<b>1V - 5V - Output 1/8" NPT, 2 Foot Cable - RoHS Compliant</b>					
100	10 - 32	MSP3101P4A1-ND	79.75	66.82	2000132
250		MSP3251P4A1-ND	79.75	66.82	2000203
500		MSP3501P4A1-ND	79.75	66.82	2000261
1000		MSP3102P4A1-ND	79.75	66.82	2000047
<b>4mA - 20mA Output - 2 Wire Regulated Supply 1/4" NPT, 2 Foot Cable</b>					
100	10 - 32	MSP3101P4-ND	79.41	68.07	2000137
250		MSP3251P4-ND	79.41	68.07	2000207
500		MSP3501P4-ND	79.41	68.07	2000264
1000		MSP3102P4-ND	79.41	68.07	2000050
2500		MSP3252P4-ND	79.41	68.07	2000227
5000	10 - 32	MSP3502P4-ND	79.41	68.07	2000101
10000		MSP3103P4-ND	79.41	68.07	2000160
<b>4mA - 20mA Output - 1/8" NPT, 2 Foot Cable</b>					
100	10 - 32	MSP3101P5A1-ND	79.41	68.07	2000136
250		MSP3251P5A1-ND	79.41	68.07	2000206
500		MSP3501P5A1-ND	79.41	68.07	2000263
1000		MSP3102P5A1-ND	79.41	68.07	2000049
<b>MSP-340 Series - RoHS Compliant</b>					
<b>100mV Output - 1/8" NPT, 2 Foot Cable</b>					
100	5	MSP6892-ND	69.81	58.50	M3421-000006-100PG
300		MSP6893-ND	69.81	58.50	M3421-000006-300PG
500		MSP6894-ND	69.81	58.50	M3421-000006-500PG
1000		MSP6895-ND	69.81	58.50	M3421-000006-01KPG
<b>0.5V - 4.5V Output - 1/8" NPT, 2 Foot Cable</b>					
100	5	MSP6896-ND	81.60	68.37	M3431-000006-100PG
300		MSP6897-ND	81.60	68.37	M3431-000006-300PG
500		MSP6898-ND	81.60	68.37	M3431-000006-500PG
1000		MSP6899-ND	81.60	68.37	M3431-000006-01KPG
<b>MSP-400 Series - RoHS Compliant</b>					
<b>1V - 5V Output - Fixed 3 Wire Supply Current 10mA maximum 1/4" NPT, 2 Foot Cable</b>					
5000	10 - 32	MSP4502P3-ND	68.61	58.81	2000455
<b>4mA - 20mA Output - 2 Wire Regulated Supply 1/4" NPT, 2 Foot Cable</b>					
1000	10 - 32	MSP4102P4-ND	78.77	67.52	2000417
5000		MSP4502P4-ND	78.77	67.52	2000457
<b>MSP-600 Series - RoHS Compliant</b>					
<b>0.5VDC - 4.5VDC Output - 7/16" SAE, Packard Connector</b>					
25	5	MSP6025P3-4-ND	69.88	59.90	2000964
50		MSP6050P3-4-ND	69.88	59.90	2000965
75		MSP6075P3-4-ND	69.88	59.90	2000966
100		MSP6101P3-4-ND	69.88	59.90	2000967
500		MSP6501P3-4-ND	69.88	59.90	2000969
1000		MSP6102P3-4-ND	69.88	59.90	2000970
<b>1VDC - 5VDC Output - 1/4" NPT, 2 Foot Cable</b>					
75	10 - 30	MSP6075P4-1-ND	73.69	63.17	2000884
<b>4mA - 20mA Output - 1/4" NPT, 2 Foot Cable</b>					
50	10 - 30	MSP6050P5-1-ND	86.39	74.06	2000879
75		MSP6075P5-1-ND	86.39	74.06	2000885
2500		MSP6252P5-1-ND	86.39	74.06	2000915
<b>MSP-610 Series - RoHS Compliant</b>					
<b>0.5V - 4.5V Output - 1/8" NPT, 2 Foot Cable</b>					
300	5	MSP6906-ND	82.90	71.06	M6131-C00006-300PG
500		MSP6907-ND	82.90	71.06	M6131-C00006-500PG
<b>0.5V - 4.5V Output - 1/4" NPT, 2 Foot Cable</b>					
100	5	MSP6903-ND	82.90	71.06	M6131-C00005-100PG
500		MSP6905-ND	82.90	71.06	M6131-C00005-500PG
<b>1V - 5V Output - 1/4" NPT, 2 Foot Cable</b>					
300	8 - 30	MSP6909-ND	86.39	74.06	M6141-C00005-300PG
500		MSP6910-ND	86.39	74.06	M6141-C00005-500PG
<b>4mA - 20mA Output - 1/4" NPT, 2 Foot Cable</b>					
100	10 - 30	MSP6911-ND	98.47	84.40	M6181-C00005-100PG
300		MSP6912-ND	98.47	84.40	M6181-C00005-300PG
500		MSP6913-ND	98.47	84.40	M6181-C00005-500PG
<b>UltraStable 5100 Series - RoHS Compliant</b>					
<b>0.5V - 4.5V Ratiometric Output - 1/4" NPT, Absolute Pressure, 2 Foot Cable</b>					
15PSIA	4.75 - 5.25	223-1000-ND	127.05	108.90	U5131-000005-015PA
30PSIA		223-1002-ND	127.05	108.90	U5131-000005-030PA
100PSIA		223-1004-ND	127.05	108.90	U5131-000005-100PA

Operating Pressure Range PSIG	Voltage Supply (VDC)	Digi-Key Part No.	Price Each		Measurement Specialties Part No.
			1	10	
<b>4mA - 20mA Output - 1/4" NPT, Absolute Pressure, 2 Foot Cable</b>					
15PSIA	9 - 30	223-1007-ND	153.48	130.23	U5151-000005-015PA
30PSIA		223-1009-ND	153.48	130.23	U5151-000005-030PA
100PSIA		223-1011-ND	153.48	130.23	U5151-000005-100PA
<b>0.5V - 4.5V Ratiometric Output - 1/4" NPT, 2 Foot Cable</b>					
15	4.75 - 5.25	223-1001-ND	127.05	108.90	U5131-000005-015PG
30		223-1003-ND	127.05	108.90	U5131-000005-030PG
100		223-1005-ND	127.05	108.90	U5131-000005-100PG
500		223-1006-ND	127.05	108.90	U5131-000005-500PG
<b>4mA - 20mA Output - 1/4" NPT, 2 Foot Cable</b>					
15	9 - 30	223-1008-ND	153.48	130.23	U5151-000005-015PG
30		223-1010-ND	153.48	130.23	U5151-000005-030PG
100		223-1012-ND	153.48	130.23	U5151-000005-100PG
500		223-1013-ND	153.48	130.23	U5151-000005-500PG
<b>M5100 Series - RoHS Compliant</b>					
<b>0.5V - 4.5V Ratiometric Output - 1/4" NPT, 2 Foot Cable</b>					
50	4.75 - 5.25	223-1038-ND	83.37	71.47	M5131-000005-050PG
75		223-1041-ND	83.37	71.47	M5131-000005-075PG
100		223-1020-ND	83.37	71.47	M5131-000005-100PG
250		223-1026-ND	83.37	71.47	M5131-000005-250PG
500		223-1032-ND	83.38	71.48	M5131-000005-500PG
1000	4.75 - 5.25	223-1014-ND	83.37	71.47	M5131-000005-01KPG
2500		223-1029-ND	83.37	71.47	M5131-000005-2K5PG
5000		223-1017-ND	83.37	71.47	M5131-000005-05KPG
10000		223-1023-ND	83.37	71.47	M5131-000005-10KPG
<b>1V - 5V Output - 1/4" NPT, 2 Foot Cable</b>					
50	8 - 30	223-1039-ND	87.35	74.87	M5141-000005-050PG
75		223-1042-ND	87.35	74.87	M5141-000005-075PG
100		223-1021-ND	87.35	74.87	M5141-000005-100PG
250		223-1027-ND	87.35	74.87	M5141-000005-250PG
500		223-1033-ND	87.35	74.87	M5141-000005-500PG
1000	8 - 30	223-1015-ND	87.35	74.87	M5141-000005-01KPG
2500		223-1030-ND	87.35	74.87	M5141-000005-2K5PG
5000		223-1018-ND	87.35	74.87	M5141-000005-05KPG
10000		223-1024-ND	87.35	74.87	M5141-000005-10KPG
<b>4mA - 20mA Output - 1/4" NPT, 2 Foot Cable</b>					
50	9 - 30	223-1040-ND	91.32	78.28	M5151-000005-050PG
75		223-1043-ND	91.32	78.28	M5151-000005-075PG
100		223-1022-ND	91.32	78.28	M5151-000005-100PG
250		223-1028-ND	91.32	78.28	M5151-000005-250PG
500		223-1034-ND	91.32	78.28	M5151-000005-500PG
1000	9 - 30	223-1016-ND	91.32	78.28	M5151-000005-01KPG
2500		223-1031-ND	91.32	78.28	M5151-000005-2K5PG
5000		223-1019-ND	91.32	78.28	M5151-000005-05KPG
10000		223-1025-ND	91.32	78.28	M5151-000005-10KPG
<b>0.5V - 4.5V Ratiometric Output - 7/16" UNF Male, O-Ring, Packard Connector</b>					
50	4.75 - 5.25	223-1045-ND	83.37	71.47	M5134-000004-050PG
75		223-1046-ND	83.37	71.47	M5134-000004-075PG
100		223-1047-ND	83.37	71.47	M5134-000004-100PG
250		223-1048-ND	83.37	71.47	M5134-000004-250PG
500		223-1049-ND	83.37	71.47	M5134-000004-500PG
1000	4.75 - 5.25	223-1050-ND	83.37	71.47	M5134-000004-01KPG
2500		223-1051-ND	83.37	71.47	M5134-000004-2K5PG
5000		223-1052-ND	83.37	71.47	M5134-000004-05KPG
7500		223-1074-ND	83.37	71.47	M5134-000004-7K5PG
10000	223-1053-ND	83.37	71.47	M5134-000004-10KPG	
<b>1V - 5V Output - 7/16" UNF Male, O-Ring, Packard Connector</b>					
50	8 - 30	223-1055-ND	87.35	74.87	M5144-000004-050PG
75		223-1056-ND	87.35	74.87	M5144-000004-075PG
100		223-1057-ND	87.35	74.87	M5144-000004-100PG
250		223-1058-ND	87.35	74.87	M5144-000004-250PG
500		223-1059-ND	87.35	74.87	M5144-000004-500PG
1000	8 - 30	223-1060-ND	87.35	74.87	M5144-000004-01KPG
2500		223-1061-ND	87.35	74.87	M5144-000004-2K5PG
5000		223-1062-ND	87.35	74.87	M5144-000004-05KPG
7500		223-1075-ND	87.35	74.87	M5144-000004-7K5PG
10000	223-1063-ND	87.35	74.87	M5144-000004-10KPG	
<b>4mA - 20mA Output - 7/16" UNF Male, O-Ring, Packard Connector</b>					
50	9 - 30	223-1065-ND	91.32	78.28	M5154-000004-050PG
75		223-1066-ND	91.32	78.28	M5154-000004-075PG
100		223-1067-ND	91.32	78.28	M5154-000004-100PG
250		223-1068-ND	91.32	78.28	M5154-000004-250PG
500		223-1069-ND	91.32	78.28	M5154-000004-500PG
1000	9 - 30	223-1070-ND	91.32	78.28	M5154-000004-01KPG
2500		223-1071-ND	91.32	78.28	M5154-000004-2K5PG
5000		223-1072-ND	91.32	78.28	M5154-000004-05KPG
7500		223-1076-ND	91.32	78.28	M5154-000004-7K5PG
10000	223-1073-ND	91.32	78.28	M5154-000004-10KPG	

◆ RoHS Compliant



## Cable Harnesses

Pre-made Cable Harnesses from SSI Technology with the industry standard Packard™ Automotive Connector.



Description	Length Inch	Digi-Key Part No.	Price Each			SSI Technologies Part No.
			1	10	25	
Cable Harness Packard	12	734-1163-ND	8.47	7.57	7.10	P2432.3
Cable Harness Packard	36	734-1164-ND	15.17	14.56	13.17	P2435.3
Cable Harness Packard	72	734-1165-ND	19.19	18.47	16.87	14306.3