



A

图	描述	电路	尺寸 "A"		Digi-Key 零件编号	价格		AMP 零件编号		
			英寸 (mm)			1	25			
13A	直角柱, 0.64 (0.025) 方形, 镀锡	2	.200 (5.08)		A19450-ND	.19	1.23	640455-2		
		3	.300 (7.62)		A19451-ND	.19	1.69	640455-3		
		4	.400 (10.16)		A19452-ND	.19	2.25	640455-4		
		5	.500 (12.70)		A19453-ND	.22	3.09	640455-5		
		6	.600 (15.24)		A19454-ND	.22	3.50	640455-6		
		7	.700 (17.78)		A19455-ND	.22	3.97	640455-7		
		8	.800 (20.32)		A19456-ND	.22	4.19	640455-8		
		9	.900 (22.86)		A19457-ND	.27	21.82	640455-9		
		10	1.000 (25.40)		A19458-ND	.97	6.14	1-640455-0		
		11	1.100 (27.94)		A19459-ND	.38	8.51	1-640455-1		
		12	1.200 (30.48)		A19460-ND	.39	8.74	1-640455-2		
		13	1.300 (33.02)		A19461-ND	.67	15.12	1-640455-3		
		14	1.400 (35.56)		A19462-ND	.69	15.59	1-640455-4		
		15	1.500 (38.10)		A23932-ND	1.35	30.43	1-640455-5		
		13B	直角柱, 0.64 (0.025) 方形, 30μ 镀金	2	.200 (5.08)		A30778-ND	.85	19.06	3-641214-2
3	.300 (7.62)				A30779-ND	1.36	30.56	3-641214-3		
4	.400 (10.16)				A30780-ND	1.43	32.19	3-641214-4		
5	.500 (12.70)				A30781-ND	1.87	42.13	3-641214-5		
6	.600 (15.24)				A30782-ND	2.17	48.73	3-641214-6		
7	.700 (17.78)				A30783-ND	2.31	52.04	3-641214-7		
8	.800 (20.32)				A30784-ND	1.44	32.47	3-641214-8		
10	1.000 (25.40)				A30753-ND	2.62	59.06	4-641214-0		
11	1.100 (27.94)				A30754-ND	2.75	61.95	4-641214-1		
12	1.200 (30.48)				A30755-ND	2.97	66.91	4-641214-2		
13	1.300 (33.02)				A30756-ND	3.23	72.69	4-641214-3		
14	1.400 (35.56)				A30757-ND	3.41	76.82	4-641214-4		
15	1.500 (38.10)				A30758-ND	3.66	82.30	4-641214-5		
柱接头, 0.100" (2.54mm) 中心, 摩擦锁紧接头										
12B	直形柱, 0.64 (0.025) 方形, 镀锡			2	.200 (5.08)		A1921-ND	.32	2.13	640456-2
		3	.300 (7.62)		A19470-ND	.34	3.02	640456-3		
		4	.400 (10.16)		A1922-ND	.33	3.88	640456-4		
		5	.500 (12.70)		A19471-ND	.38	5.41	640456-5		
		6	.600 (15.24)		A1923-ND	.37	5.90	640456-6		
		7	.700 (17.78)		A19472-ND	.39	7.09	640456-7		
		8	.800 (20.32)		A1924-ND	.39	7.56	640456-8		
		9	.900 (22.86)		A19473-ND	.50	11.25	640456-9		
		10	1.000 (25.40)		A1925-ND	.40	8.98	1-640456-0		
		11	1.100 (27.94)		A19474-ND	.56	12.52	1-640456-1		
		12	1.200 (30.48)		A19475-ND	.57	12.76	1-640456-2		
		13	1.300 (33.02)		A19476-ND	.79	17.72	1-640456-3		
		14	1.400 (35.56)		A19477-ND	.82	18.43	1-640456-4		
		15	1.500 (38.10)		A24930-ND	1.19	26.79	1-640456-5		
		16	1.600 (40.64)		A29106-ND	1.27	28.68	1-640456-6		
		20	2.000 (50.80)		A29104-ND	1.55	34.92	2-640456-0		
		24	2.400 (60.96)		A29105-ND	1.93	43.38	2-640456-4		
		12A	直形柱, 0.64 (0.025) 方形, 30μ 镀金	2	.200 (5.08)		A30786-ND	.50	11.15	3-641215-2
				3	.300 (7.62)		A30787-ND	.77	17.42	3-641215-3
				4	.400 (10.16)		A30788-ND	.99	22.30	3-641215-4
				5	.500 (12.70)		A30789-ND	1.36	30.68	3-641215-5
				6	.600 (15.24)		A30790-ND	1.54	34.61	3-641215-6
				7	.700 (17.78)		A30791-ND	1.71	38.55	3-641215-7
				8	.800 (20.32)		A30792-ND	1.28	28.76	3-641215-8
9	.900 (22.86)				A30793-ND	2.13	47.99	3-641215-9		
10	1.000 (25.40)				A30759-ND	2.24	50.35	4-641215-0		
11	1.100 (27.94)				A30760-ND	2.48	55.85	4-641215-1		
12	1.200 (30.48)				A30761-ND	2.66	59.79	4-641215-2		
14	1.400 (35.56)				A30762-ND	3.11	70.02	4-641215-4		
15	1.500 (38.10)				A30763-ND	5.52	124.30	4-641215-5		
13B	直角柱, 0.64 (0.025) 方形, 镀锡			2	.200 (5.08)		A1926-ND	.35	2.30	640457-2
				3	.300 (7.62)		A19480-ND	.37	3.35	640457-3
		4	.400 (10.16)		A1927-ND	.36	4.19	640457-4		
		5	.500 (12.70)		A19481-ND	.47	6.62	640457-5		
		6	.600 (15.24)		A1928-ND	.45	7.09	640457-6		
		7	.700 (17.78)		A19482-ND	.41	7.32	640457-7		
		8	.800 (20.32)		A1929-ND	.44	8.51	640457-8		
		9	.900 (22.86)		A19483-ND	.40	8.98	640457-9		
		10	1.000 (25.40)		A1930-ND	.44	9.92	1-640457-0		
		11	1.100 (27.94)		A19484-ND	.46	10.40	1-640457-1		
		12	1.200 (30.48)		A19485-ND	.48	10.87	1-640457-2		
		13	1.300 (33.02)		A19486-ND	1.40	31.51	1-640457-3		
		14	1.400 (35.56)		A19487-ND	.50	11.34	1-640457-4		

图	描述	电路	尺寸 "A"		Digi-Key 零件编号	价格		AMP 零件编号			
			英寸 (mm)			1	25				
13B	直角柱, 0.64 (0.025) 方形, 30μ 镀金	2	.200 (5.08)		A30794-ND	.77	17.42	3-641216-2			
		3	.300 (7.62)		A30795-ND	1.08	24.39	3-641216-3			
		4	.400 (10.16)		A30796-ND	1.50	33.83	3-641216-4			
		5	.500 (12.70)		A30797-ND	1.71	38.55	3-641216-5			
		6	.600 (15.24)		A30798-ND	1.96	44.05	3-641216-6			
		7	.700 (17.78)		A30799-ND	2.06	46.41	3-641216-7			
		8	.800 (20.32)		A30800-ND	1.44	32.47	3-641216-8			
		9	.900 (22.86)		A30801-ND	2.24	50.35	3-641216-9			
		10	1.000 (25.40)		A30764-ND	2.38	53.49	4-641216-0			
		11	1.100 (27.94)		A30765-ND	2.66	59.79	4-641216-1			
		12	1.200 (30.48)		A30766-ND	4.34	97.71	4-641216-2			
		13	1.300 (33.02)		A30767-ND	3.15	70.80	4-641216-3			
		14	1.400 (35.56)		A30768-ND	3.39	76.31	4-641216-4			
		15	1.500 (38.10)		A30769-ND	5.59	125.87	4-641216-5			
		屏幕接头, 0.100" (2.54mm)									
14	直形柱, 0.64 (0.025) 方形带柱, 镀锡	2	—		A30892-ND†	.60	13.58	2-644486-2			
		3	—		A30893-ND†	.68	15.41	2-644486-3			
		4	—		A30894-ND†	.66	14.83	2-644486-4			
		5	—		A30895-ND†	.89	19.97	2-644486-5			
		6	—		A30896-ND†	.97	21.78	2-644486-6			
		8	—		A30898-ND†	.47	10.57	2-644486-8			
		10	—		A30854-ND†	1.61	36.30	3-644486-0			
		12	—		A30856-ND†	1.94	43.56	3-644486-2			
		13	—		A30857-ND†	2.10	47.19	3-644486-3			
		14	—		A30858-ND†	2.26	50.82	3-644486-4			
		2	—		A30931-ND†	.33	7.39	2-644861-2			
		3	—		A30932-ND†	.47	10.55	2-644861-3			
		4	—		A30933-ND†	.66	14.83	2-644861-4			
		5	—		A30934-ND†	.89	19.97	2-644861-5			
6	—		A30935-ND†	.97	21.78	2-644861-6					
7	—		A30936-ND†	1.13	25.41	2-644861-7					
8	—		A30937-ND†	.47	10.57	2-644861-8					
9	—		A30938-ND†	1.45	32.67	2-644861-9					
10	—		A30879-ND†	1.61	36.30	3-644861-0					
12	—		A30881-ND†	1.94	43.56	3-644861-2					
13	—		A30882-ND†	2.10	47.19	3-644861-3					
14	—		A30883-ND†	2.26	50.82	3-644861-4					
15A	直角柱, 0.64 (0.025) 方形, 前弯角不带柱, 镀锡	2	.284 (7.21)		A30900-ND†	.34	7.68	2-644488-2			
		3	.384 (9.75)		A30901-ND†	.51	11.51	2-644488-3			
		4	.484 (12.29)		A30902-ND†	.68	15.35	2-644488-4			
		6	.684 (17.37)		A30904-ND†	1.00	22.54	2-644488-6			
		10	1.084 (27.53)		A30859-ND†	1.67	37.57	3-644488-0			
		11	1.184 (30.07)		A30860-ND†	1.84	41.33	3-644488-1			
		13	1.384 (35.15)		A30862-ND†	2.17	48.84	3-644488-3			
15B	直角柱, 0.64 (0.025) 方形, 后弯角不带柱, 镀锡	2	.284 (7.21)		A30924-ND†	.34	7.68	2-644803-2			
		3	.384 (9.75)		A30925-ND†	.51	11.51	2-644803-3			
		4	.484 (12.29)		A30926-ND†	.68	15.35	2-644803-4			
		5	.584 (14.83)		A30927-ND†	.92	20.67	2-644803-5			
		6	.684 (17.37)		A30928-ND†	1.00	22.54	2-644803-6			
		9	.984 (24.99)		A30830-ND†	.20	2.96	2-644803-9			
		10	1.084 (27.53)		A30874-ND†	1.67	37.57	3-644803-0			
		12	1.284 (32.61)		A30876-ND†	2.00	45.09	3-644803-2			
		13	1.384 (35.15)		A30877-ND†	2.17	48.84	3-644803-3			
		用于 MTA 0.100" (2.54mm) 的 T 手柄工具						A9982-ND	17.30	—	59803-1
		用于 MTA 0.100" (2.54mm) 贯通插座的压接模具 (必须使用手柄 A2031-ND) 与图 1 配合使用						A9973-ND	619.50	—	58442-1
		用于 MTA 0.100" (2.54mm) IDC 闭端插座的压接模具 (必须与 A2031-ND 手柄一起使用) 与图 1 配合使用						A1998-ND	118.95	—	58246-1
		用于金属和全塑料外壳连接器的手动枪式手柄。 (必须另行订购压接模具) 与图 1 配合使用						A2031-ND	63.72	—	58074-1
用于 CST-100 的压接工具, 带模具						A19530-ND	318.60	—	58517-1		
用于 CST-100 的模具 (与 A9996-ND 配合使用)						A19531-ND	267.30	—	58517-2		
用于 CST-100 的压接工具手柄						A9996-ND	45.36	—	354940-1		

† UL94V-0 - 黑色底座

全部产品均以美元计价。 \$30 美元基本运费

www.digikey.cn — 免费电话: 4008 824 440, 电话: (852) 3104 0500 — 传真: (852) 3104 0686 (CN2011-ZH) 199