



C

图	VCEO (V)	IC (mA)	最小 HFE	Digi-Key 零件编号	价格			带卷§	
					1	25	100	数量	价格
<b>NPN 晶体管</b>									
<b>TO-92</b>									
10	500	15		PN5134-ND◆	.44	5.00	14.00	—	—
15	50	20		2N5770-ND◆	.50	5.63	15.75	—	—
15	200	20		2N5769-ND	.47	5.38	15.05	—	—
15	200	20		PN2369-ND	.46	5.23	14.63	—	—
15	200	18		PN4275-ND◆	.44	5.00	14.00	—	—
15	200	20		PN2369A-ND◆	.46	5.25	14.70	—	—
20	1,200	20,000		MPSA12-ND	.58	6.60	18.48	—	—
25	50	60		MPSH10FS-ND◆	.45	6.25	18.92	—	—
25	100	150		MPS2924-ND	.35	5.80	18.87	—	—
25	200	15		PN5135-ND	.43	5.97	18.08	—	—
25	200	150		MPS6515-ND	.48	5.45	15.26	—	—
25	500	150		PN3565-ND◆	.52	5.88	16.45	—	—
30	100	300		2N5088BU-ND◆	.42	4.50	12.00	—	—
30	100	420		BC548C-ND	.52	5.90	16.52	—	—
30	500	100		BC184C-ND◆	.52	5.95	16.66	—	—
30	500	100		BC184L-ND◆	.52	5.90	16.52	—	—
30	600	35		PN2222BU-ND	.47	4.99	13.30	—	—
30	1,200	5,000		MPSA13-ND◆	.58	6.60	18.48	—	—
30	1,200	10,000		MPSA14-ND◆	.58	6.60	18.48	—	—
30	1,200	30,000		BC517-ND◆	.60	6.78	18.97	—	—
40	200	40		2N3904FS-ND◆	.42	4.50	12.00	—	—
40	200	30		2N3904D26ZCT-ND◆Δ	.41	4.39	11.70	2,000	32.00/M
40	200	30		2N3904TFCT-ND◆Δ	.41	4.39	11.70	2,000	32.00/M
40	500	100		PN3569-ND◆	.43	4.85	13.59	—	—
40	600	20		2N4400-ND◆	.47	4.99	13.30	—	—
40	600	20		2N4401-ND◆	.47	4.99	13.30	—	—
40	600	20		2N4401D26ZCT-ND◆Δ	.47	4.99	13.30	2,000	36.00/M
40	600	20		2N4401D75ZCT-ND◆Δ◇	.47	4.99	13.30	2,000	36.00/M
40	600	20		2N4401TFCT-ND◆Δ	.47	4.99	13.30	—	—
40	600	40		PN3567-ND◆	.43	4.85	13.59	—	—
40	1,000	35		PN2222AFS-ND	.47	4.99	13.30	—	—
40	1,000	35		PN2222AD26ZCT-ND◆Δ	.47	4.99	13.30	2,000	36.00/M
45	100	400		MPSA18-ND◆	.52	5.88	16.45	—	—
45	100	80		PN100RMCT-ND◆Δ◇	.59	6.76	18.80	—	—
45	100	110		BC547-ND◆	.52	5.90	16.52	—	—
45	100	110		BC547BFS-ND◆	.52	5.95	16.66	—	—
45	100	110		BC547BTACT-ND◆Δ◇	.42	4.50	12.00	2,000	32.40/M
45	100	110		BC550-ND◆	.52	5.90	16.52	—	—
45	800	60		BC337-ND◆	.44	6.18	18.71	—	—
45	800	100		BC33725TACT-ND◆Δ◇	.48	5.14	13.70	2,000	36.99/M
45	800	170		BC33740TACT-ND◆Δ◇	.50	5.40	14.40	2,000	38.88/M
50	100	200		2N5210-ND◆	.42	4.50	12.00	—	—
50	100	40		BC182-ND◆	.52	5.95	16.66	—	—
60	100	20		PN2484-ND◆	.53	6.05	16.94	—	—
65	100	110		BC546-ND◆	.52	5.95	16.66	—	—
80	500	100		MPSA06-ND◆	.40	5.55	16.80	—	—
80	500	100		MPSA06RACT-ND◆Δ	.44	6.26	19.02	2,000	63.00/M
80	1,000	25		BC639-ND◆	.42	5.93	17.97	—	—
100	200	60		2N5830-ND	.45	5.15	14.42	—	—
100	1,500	1,000		2N7052-ND◆	.43	6.26	20.02	—	—
200	200	25		MPSA43-ND	.41	5.76	17.44	—	—
300	500	25		MPSA42FS-ND◆	.38	5.25	15.90	—	—
300	500	25		MPSA42_D26ZTR-ND	—	—	—	8,000	54.00/M
400	300	40		KSP44TACT-ND◆Δ◇	.62	7.13	19.84	2,000	58.28/M
400	1,500	5		FJN13003TACT-ND◆Δ◇	.46	7.61	25.00	2,000	105.77/M
400	1,500	5		FJN3303TACT-ND◆Δ◇	.59	8.30	25.20	2,000	71.65/M

图	VCEO (V)	IC (mA)	最小 HFE	Digi-Key 零件编号	价格			带卷§	
					1	25	100	数量	价格
<b>SOT-23 - 符合 RoHS 规范要求</b>									
12	50	25		MMBT5179CT-NDΔ	.43	4.92	13.68	3,000	40.19/M
12	200	25		BSV52CT-NDΔ	.41	4.35	11.60	3,000	31.00/M
15	200	20		MMBT2369ACT-NDΔ	.49	5.21	13.90	3,000	37.53/M
25	50	60		MMBT10FSCCT-NDΔ	.43	4.92	13.68	3,000	40.00/M
25	100	300		MMBT5089CT-NDΔ	.38	4.37	12.16	3,000	36.00/M
25	200	60		KST10MTFCT-NDΔ	.46	4.95	13.20	3,000	36.00/M
30	100	300		MMBT5088CT-NDΔ	.51	5.48	14.60	3,000	39.42/M
30	100	110		BC848CMTFCT-NDΔ	.41	4.35	11.60	3,000	31.00/M
30	1,200	4,000		BCV27CT-NDΔ	.41	4.66	12.96	3,000	38.00/M
30	1,200	5,000		MMBTA13FSCCT-NDΔ	.44	5.06	14.08	3,000	41.00/M
40	200	30		MMBT3904FSCCT-NDΔ	.35	3.79	10.10	3,000	27.00/M
40	600	20		MMBT4401FSCCT-NDΔ	.43	4.65	12.40	3,000	33.48/M
40	800	35		BSR14CT-NDΔ	.44	4.73	12.60	3,000	34.02/M
40	200	30		BSR17ACT-NDΔ	.46	4.95	13.20	3,000	36.00/M
40	1,000	35		MMBT2222AFSCCT-NDΔ	.39	4.13	11.00	3,000	29.70/M
40	1,200	10,000		MMBT6427FSCCT-NDΔ	.46	5.23	14.56	3,000	43.00/M
45	100	110		BC847BMTFCT-NDΔ	.41	4.35	11.60	3,000	31.00/M
45	100	110		BC847CMTFCT-NDΔ	.41	4.35	11.60	3,000	31.00/M
45	800	100		BC81725MTFCT-NDΔ	.50	5.40	14.40	3,000	39.00/M
50	500	250		MMBT6428CT-NDΔ	.51	5.48	14.60	3,000	39.42/M
50	800	100		BC81740MTFCT-NDΔ	.50	5.40	14.40	3,000	38.88/M
65	100	110		BC846BMTFCT-NDΔ	.41	4.35	11.60	3,000	31.00/M
80	500	100		MMBTA06FSCCT-NDΔ	.52	5.98	16.64	3,000	49.00/M
160	600	30		MMBT5551FSCCT-NDΔ	.38	4.37	12.16	3,000	35.72/M
300	500	25		MMBTA42FSCCT-NDΔ	.56	6.38	17.76	3,000	52.00/M
300	500	25		KST42MTFCT-NDΔ	.38	4.34	12.08	3,000	35.49/M
<b>SOT-223 - 符合 RoHS 规范要求</b>									
3	40	1,000	35	PZT2222ACT-NDΔ	.59	8.60	27.75	2,500	100.00/M
60	1,500	25		BCP55FSCCT-NDΔ	.50	8.11	26.64	2,500	113.00/M
80	500	100		PZTA06CT-NDΔ	.52	8.51	27.96	2,500	118.00/M
300	500	25		PZTA42CT-NDΔ	.48	7.81	25.66	2,500	109.00/M
<b>TO-264 - 符合 RoHS 规范要求</b>									
4	230	15,000	35	FJL43150TU-ND	2.32	46.76	168.35	—	—
230	15,000	80		2SC52000TU-ND	2.60	52.50	189.00	—	—
230	15,000	55		2SC5200RTU-ND	2.60	52.50	189.00	—	—
<b>TO-220 - 符合 RoHS 规范要求</b>									
60	2,000	500		TIP110-ND	.66	12.69	44.23	—	—
60	5,000	1,000		TIP120-ND	.66	12.69	44.23	—	—
80	10,000	35		KSE44H11TU-ND	.73	14.08	49.06	—	—
80	6,000	15		TIP41B-ND	.65	11.94	40.95	—	—
100	1,000	15		TIP29CFS-ND	.55	10.11	34.65	—	—
100	1,000	15		TIP29CTU-ND	.53	9.74	33.39	—	—
100	2,000	500		TIP112TU-ND	.66	12.69	44.23	—	—
100	3,000	10		TIP31CFS-ND	.53	9.74	33.39	—	—
100	3,000	10		TIP31CTU-ND	.49	8.98	30.79	—	—
100	5,000	1,000		TIP122FS-ND	.66	12.69	44.23	—	—
100	5,000	1,000		TIP122TU-ND	.66	12.69	44.23	—	—
100	6,000	15		TIP41CTU-ND	.67	12.31	42.21	—	—
100	6,000	30		TIP41C-ND	.67	12.41	42.54	—	—
100	8,000	200		TIP102TU-ND	.94	18.75	65.61	—	—
100	8,000	200		TIP102-ND	.94	18.75	65.61	—	—
100	8,000	750		BDX53C-ND	.71	13.83	48.20	—	—
100	12,000	100		BDW93CFS-ND	.98	19.70	68.94	—	—
200	7,000	—		BU406FS-ND	.84	16.36	57.00	—	—
230	15,000	55		FJPS200RTU-ND	1.30	26.02	91.07	—	—
230	15,000	80		FJPS2000TU-ND	1.30	26.02	91.07	—	—
300	1,000	10		TIP48-ND	.60	11.12	38.13	—	—
350	1,000	10		TIP49FS-ND	.49	9.06	31.08	—	—
400	1,000	10		TIP50-ND	.60	11.12	38.13	—	—
400	1,500	5		KSE13003TH2ATU-ND	.67	13.04	45.41	—	—
400	4,000	8		FJP3305-ND	.62	11.			