

L (μH)	最小 Q 值	测试频率 (MHz)	最大 SRF 值 (MHz)	最大 DCR 值 (Ω)	dc 电流 (mA)	Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		J.W. Miller 零件编号
							1	10	100		数量	价格	
PM1812 系列 10%													
0.10	28.00	25.20	300.00	0.18	800.00	M8526CT-ND	.45	.41	.34	—	—	—	PM1812-R10K-RC
PM1812 系列 5%													
1.00	50.00	7.96	100.00	0.50	450.00	M8527CT-ND	.45	.41	.34	—	—	—	PM1812-1R0J-RC
3.30	50.00	7.96	45.00	0.80	355.00	M8530CT-ND	.45	.41	.34	M8530TR-ND	500	66.75	PM1812-3R3J-RC
10.00	50.00	2.52	20.00	1.60	250.00	M8531CT-ND	.45	.41	.34	—	—	—	PM1812-100J-RC
12.00	50.00	2.52	18.00	2.00	225.00	M8532CT-ND	.45	.41	.34	M8532TR-ND	500	66.75	PM1812-120J-RC
220.00	40.00	0.796	4.00	10.00	100.00	M8536CT-ND	.45	.41	.34	—	—	—	PM1812-221J-RC
330.00	30.00	0.796	3.00	14.00	85.00	M8537CT-ND	.45	.41	.34	M8537TR-ND	500	66.75	PM1812-331J-RC
PM1210 系列 5%													
1.00	28.00	7.96	120.00	0.70	400.00	M8540CT-ND	.45	.41	.34	—	—	—	PM1210-1R0J-RC
1.50	28.00	7.96	85.00	0.85	370.00	M8541CT-ND	.45	.41	.34	M8541TR-ND	2,000	133.50/M	PM1210-1R5J-RC
2.20	30.00	7.96	75.00	1.00	320.00	M8542CT-ND	.45	.41	.34	M8542TR-ND	2,000	133.50/M	PM1210-2R2J-RC
4.70	30.00	7.96	50.00	1.70	220.00	M8543CT-ND	.45	.41	.34	M8543TR-ND	2,000	133.50/M	PM1210-4R7J-RC
5.60	30.00	7.96	47.00	1.80	200.00	M8544CT-ND	.45	.41	.34	M8544TR-ND	2,000	133.50/M	PM1210-5R6J-RC
12.00	30.00	2.52	33.00	2.80	140.00	M8546CT-ND	.45	.41	.34	—	—	—	PM1210-120J-RC
15.00	30.00	2.52	30.00	3.20	130.00	M8547CT-ND	.45	.41	.34	M8547TR-ND	2,000	133.50/M	PM1210-150J-RC
33.00	30.00	2.52	17.00	5.60	70.00	M8548CT-ND	.45	.41	.34	—	—	—	PM1210-330J-RC
47.00	30.00	2.52	15.00	7.00	60.00	M8549CT-ND	.45	.41	.34	M8549TR-ND	2,000	133.50/M	PM1210-470J-RC
68.00	30.00	2.52	12.00	9.00	50.00	M8550CT-ND	.45	.41	.34	M8550TR-ND	2,000	133.50/M	PM1210-680J-RC
82.00	30.00	2.52	11.00	10.00	45.00	M8551CT-ND	.45	.41	.34	—	—	—	PM1210-820J-RC
100.00	20.00	0.796	10.00	10.00	40.00	M8552CT-ND	.45	.41	.34	—	—	—	PM1210-101J-RC
120.00	20.00	0.796	10.00	11.00	70.00	M8553CT-ND	.45	.41	.34	—	—	—	PM1210-121J-RC
150.00	20.00	0.796	8.00	15.00	65.00	M8554CT-ND	.45	.41	.34	—	—	—	PM1210-151J-RC
180.00	20.00	0.796	7.00	17.00	60.00	M8555CT-ND	.45	.41	.34	—	—	—	PM1210-181J-RC
220.00	20.00	0.796	7.00	21.00	50.00	M8556CT-ND	.45	.41	.34	M8556TR-ND	2,000	133.50/M	PM1210-221J-RC




表面安装高功率电感器

PM7232S、PM12639S、PM12645S、PM12651S、PM13560S 和 PM13666S 系列

特点:

- 特别适于大电流 DC/DC 转换器输出的电感器
- 磁屏蔽、低辐射
- 高饱和电流
- 低直流电阻
- 小尺寸
- 测试频率: 100kHz
- 工作温度: -40°C - 150°C



L (μH) ±20%	最大 DCR 值 (Ω)	额定电流 (A)	尺寸 (mm)								Digi-Key 零件编号	剪切带单价			Digi-Key 零件编号	带卷		J.W. Miller 零件编号
			A	B	C	D	E	F	G	H		1	10	100		数量	价格	
图 1 - PM7232S 系列																		
0.10	0.0011	22	7.2	6.6	3.2	3.5	1.3	3.0	4.0	7.5	M8494CT-ND	2.41	2.20	1.64	M8494TR-ND	1,500	1020.00/M	PM7232S-R10M-RC
0.22	0.0017	17	7.2	6.6	3.2	3.5	1.3	3.0	4.0	7.5	M8495CT-ND	2.41	2.20	1.64	M8495TR-ND	1,500	1020.00/M	PM7232S-R22M-RC
0.72	0.0080	12.5	7.2	6.6	3.2	3.5	1.3	3.0	4.0	7.5	M8497CT-ND	2.41	2.20	1.64	M8497TR-ND	1,500	1020.00/M	PM7232S-R72M-RC
1.5	0.0095	9	7.2	6.6	3.2	3.5	1.3	3.0	4.0	7.5	M8498CT-ND	2.41	2.20	1.64	—	—	—	PM7232S-1R5M-RC
图 1 - PM12639S 系列																		
0.67	0.0014	23	12.6	12.6	3.9	5.8	2.4	6.0	6.5	13.0	M8105CT-ND	3.12	2.84	2.12	—	—	—	PM12639S-R67M-RC
1.2	0.0028	18.5	12.6	12.6	3.9	5.8	2.4	6.0	6.5	13.0	M8106CT-ND	3.12	2.84	2.12	M8106TR-ND	800	1056.00	PM12639S-1R2M-RC
图 1 - PM12645S 系列																		
1.2	0.0018	21	12.6	12.6	4.5	5.8	2.4	6.0	6.5	13.0	M8107CT-ND	2.54	2.31	1.72	M8107TR-ND	800	858.00	PM12645S-1R2M-RC
2.7	0.0044	15	12.6	12.6	4.5	5.8	2.4	6.0	6.5	13.0	M8109CT-ND	2.54	2.31	1.72	—	—	—	PM12645S-2R7M-RC
图 1 - PM13560S 系列																		
10	0.0149	7.5	13.0	12.6	5.6	5.8	2.4	6.4	6.5	13.4	M8502CT-ND	2.59	2.36	1.76	M8502TR-ND	500	547.50	PM13560S-100M-RC
图 2 - PM13666S 系列																		
1.0	0.0012	25	13.6	12.6	6.6	2.4	3.5	5.3	5.0	14.7	M8499CT-ND	2.59	2.36	1.76	M8499TR-ND	500	547.50	PM13666S-1R0M-RC


全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电信) — 10800-8527031 (CNCG - 中国网通)

digkey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686

(CN082-09) 1597



特点: • 线绕式瓷芯, 高可靠性 • 高自谐振频率 • 顶面平坦, 易于自动取放



L ±20% (μH)	最大直 流电阻 Ω	饱和 电流 A	RMS 电流 A	Digi-Key 零件编号	剪切带 单价			带卷 价格* 3,000	J.W. Miller 零件编号		
					1	10	100				
PM0603 系列											
3.9	±0.3nH	22	250	0.08	700	M8489CT-ND	.39	.36	.30	117.00/M	PM0603-3N9-RC
10	±5%	30	250	0.15	700	M8484CT-ND	.39	.36	.30	—	PM0603-10N-RC
18	±5%	35	250	0.17	700	M8485CT-ND	.39	.36	.30	117.00/M	PM0603-18N-RC
27	±5%	40	250	0.23	700	M8486CT-ND	.39	.36	.30	117.00/M	PM0603-27N-RC
33	±5%	43	250	0.23	600	M8487CT-ND	.39	.36	.30	—	PM0603-33N-RC
39	±5%	43	250	0.25	600	M8488CT-ND	.39	.36	.30	117.00/M	PM0603-39N-RC
47	±5%	40	200	0.28	600	M8490CT-ND	.39	.36	.30	117.00/M	PM0603-47N-RC
82	±5%	35	150	0.54	400	M8491CT-ND	.39	.36	.30	117.00/M	PM0603-82N-RC
120	±5%	35	150	0.65	300	M8493CT-ND	.39	.36	.30	117.00/M	PM0603-R12J-RC


* 将 CT-ND 改为 TR-ND, 即为带卷包装的零件编号。

L 公差	最小 Q 值	电感测 试频率 MHz	最大直 流电阻 Ω	最大 DC 电流 mA	Digi-Key 零件编号	剪切带 单价			带卷 价格* 2,000	J.W. Miller 零件编号	
						1	10	100			
PM0805 系列											
6.8nH	20	50	250	0.11	600	M8452CT-ND	.40	.36	.30	—	PM0805-6N8M-RC
8.2nH	20	50	250	0.12	600	M8453CT-ND	.40	.36	.30	—	PM0805-8N2M-RC
12nH	20	50	250	0.15	600	M8454CT-ND	.40	.36	.30	—	PM0805-12NM-RC
22nH	20	55	250	0.22	500	M8455CT-ND	.40	.36	.30	120.00/M	PM0805-22NM-RC
27nH	20	55	250	0.25	500	M8456CT-ND	.40	.36	.30	120.00/M	PM0805-27NM-RC
33nH	20	60	250	0.27	500	M8457CT-ND	.40	.36	.30	120.00/M	PM0805-33NM-RC
39nH	20	60	250	0.29	500	M8458CT-ND	.40	.36	.30	120.00/M	PM0805-39NM-RC
47nH	20	60	200	0.31	500	M8459CT-ND	.40	.36	.30	120.00/M	PM0805-47NM-RC
0.056μH	10	60	200	0.34	500	M8460CT-ND	.40	.36	.30	—	PM0805-56NK-RC
0.069μH	10	60	200	0.38	500	M8461CT-ND	.40	.36	.30	—	PM0805-69NK-RC
0.082μH	10	65	150	0.42	400	M8462CT-ND	.40	.36	.30	120.00/M	PM0805-82NK-RC
0.10μH	10	65	150	0.46	400	M8463CT-ND	.40	.36	.30	120.00/M	PM0805-R10K-RC
0.15μH	10	50	100	0.56	400	M8465CT-ND	.40	.36	.30	—	PM0805-R15K-RC
0.22μH	10	50	100	0.70	400	M8466CT-ND	.40	.36	.30	120.00/M	PM0805-R22K-RC
PM1008 系列											
18nH	20	50	50	0.11	1000	M8467CT-ND	.40	.36	.30	—	PM1008-18NM-RC
27nH	20	55	50	0.13	1000	M8469CT-ND	.40	.36	.30	120.00/M	PM1008-27NM-RC
68nH	20	65	50	0.20	1000	M8470CT-ND	.40	.36	.30	—	PM1008-68NK-RC
82nH	10	60	50	0.22	1000	M8471CT-ND	.40	.36	.30	120.00/M	PM1008-82NK-RC
33μH	10	45	25	1.05	450	M8472CT-ND	.40	.36	.30	120.00/M	PM1008-R33K-RC
47μH	10	45	25	1.19	470	M8473CT-ND	.40	.36	.30	—	PM1008-R47K-RC
68μH	10	45	25	1.47	400	M8474CT-ND	.40	.36	.30	120.00/M	PM1008-R68K-RC
82μH	10	45	25	1.61	400	M8475CT-ND	.40	.36	.30	120.00/M	PM1008-R82K-RC
1.0μH	10	35	25	1.75	370	M8476CT-ND	.40	.36	.30	120.00/M	PM1008-R10K-RC
1.2μH	10	35	7.9	2.00	340	M8477CT-ND	.40	.36	.30	120.00/M	PM1008-R12K-RC
1.5μH	10	28	7.9	2.30	330	M8478CT-ND	.40	.36	.30	120.00/M	PM1008-R15K-RC
1.8μH	10	28	7.9	2.60	300	M8479CT-ND	.40	.36	.30	120.00/M	PM1008-R18K-RC
2.2μH	10	28	7.9	2.80	290	M8480CT-ND	.40	.36	.30	120.00/M	PM1008-R22K-RC
2.7μH	10	22	7.9	3.20	290	M8481CT-ND	.40	.36	.30	—	PM1008-R27K-RC
3.3μH	10	22	7.9	3.40	290	M8482CT-ND	.40	.36	.30	120.00/M	PM1008-3R3K-RC
4.7μH	10	20	7.9	4.00	260	M8483CT-ND	.40	.36	.30	120.00/M	PM1008-4R7K-RC

* 将 CT-ND 改为 TR-ND, 即为带卷包装的零件编号。

表面安装功率电感器

PM3308 系列




L ±20% (μH)	最大直 流电阻 Ω	饱和 电流 A	RMS 电流 A	Digi-Key 零件编号	剪切带 单价			带卷 价格* 1,000	J.W. Miller 零件编号
					1	10	100		
10	0.11	2.4	2.0	M8576CT-ND	1.70	1.53	1.28	510.00	PM3308-100M-RC
22	0.23	1.6	1.3	M8577CT-ND	1.70	1.53	1.28	510.00	PM3308-220M-RC
33	0.30	1.4	1.1	M8578CT-ND	1.70	1.53	1.28	510.00	PM3308-330M-RC
47	0.39	1.0	0.8	M8579CT-ND	1.70	1.53	1.28	510.00	PM3308-470M-RC
68	0.66	0.9	0.7	M8580CT-ND	1.70	1.53	1.28	510.00	PM3308-680M-RC
330	2.7	0.4	0.3	M8581CT-ND	1.70	1.53	1.28	510.00	PM3308-331M-RC
470	4.0	0.3	0.2	M8582CT-ND	1.70	1.53	1.28	510.00	PM3308-471M-RC

* 将 CT-ND 改为 TR-ND, 即为带卷包装的零件编号。

表面安装功率电感器

PM3316 系列




L ±20% (μH)	最大直 流电阻 Ω	饱和 电流 A	RMS 电流 A	Digi-Key 零件编号	剪切带 单价			带卷 价格* 500	J.W. Miller 零件编号
					1	10	100		
1.0	0.009	9.0	6.8	M8557CT-ND	1.65	1.49	1.24	247.50	PM3316-1R0M-RC
1.5	0.010	8.0	6.4	M8558CT-ND	1.65	1.49	1.24	247.50	PM3316-1R5M-RC
2.2	0.012	7.0	6.1	M8559CT-ND	1.65	1.49	1.24	247.50	PM3316-2R2M-RC
4.7	0.018	5.4	4.8	M8561CT-ND	1.20	1.08	.90	247.50	PM3316-4R7M-RC
33	0.10	2.0	2.1	M8566CT-ND	1.65	1.49	1.24	—	PM3316-330M-RC
68	0.20	1.4	1.5	M8568CT-ND	1.65	1.49	1.24	247.50	PM3316-680M-RC
100	0.28	1.2	1.3	M8569CT-ND	1.65	1.49	1.24	247.50	PM3316-101M-RC
150	0.40	1.0	1.0	M8570CT-ND	1.65	1.49	1.24	247.50	PM3316-151M-RC
330	1.02	0.6	0.6	M8572CT-ND	1.65	1.49	1.24	—	PM3316-331M-RC
470	1.27	0.5	0.5	M8573CT-ND	1.65	1.49	1.24	247.50	PM3316-471M-RC
1000	3.00	0.3	0.3	M8575CT-ND	1.20	1.08	.90	—	PM3316-102M-RC

* 将 CT-ND 改为 TR-ND, 即为带卷包装的零件编号。

表面安装功率电感器

PM3340 系列




L ±20% (μH)	最大直 流电阻 Ω	饱和 电流 A	RMS 电流 A	Digi-Key 零件编号	剪切带 单价			带卷 价格* 225	J.W. Miller 零件编号
					1	10	100		
10	0.033	8.0	3.5	M8583CT-ND	1.75	1.58	1.32	118.13	PM3340-100M-RC
15	0.042	7.0	3.0	M8584CT-ND	1.75	1.58	1.32	118.13	PM3340-150M-RC
22	0.054	5.5	2.5	M8585CT-ND	1.75	1.58	1.32	118.13	PM3340-220M-RC
33	0.08	4.0	2.0	M8586CT-ND	1.75	1.58	1.32	118.13	PM3340-330M-RC
47	0.1	3.8	1.6	M8587CT-ND	1.75	1.58	1.32	118.13	PM3340-470M-RC
68	0.17	3.0	1.2	M8588CT-ND	1.75	1.58	1.32	118.13	PM3340-680M-RC
100	0.22	2.5	1.2	M8589CT-ND	1.75	1.58	1.32	118.13	PM3340-101M-RC
150	0.34	2.0	0.9	M8590CT-ND	1.75	1.58	1.32	118.13	PM3340-151M-RC
220	0.44	1.6	0.7	M8591CT-ND	1.75	1.58	1.32	118.13	PM3340-221M-RC
330	0.7	1.2	0.6	M8592CT-ND	1.75	1.58	1.32	118.13	PM3340-331M-RC
1000	2.0	0.8	0.1	M8593CT-ND	1.75	1.58	1.32	118.13	PM3340-102M-RC

* 将 CT-ND 改为 TR-ND, 即为带卷包装的零件编号。

表面安装功率电感器

PM5022 系列




L ±20% (μH)	最大直 流电阻 Ω	饱和 电流 A	RMS 电流 A	Digi-Key 零件编号	剪切带 单价			带卷 价格* 250	J.W. Miller 零件编号
					1	10	100		
5.6	0.022	12	5.3	M8594CT-ND	1.35	1.22	1.02	101.25	PM5022-5R6M-RC
10	0.032	10	4.3	M8597CT-ND	1.35	1.22	1.02	101.25	PM5022-100M-RC
68	0.13	3.5	2.3	M8602CT-ND	1.35	1.22	1.02	101.25	PM5022-680M-RC
100	0.19	3.0	1.8	M8603CT-ND	1.35	1.22	1.02	101.25	PM5022-101M-RC
220	0.38	2.4	1.2	M8605CT-ND	1.35	1.22	1.02	101.25	PM5022-221M-RC
470	0.85	1.4	0.82	M8607CT-ND	1.35	1.22	1.02	101.25	PM5022-471M-RC
680	1.2	1.2	0.72	M8608CT-ND	1.35	1.22	1.02	101.25	PM5022-681M-RC
1000	1.8	1.0	0.56	M8609CT-ND	1.35	1.22	1.02	101.25	PM5022-102M-RC

* 将 CT-ND 改为 TR-ND, 即为带卷包装的零件编号。

全部产品均以美元计价。

免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)



尺寸 (mm)						
系列	A	B	C	D 标准	E 标准	F 标准
PM43	4.0 ± 0.3	4.5 ± 0.3	3.2 ± 0.3	4.5	4.0	1.2
PM54	5.2 ± 0.3	5.8 ± 0.3	4.5 ± 0.3	5.8	5.2	1.3
PM105	9.0 ± 0.4	10.0 ± 0.4	5.4 ± 0.4	10.0	9.5	2.5
PM105S/SB	9.2 ± 0.4	10.0 ± 0.4	5.0 ± 0.5	10.0	9.5	2.5

L (μH)	公差 %	测试频率	最大 DCR Ω	额定电流 A	Digi-Key 零件编号	剪切带 单价			带卷 价格* 1,500	J.W. Miller 零件编号
						1	10	100		
PM43 系列										
10	20	2.5MHz	0.182	1.04	M8503CT-ND	1.45	1.31	1.09	435.00/M	PM43-100M-RC
22	20	2.5MHz	0.378	0.68	M8506CT-ND	1.45	1.31	1.09	435.00/M	PM43-220M-RC
33	10	2.5MHz	0.540	0.56	M8507CT-ND	1.45	1.31	1.09	435.00/M	PM43-330K-RC
56	10	2.5MHz	0.937	0.42	M8509CT-ND	1.45	1.31	1.09	435.00/M	PM43-560K-RC
68	10	2.5MHz	1.117	0.37	M8510CT-ND	1.45	1.31	1.09	—	PM43-680K-RC
PM54 系列										
10	20	2.5MHz	0.10	1.44	M8511CT-ND	1.45	1.31	1.09	435.00/M	PM54-100M-RC
12	20	2.5MHz	0.12	1.40	M8513CT-ND	1.45	1.31	1.09	435.00/M	PM54-120M-RC
18	20	2.5MHz	0.15	1.23	M8516CT-ND	1.45	1.31	1.09	—	PM54-180M-RC
22	20	2.5MHz	0.18	1.11	M8518CT-ND	1.45	1.31	1.09	—	PM54-220M-RC
27	20	2.5MHz	0.20	0.97	M8520CT-ND	1.45	1.31	1.09	435.00/M	PM54-270M-RC
33	15	2.5MHz	0.23	0.88	M8521CT-ND	1.45	1.31	1.09	435.00/M	PM54-330L-RC
39	15	2.5MHz	0.32	0.80	M8522CT-ND	1.45	1.31	1.09	—	PM54-390L-RC
47	15	2.5MHz	0.37	0.72	M8523CT-ND	1.45	1.31	1.09	435.00/M	PM54-470L-RC
68	10	2.5MHz	0.46	0.61	M8524CT-ND	1.45	1.31	1.09	435.00/M	PM54-680K-RC
82	10	2.5MHz	0.60	0.58	M8525CT-ND	1.45	1.31	1.09	435.00/M	PM54-820K-RC
100	10	1kHz	0.70	0.52	M8512CT-ND	1.45	1.31	1.09	—	PM54-101K-RC
150	10	1kHz	1.10	0.40	M8515CT-ND	1.45	1.31	1.09	—	PM54-151K-RC
180	10	1kHz	1.38	0.38	M8517CT-ND	1.45	1.31	1.09	435.00/M	PM54-181K-RC

* 将 CT-ND 改为 TR-ND, 即为带卷包装的零件编号。


L (μH)	公差 %	测试频率	最大 DCR Ω	额定电流 A	Digi-Key 零件编号	剪切带 单价			带卷 价格* 500	J.W. Miller 零件编号
						1	10	100		
PM105 系列										
39	20	2.5MHz	0.14	1.37	M8417CT-ND	1.90	1.71	1.43	—	PM105-390M-RC
47	10	2.5MHz	0.17	1.28	M8418CT-ND	1.90	1.71	1.43	—	PM105-470K-RC
82	10	2.5MHz	0.25	1.00	M8421CT-ND	1.90	1.71	1.43	285.00	PM105-820K-RC
100	10	1kHz	0.35	0.97	M8422CT-ND	1.90	1.71	1.43	—	PM105-101K-RC
120	10	1kHz	0.40	0.89	M8423CT-ND	1.90	1.71	1.43	—	PM105-121K-RC
180	10	1kHz	0.63	0.72	M8425CT-ND	1.90	1.71	1.43	—	PM105-181K-RC
270	10	1kHz	0.97	0.57	M8427CT-ND	1.90	1.71	1.43	285.00	PM105-271K-RC
330	10	1kHz	1.15	0.52	M8428CT-ND	1.90	1.71	1.43	—	PM105-331K-RC
470	10	1kHz	1.48	0.42	M8429CT-ND	1.90	1.71	1.43	285.00	PM105-471K-RC
560	10	1kHz	1.90	0.33	M8430CT-ND	1.90	1.71	1.43	285.00	PM105-561K-RC
680	10	1kHz	2.25	0.28	M8431CT-ND	1.90	1.71	1.43	285.00	PM105-681K-RC
PM105SB (带屏蔽) 系列										
12	20	2.5MHz	0.07	1.94	M8434CT-ND	1.47	1.33	1.11	—	PM105SB-120M-RC
15	20	2.5MHz	0.07	1.72	M8435CT-ND	1.47	1.33	1.11	220.50	PM105SB-150M-RC
27	20	2.5MHz	0.10	1.32	M8438CT-ND	1.47	1.33	1.11	220.50	PM105SB-270M-RC

L (μH)	公差 %	测试频率	最大 DCR Ω	额定电流 A	Digi-Key 零件编号	剪切带 单价			带卷 价格* 500	J.W. Miller 零件编号
						1	10	100		
33	15	2.5MHz	0.11	1.16	M8439CT-ND	1.47	1.33	1.11	—	PM105SB-330L-RC
56	15	2.5MHz	0.19	0.93	M8442CT-ND	1.47	1.33	1.11	—	PM105SB-560L-RC
82	15	2.5MHz	0.28	0.79	M8443CT-ND	1.47	1.33	1.11	220.50	PM105SB-820L-RC
100	10	1kHz	0.34	0.72	M8444CT-ND	1.47	1.33	1.11	—	PM105SB-101K-RC
120	10	1kHz	0.37	0.63	M8445CT-ND	1.47	1.33	1.11	—	PM105SB-121K-RC
150	10	1kHz	0.51	0.55	M8446CT-ND	1.47	1.33	1.11	220.50	PM105SB-151K-RC
330	10	1kHz	1.20	0.37	M8450CT-ND	1.47	1.33	1.11	—	PM105SB-331K-RC

* 将 CT-ND 改为 TR-ND, 即为带卷包装的零件编号。

表面安装大电流环形电感器 -

PM2110 和 PM2120 系列



在 1kHz 时的 L (μH)	DC 电流 (A)	额定电流 时的 L (μH) ±20%	最大 DCR 值 (Ω)	尺寸 A (mm) (最大)	Digi-Key 零件编号	单价			J.W. Miller 零件编号
						1	10	25	
PM2110 系列 20%									
1.00	22.70	0.80	0.00	14.48	M8754-ND	2.73	2.05	1.82	PM2110-1R0M-RC
5.60	13.70	3.90	0.01	14.48	M8755-ND	2.73	2.05	1.82	PM2110-5R6M-RC
PM2110 系列 10%									
10.00	11.70	6.50	0.01	14.48	M8756-ND	2.73	2.05	1.82	PM2110-100K-RC
12.00	11.30	7.60	0.01	14.48	M8757-ND	2.73	2.05	1.82	PM2110-120K-RC
15.00	10.70	9.20	0.01	14.48	M8758-ND	2.73	2.05	1.82	PM2110-150K-RC
18.00	10.20	10.70	0.01	14.48	M8759-ND	2.73	2.05	1.82	PM2110-180K-RC
22.00	9.70	12.70	0.01	14.48	M8760-ND	2.73	2.05	1.82	PM2110-220K-RC
27.00	8.20	16.00	0.01	13.72	M8761-ND	2.73	2.05	1.82	PM2110-270K-RC
33.00	7.00	20.10	0.02	13.21	M8762-ND	2.73	2.05	1.82	PM2110-330K-RC
39.00	6.80	23.20	0.02	15.75	M8763-ND	2.73	2.05	1.82	PM2110-390K-RC
47.00	6.50	27.20	0.02	15.75	M8764-ND	2.73	2.05	1.82	PM2110-470K-RC
56.00	6.20	31.60	0.02	15.75	M8765-ND	2.73	2.05	1.82	PM2110-560K-RC
68.00	5.90	37.10	0.03	15.75	M8766-ND	2.73	2.05	1.82	PM2110-680K-RC
100.00	5.40	51.40	0.03	15.75	M8767-ND	2.73	2.05	1.82	PM2110-101K-RC
150.00	4.30	77.30	0.05	14.99	M8768-ND	2.73	2.05	1.82	PM2110-151K-RC
180.00	3.70	96.30	0.07	13.46	M8769-ND	2.73	2.05	1.82	PM2110-181K-RC
220.00	3.50	113.80	0.07	15.24	M8770-ND	2.73	2.05	1.82	PM2110-221K-RC
270.00	3.40	134.90	0.08	15.24	M8771-ND	2.73	2.05	1.82	PM2110-271K-RC
330.00	3.20	159.50	0.09	15.24	M8772-ND	2.73	2.05	1.82	PM2110-331K-RC
390.00	3.10	182.90	0.10	15.24	M8773-ND	2.73	2.05	1.82	PM2110-391K-RC
470.00	2.60	230.40	0.13	14.48	M8774-ND	2.73	2.05	1.82	PM2110-471K-RC
820.00	2.00	394.10	0.22	15.24	M8775-ND	2.73	2.05	1.82	PM2110-821K-RC
1000.00	1.90	463.70	0.24	15.24	M8776-ND	2.73	2.05	1.82	PM2110-102K-RC
PM2120 系列 20%									
2.20	19.70	1.80	0.00	20.83	M8777-ND	3.00	2.25	2.00	PM2120-2R2M-RC
4.70	16.60	3.70	0.01	20.83	M8778-ND	3.00	2.25	2.00	PM2120-4R7M-RC
5.60	15.60	4.20	0.01	20.83	M8779-ND	3.00	2.25	2.00	PM2120-5R6M-RC
6.80	14.70	5.00	0.01	20.83	M8780-ND	3.00	2.25	2.00	PM2120-6R8M-RC
PM2120 系列 10%									
10.00	13.90	7.20	0.01	20.83	M8781-ND	3.00	2.25	2.00	PM2120-100K-RC
12.00	12.70	8.30	0.01	20.83	M8782-ND	3.00	2.25	2.00	PM2120-120K-RC
15.00	12.20	10.20	0.01	20.83	M8783-ND	3.00	2.25	2.00	PM2120-150K-RC
18.00	11.80	12.00	0.01	20.83	M8784-ND	3.00	2.25	2.00	PM2120-180K-RC
22.00	11.00	14.20	0.01	20.83	M8785-ND	3.00	2.25	2.00	PM2120-220K-RC
27.00	10.40	16.90	0.01	20.83	M8786-ND	3.00	2.25	2.00	PM2120-270K-RC
33.00	10.10	20.30	0.01	20.83	M8787-ND	3.00	2.25	2.00	PM2120-330K-RC
39.00	9.60	23.30	0.01	20.83	M8788-ND	3.00	2.25	2.00	PM2120-390K-RC
47.00	8.20	29.20	0.02	20.83	M8789-ND	3.00	2.25	2.00	PM2120-470K-RC
56.00	7.90	33.90	0.02	20.07	M8790-ND	3.00	2.25	2.00	PM2120-560K-RC
68.00	6.70	42.20	0.03	19.56	M8791-ND	3.00	2.25	2.00	PM2120-680K-RC
82.00	6.40	49.50	0.03	22.10	M8792-ND	3.00	2.25	2.00	PM2120-820K-RC
100.00	6.10	58.70	0.04	22.10	M8793-ND	3.00	2.25	2.00	PM2120-101K-RC
120.00	5.80	68.10	0.04	22.10	M8794-ND	3.00	2.25	2.00	PM2120-121K-RC
150.00	5.50	82.50	0.04	22.10	M8795-ND	3.00	2.25	2.00	PM2120-151K-RC
180.00	5.30	96.20	0.05	21.08	M8796-ND	3.00	2.25	2.00	PM2120-181K-RC
220.00	5.00	113.70	0.05	21.08	M8797-ND	3.00	2.25	2.00	PM2120-221K-RC
330.00	3.60	183.40	0.10	19.81	M8798-ND	3.00	2.25		