


A


BNC PC Board/Panel Mount Jack Connectors with Mounting Flanges 50 Ohm



Hardware Sold Separately

| Description | Center Contact | Mount. Height Inch (mm) | Body Material | Digi-Key Part No. | Price Each 1 25 | Tyco Electronics Part No. |
|-------------|----------------|-------------------------|---------------|-------------------|-----------------|---------------------------|
| Right Angle | Tin | .625 (15.88) | VALOX, White | A32242-ND | 7.57 6.52 | 5226978-1 |
| Right Angle | Gold | .625 (15.88) | VALOX, White | A32252-ND | 7.66 6.59 | 5226978-3 |


BNC PC Board/Panel Mount Right Angle Jack Connectors 50 Ohm



Hardware Sold Separately

| Description | Center Contact | Mount. Height A Inch (mm) | Body Material | Digi-Key Part No. | Price Each 1 25 | Tyco Electronics Part No. |
|------------------------|----------------|---------------------------|---------------|-------------------|-----------------|---------------------------|
| Without Mounting Posts | Tin | .625 (15.88) | VALOX, White | A32253-ND | 3.48 3.00 | 5226990-1 |
| With Mounting Posts | Tin | .625 (15.88) | VALOX, White | A32244-ND | 3.31 2.85 | 5227161-1 |
| Without Mounting Posts | Gold | .625 (15.88) | VALOX, White | A32254-ND | 2.81 2.42 | 5226990-3 |
| With Mounting Posts | Gold | .625 (15.88) | VALOX, White | A32258-ND | 3.46 2.97 | 5227161-3 |
| With Mounting Posts | Gold | .519 (13.18) | VALOX, White | A32260-ND | 3.20 2.76 | 5227161-7 |
| With Mounting Posts | Tin | .625 (15.88) | VALOX, Black | A32245-ND | 3.06 2.63 | 5227161-2 |
| Without Mounting Posts | Gold | .625 (15.88) | VALOX, Black | A32255-ND | 2.95 2.55 | 5226990-6 |
| With Mounting Posts | Gold | .625 (15.88) | VALOX, Black | A32259-ND | 3.25 2.80 | 5227161-6 |
| With Mounting Posts | Gold | .519 (13.18) | VALOX, Black | A32261-ND | 3.18 2.73 | 5227161-9 |
| Without Mounting Posts | Tin | .625 (15.88) | Metal | A32264-ND | 7.69 6.62 | 5227433-1 |
| With Mounting Posts | Tin | .625 (15.88) | Metal | A32248-ND | 4.13 3.55 | 5227661-1 |
| Without Mounting Posts | Gold | .625 (15.88) | Metal | A32267-ND | 3.46 2.97 | 5227676-1 |
| With Mounting Posts | Gold | .625 (15.88) | Metal | A32268-ND | 4.99 4.30 | 5227677-1 |
| With Mounting Posts | Gold | .500 (12.70) | Metal | A32273-ND | 7.57 6.52 | 5413879-1 |
| Zinc Die Cast | | | | | | |
| With Mounting Posts | Gold | .518 (13.16) | Zinc, White | A97552-ND | 2.90 2.49 | 1-1337542-0 |
| With Mounting Posts | Gold | .622 (15.80) | Zinc, White | A97553-ND | 2.58 2.22 | 1-1337543-0 |
| With Mounting Posts | Gold | .518 (13.16) | Zinc, Black | A97554-ND | 3.12 2.68 | 1-1634613-0 |
| With Mounting Posts | Gold | .622 (15.80) | Zinc, Black | A97555-ND | 2.58 2.22 | 1-1634612-0 |
| With Mounting Posts | Gold | .598 (15.20) | Zinc | A97556-ND | 4.04 3.48 | 1-1337494-0 |

BNC PC Board/Panel Mount Vertical Jack Connectors 50 Ohm



Hardware Sold Separately

| Description | Center Contact | Body Material | Digi-Key Part No. | Price Each 1 25 | Tyco Electronics Part No. |
|---------------------------------------|----------------|---------------|-------------------|-----------------|---------------------------|
| Without Mounting Posts | Tin-Lead | VALOX, White | A24501-ND | 7.05 6.06 | 226993-1 |
| Without Mounting Posts | Tin | VALOX, White | A32256-ND | 7.57 6.52 | 5226993-1 |
| With Mounting Posts | Tin | VALOX, White | A32246-ND | 3.00 2.58 | 5227222-1 |
| Without Mounting Posts | Gold | VALOX, White | A32257-ND | 8.00 6.88 | 5226993-3 |
| With Mounting Posts | Gold | VALOX, White | A32262-ND | 3.25 2.80 | 5227222-3 |
| Without Mounting Posts | Tin | VALOX, Black | A32243-ND | 9.20 7.92 | 5226993-2 |
| With Mounting Posts | Tin | VALOX, Black | A32247-ND | 3.48 3.00 | 5227222-2 |
| With Mounting Posts | Gold | VALOX, Black | A32263-ND | 3.57 3.07 | 5227222-6 |
| With Mounting Posts | Tin | Metal | A32265-ND | 3.48 3.00 | 5227671-1 |
| With Mounting Posts | Gold | Metal | A32266-ND | 3.51 3.02 | 5227673-1 |
| Zinc Die Cast — RoHS Compliant | | | | | |
| With Mounting Posts | Gold | Zinc, White | A97557-ND | 2.39 2.06 | 1-1337541-0 |
| With Mounting Posts | Gold | Zinc, Black | A97558-ND | 2.50 2.15 | 1-1634505-0 |

◆ RoHS Compliant


Jack Accessories 50 and 75 Ohm

| Description | Digi-Key Part No. | Price Each 1 25 | Tyco Electronics Part No. |
|--|-------------------|-----------------|---------------------------|
| Insulating Bushing for Mounting Jacks, Nylon | A24532-ND | .49 .43 | 222163-1 |
| Insulating Bushing for Bulkhead Solder Jacks | A24533-ND | .27 .24 | 227223-1 |

| Description | Digi-Key Part No. | Price Each 1 25 | Tyco Electronics Part No. |
|---|-------------------|-----------------|---------------------------|
| Screw for panel thickness of 3/32 (2.38mm) or greater | A24534-ND | .43 .37 | 221108-2 |
| Screw for panel thickness of less than 3/32 (2.38mm) | A24535-ND | .28 .25 | 221108-4 |
| Lockwasher | A1129-ND | .25 .22 | 1-329632-2 |
| Hex Nut | A1128-ND | .26 .24 | 1-329631-2 |
| Zinc Die Cast — RoHS Compliant | | | |
| BNC/TNC Hexagonal Nut | A97566-ND | .76 .66 | 1-1634816-0 |
| BNC/TNC Lockwasher | A97567-ND | .33 .29 | 1-1634817-0 |

◆ RoHS Compliant


BNC Vertical Metallized PC Board Mount Jack Connectors 50 Ohm



| Fig. | Body Plating | Center Contact | Body Material | Digi-Key Part No. | Price Each 1 25 | Tyco Electronics Part No. |
|---------------------------------------|--------------|----------------|---------------|-------------------|-----------------|---------------------------|
| 1 | Nickel | Silver | VALOX | A24512-ND | 4.41 3.79 | 227699-1 |
| | Nickel | Silver | VALOX | A33798-ND | 3.82 3.29 | 5227699-1 |
| | Nickel | Gold | VALOX | A32269-ND | 4.94 4.25 | 5227699-2 |
| | Nickel | Tin | VALOX | A32249-ND | 4.13 3.55 | 5227699-3 |
| 2 | Nickel | Gold | VALOX | A32241-ND | 4.54 3.91 | 5221123-2 |
| | Nickel | Silver | VALOX | A24516-ND | 10.83 9.32 | 222420-1 |
| 3 | Nickel | Silver | VALOX | A32251-ND | 7.44 6.40 | 5222420-1 |
| | Tin-Lead | Silver | VALOX | A24517-ND | 4.19 3.60 | 414305-1 |
| | Tin | Silver | VALOX | A32493-ND | 5.14 4.42 | 5414305-1 |
| Zinc Die Cast — RoHS Compliant | | | | | | |
| 3 | Nickel | Gold | Zinc | A97581-ND | 1.68 1.45 | 5-1634503-1 |
| | Nickel | Gold | Zinc | A97583-ND | 2.28 1.96 | 5-1634506-1 |


◆ RoHS Compliant

BNC Press-Fit Terminal Jack Connectors 50 Ohm



| Body Plating | Center Contact | Body Material | Digi-Key Part No. | Price Each 1 25 | Tyco Electronics Part No. |
|--------------|----------------|---------------|-------------------|-----------------|---------------------------|
| Nickel | Gold | TEFLON | A32250-ND | 5.53 4.76 | 5222006-1 |


BNC Right-Angle PC Board Mount Jack Connectors



| Fig. | Body Plating | Center Contact Length - In (mm) | Digi-Key Part No. | Price Each 1 25 | Tyco Electronics Part No. |
|------|--------------|---------------------------------|-------------------|-----------------|---------------------------|
| 1 | Nickel | .171 (4.34) | A32270-ND | 7.89 6.78 | 5413631-1 |
| | Tin | .171 (4.34) | A32271-ND | 7.72 6.64 | 5413631-2 |
| | Nickel | .131 (3.33) | A32272-ND | 29.21 25.12 | 5413631-3 |
| | Nickel | .131 (3.33) | A97570-ND | 3.93 3.38 | 5-1634556-0 |
| 2 | Nickel | — | A24539-ND | 4.54 3.91 | 414373-1 |
| | Nickel | — | A32274-ND | 3.18 2.73 | 5414373-1 |

◆ RoHS Compliant † Zinc Die Cast

BNC Twist-On Connectors 50 Ohm



Center Contact: Gold Body Plating: Nickel

| Description | Dielectric | Cable Group RG/U | Digi-Key Part No. | Price Each 1 25 | Tyco Electronics Part No. |
|-------------|-------------------|------------------|-------------------|-----------------|---------------------------|
| Plug | Polymethylpentene | 59, 59A, 59B | A24483-ND | 3.42 2.95 | 414265-3 |
| Plug | Polymethylpentene | 59, 59A, 59B | A33797-ND | 40.04 34.43 | 5414265-3 |

◆ RoHS Compliant

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.