

Amphenol® Commercial Products

RJ45 模块化插孔



A






图	说明	尺寸 (mm)			Digi-Key 零件编号		单价		Amphenol 零件编号
		A	B	C	1	10	1	10	
PCB 垂直									
无屏蔽									
1	无 LED	15.50	15.75	12.83	RJHSE-3080-ND		2.42	1.49	RJHSE-3080
	LED 绿色 - 黄色	15.50	15.75	12.83	RJHSE-3081-ND		2.56	1.64	RJHSE-3081
	LED 绿色 - 绿色	15.50	15.75	12.83	RJHSE-3085-ND		2.56	1.64	RJHSE-3085
屏蔽									
1	无 LED	15.88	16.51	13.59	RJHSE-3380-ND		2.73	1.76	RJHSE-3380
	LED 黄色 - 绿色	15.88	16.51	13.59	RJHSE-3381-ND		3.33	2.23	RJHSE-3381
	LED 绿色 - 黄色	15.88	16.51	13.59	RJHSE-3384-ND		3.33	2.23	RJHSE-3384
	LED 绿色 - 绿色	15.88	16.51	13.59	RJHSE-3385-ND		3.33	2.23	RJHSE-3385
	LED 两者均两色	15.88	16.51	13.59	RJHSE-338A-ND		4.97	3.37	RJHSE-338A
	PCB 直角								
无屏蔽									
2	无 LED	14.99	15.75	13.21	RJHSE-5080-ND		1.38	.82	RJHSE-5080
	LED 黄色 - 绿色	14.99	15.75	13.21	RJHSE-5081-ND		1.89	1.17	RJHSE-5081
	LED 绿色 - 黄色	14.99	15.75	13.21	RJHSE-5084-ND		1.89	1.17	RJHSE-5084
	LED 绿色 - 绿色	14.99	15.75	13.21	RJHSE-5085-ND		1.89	1.17	RJHSE-5085
	无 LED	18.67	14.60	12.95	FRJAE-408-ND		3.00	1.95	FRJAE-408
屏蔽									
2	无 LED	15.75	16.51	13.46	RJHSE-5380-ND		2.04	1.33	RJHSE-5380
	LED 黄色 - 绿色	15.75	16.51	13.46	RJHSE-5381-ND		2.55	1.61	RJHSE-5381
	LED 绿色 - 黄色	15.75	16.51	13.46	RJHSE-5384-ND		2.55	1.61	RJHSE-5384
	LED 绿色 - 绿色	15.75	16.51	13.46	RJHSE-5385-ND		2.55	1.61	RJHSE-5385
	LED 两者均为双色	15.75	16.51	13.46	RJHSE-538A-ND		3.81	2.52	RJHSE-538A
	有接片, 无 LED	15.75	16.51	13.46	RJHSE-5480-ND		2.04	1.33	RJHSE-5480
	有接片, LED 黄色 - 绿色	15.75	16.51	13.46	RJHSE-5481-ND		2.55	1.61	RJHSE-5481
	经过滤波, 无 LED	18.03	13.97	12.70	FRJAE-418-ND		3.56	2.28	FRJAE-418
	前接片, 无 LED	18.03	13.97	12.70	FRJAE-438-ND		3.44	2.24	FRJAE-438

图	说明	尺寸 (mm)			Digi-Key 零件编号	单价		Amphenol 零件编号
		A	B	C		1	10	
2	经过滤波, 后接片, 无 LED	18.03	13.97	12.70	FRJAE-468-ND	3.56	2.28	FRJAE-468
	后接片, 无 LED	18.03	13.97	12.70	FRJAE-488-ND	3.44	2.24	FRJAE-488
PCB 直角 - 多端口								
无屏蔽								
2	LED 绿色 - 绿色, 2 个端口	15.00	31.56	12.70	RJHSE-5085-02-ND	3.67	2.43	RJHSE-5085-02
屏蔽								
2	无 LED 1x2	15.75	32.26	13.46	RJHSE-5380-02-ND	3.67	2.43	RJHSE-5380-02
	LED 黄色 - 绿色, 2 个端口	15.75	32.26	13.46	RJHSE-5381-02-ND	4.99	3.28	RJHSE-5381-02
	LED 绿色 - 黄色, 2 个端口	15.75	32.26	13.46	RJHSE-5384-02-ND	4.99	3.28	RJHSE-5384-02
	LED 绿色 - 绿色, 2 个端口	15.75	32.26	13.46	RJHSE-5385-02-ND	4.99	3.28	RJHSE-5385-02
	LED 黄色 - 绿色, 4 个端口	15.76	63.75	13.46	RJHSE-5381-04-ND	6.15	4.10	RJHSE-5381-04
	LED 绿色 - 黄色, 4 个端口	15.76	63.75	13.46	RJHSE-5384-04-ND	6.15	4.10	RJHSE-5384-04
LED 绿色 - 绿色, 4 个端口	15.76	63.75	13.46	RJHSE-5385-04-ND	6.15	4.10	RJHSE-5385-04	
屏蔽 - 层叠								
3	LED 黄色 - 绿色, 2 个端口	28.15	16.51	25.40	RJSAE-5381-02-ND	6.92	4.82	RJSAE-5381-02
	LED 绿色 - 绿色, 2 个端口	28.15	16.51	25.40	RJSAE-5385-02-ND	6.92	4.82	RJSAE-5385-02
	LED 两者均两色, 2 个端口	28.15	16.51	25.40	RJSAE-538A-02-ND	8.11	5.76	RJSAE-538A-02
	LED 黄色 - 绿色, 4 个端口	28.15	32.26	25.40	RJSAE-5381-04-ND	11.18	8.27	RJSAE-5381-04
	LED 绿色 - 绿色, 4 个端口	28.15	32.26	25.40	RJSAE-5385-04-ND	11.18	8.27	RJSAE-5385-04
	LED 两者均两色, 4 个端口	28.15	32.26	25.40	RJSAE-538A-04-ND	13.01	9.76	RJSAE-538A-04
	LED 黄色 - 绿色, 8 个端口	28.15	63.75	25.40	RJSAE-5381-08-ND	18.24	13.88	RJSAE-5381-08
	LED 绿色 - 绿色, 8 个端口	28.15	63.75	25.40	RJSAE-5385-08-ND	18.24	13.88	RJSAE-5385-08
	LED 两者均两色, 8 个端口	28.15	63.75	25.40	RJSAE-538A-08-ND	21.69	17.06	RJSAE-538A-08
	表面贴装直角							
无屏蔽								
4	1 个端口	15.19	16.10	13.08	RJSSE-5080-ND	1.87	1.25	RJSSE-5080
	2 个端口	15.20	31.73	13.27	RJSSE-5080-02-ND	3.13	2.03	RJSSE-5080-02
	4 个端口	15.20	63.30	12.81	RJSSE-5080-04-ND	4.95	3.30	RJSSE-5080-04
屏蔽								
4	1 个端口	15.75	16.51	13.34	RJSSE-5380-ND	2.33	1.52	RJSSE-5380
	2 个端口	15.75	32.26	13.34	RJSSE-5380-02-ND	4.28	2.90	RJSSE-5380-02
	4 个端口	15.75	63.75	13.34	RJSSE-5380-04-ND	6.82	4.84	RJSSE-5380-04
表面贴装, 直角带灯管								
无屏蔽								
4	1 个端口	15.20	15.98	13.38	RJSSE-5081-ND	2.07	1.28	RJSSE-5081
	2 个端口	15.20	31.73	13.38	RJSSE-5081-02-ND	3.47	2.31	RJSSE-5081-02
	4 个端口	15.20	63.30	13.38	RJSSE-5081-04-ND	5.45	3.76	RJSSE-5081-04
屏蔽								
4	1 个端口	15.75	16.51	13.34	RJSSE-5381-ND	2.52	1.57	RJSSE-5381
	2 个端口	15.75	32.26	13.34	RJSSE-5381-02-ND	3.47	2.31	RJSSE-5381-02
	4 个端口	15.75	63.75	13.34	RJSSE-5381-04-ND	6.93	4.92	RJSSE-5381-04

I/O INTERCONNECT / Digi-Key®

IDC 模块化 线缆组件



样式	位置/触点	Digi-Key* 零件编号	单价	
直形				
1	4/4	H1443-07-ND	2.51	2.13
	6/4	H1643-14-ND	3.44	2.92
	8/8	H1883-14-ND	5.58	4.74
2	4/4	H244□-14-ND	3.09	2.63
	4/4	H2443-25-ND	4.02	3.41
	8/8	H288□-14-ND	5.58	4.74
	8/8	H2883-25-ND	7.52	6.39

样式	位置/触点	Digi-Key* 零件编号	单价			
3	6/4	H3643-14-ND	2.30	1.96	1.66	1.42
	8/8	H3881-07-ND	2.79	2.37	2.00	1.71
	8/8	H3881-14-ND	4.03	3.42	2.89	2.47
	8/8	H3882-14-ND	4.03	3.42	2.89	2.47
线圈型						
1	6/6	H1661-05C-ND	5.02	4.27	3.61	3.09
	6/6	H1663-05C-ND	5.02	4.27	3.61	3.09

样式	位置/触点	Digi-Key* 零件编号	单价			
1	8/8	H1883-14C-ND	10.31	8.76	7.39	6.33
2	4/4	H2441-07C-ND	4.39	3.73	3.15	2.69
	4/4	H2442-07C-ND	4.39	3.73	3.15	2.69
	4/4	H2442-10C-ND	5.92	5.03	4.25	3.64
	6/4	H264□-05C-ND	4.60	3.91	3.30	2.82
3	8/8	H2881-05C-ND	8.05	6.84	5.78	4.94
	8/8	H2883-07C-ND	7.76	6.60	5.57	4.77
3	6/6	H3662-05C-ND	3.74	3.18	2.69	2.30

注: 还供有定制长度 — 需要达到最低订购量。

*1=白色, 2=黑色, 3=银, 压光。

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)