



BNC PC Board/Panel Mount Jack Connectors with Mounting Flanges 50 Ohm



Hardware Sold Separately

Description	Center Contact	Mount. Height Inch (mm)	Body Material	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Right Angle	Tin	.625 (15.88)	VALOX, White	A32242-ND	5.41 4.65	5226978-1
Right Angle	Gold	.625 (15.88)	VALOX, White	A32252-ND	5.47 4.71	5226978-3


BNC PC Board/Panel Mount Right Angle Jack Connectors 50 Ohm



Hardware Sold Separately

Description	Center Contact	Mount. Height A Inch (mm)	Body Material	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Without Mounting Posts	Tin	.625 (15.88)	VALOX, White	A32253-ND	2.48 2.14	5226990-1
With Mounting Posts	Tin	.625 (15.88)	VALOX, White	A32244-ND	2.36 2.04	5227161-1
Without Mounting Posts	Gold	.625 (15.88)	VALOX, White	A32254-ND	2.00 1.72	5226990-3
With Mounting Posts	Gold	.625 (15.88)	VALOX, White	A32258-ND	2.47 2.12	5227161-3
With Mounting Posts	Gold	.519 (13.18)	VALOX, White	A32260-ND	2.28 1.97	5227161-7
With Mounting Posts	Tin	.625 (15.88)	VALOX, Black	A32245-ND	2.19 1.88	5227161-2
Without Mounting Posts	Gold	.625 (15.88)	VALOX, Black	A32255-ND	2.11 1.82	5226990-6
With Mounting Posts	Gold	.625 (15.88)	VALOX, Black	A32259-ND	2.32 2.00	5227161-6
With Mounting Posts	Gold	.519 (13.18)	VALOX, Black	A32261-ND	2.27 1.95	5227161-9
Without Mounting Posts	Tin	.625 (15.88)	Metal	A32264-ND	5.49 4.72	5227433-1
With Mounting Posts	Tin	.625 (15.88)	Metal	A32248-ND	2.95 2.54	5227661-1
Without Mounting Posts	Gold	.625 (15.88)	Metal	A32267-ND	2.47 2.12	5227676-1
With Mounting Posts	Gold	.625 (15.88)	Metal	A32268-ND	3.56 3.07	5227677-1
With Mounting Posts	Gold	.500 (12.70)	Metal	A32273-ND	5.41 4.65	5413879-1
Zinc Die Cast						
With Mounting Posts	Gold	.518 (13.16)	Zinc, White	A97552-ND	2.07 1.78	1-1337542-0
With Mounting Posts	Gold	.622 (15.80)	Zinc, White	A97553-ND	1.84 1.59	1-1337543-0
With Mounting Posts	Gold	.518 (13.16)	Zinc, Black	A97554-ND	2.23 1.92	1-1634613-0
With Mounting Posts	Gold	.622 (15.80)	Zinc, Black	A97555-ND	1.84 1.59	1-1634612-0
With Mounting Posts	Gold	.598 (15.20)	Zinc	A97556-ND	2.88 2.48	1-1337494-0

BNC PC Board/Panel Mount Vertical Jack Connectors 50 Ohm



Hardware Sold Separately

Description	Center Contact	Body Material	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Without Mounting Posts	Tin-Lead	VALOX, White	A24501-ND	5.03 4.33	226993-1
Without Mounting Posts	Tin	VALOX, White	A32256-ND	5.41 4.65	5226993-1
With Mounting Posts	Tin	VALOX, White	A32246-ND	2.14 1.85	5227222-1
Without Mounting Posts	Gold	VALOX, White	A32257-ND	5.71 4.91	5226993-3
With Mounting Posts	Gold	VALOX, White	A32262-ND	2.32 2.00	5227222-3
Without Mounting Posts	Tin	VALOX, Black	A32243-ND	6.57 5.65	5226993-2
With Mounting Posts	Tin	VALOX, Black	A32247-ND	2.48 2.14	5227222-2
With Mounting Posts	Gold	VALOX, Black	A32263-ND	2.55 2.19	5227222-6
With Mounting Posts	Tin	Metal	A32265-ND	2.48 2.14	5227671-1
With Mounting Posts	Gold	Metal	A32266-ND	2.51 2.16	5227673-1
Zinc Die Cast — RoHS Compliant					
With Mounting Posts	Gold	Zinc, White	A97557-ND	1.71 1.47	1-1337541-0
With Mounting Posts	Gold	Zinc, Black	A97558-ND	1.79 1.54	1-1634505-0

◆ RoHS Compliant

Jack Accessories 50 and 75 Ohm

Description	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Insulating Bushing for Mounting Jacks, Nylon	A24532-ND	.35 .31	222163-1
Insulating Bushing for Bulkhead Solder Jacks	A24533-ND	.19 .17	222723-1

Description	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Screw for panel thickness of 3/32 (2.38mm) or greater	A24534-ND	.30 .26	221108-2
Screw for panel thickness of less than 3/32 (2.38mm)	A24535-ND	.20 .18	221108-4
Lockwasher	A1129-ND	.20 .18	1-329632-2
Hex Nut	A1128-ND	.22 .20	1-329631-2
Zinc Die Cast — RoHS Compliant			
BNC/TNC Hexagonal Nut	A97566-ND	.51 .45	1-1634816-0
BNC/TNC Lockwasher	A97567-ND	.18 .15	1-1634817-0

◆ RoHS Compliant

BNC Vertical Metallized PC Board Mount Jack Connectors 50 Ohm





Fig.	Body Plating	Center Contact	Body Material	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
1	Nickel	Silver	VALOX	A24512-ND	3.15 2.71	227699-1
	Nickel	Silver	VALOX	A33798-ND	2.72 2.35	5227699-1
	Nickel	Gold	VALOX	A32269-ND	3.52 3.04	5227699-2
2	Nickel	Tin	VALOX	A32249-ND	2.95 2.54	5227699-3
	Nickel	Gold	VALOX	A32241-ND	3.24 2.79	5221123-2
3	Nickel	Silver	VALOX	A24516-ND	7.73 6.65	222420-1
	Nickel	Silver	VALOX	A32251-ND	5.31 4.57	5222420-1
	Tin-Lead	Silver	VALOX	A24517-ND	2.99 2.57	414305-1
3	Nickel	Silver	VALOX	A32493-ND	3.67 3.16	5414305-1
	Nickel	Gold	Zinc	A97581-ND	1.20 1.04	5-1634503-1
	Nickel	Gold	Zinc	A97583-ND	1.63 1.40	5-1634506-1

◆ RoHS Compliant

BNC Press-Fit Terminal Jack Connectors 50 Ohm



Body Plating	Center Contact	Body Material	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Nickel	Gold	TEFLON	A32250-ND	3.95 3.40	5222006-1

BNC Right-Angle PC Board Mount Jack Connectors





Fig.	Body Plating	Center Contact Length - In (mm)	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
1	Nickel	.171 (4.34)	A32270-ND	5.63 4.84	5413631-1
	Tin	.171 (4.34)	A32271-ND	5.51 4.74	5413631-2
	Nickel	.131 (3.33)	A32272-ND	20.84 17.93	5413631-3
2	Nickel	.131 (3.33)	A97570-ND	2.80 2.42	5-1634556-0
	Nickel	—	A24539-ND	3.24 2.79	414373-1
	Nickel	—	A32274-ND	2.27 1.95	5414373-1

◆ RoHS Compliant † Zinc Die Cast

BNC Twist-On Connectors 50 Ohm



Center Contact: Gold Body Plating: Nickel

Description	Dielectric	Cable Group RG/U	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Plug	Polymethylpentene	59, 59A, 59B	A24483-ND	2.44 2.11	414265-3
Plug	Polymethylpentene	59, 59A, 59B	A33797-ND	28.57 24.57	5414265-3

◆ RoHS Compliant