



## 肖特基势垒

包装	电路	IO (A)	VR (V)	IFSM (A)	最大 VF (V)	Digi-Key 零件编号	剪切带价格			带卷*		Rohm 零件编号	
							1	25	100	数量	价格		
SC-74A	A	0.1	40	1	0.34	RB471ET148CT-ND	.50	9.63	27.72	3,000	131.00/M	RB471ET148	
SOD-106	—	3.0	40	70	0.55	RB050L-40TE25CT-ND	.93	18.54	55.62	1,500	319.00/M	RB050L-40TE25	
		3.0	20	70	0.45	RB051L-40TE25CT-ND	.61	12.10	36.30	1,500	194.00/M	RB051L-40TE25	
		5	20	70	0.45	RB081L-20TE25CT-ND	1.04	20.79	62.37	1,500	358.00/M	RB081L-20TE25	
		1	40	70	0.55	RB160L-40TE25CT-ND	.42	7.66	21.56	1,500	98.00/M	RB160L-40TE25	
		1	20	70	0.40	RB161L-40TE25CT-ND	.42	8.13	23.40	1,500	117.00/M	RB161L-40TE25	
SOD-123	—	1	20	30	0.35	RB161M-20CT-ND	.52	10.00	28.80	3,000	136.00/M	RB161M-20TR	
		1.5	30	30	0.49	RB070M-30CT-ND	.50	10.00	30.00	3,000	150.00/M	RB070M-30TR	
		1	30	30	0.48	RB160M-30CT-ND	.44	8.13	22.88	3,000	94.00/M	RB160M-30TR	
		1	40	30	0.51	RB160M-40CT-ND	.42	8.13	23.40	3,000	111.00/M	RB160M-40TR	
		1	60	30	0.55	RB160M-60CT-ND	.46	8.75	25.20	3,000	119.00/M	RB160M-60TR	
		0.7	200	1	0.85	RF071M2SCT-ND	.55	10.50	30.24	3,000	143.00/M	RF071M2STR	
SOD-323	—	0.1	40	1	0.45	RB500V-40TE-17CT-ND	.57	11.00	31.68	3,000	150.00/M	RB500V-40TE	
		0.1	40	1	0.34	RB501V-40TE-17CT-ND	.50	9.22	25.96	3,000	106.00/M	RB501V-40TE	
		0.03	30	2	0.37	RB751V-40TE-17CT-ND	.40	7.63	21.96	3,000	104.00/M	RB751V-40TE	
SOD-523	—	0.03	30	2	0.37	RB751S-40TE61CT-ND	.44	8.13	22.88	3,000	94.00/M	RB751S-40TE61	
		0.2	30	1	0.60	RB520S-30TE61CT-ND	.38	7.03	19.80	3,000	81.00/M	RB520S-30TE61	
		0.2	30	1	0.50	RB521S-30TE61CT-ND	.38	7.03	19.80	3,000	81.00/M	RB521S-30TE61	
		0.2	40	1	0.55	RB520S-40TE61CT-ND	.46	8.44	23.76	3,000	97.00/M	RB520S-40TE61	
SOT-323	B	0.03	40	.2	—	RB706F-40T106CT-ND	.50	10.00	30.00	3,000	150.00/M	RB706F-40T	
		0.03	40	.2	0.37	RB715FT106CT-ND	.42	7.13	19.76	3,000	76.00/M	RB715FT106	
		0.03	40	.2	0.37	RB717FT106CT-ND	.46	8.75	25.20	3,000	119.00/M	RB717FT106	
SOT-343	C	0.1	40	1	—	RB480KTLCT-ND	.53	10.13	29.16	3,000	138.00/M	RB480KTL	
		B	0.03	40	.2	—	RB706D-40T146CT-ND	.48	9.25	26.64	3,000	126.00/M	RB706D-40T
		D	0.5	40	3	0.55	RB400DT146CT-ND	.58	11.60	34.80	3,000	174.00/M	RB400DT146
		D	0.5	20	3	0.3	RB411DT146CT-ND	.49	9.06	25.52	3,000	104.00/M	RB411DT146
		D	0.1	40	1	0.45	RB420DT146CT-ND	.46	8.44	23.76	3,000	97.00/M	RB420DT146
		E	0.1	40	1	0.34	RB425DT146CT-ND	.44	8.38	24.12	3,000	114.00/M	RB425DT146
		D	—	20	3	0.45	RB491DT146CT-ND	.46	8.75	25.20	3,000	119.00/M	RB491DT146
SOT-363	—	0.1	30	1	0.53	RB530XNCT-ND	.55	11.00	33.00	3,000	165.00/M	RB530XNTR	
		0.1	30	1	0.43	RB531XNCT-ND	.55	11.00	33.00	3,000	165.00/M	RB531XNTR	
		0.03	40	.2	0.37	RB731UT108CT-ND	.47	9.00	25.92	3,000	122.00/M	RB731UT108	
SOT-457	F	0.03	40	.2	0.37	RB715WTLCT-ND	.50	9.63	27.72	3,000	131.00/M	RB715WTL	
		0.03	40	.2	0.37	RB715WTLCT-ND	.50	9.63	27.72	3,000	131.00/M	RB715WTL	
PMDT	—	3.0	30	70	0.45	RB050LA-30CT-ND	.93	18.54	55.62	3,000	294.00/M	RB050LA-30TR	
		3.0	40	70	0.55	RB050LA-40CT-ND	.93	18.54	55.62	3,000	294.00/M	RB050LA-40TR	
		3.0	30	70	0.42	RSX301LA-30CT-ND	.75	15.03	45.09	3,000	238.00/M	RSX301LA-30TR	
TUMD2	—	1	20	5	0.42	RB161VA-20CT-ND	.52	10.00	28.80	3,000	136.00/M	RB161VA-20TR	
		0.5	40	3	0.55	RB400VA-50CT-ND	.58	11.60	34.80	3,000	174.00/M	RB400VA-50TR	
		0.5	30	5	0.39	RSX051VA-30CT-ND	.46	8.88	25.56	3,000	121.00/M	RSX051VA-30TR	
		0.7	30	5	0.42	RSX071VA-30CT-ND	.46	8.88	25.56	3,000	121.00/M	RSX071VA-30TR	
VMD2	—	.03	30	.2	0.37	RB751G-40T2RCT-ND	.52	10.00	28.80	8,000	128.00/M	RB751G-40T2R	
VMD3	—	.03	30	.2	0.37	RB715ZT2LCT-ND	.57	10.88	31.32	8,000	139.00/M	RB715ZT2L	

## 开关二极管

包装	电路	VRM (V)	VR (V)	IFM (mA)	IO (mA)	Digi-Key 零件编号	剪切带价格			带卷*		Rohm 零件编号
							1	25	100	数量	价格	
DO-34	—	90	80	400	130	1S133T-77CT-ND†	.24	3.20	7.20	5,000	19.00/M	1S133T-77
DO-35	—	100	75	450	150	1N4148T-73CT-ND	.20	2.68	6.03	5,000	16.00/M	1N4148T-73
DO-41	—	500	400	30A	1.0A	1SR153-400T-32CT-ND†	.48	9.25	26.64	2,500	126.00/M	1SR153-400T-32
SOD-106	—	400	—	30A	1.0A	1SR154-400TE25CT-ND	.34	5.81	16.12	1,500	71.00/M	1SR154-400TE25
		600	—	30A	1.0A	1SR154-600TE25CT-ND	.49	9.06	25.52	1,500	116.00/M	1ST154-600TE25
SOD-123	—	—	400	25A	0.7A	RR264M-400CT-ND	.44	7.50	20.80	3,000	80.00/M	RR264M-400

\* 将 CT-ND 改为 TR-ND, 即为带卷包装的零件编号。 † 将 CT-ND 改为 TB-ND, 即为带盒包装的零件编号。 (转下页)

Digi-Reel® Digi-Reel® 中含有大多数的 SMT 切割零件。将 1-ND 改为 6-ND, 或将 CT-ND 改为 DKR-ND, 即为 Digi-Reel 零件编号。请参见第 2 页上的 Digi-Key® 服务以获得更多信息。