

HARWIN PCB Terminals and Sockets



A




Fig.	Dimensions - mm				Digi-Key Part No.	Price Each				Harwin Part No.
	A	B	C	D		1	10	50	100	
PC Board Turned Terminals										
Turret Lugs										
1	4.78	2.38	3.18	0.79	952-1425-ND	.39	.28	.21	.19	H2051-01
	6.35	3.17	3.18	1.19	952-1426-ND	.39	.28	.21	.19	H2055-01
2	9.12	1.78	3.18	4.75	952-1427-ND	.72	.57	.48	.43	H2071Z01
	6.35	1.07	3.25	3.96	952-1428-ND	.59	.47	.40	.36	H2072-01
	6.52	1.24	2.54	3.96	952-1429-ND	.54	.42	.36	.32	H2072Z01
	6.52	1.24	2.54	3.96	952-1430-ND	.56	.44	.38	.34	H2072ZL1
3	9.12	1.78	3.18	4.75	952-1431-ND	.45	.32	.25	.22	H2073Z01
	8.74	1.60	4.57	6.35	952-1432-ND	.92	.76	.64	.57	H2074Z01
4	5.15	0.58	2.39	3.18	952-1440-ND	.41	.29	.23	.20	H2121-01
5	2.39	0.46	1.02	1.57	952-1450-ND	.40	.25	.17	.15	H9001-01
	4.74	1.19	1.81	3.18	952-1451-ND	.41	.29	.23	.20	H9004-01
6	7.65	0.58	2.36	3.18	952-1452-ND	.50	.35	.27	.24	H9020-01
	7.65	0.58	2.36	3.18	952-1453-ND	.45	.32	.25	.22	H9021-01
	3.96	0.78	1.83	0.71	952-1454-ND	.40	.32	.27	.25	H9023-01
0.5mm										
7	5.70	0.38	—	—	952-1447-ND	.36	.22	.15	.13	H3108-01
0.8mm										
8	5.05	4.48	—	—	952-1436-ND	.32	.21	.14	.12	H2105-01
9	4.11	0.51	—	—	952-1437-ND	.45	.32	.25	.22	H2105A01
	4.11	0.51	—	—	952-1438-ND	.41	.29	.23	.20	H2106A01
10	6.30	0.81	—	—	952-1438-ND	.45	.32	.25	.22	H2105B01
1.0mm										
8	8.23	6.07	0.91	2.39	952-1433-ND	.45	.32	.25	.22	H2101-01
10	8.39	0.93	—	—	952-1456-ND	.41	.29	.23	.20	H2101B01
	9.20	0.93	—	—	952-1435-ND	.41	.29	.23	.20	H2102B01
11	6.53	0.51	—	—	952-1434-ND	.36	.22	.15	.13	H2101A01
	13.21	0.51	—	—	952-1442-ND	.41	.29	.23	.20	H2170-01
	8.13	0.51	—	—	952-1443-ND	.37	.26	.21	.18	H2173-01

Fig.	Dimensions - mm				Digi-Key Part No.	Price Each				Harwin Part No.
	A	B	C	D		1	10	50	100	
PC Board Sockets										
Sub-Miniature 0.5mm										
12	4.32	0.51	—	—	952-1444-ND	.32	.23	.18	.16	H2174-01
	4.90	0.35	—	—	952-1445-ND	.30	.21	.16	.14	H2175-01
	9.53	0.51	—	—	952-1446-ND	.37	.23	.16	.14	H2176-01
13	7.00	0.50	0.97	1.59	952-1448-ND	.26	.17	.11	.10	H3150-01
14	5.59	4.41	0.97	1.59	952-1449-ND	.38	.27	.21	.18	H3151-01
1.2mm										
15	11.40	1.00	1.21	2.00	952-1441-ND	.35	.22	.15	.13	H2157-01
Solder Cup Pin										
16	6.35	5.08	3.18	2.39	952-1455-ND	.40	.32	.27	.25	H9026-01
PC Board Sockets										
Sub-Miniature 0.5mm										
17	—	—	—	—	952-1457-ND	.36	.23	.15	.13	H3153-01
18	—	—	—	—	952-1458-ND	.30	.21	.17	.14	H3155-01
19	—	—	—	—	952-1459-ND	.40	.28	.22	.19	H3190-01
20	—	—	—	—	952-1460-ND	.45	.32	.25	.22	H3191-01
21	—	—	—	—	952-1461-ND	.50	.35	.27	.24	H3192-01
0.8mm										
22	—	—	—	—	952-1462-ND	.50	.39	.34	.30	H8505-01
23	—	—	—	—	952-1463-ND	.44	.35	.29	.27	H8501-01
24	—	—	—	—	952-1464-ND	.45	.32	.25	.22	H8502-01
1.00mm										
25	—	—	—	—	952-1465-ND	.45	.32	.25	.22	H3165-01
26	—	—	—	—	952-1466-ND	.41	.29	.23	.20	H3182-01
27	—	—	—	—	952-1467-ND	.31	.22	.17	.15	H3161-01
28	—	—	—	—	952-1468-ND	.40	.29	.22	.20	H3183-01
29	—	—	—	—	952-1469-ND	.47	.37	.31	.28	H3169-01
30	—	—	—	—	952-1470-ND	.40	.32	.27	.25	H3185-01
31	—	—	—	—	952-1471-ND	1.27	1.06	.88	.79	H3194-01
2.00mm										
32	—	—	—	—	952-1472-ND	1.13	.94	.79	.70	H3490-01
33	—	—	—	—	952-1473-ND	1.10	.92	.77	.68	H3492-01