



BNC PC Board/Panel Mount Jack Connectors with Mounting Flanges 50 Ohm



Hardware Sold Separately

Description	Center Contact	Mount. Height Inch (mm)	Body Material	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Right Angle	Tin	.625 (15.88)	VALOX, White	A32242-ND	4.94 4.25	5226978-1
Right Angle	Gold	.625 (15.88)	VALOX, White	A32252-ND	4.94 4.25	5226978-3


BNC PC Board/Panel Mount Right Angle Jack Connectors 50 Ohm



Hardware Sold Separately

Description	Center Contact	Mount. Height A Inch (mm)	Body Material	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Without Mounting Posts	Tin	.625 (15.88)	VALOX, White	A32253-ND	2.51 2.17	5226990-1
With Mounting Posts	Tin	.625 (15.88)	VALOX, White	A32244-ND	1.85 1.60	5227161-1
Without Mounting Posts	Gold	.625 (15.88)	VALOX, White	A32254-ND	2.16 1.86	5226990-3
With Mounting Posts	Gold	.625 (15.88)	VALOX, White	A32258-ND	1.85 1.60	5227161-3
With Mounting Posts	Gold	.519 (13.18)	VALOX, White	A32260-ND	1.85 1.60	5227161-7
With Mounting Posts	Tin	.625 (15.88)	VALOX, Black	A32245-ND	1.85 1.60	5227161-2
Without Mounting Posts	Gold	.625 (15.88)	VALOX, Black	A32255-ND	2.16 1.86	5226990-6
With Mounting Posts	Gold	.625 (15.88)	VALOX, Black	A32259-ND	1.85 1.60	5227161-6
With Mounting Posts	Gold	.519 (13.18)	VALOX, Black	A32261-ND	1.85 1.60	5227161-9
Without Mounting Posts	Tin	.625 (15.88)	Metal	A32264-ND	4.96 4.27	5227433-1
With Mounting Posts	Tin	.625 (15.88)	Metal	A32248-ND	2.50 2.16	5227661-1
Without Mounting Posts	Gold	.625 (15.88)	Metal	A32267-ND	2.57 2.21	5227676-1
With Mounting Posts	Gold	.625 (15.88)	Metal	A32268-ND	2.50 2.16	5227677-1
With Mounting Posts	Gold	.500 (12.70)	Metal	A32273-ND	4.43 3.81	5413879-1
Zinc Die Cast						
With Mounting Posts	Gold	.518 (13.16)	Zinc, White	A97552-ND	1.76 1.52	1-1337542-0
With Mounting Posts	Gold	.622 (15.80)	Zinc, White	A97553-ND	1.76 1.52	1-1337543-0
With Mounting Posts	Gold	.518 (13.16)	Zinc, Black	A97554-ND	1.76 1.52	1-1634613-0
With Mounting Posts	Gold	.622 (15.80)	Zinc, Black	A97555-ND	1.76 1.52	1-1634612-0
With Mounting Posts	Gold	.598 (15.20)	Zinc	A97556-ND	2.76 2.38	1-1337494-0

BNC PC Board/Panel Mount Vertical Jack Connectors 50 Ohm



Hardware Sold Separately

Description	Center Contact	Body Material	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Without Mounting Posts	Tin-Lead	VALOX, White	A24501-ND	4.65 4.00	226993-1
Without Mounting Posts	Tin	VALOX, White	A32256-ND	4.21 3.63	5226993-1
With Mounting Posts	Tin	VALOX, White	A32246-ND	1.85 1.60	5227222-1
Without Mounting Posts	Gold	VALOX, White	A32257-ND	4.31 3.70	5226993-3
With Mounting Posts	Gold	VALOX, White	A32262-ND	1.85 1.60	5227222-3
Without Mounting Posts	Tin	VALOX, Black	A32243-ND	4.94 4.25	5226993-2
With Mounting Posts	Tin	VALOX, Black	A32247-ND	2.11 1.82	5227222-2
With Mounting Posts	Gold	VALOX, Black	A32263-ND	2.11 1.82	5227222-6
With Mounting Posts	Tin	Metal	A32265-ND	2.05 1.77	5227671-1
With Mounting Posts	Gold	Metal	A32266-ND	2.13 1.84	5227673-1
Zinc Die Cast — RoHS Compliant					
With Mounting Posts	Gold	Zinc, White	A97557-ND	1.84 1.58	1-1337541-0
With Mounting Posts	Gold	Zinc, Black	A97558-ND	1.84 1.58	1-1634505-0

◆ RoHS Compliant

Jack Accessories 50 and 75 Ohm

Description	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Insulating Bushing for Mounting Jacks, Nylon	A24532-ND	.33 .29	222163-1
Insulating Bushing for Bulkhead Solder Jacks	A24533-ND	.17 .15	227223-1

Description	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Screw for panel thickness of 3/32 (2.38mm) or greater	A24534-ND	.28 .24	221108-2
Screw for panel thickness of less than 3/32 (2.38mm)	A24535-ND	.28 .24	221108-4
Lockwasher	A1129-ND	.23 .20	1-329632-2
Hex Nut	A1128-ND	.24 .22	1-329631-2
Zinc Die Cast — RoHS Compliant			
BNC/TNC Hexagonal Nut	A97566-ND	.26 .23	1-1634816-0
BNC/TNC Lockwasher	A97567-ND	.13 .12	1-1634817-0

◆ RoHS Compliant

BNC Vertical Metallized PC Board Mount Jack Connectors 50 Ohm





Fig.	Body Plating	Center Contact	Body Material	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
1	Nickel	Silver	VALOX	A24512-ND	3.27 2.81	227699-1
	Nickel	Silver	VALOX	A33798-ND	3.01 2.59	5227699-1
	Nickel	Gold	VALOX	A32269-ND	3.01 2.59	5227699-2
2	Nickel	Tin	VALOX	A32249-ND	3.01 2.59	5227699-3
	Nickel	Gold	VALOX	A24515-ND	4.61 3.97	221123-2
	Nickel	Gold	VALOX	A32241-ND	2.93 2.52	5221123-2
3	Nickel	Silver	VALOX	A24516-ND	4.31 3.70	222420-1
	Nickel	Silver	VALOX	A32251-ND	4.76 4.09	5222420-1
	Tin-Lead	Silver	VALOX	A24517-ND	3.98 3.42	414305-1
3	Tin	Silver	VALOX	A32493-ND	3.65 3.14	5414305-1
	Zinc Die Cast — RoHS Compliant					
3	Nickel	Gold	Zinc	A97581-ND	1.31 1.13	5-1634503-1
	Nickel	Gold	Zinc	A97583-ND	1.29 1.11	5-1634506-1

◆ RoHS Compliant

BNC Press-Fit Terminal Jack Connectors 50 Ohm



Body Plating	Center Contact	Body Material	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Nickel	Gold	TEFLON	A32250-ND	3.81 3.28	5222006-1

BNC Right-Angle PC Board Mount Jack Connectors





Fig.	Body Plating	Center Contact Length - In (mm)	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
1	Nickel	.171 (4.34)	A32270-ND	5.03 4.33	5413631-1
	Tin	.171 (4.34)	A32271-ND	5.01 4.31	5413631-2
	Nickel	.131 (3.33)	A32272-ND	5.59 4.81	5413631-3
	Nickel	.131 (3.33)	A97570-ND	2.49 2.14	5-1634556-0
2	Nickel	—	A24539-ND	2.40 2.07	414373-1
	Nickel	—	A32274-ND	2.03 1.75	5414373-1

◆ RoHS Compliant † Zinc Die Cast

BNC Twist-On Connectors 50 Ohm



Center Contact: Gold Body Plating: Nickel

Description	Dielectric	Cable Group RG/U	Digi-Key Part No.	Price Each 1 25	Tyco Electronics Part No.
Plug	Polymethylpentene	59, 59A, 59B	A24483-ND	3.98 3.42	414265-3
			A33797-ND	3.43 2.95	5414265-3

◆ RoHS Compliant

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

uk.digikey.com — FREEPHONE: 0-800-587-0991 • 0-800-904-7786 — FREEFAX: 0-800-587-0992 • 0-800-904-7783