



ANALOG DEVICES  (Cont.)		POWER MANAGEMENT			
Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25 100	
ADP3309ARTZ-3.3-R7CT-ND	Regulator LDO 3.3V, 100mA	SOT-23-5	1.65	1.38 1.10	
ADP3309ARTZ-3.3-R7TR-ND	Regulator LDO 3.3V, 100mA	SOT-23-5	2144.45/3,000		
ADP3309ARTZ-2.5-R7CT-ND	Regulator LDO 2.5V, 200mA	SOT-23-6	1.74	1.49 1.05	
ADP3309ARTZ-2.5-R7TR-ND	Regulator LDO 2.5V, 200mA	SOT-23-6	2671.64/3,000		
ADP3309ARTZ-3-RL7CT-ND	Regulator LDO 3.3V, 200mA	SOT-23-6	1.74	1.40 1.05	
ADP3309ARTZ-3-RL7TR-ND	Regulator LDO 3.3V, 200mA	SOT-23-6	2671.64/3,000		
ADP3311ARTZ-REEL7CT-ND	Regulator LDO Adj. 200mA	SOT-23-6	1.74	1.40 1.05	
ADP3311ARTZ-REEL7TR-ND	Regulator LDO Adj. 200mA	SOT-23-6	2671.64/3,000		
ADP3333ARMZ-5-R7CT-ND	Regulator LDO 5.0V, 300mA	8-MSOP	2.33	1.87 1.40	
ADP3333ARMZ-5-R7TR-ND	Regulator LDO 5.0V, 300mA	8-MSOP	1210.81/1,000		
ADP3334ARZ-ND	Regulator LDO Adj. 500mA	8-SOIC	2.45	1.96 1.47	
ADP3335ACPZ-3.3-R7CT-ND	Regulator LDO 3.3V, 500mA	8-LFSCP	2.56	2.05 1.54	
ADP3335ACPZ-3.3-R7TR-ND	Regulator LDO 3.3V, 500mA	8-LFSCP	1991.27/1,500		
ADP3335ARMZ-2.5-RLCT-ND	Regulator LDO 2.5V, 500mA	8-MSOP	2.58	2.07 1.55	
ADP3335ARMZ-3.3-RLCT-ND	Regulator LDO 3.3V, 500mA	8-MSOP	2.58	2.07 1.55	
ADP3335ARMZ-3.3-RLTR-ND	Regulator LDO 3.3V, 500mA	8-MSOP	3964.37/3,000		
ADP3335ARMZ-500mA Adj.	Regulator LDO 500mA, Adj.	8-MSOP	2.58	2.07 1.55	
ADP3335ARMZ-REEL7TR-ND	Regulator LDO 500mA, Adj.	8-MSOP	1342.10/1,000		
ADP3338AKCZ-1.5-R7CT-ND	Regulator LDO 1A Precision 1.5V	SOT-223	2.78	2.23 1.73	
ADP3338AKCZ-1.5-R7TR-ND	Regulator LDO 1A Precision 1.5V	SOT-223	802.34/500		
ADP3338AKCZ-1.8-R7CT-ND	Regulator LDO 1A Precision 1.8V	SOT-223	2.78	2.23 1.73	
ADP3338AKCZ-1.8-R7TR-ND	Regulator LDO 1A Precision 1.8V	SOT-223	802.34/500		
ADP3338AKCZ-2.5RL7CT-ND	Regulator LDO 1A Precision 2.5V	SOT-223	2.78	2.23 1.73	
ADP3338AKCZ-2.5RL7TR-ND	Regulator LDO 1A Precision 2.5V	SOT-223	802.34/500		
ADP3338AKCZ-3.3RL7CT-ND	Regulator LDO 1A Precision 3.3V	SOT-223	2.78	2.23 1.73	
ADP3338AKCZ-3.3RL7TR-ND	Regulator LDO 1A Precision 3.3V	SOT-223	802.34/500		
ADP3338AKCZ-5-R7CT-ND	Regulator LDO 1A Precision 5V	SOT-223	2.78	2.23 1.73	
ADP3338AKCZ-5-R7TR-ND	Regulator LDO 1A Precision 5V	SOT-223	802.34/500		
ADP3339AKCZ-1.5-R7CT-ND	Regulator LDO 1.5A, 1.5V	SOT-223	2.98	2.39 1.86	
ADP3339AKCZ-1.5-R7TR-ND	Regulator LDO 1.5A, 1.5V	SOT-223	860.70/500		
ADP3339AKCZ-1.8-R7CT-ND	Regulator LDO 1.5A, 1.8V	SOT-223	2.98	2.39 1.86	
ADP3339AKCZ-1.8-R7TR-ND	Regulator LDO 1.5A, 1.8V	SOT-223	860.70/500		
ADP3339AKCZ-2.5-R7CT-ND	Regulator LDO 1.5A, 2.5V	SOT-223	2.98	2.39 1.86	
ADP3339AKCZ-2.5-R7TR-ND	Regulator LDO 1.5A, 2.5V	SOT-223	860.70/500		
ADP3339AKCZ-3-RL7CT-ND	Regulator LDO 1.5A, 3V	SOT-223	2.98	2.39 1.86	
ADP3339AKCZ-3-RL7TR-ND	Regulator LDO 1.5A, 3V	SOT-223	860.70/500		
ADP3339AKCZ-3.3-R7CT-ND	Regulator LDO 1.5A, 3.3V	SOT-223	2.98	2.39 1.86	
ADP3339AKCZ-3.3-R7TR-ND	Regulator LDO 1.5A, 3.3V	SOT-223	860.70/500		
ADP3339AKCZ-5-R7CT-ND	Regulator LDO 1.5A, 5V	SOT-223	2.98	2.39 1.86	
ADP3339AKCZ-5-R7TR-ND	Regulator LDO 1.5A, 5V	SOT-223	860.70/500		
ADP3367ARZ-ND	Regulator LDO Adjustable 5V	8-SOIC	4.57	3.66 2.85	
ADP5020ACPZ-R7CT-ND	Regulator LDO Dual, Step-Down <b>NEW!</b>	20-LFSCP	3.79	3.03 2.36	
ADP5020ACPZ-R7TR-ND	Regulator LDO Dual, Step-Down <b>NEW!</b>	20-LFSCP	3219.20/1,500		
<b>Voltage Reference</b>					
AD580LH-ND	Precision Voltage Reference 2.5V*	TO-52-3	6.78	5.43 4.58	
AD580LH-ND	Precision Voltage Reference 2.5V*	TO-52-3	15.69	14.13 12.53	
AD580LH-ND	Precision Voltage Reference 2.5V*	TO-52-3	27.02	25.22 23.42	
AD581HJ-ND	Precision Voltage Reference 10V*	TO-5-3	10.37	8.30 7.00	
AD581KH-ND	Precision Voltage Reference 10V*	TO-5-3	13.96	12.21 10.83	
AD581LH-ND	Precision Voltage Reference 10V*	TO-5-3	24.84	23.19 21.54	
AD584JH-ND	Precision Voltage Reference Programmable	TO-99-8	10.19	9.18 8.14	
AD584JNZ-ND	Precision Voltage Reference Programmable*	8-Dip	7.14	5.71 4.82	
AD584KNZ-ND	Precision Voltage Reference Programmable*	8-Dip	11.68	10.53 9.33	
AD584TH-ND	Precision Voltage Reference Programmable	TO-99-8	37.63	35.12 32.61	
AD586ARZ-REELCT-ND	Precision Voltage Reference 5V*	8-SOIC	9.43	8.49 7.53	
AD586ARZ-REELTR-ND	Precision Voltage Reference 5V*	8-SOIC	17179.15/2,500		
AD586BRZ-ND	Precision Voltage Reference 5V*	8-SOIC	13.11	11.80 10.47	
AD586BRZ-REELCT-ND	Precision Voltage Reference 5V*	8-SOIC	13.11	11.80 10.47	
AD586JRZ-ND	Precision Voltage Reference 5V*	8-SOIC	6.82	5.46 4.61	
AD586KNZ-ND	Precision Voltage Reference 5V*	8-Dip	8.28	6.63 5.59	
AD586KRZ-ND	Precision Voltage Reference 5V*	8-SOIC	9.00	7.20 6.08	
AD586LRZ-ND	Precision Voltage Reference 5V*	8-SOIC	10.28	9.26 8.21	
AD586MMZ-ND	Precision Voltage Reference 5V*	8-Dip	11.09	9.99 8.86	
AD587JNZ-ND	Precision Voltage Reference 10V*	8-Dip	5.99	4.80 4.05	
AD587JRZ-ND	Precision Voltage Reference 10V*	8-SOIC	6.82	5.46 4.61	
AD587KRZ-ND	Precision Voltage Reference 10V*	8-SOIC	7.74	6.20 5.23	
AD588AQ-ND	Precision Voltage Reference Programmable	16-Dip	30.15	28.14 26.13	
AD588JQ-ND	Precision Voltage Reference Programmable	16-Dip	25.85	24.14 22.41	
AD588JZ-ND	Voltage Reference 1.235V, 2-Terminal*	TO-51-2	9.61	7.69 6.49	
AD588JRZ-ND	Voltage Reference 1.235V, 2-Terminal*	8-SOIC	4.30	3.34 2.68	
AD588KH-ND	Voltage Reference 1.235V, 2-Terminal*	TO-51-2	10.40	8.35 7.05	
AD680AMZ-ND	Voltage Reference 2.5V, Low Power*	8-Dip	7.32	5.86 4.94	
AD680JR-REEL7CT-ND	Voltage Reference 2.5V Low Power*	8-SOIC	5.63	4.51 3.51	
AD680JRZ-ND	Voltage Reference 2.5V Low Power*	8-SOIC	4.67	3.74 2.91	
AD680JZ-ND	Voltage Reference 2.5V Low Power*	TO-92-3	27.61	25.77 23.93	
AD688AQ-ND	Precision Voltage Reference +/-10V	16-Dip	46.56	43.46 40.36	
AD688BRZ-ND	Precision Voltage Reference +/-10V	16-Dip	8.98	7.19 6.06	
AD780AMZ-ND	Precision Voltage Reference 2.5V/3.0V*	8-SOIC	8.98	7.19 6.06	
AD780ARZ-ND	Precision Voltage Reference 2.5V/3.0V*	8-Dip	10.81	9.73 8.63	
AD780BRZ-ND	Precision Voltage Reference 2.5V/3.0V*	8-SOIC	10.81	9.73 8.63	
AD1580ARTZ-REEL7CT-ND	Voltage Reference 1.225V*	SOT-23	1.89	1.51 1.13	
AD1580ARTZ-REEL7TR-ND	Voltage Reference 1.225V*	SOT-23	2887.09/3,000		
AD1580BRTZ-REEL7CT-ND	Voltage Reference 1.225V*	SOT-23	2.02	1.62 1.22	
AD1580BRTZ-REEL7TR-ND	Voltage Reference 1.225V*	SOT-23	3102.55/3,000		
AD1582ARTZ-REEL7CT-ND	Voltage Reference 2.5V*	SOT-23	1.51	1.22 91	
AD1582ARTZ-REEL7TR-ND	Voltage Reference 2.5V*	SOT-23	2326.91/3,000		
AD1582BRTZ-REEL7CT-ND	Voltage Reference 2.5V*	SOT-23-3	2.11	1.69 1.27	
AD1582BRTZ-REEL7TR-ND	Voltage Reference 2.5V*	SOT-23-3	3231.82/3,000		
AD1583ARTZ-REEL7CT-ND	Voltage Reference 3V*	SOT-23-3	1.51	1.22 91	
AD1583ARTZ-REEL7TR-ND	Voltage Reference 3V*	SOT-23-3	2326.91/3,000		
AD1583BRTZ-REEL7CT-ND	Voltage Reference 3V*	SOT-23	2.11	1.69 1.27	
AD1583BRTZ-REEL7TR-ND	Voltage Reference 3V*	SOT-23	3231.82/3,000		
AD1584ARTZ-REEL7CT-ND	Voltage Reference 4.096V*	SOT-23-3	1.51	1.22 91	
AD1584ARTZ-REEL7TR-ND	Voltage Reference 4.096V*	SOT-23-3	2326.91/3,000		
AD1584BRTZ-REEL7CT-ND	Voltage Reference 1.096V*	SOT-23	2.11	1.69 1.27	
AD1584BRTZ-REEL7TR-ND	Voltage Reference 1.096V*	SOT-23	3231.82/3,000		
AD101ARZ-ND	Precision Voltage Reference 10V, 10mA*	8-SOIC	2.73	2.18 1.64	
AD101AUJZ-REEL7CT-ND	Precision Voltage Reference 10V, 10mA*	TSOT-23-5	2.75	2.20 1.65	
AD101AUJZ-REEL7TR-ND	Precision Voltage Reference 10V, 10mA*	TSOT-23-5	4222.91/3,000		
AD101BRZ-ND	Precision Voltage Reference 10V, 10mA*	8-SOIC	5.71	4.57 3.56	
AD102AKSZ-REEL7CT-ND	Precision Voltage Reference 5V, 10mA*	TSOT-23-5	2.78	2.23 1.73	
AD102AKSZ-REEL7TR-ND	Precision Voltage Reference 5V, 10mA*	TSOT-23-5	4665.94/3,000		
AD102ARZ-ND	Precision Voltage Reference 5V, 10mA*	8-SOIC	2.73	2.18 1.64	
AD102AUJZ-REEL7CT-ND	Precision Voltage Reference 5V, 10mA*	TSOT-23-5	2.75	2.20 1.65	
AD102AUJZ-REEL7TR-ND	Precision Voltage Reference 5V, 10mA*	TSOT-23-5	4222.91/3,000		
AD102BKSZ-REEL7CT-ND	Precision Voltage Reference 5V, 10mA*	TSOT-23-5	5.15	4.13 3.21	

ANALOG DEVICES  (Cont.)		POWER MANAGEMENT			
Digi-Key Part No.	Description	Pkg.	Price Each*		
			1	25 100	
AD102BKSZ-REEL7TR-ND	Precision Voltage Reference 5V, 10mA*	TSOT-23-5	5.15	4.13 3.21	
AD102BRZ-ND	Precision Voltage Reference 5V, 10mA*	8-SOIC	5.71	4.57 3.56	
AD102BUJZ-REEL7CT-ND	Precision Voltage Reference 5V, 10mA*	TSOT-23-5	5.15	4.13 3.21	
AD102BUJZ-REEL7TR-ND	Precision Voltage Reference 5V, 10mA*	TSOT-23-5	8653.20/3,000		
AD103AKSZ-REEL7CT-ND	Precision Voltage Reference 2.5V, 10mA*	TSOT-23-5	2.78	2.23 1.73	
AD103AKSZ-REEL7TR-ND	Precision Voltage Reference 2.5V, 10mA*	TSOT-23-5	4665.94/3,000		
AD103ARZ-ND	Precision Voltage Reference 2.5V, 10mA*	8-SOIC	2.73	2.18 1.64	
AD103AUJZ-REEL7CT-ND	Precision Voltage Reference 2.5V, 10mA*	TSOT-23-5	2.75	2.20 1.65	
AD103AUJZ-REEL7TR-ND	Precision Voltage Reference 2.5V, 10mA*	TSOT-23-5	4222.91/3,000		
AD103BKSZ-REEL7CT-ND	Precision Voltage Reference 2.5V, 10mA*	TSOT-23-5	5.15	4.13 3.21	
AD103BKSZ-REEL7TR-ND	Precision Voltage Reference 2.5V, 10mA*	TSOT-23-5	8653.20/3,000		
AD103BRZ-ND	Precision Voltage Reference 2.5V, 10mA*	8-SOIC	2.73	2.18 1.64	
AD103BUJZ-REEL7CT-ND	Precision Voltage Reference 2.5V, 10mA*	TSOT-23-5	2.75	2.20 1.65	
AD103BUJZ-REEL7TR-ND	Precision Voltage Reference 2.5V, 10mA*	TSOT-23-5	4222.91/3,000		
AD106AKSZ-REEL7CT-ND	Precision Voltage Reference 3V, 10mA*	TSOT-23-5	2.78	2.23 1.73	
AD106AKSZ-REEL7TR-ND	Precision Voltage Reference 3V, 10mA*	TSOT-23-5	4665.94/3,000		
AD106ARZ-ND	Precision Voltage Reference 3V, 10mA*	8-SOIC	2.73	2.18 1.64	
AD106AUJZ-REEL7CT-ND	Precision Voltage Reference 3V, 10mA*	TSOT-23-5	2.75	2.20 1.65	
AD106AUJZ-REEL7TR-ND	Precision Voltage Reference 3V, 10mA*	TSOT-23-5	4222.91/3,000		
AD121AUJZ-REEL7CT-ND	Precision Voltage Reference 2.5V*	SOT-23-6	5.71	4.57 3.56	
AD121AUJZ-REEL7TR-ND	Precision Voltage Reference 2.5V*	SOT-23-6	3964.37/3,000		
AD125AUJZ-REEL7CT-ND	Precision Voltage Reference 2.5V*	SOT-23-6	5.71	4.57 3.56	
AD125AUJZ-REEL7TR-ND	Precision Voltage Reference 2.5V*	SOT-23-6	3964.37/3,000		
AD127AUJZ-REEL7CT-ND	Precision Voltage Reference 1.25V*	TSOT-23-6	2.58	2.07 1.55	
AD127AUJZ-REEL7TR-ND	Precision Voltage Reference 1.25V*	TSOT-23-6	3964.37/3,000		
AD130AUJZ-REEL7CT-ND	Precision Voltage Reference Sub-Band Gap*	TSOT-6	2.58	2.07 1.55	
AD130AUJZ-REEL7TR-ND	Precision Voltage Reference Sub-Band Gap*	TSOT-6	3964.37/3,000		
AD130BUJZ-REEL7CT-ND	Precision Voltage Reference Sub-Band Gap*	TSOT-6	3.82	3.05 2.38	
AD130BUJZ-REEL7TR-ND	Precision Voltage Reference Sub-Band Gap*	TSOT-6	6405.06/3,000		
AD182BKAZ-REEL7CT-ND	Voltage Reference High PSRR 1.2V*	TSOT-6	2.19	1.76 1.32	
AD182BKAZ-REEL7TR-ND	Voltage Reference High PSRR 1.2V*	TSOT-6	3361.09/3,000		
AD182BARTZ-REEL7CT-ND	Voltage Reference High PSRR 1.2V*	SOT-23	2.19	1.76 1.32	
AD182BARTZ-REEL7TR-ND	Voltage Reference High PSRR 1.2V*	SOT-23	3361.09/3,000		
ADR21ERZ-ND	Precision Voltage Reference 2.5V, 5mA Out*	8-SOIC	10.58	9.53 8.45	
ADR21FRZ-ND	Precision Voltage Reference 2.5V, 5mA Out*	8-SOIC	5.75	4.60 3.88	
ADR21GRZ-ND	Precision Voltage Reference 2.5V, 5mA Out*	8-TSSOP	5.98	4.79 3.73	
ADR21GRZ-ND	Precision Voltage Reference 2.5V, 5mA Out*	8-SOIC	4.60	3.68 2.86	
ADR22ERZ-ND	Precision Voltage Reference 4.096V, 5mA*	8-SOIC	10.58	9.53 8.45	
ADR22GRZ-ND	Precision Voltage Reference 4.096V, 5mA*	8-SOIC	4.60	3.68 2.86	
ADR22GRZ-ND	Precision Voltage Reference 4.096V, 5mA*	8-TSSOP	5.98	4.79 3.73	
ADR23GRZ-ND	Precision Voltage Reference 5V*	8-SOIC	4.80	3.84 2.99	
ADR23GRZ-ND	Precision Voltage Reference 5V*	8-SOIC	10.58	9.53 8.45	
ADR360AUJZ-RZCT-ND	Precision Reference Low Power 2.048V*	5-TSOT	2.95	2.36 1.77	
ADR360AUJZ-RZTR-ND	Precision Reference Low Power 2.048V*	5-TSOT	391.78/250		
ADR360BUJZ-RZCT-ND	Precision Reference Low Power 2.048V*	5-TSOT	4.04	3.24 2.52	
ADR360BUJZ-RZTR-ND	Precision Reference Low Power 2.048V*	5-TSOT	596.99/250		
ADR361AUJZ-RZCT-ND	Precision Reference Low Power 2.5V*	5-TSOT	2.67	2.14 1.60	
ADR361AUJZ-RZTR-ND	Precision Reference Low Power 2.5V*	5-TSOT	373.		