

ANALOG DEVICES		DigiKey Reel (Cont.)		AMPLIFIERS		
Digi-Key Part No.	Description	Pkg.	Price Each*			
			1	25	100	
AD8032BRZ-REEL7CT-ND	Voltage-Feedback Amp Dual Rail-to-Rail*	8-SOIC	7.09	5.68	4.79	
AD8032BRZ-REEL7TR-ND	Voltage-Feedback Amp Dual Rail-to-Rail*	8-SOIC		3377.59/750		
AD8033AKSZ-REEL7CT-ND	Voltage-Feedback Amp with FastFET™	SC70-5	2.60	2.09	1.62	
AD8033AKSZ-REEL7TR-ND	Voltage-Feedback Amp with FastFET™	SC70-5		4769.02/3,000		
AD8033ARZ-ND	Voltage-Feedback Amp with FastFET™	8-SOIC	2.38	2.23	1.73	
AD8034ARTZ-REEL7CT-ND	Voltage-Feedback Amp Dual with FastFET™	SOT-23-8	4.06	3.26	2.53	
AD8034ARTZ-REEL7TR-ND	Voltage-Feedback Amp Dual with FastFET™	SOT-23-8		6829.24/3,000		
AD8034ARZ-ND	Voltage-Feedback Amp Dual with FastFET™	8-SOIC	4.14	3.32	2.58	
AD8036ANZ-ND	Voltage-Feedback Clamp Amp*	8-Dip	9.96	7.98	6.73	
AD8036ARZ-ND	Voltage-Feedback Clamp Amp*	8-SOIC	9.96	7.98	6.73	
AD8037ANZ-ND	Voltage-Feedback Amp Output Clamping*	8-Dip	9.58	7.67	6.47	
AD8037ARZ-ND	Voltage-Feedback Amp Output Clamping*	8-SOIC	9.58	7.67	6.47	
AD8038AKSZ-REEL7CT-ND	Voltage-Feedback Amp 350MHz Low Power*	SC70-5	2.41	1.93	1.45	
AD8038AKSZ-REEL7TR-ND	Voltage-Feedback Amp 350MHz Low Power*	SC70-5		3705.82/3,000		
AD8038ARZ-ND	Voltage-Feedback Amp 350MHz Low Power*	8-SOIC	2.47	1.98	1.49	
AD8039ARZ-ND	Voltage-Feedback Amp 350MHz Low Power*	8-SOIC	3.13	2.51	1.95	
AD8039ARTZREEL7CT-ND	Voltage-Feedback Amp 350MHz Low Power*	SOT-23-8	3.05	2.45	1.91	
AD8039ARTZREEL7TR-ND	Voltage-Feedback Amp 350MHz Low Power*	SOT-23-8		5132.54/3,000		
AD8040ARZ-ND	Low Power, High Speed, Rail-to-Rail In/Out Amp*	14-SOIC	4.16	3.34	2.60	
AD8041ANZ-ND	Voltage-Feedback Amp with Disable*	8-Dip	4.75	3.80	2.96	
AD8041ARZ-ND	Voltage-Feedback Amp with Disable*	8-SOIC	4.75	3.80	2.96	
AD8042ARZ-ND	Voltage-Feedback Amp Dual Rail-to-Rail*	8-SOIC	5.88	4.71	3.67	
AD8044ANZ-ND	Voltage-Feedback Amp Rail-to-Rail Quad*	14-Dip	9.20	7.37	6.22	
AD8044ARZ-ND	Voltage-Feedback Amp Rail-to-Rail Quad*	14-SOIC	9.20	7.37	6.22	
AD8045ACPZ-REEL7CT-ND	Voltage-Feedback Amp Ultralow Distortion*	8-LFCSOP	3.56	2.85	2.22	
AD8045ACPZ-REEL7TR-ND	Voltage-Feedback Amp Ultralow Distortion*	8-LFCSOP		3026.05/1,500		
AD8045ARDZ-ND	Voltage-Feedback Amp Ultralow Distortion*	8-SOIC	3.64	2.91	2.27	
AD8047ANZ-ND	Voltage-Feedback Amp 250MHz*	8-Dip	6.14	4.91	3.82	
AD8047ARZ-ND	Voltage-Feedback Amp 250MHz*	8-SOIC	6.14	4.91	3.82	
AD8048ARZ-ND	Voltage-Feedback Amp General Purpose*	8-SOIC	5.58	4.47	3.48	
AD8051ARZ-ND	Voltage-Feedback Amp Single High Speed*	8-SOIC	2.45	1.96	1.47	
AD8051ARTZ-REEL7CT-ND	Voltage-Feedback Amp Single High Speed*	SOT-23-5		3748.91/3,000		
AD8052ARZ-ND	Voltage-Feedback Amp Dual High Speed*	8-SOIC	4.16	3.34	2.60	
AD8052ARMZ-ND	Voltage-Feedback Amp Dual High Speed*	8-MSOP	4.16	3.34	2.60	
AD8054AR-REEL7CT-ND	Voltage-Feedback Amp Quad High Speed*	14-SOIC	7.65	6.13	4.77	
AD8054ARZ-ND	Voltage-Feedback Amp Quad High Speed*	14-SOIC		6.62	5.30	4.17
AD8054ARUZ-ND	Voltage-Feedback Amp Quad High Speed*	14-TSSOP	6.96	5.57	4.70	
AD8055ANZ-ND	Voltage-Feedback Amp Single*	8-Dip	2.47	1.98	1.49	
AD8055ARZ-ND	Voltage-Feedback Amp Single*	8-SOIC	2.47	1.98	1.49	
AD8055ARTZ-REEL7CT-ND	Voltage-Feedback Amp Single*	SOT-23-5	2.11	1.69	1.27	
AD8055ARTZ-REEL7TR-ND	Voltage-Feedback Amp Single*	SOT-23-5		3231.82/3,000		
AD8056AR-REEL7TR-ND	Voltage-Feedback Amp Dual*	8-SOIC	2089.74/750			
AD8056ARMZ-ND	Voltage-Feedback Amp Dual*	8-MSOP	4.16	3.34	2.60	
AD8056ARZ-ND	Voltage-Feedback Amp Dual*	8-SOIC	4.16	3.34	2.60	
AD8057ARTZ-REEL7CT-ND	Voltage-Feedback Amp Single*	SOT-23-5	2.11	1.69	1.27	
AD8057ARTZ-REEL7TR-ND	Voltage-Feedback Amp Single*	SOT-23-5		3231.82/3,000		
AD8057ARZ-ND	Voltage-Feedback Amp Single*	8-SOIC	2.47	1.98	1.49	
AD8058ARMZ-ND	Voltage-Feedback Amp Dual*	8-MSOP	4.16	3.34	2.60	
AD8058ARZ-ND	Voltage-Feedback Amp Dual*	8-SOIC	4.16	3.34	2.60	
AD8061ARTZ-REEL7CT-ND	Voltage-Feedback Amp Rail-to-Rail*	SOT-23-5	2.11	1.69	1.27	
AD8061ARTZ-REEL7TR-ND	Voltage-Feedback Amp Rail-to-Rail*	SOT-23-5		3231.82/3,000		
AD8062ARZ-ND	Voltage-Feedback Amp Rail-to-Rail*	8-SOIC	4.16	3.34	2.60	
AD8062ARMZ-R7CT-ND	Voltage-Feedback Amp Rail-to-Rail*	8-MSOP	4.16	3.34	2.60	
AD8062ARMZ-R7TR-ND	Voltage-Feedback Amp Rail-to-Rail*	8-MSOP		2360.74/1,000		
AD8063ARZ-ND	Voltage-Feedback Amp Rail-to-Rail*	8-SOIC	2.45	1.96	1.47	
AD8065ARZ-ND	Voltage-Feedback Amp Single High Speed*	8-SOIC	4.14	3.32	2.58	
AD8065ARTZ-REEL7CT-ND	Voltage-Feedback Amp Single High Speed*	SOT-23-5	4.06	3.26	2.53	
AD8065ARTZ-REEL7TR-ND	Voltage-Feedback Amp Single High Speed*	SOT-23-5		6829.24/3,000		
AD8066ARZ-ND	Voltage-Feedback Amp Dual High Speed*	8-SOIC	5.98	4.79	3.73	
AD8066ARMZ-ND	Voltage-Feedback Amp Dual High Speed*	8-MSOP	5.98	4.79	3.73	
AD8067ARTZ-REEL7CT-ND	Precision FastFET™ Op Amp*	SOT-23-5	5.86	4.69	3.65	
AD8067ARTZ-REEL7TR-ND	Precision FastFET™ Op Amp*	SOT-23-5		9840.89/3,000		
AD8091ARTZ-R7CT-ND	Voltage-Feedback Amp Single Rail-to-Rail*	SOT-23-5	1.96	1.58	1.18	
AD8091ARTZ-R7TR-ND	Voltage-Feedback Amp Single Rail-to-Rail*	SOT-23-5		3016.37/3,000		
AD8091ARZ-ND	Voltage-Feedback Amp Single Rail-to-Rail*	8-SOIC	2.00	1.60	1.20	
AD8092ARMZ-ND	Voltage-Feedback Amp Dual Rail-to-Rail*	8-MSOP	2.58	2.07	1.55	
AD8092ARZ-ND	Voltage-Feedback Amp Dual Rail-to-Rail*	8-SOIC	2.58	2.07	1.55	
AD8099ACPZ-REEL7CT-ND	Voltage-Feedback High Speed Op Amp*	8-LFCSOP	5.05	4.04	3.15	
AD8099ACPZ-REEL7TR-ND	Voltage-Feedback High Speed Op Amp*	8-LFCSOP		4292.26/1,500		
AD8099ARDZ-ND	Voltage-Feedback High Speed Op Amp*	8-SOIC	5.17	4.15	3.23	
AD8132ARZ-ND	Differential Amp 350MHz High Speed*	8-SOIC	4.32	3.46	2.69	
AD8132ARMZ-ND	Differential Amp 350MHz High Speed*	8-MSOP	4.32	3.46	2.69	
AD8132WARMZ-R7CT-ND	Differential Amp 350MHz High Speed* <b>NEW!</b>	8-MSOP	4.62	3.72	2.88	
AD8132WARMZ-R7TR-ND	Differential Amp 350MHz High Speed* <b>NEW!</b>	8-MSOP		2518.28/1,000		
AD8137VCPZ-REEL7CT-ND	Differential 12-Bit ADC Driver*	8-LFCSOP	2.78	2.23	1.73	
AD8137VCPZ-REEL7TR-ND	Differential 12-Bit ADC Driver*	8-LFCSOP		2600.74/1,500		
AD8137VPZ-ND	Differential 12-Bit ADC Driver*	8-SOIC	2.85	2.29	1.78	
AD8138ARZ-ND	Differential ADC Driver Low Distortion*	8-SOIC	8.42	6.74	5.69	
AD8138ARMZ-ND	Differential ADC Driver Low Distortion*	8-MSOP	8.42	6.74	5.69	
AD8139ACPZ-REEL7CT-ND	Differential Low Noise Rail-to-Rail ADC Driver*	8-LFCSOP	8.42	6.74	5.69	
AD8139ACPZ-REEL7TR-ND	Differential Low Noise Rail-to-Rail ADC Driver*	8-LFCSOP		7890.19/1,500		
AD8139ARDZ-ND	Differential Low Noise Rail-to-Rail ADC Driver*	8-SOIC	8.42	6.74	5.69	
AD8397ARDZ-ND	Voltage-Feedback Amp Dual Rail-to-Rail*	8-SOIC	5.98	4.79	3.73	
AD8644ARZ-ND	Op Amp 18V Quad 5.5MHz*	14-SOIC	6.16	4.93	3.84	
AD8646ARMZ-REELCT-ND	24MHz Rail-to-Rail Dual Amp*	8-MSOP	1.80	1.44	1.08	
AD8646ARZ-ND	24MHz Rail-to-Rail Dual Amp*	8-SOIC	1.80	1.44	1.08	
AD9631ARZ-ND	Voltage-Feedback Op Amp Wide Bandwidth*	8-SOIC	10.95	8.77	7.40	
ADA4850-1YCPZ-R2CT-ND	Op Amp High Speed Rail-to-Rail Out*	8-LFCSOP	1.96	1.58	1.18	
ADA4850-2YCPZ-R2CT-ND	Op Amp High Speed Rail-to-Rail Out*	8-LFCSOP		274.93/250		
ADA4850-2YCPZ-R2TR-ND	Op Amp High Speed Rail-to-Rail Out*	8-LFCSOP	2.45	1.96	1.47	
OP42FZ-ND	Op Amp Precision High Speed Fast Set*	8-CDip	8.17	6.54	5.42	
OP42GZ-ND	Op Amp Precision High Speed Fast Set*	8-Dip	5.51	4.41	3.43	
OP42GSZ-ND	Op Amp Precision High Speed Fast Set*	8-SOIC	5.51	4.41	3.43	
OP162GSZ-ND	Op Amp 15MHz Rail-to-Rail*	8-SOIC	4.14	3.32	2.58	
OP249GPZ-ND	Op Amp Dual JFET Precision High Speed*	8-Dip	4.52	3.62	2.82	
OP249GSZ-ND	Op Amp Dual JFET Precision High Speed*	8-SOIC	4.52	3.62	2.82	
OP462GSZ-ND	Op Amp Quad Rail-to-Rail High Speed*	14-SOIC	8.91	7.13	6.02	
OP467GPZ-ND	Op Amp Quad Precision High Speed*	14-Dip	13.47	12.12	10.75	
OP467GSZ-ND	Op Amp Quad Precision High Speed*	16-SOIC	14.51	13.07	11.59	
OP482GPZ-ND	Op Amp Quad JFET High Speed Low Power*	14-Dip	5.43	4.35	3.38	
OP482GSZ-ND	Op Amp Quad JFET High Speed Low Power*	14-SOIC	4.87	3.90	3.04	
<b>Instrumentation</b>						
AD521JDZ-ND	Instrumentation Amp Precision*	14-CDip	38.23	35.68	33.13	

\* RoHS Compliant

★ CALL FOR LOWER PRICING ON LARGER QUANTITIES! ★

(Continued)

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380

(CA2011) 837

