

TEXAS INSTRUMENTS		DigiKey® (Cont.)		DIGITAL LOGIC		RoHS Compliant Parts Available	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
SN74HC02PWR	296-8206-1-ND	Quad 2-Input NOR Gate	14-TSSOP	.63	.42	.34	
SN74HC02PWR	296-8206-2-ND	Quad 2-Input NOR Gate	14-TSSOP	285.03/2,000			
SN74HC02DRQ1	296-24747-1-ND	Quad 2-Input NOR Gate NEW!	14-SOIC	.73	.48	.39	
SN74HC02DRQ1	296-24747-2-ND	Quad 2-Input NOR Gate NEW!	14-SOIC	412.39/2,500			
SN74HC02PWREP	296-19505-1-ND	Quad 2-Input NOR Gate	14-TSSOP	1.03	.81	.71	
SN74HC02PWREP	296-19505-2-ND	Quad 2-Input NOR Gate	14-TSSOP	683.40/2,000			
SN74HC03D	296-9817-5-ND	Quad 2-In. NAND Gate with OD Output	14-SOIC	.50	.38	.32	
SN74HC03DR	296-14826-1-ND	Quad 2-In. NAND Gate with OD Output	14-SOIC	.64	.43	.35	
SN74HC03DR	296-14826-2-ND	Quad 2-In. NAND Gate with OD Output	14-SOIC	364.70/2,500			
SN74HC03N	296-8207-5-ND	Quad 2-In. NAND Gate with OD Output	14-Dip	.64	.42	.35	
SN74HC04D	296-1189-5-ND	Hex Inverter	14-SOIC	.49	.37	.31	
SN74HC04DBR	296-19247-1-ND	Hex Inverter	14-SSOP	.70	.46	.38	
SN74HC04DBR	296-19247-2-ND	Hex Inverter	14-SSOP	314.20/2,000			
SN74HC04DR	296-1189-1-ND	Hex Inverter	14-SOIC	.63	.42	.34	
SN74HC04DR	296-1189-2-ND	Hex Inverter	14-SOIC	356.29/2,500			
SN74HC04PWRG4Q1	296-24325-1-ND	Hex Inverter NEW!	14-TSSOP	.70	.46	.38	
SN74HC04PWRG4Q1	296-24325-2-ND	Hex Inverter NEW!	14-TSSOP	314.20/2,000			
SN74HC04N	296-1566-5-ND	Hex Inverter	14-Dip	.62	.42	.34	
SN74HC04NSR	296-12883-1-ND	Hex Inverter	14-SOP	.70	.46	.38	
SN74HC04NSR	296-12883-2-ND	Hex Inverter	14-SOP	314.20/2,000			
SN74HC04PWR	296-8208-1-ND	Hex Inverter	14-TSSOP	.63	.42	.34	
SN74HC04PWR	296-8208-2-ND	Hex Inverter	14-TSSOP	285.03/2,000			
SN74HC05D	296-1190-5-ND	Hex Inverter with OD	14-SOIC	.50	.38	.32	
SN74HC05DR	296-1190-1-ND	Hex Inverter with OD	14-SOIC	.64	.43	.35	
SN74HC05DR	296-1190-2-ND	Hex Inverter with OD	14-SOIC	364.70/2,500			
SN74HC05N	296-1568-5-ND	Hex Inverter with OD	14-Dip	.64	.42	.35	
SN74HC08D	296-1191-1-ND	Quad 2-Input Positive-AND Gate	14-SOIC	.49	.37	.31	
SN74HC08DR	296-1191-2-ND	Quad 2-Input Positive-AND Gate	14-SOIC	.63	.42	.34	
SN74HC08N	296-1570-5-ND	Quad 2-Input Positive-AND Gate	14-Dip	.62	.42	.34	
SN74HC08NSR	296-12884-1-ND	Quad 2-Input Positive-AND Gate	14-SOP	.70	.46	.38	
SN74HC08NSR	296-12884-2-ND	Quad 2-Input Positive-AND Gate	14-SOP	314.20/2,000			
SN74HC08PWR	296-26459-5-ND	Quad 2-Input Pos.-AND Gate NEW!	14-TSSOP	.49	.37	.31	
SN74HC08PWR	296-8210-1-ND	Quad 2-Input Positive-AND Gate	14-TSSOP	.63	.42	.34	
SN74HC08PWR	296-8210-2-ND	Quad 2-Input Positive-AND Gate	14-TSSOP	285.03/2,000			
SN74HC08DRG4Q1	296-24748-1-ND	Quad 2-Input Pos.-AND Gate NEW!	14-SOIC	.73	.48	.39	
SN74HC08DRG4Q1	296-24748-2-ND	Quad 2-Input Pos.-AND Gate NEW!	14-SOIC	412.39/2,500			
SN74HC08OPWRQ1	296-23612-1-ND	Quad 2-Input Positive-AND Gate	14-TSSOP	.73	.48	.39	
SN74HC08OPWRQ1	296-23612-2-ND	Quad 2-Input Positive-AND Gate	14-TSSOP	329.92/2,000			
SN74HC10D	296-8213-5-ND	Triple 3-Input NAND Gate	14-SOIC	.49	.37	.31	
SN74HC10DR	296-14828-1-ND	Triple 3-Input NAND Gate	14-SOIC	.63	.42	.34	
SN74HC10DR	296-14828-2-ND	Triple 3-Input NAND Gate	14-SOIC	356.29/2,500			
SN74HC10N	296-8214-5-ND	Triple 3-Input NAND Gate	14-Dip	.62	.42	.34	
SN74HC10DREP	296-22295-1-ND	Triple 3-Input NAND Gate	14-SOIC	1.03	.81	.71	
SN74HC10DREP	296-22295-2-ND	Triple 3-Input NAND Gate	14-SOIC	854.24/2,500			
SN74HC10PWREP	296-22296-1-ND	Triple 3-Input NAND Gate	14-TSSOP	1.03	.81	.71	
SN74HC10PWREP	296-22296-2-ND	Triple 3-Input NAND Gate	14-TSSOP	683.40/2,000			
SN74HC10OPWRG4Q1	296-23852-1-ND	Triple 3-Input NAND Gate	14-TSSOP	.73	.48	.39	
SN74HC10OPWRG4Q1	296-23852-2-ND	Triple 3-Input NAND Gate	14-TSSOP	329.92/2,000			
SN74HC11D	296-8216-5-ND	Triple 3-Input Positive AND Gate	14-SOIC	.50	.38	.32	
SN74HC11DR	296-14830-1-ND	Triple 3-Input Positive AND Gate	14-SOIC	.64	.43	.35	
SN74HC11DR	296-14830-2-ND	Triple 3-Input Positive AND Gate	14-SOIC	364.70/2,500			
SN74HC11N	296-8217-5-ND	Triple 3-Input Positive AND Gate	14-Dip	.64	.42	.35	
SN74HC11NSR	296-12885-1-ND	Triple 3-Input Positive AND Gate	14-SOP	.71	.47	.39	
SN74HC11NSR	296-12885-2-ND	Triple 3-Input Positive AND Gate	14-SOP	323.18/2,000			
SN74HC11PWR	296-13611-1-ND	Triple 3-Input Positive AND Gate	14-TSSOP	.64	.43	.35	
SN74HC11PWR	296-13611-2-ND	Triple 3-Input Positive AND Gate	14-TSSOP	291.76/2,000			
SN74HC14D	296-1194-5-ND	Hex Schmitt-Trigger Inverter	14-SOIC	.49	.37	.31	
SN74HC14DR	296-1194-1-ND	Hex Schmitt-Trigger Inverter	14-SOIC	.63	.42	.34	
SN74HC14DR	296-1194-2-ND	Hex Schmitt-Trigger Inverter	14-SOIC	356.29/2,500			
SN74HC14N	296-1577-5-ND	Hex Schmitt-Trigger Inverter	14-Dip	.62	.42	.34	
SN74HC14NSR	296-12887-1-ND	Hex Schmitt-Trigger Inverter	14-SOP	.70	.46	.38	
SN74HC14NSR	296-12887-2-ND	Hex Schmitt-Trigger Inverter	14-SOP	314.20/2,000			
SN74HC14PWR	296-8234-1-ND	Hex Schmitt-Trigger Inverter	14-TSSOP	.63	.42	.34	
SN74HC14PWR	296-8234-2-ND	Hex Schmitt-Trigger Inverter	14-TSSOP	285.03/2,000			
SN74HC14DRQ1	296-19248-1-ND	Hex Schmitt-Trigger Inverter	14-SOIC	.73	.48	.39	
SN74HC14DRQ1	296-19248-2-ND	Hex Schmitt-Trigger Inverter	14-SOIC	412.39/2,500			
SN74HC14OPWRQ1	296-17530-1-ND	Hex Schmitt-Trigger Inverter	14-TSSOP	.73	.48	.39	
SN74HC14OPWRQ1	296-17530-2-ND	Hex Schmitt-Trigger Inverter	14-TSSOP	329.92/2,000			
SN74HC20DR	296-8263-1-ND	Dual 4-Input NAND Gate	14-SOIC	.64	.43	.35	
SN74HC20DR	296-8263-2-ND	Dual 4-Input NAND Gate	14-SOIC	364.70/2,500			
SN74HC20N	296-12892-5-ND	Dual 4-Input NAND Gate	14-Dip	.64	.42	.35	
SN74HC20NSR	296-12893-1-ND	Dual 4-Input NAND Gate	14-SOP	.71	.47	.39	
SN74HC20NSR	296-12893-2-ND	Dual 4-Input NAND Gate	14-SOP	323.18/2,000			
SN74HC21D	296-8265-5-ND	Dual 4-Input Positive AND Gate	14-SOIC	.50	.38	.32	
SN74HC21DR	296-14842-1-ND	Dual 4-Input Positive AND Gate	14-SOIC	.64	.43	.35	
SN74HC21DR	296-14842-2-ND	Dual 4-Input Positive AND Gate	14-SOIC	364.70/2,500			
SN74HC21N	296-8266-5-ND	Dual 4-Input Positive AND Gate	14-Dip	.64	.42	.35	
SN74HC21PWR	296-26472-5-ND	Dual 4-Input Pos. AND Gate NEW!	14-TSSOP	.50	.38	.32	
SN74HC21PWR	296-15846-1-ND	Dual 4-Input Positive AND Gate	14-TSSOP	.64	.43	.35	
SN74HC21PWR	296-15846-2-ND	Dual 4-Input Positive AND Gate	14-TSSOP	291.76/2,000			
SN74HC21DRQ1	296-24750-1-ND	Dual 4-Input Pos. AND Gate NEW!	14-SOIC	.56	.40	.34	
SN74HC21DRQ1	296-24750-2-ND	Dual 4-Input Pos. AND Gate NEW!	14-SOIC	395.56/2,500			
SN74HC21OPWRG4Q1	296-24429-1-ND	Dual 4-Input Positive AND Gate NEW!	14-TSSOP	.56	.40	.34	
SN74HC21OPWRG4Q1	296-24429-2-ND	Dual 4-Input Positive AND Gate NEW!	14-TSSOP	316.45/2,000			
SN74HC21OPWRQ1	296-18317-1-ND	Dual 4-Input Positive AND Gate	14-TSSOP	.56	.40	.34	
SN74HC21OPWRQ1	296-18317-2-ND	Dual 4-Input Positive AND Gate	14-TSSOP	316.45/2,000			
SN74HC27D	296-8298-5-ND	Triple 3-Input NOR Gate	14-SOIC	.62	.41	.33	
SN74HC27N	296-12896-5-ND	Triple 3-Input NOR Gate	14-Dip	.56	.38	.31	
SN74HC27NSR	296-8299-1-ND	Triple 3-Input NOR Gate	14-SOP	.63	.42	.34	
SN74HC27NSR	296-8299-2-ND	Triple 3-Input NOR Gate	14-SOP	285.03/2,000			
SN74HC32D	296-1199-5-ND	Quad 2-Input Positive OR Gate	14-SOIC	.49	.37	.31	
SN74HC32DR	296-1199-1-ND	Quad 2-Input Positive OR Gate	14-SOIC	.63	.42	.34	
SN74HC32DR	296-1199-2-ND	Quad 2-Input Positive OR Gate	14-SOIC	356.29/2,500			
SN74HC32DBR	296-8301-1-ND	Quad 2-Input Positive OR Gate	14-SSOP	.70	.46	.38	
SN74HC32DBR	296-8301-2-ND	Quad 2-Input Positive OR Gate	14-SSOP	314.20/2,000			
SN74HC32N	296-1589-5-ND	Quad 2-Input Positive OR Gate	14-Dip	.62	.42	.34	
SN74HC32NSR	296-26477-1-ND	Quad 2-Input Pos. OR Gate NEW!	14-SOP	.70	.46	.38	
SN74HC32NSR	296-26477-2-ND	Quad 2-Input Pos. OR Gate NEW!	14-SOP	314.20/2,000			
SN74HC32PWR	296-8302-1-ND	Quad 2-Input Positive OR Gate	14-TSSOP	.63	.42	.34	
SN74HC32PWR	296-8302-2-ND	Quad 2-Input Positive OR Gate	14-TSSOP	285.03/2,000			

TEXAS INSTRUMENTS		DigiKey® (Cont.)		DIGITAL LOGIC		RoHS Compliant Parts Available	
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*			
				1	25	100	
SN74HC42D	296-8331-5-ND	4-to-10 Line Decoder (1 of 10)	16-SOIC	1.13	.91	.80	
SN74HC42DR	296-8331-1-ND	4-to-10 Line Decoder (1 of 10)	16-SOIC	1.19	.92	.81	
SN74HC42DR	296-8331-2-ND	4-to-10 Line Decoder (1 of 10)	16-SOIC	976.28/2,500			
SN74HC42N	296-8332-5-ND	4-to-10 Line Decoder (1 of 10)	16-Dip	1.03	.83	.73	
SN74HC74D	296-1204-5-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-SOIC	4.9	.37	.31	
SN74HC74DR	296-1204-1-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-SOIC	.63	.42	.34	
SN74HC74DR	296-1204-2-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-SOIC	356.29/2,500			
SN74HC74DBR	296-8370-1-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-SSOP	.70	.46	.38	
SN74HC74DBR	296-8370-2-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-SSOP	314.20/2,000			
SN74HC74MPWRP	296-23317-1-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-TSSOP	1.03	.81	.71	
SN74HC74MPWRP	296-23317-2-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-TSSOP	683.40/2,000			
SN74HC74N	296-1602-5-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-Dip	.62	.42	.34	
SN74HC74NSR	296-8371-1-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-SOP	.70	.46	.38	
SN74HC74NSR	296-8371-2-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-SOP	314.20/2,000			
SN74HC74PWR	296-8372-1-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-TSSOP	.63	.42	.34	
SN74HC74PWR	296-8372-2-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-TSSOP	285.03/2,000			
SN74HC74DRQ1	296-23566-1-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-SOIC	.73	.48	.39	
SN74HC74DRQ1	296-23566-2-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres	14-SOIC	774.29/5,000			
SN74HC74DRG4Q1	296-24430-1-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres NEW!	14-SOIC	.73	.48	.39	
SN74HC74DRG4Q1	296-24430-2-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres NEW!	14-SOIC	774.29/5,000			
SN74HC74QPWRG4Q1	296-24550-1-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres NEW!	14-TSSOP	.73	.48	.39	
SN74HC74QPWRG4Q1	296-24550-2-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres NEW!	14-TSSOP	329.92/2,000			
SN74HC74OPWRQ1	296-19255-1-ND	Dual D-Type Positive-Edge-Triggered Flip-Flop with Clear/Pres					