



## WE-HCA Series — High Current Flat Wire SMD Inductors



**Features:** • Flat wire coil for low loss at high frequency • Low stray field • Extremely low profile design • Extremely low core loss allows design optimization for high ripple currents • Current capability up to 65A • Operating temperature: -40°C - 155°C • Recommended solder profile: Reflow • Inductance Tolerance: ±20% **Applications:** • Graphic cards • Laptops • Industrial computers • Motherboards • High current switching regulators • High temperature electronics • Polyphase switching regulators

Dimensions in mm




Fig.	Inductance (µH)	DCR Max. (mΩ)	Rated Current (A)	Digi-Key Part No.	Cut Tape Price Each			Tape and Reel		Würth Part No.
					1	25	100	Qty.	Pricing	
1	0.19	0.72	29	732-1112-1-ND	5.50	4.59	3.90	400	1008.07	744355019
	0.47	1.30	26	732-1114-1-ND	5.50	4.59	3.90	—	—	744355047
	0.90	1.90	24	732-1115-1-ND	5.50	4.59	3.90	—	—	744355090
	1.40	2.80	22	732-1116-1-ND	5.50	4.59	3.90	—	—	7443550140
	2.30	4.50	17.5	732-1117-1-ND	5.50	4.59	3.90	—	—	7443550230
	4.80	12.00	11	732-1119-1-ND	5.50	4.59	3.90	400	1008.07	7443550480
2	6.00	15.00	9.5	732-1120-1-ND	5.50	4.59	3.90	—	—	7443550600
	0.20	0.43	32	732-1121-1-ND	5.72	4.78	4.06	—	—	744355122
	0.47	0.80	30	732-1122-1-ND	5.72	4.78	4.06	400	1050.13	744355147
	1.30	2.00	25	732-1124-1-ND	5.72	4.78	4.06	400	1050.13	7443551130
	2.00	3.00	23	732-1125-1-ND	5.72	4.78	4.06	400	1050.13	7443551200
	3.70	5.30	17	732-1127-1-ND	5.72	4.78	4.06	400	1050.13	7443551370
	4.70	7.70	13	732-1128-1-ND	5.72	4.78	4.06	400	1050.13	7443551470
	6.00	9.00	12	732-1129-1-ND	5.72	4.78	4.06	400	1050.13	7443551600

Fig.	Inductance (µH)	DCR Max. (mΩ)	Rated Current (A)	Digi-Key Part No.	Cut Tape Price Each			Tape and Reel		Würth Part No.
					1	25	100	Qty.	Pricing	
2	7.30	6.40	13	732-1137-1-ND	5.72	4.78	4.06	400	1050.13	7443551730
	9.20	8.40	12	732-1138-1-ND	5.72	4.78	4.06	400	1050.13	7443551920
	11.30	10.00	11	732-1139-1-ND	5.72	4.78	4.06	400	1050.13	7443551111
	13.00	12.50	10	732-1140-1-ND	5.72	4.78	4.06	400	1050.13	7443551131
	15.40	16.00	9	732-1141-1-ND	5.72	4.78	4.06	400	1050.13	7443551151
3	0.15	0.72	25	732-1142-1-ND	4.96	4.14	3.52	—	—	744355215
	0.30	1.30	22	732-1130-1-ND	4.96	4.14	3.52	—	—	744355230
	0.56	1.80	20	732-1131-1-ND	4.96	4.14	3.52	800	1588.82	744355256
	1.00	3.80	16	732-1132-1-ND	4.96	4.14	3.52	800	1588.82	7443552100
	1.50	5.70	14	732-1133-1-ND	4.96	4.14	3.52	800	1588.82	7443552150
	4.30	17.00	8	732-1136-1-ND	4.96	4.14	3.52	800	1588.82	7443552430
4	8.20	11.60	10	732-2184-1-ND	5.50	4.59	3.90	400	1008.07	7443550820
5	22.00	24.70	6	732-2183-1-ND	5.74	4.78	4.07	400	1051.56	7443551221

✓ **NEW!** † For Tape and Reel part number, change 1-ND to 2-ND. ‡ ±30% Tolerance  
 732-1921-ND (744355) WE-HC/HCA Series Kit (See Digi-Key website for contents of kit) ..... **\$161.32**  
 732-1922-ND (744356) WE-HC/HCA Series Kit (See Digi-Key website for contents of kit) ..... **\$188.21**

## WE-HC Series — High Current Flat Wire SMD Inductors



**Features:** • Flat wire coil for low loss at high frequency • Low stray field • Extremely low profile design • Extremely low core loss allows design optimization for high ripple currents • Current capability up to 40A • Operating temperature: -40°C - 155°C • Recommended solder profile: Reflow • Inductance Tolerance: ±20% **Applications:** • Graphic cards • Laptops • Industrial computers • Motherboards • High current switching regulators • High temperature electronics • Polyphase - switching regulators

Dimensions in mm




Fig.	Inductance (µH)	DCR Max. (mΩ)	Rated Current (A)	Digi-Key Part No.	Cut Tape Price Each			Tape and Reel		Würth Part No.
					1	25	100	Qty.	Pricing	
1	0.13	.91	22	732-1143-1-ND	3.90	3.25	2.76	—	—	744310013
	0.24	1.6	18	732-1144-1-ND	3.90	3.25	2.76	1,500	1297.73/M	744310024
	0.52	3.7	14	732-1145-1-ND	3.90	3.25	2.76	1,500	1297.73/M	744310055
	0.95	6.2	11	732-1146-1-ND	3.90	3.25	2.76	1,500	1297.73/M	744310095
	1.15	8.6	8.5	732-1147-1-ND	3.90	3.25	2.76	1,500	1297.73/M	744310115
	2	14.2	6.5	732-1148-1-ND	3.90	3.25	2.76	—	—	744310200
2	0.68	3.1	17	732-1149-1-ND	3.97	3.31	2.82	1,000	1324.02	744311068
	1.5	7.8	11	732-1150-1-ND	3.97	3.31	2.82	1,000	1324.02	744311150
	2.2	11.4	9	732-1151-1-ND	3.97	3.31	2.82	1,000	1324.02	744311220
	3.3	17.2	6.5	732-1152-1-ND	3.97	3.31	2.82	1,000	1324.02	744311330
	4.7	19.5	6	732-1153-1-ND	3.97	3.31	2.82	1,000	1324.02	744311470
3	0.24	1.15	20	732-1154-1-ND	4.19	3.51	2.98	—	—	744314024
	0.47	2.00	18	732-1155-1-ND	4.19	3.51	2.98	1,000	1400.49	744314047
	0.76	2.90	15.5	732-1156-1-ND	4.19	3.51	2.98	—	—	744314076
	1.10	3.80	15	732-1157-1-ND	4.19	3.51	2.98	1,000	1400.49	744314110
	1.50	5.20	13	732-1158-1-ND	4.19	3.51	2.98	1,000	1400.49	744314150

Fig.	Inductance (µH)	DCR Max. (mΩ)	Rated Current (A)	Digi-Key Part No.	Cut Tape Price Each			Tape and Reel		Würth Part No.
					1	25	100	Qty.	Pricing	
3	2.00	7.00	11.5	732-1159-1-ND	4.19	3.51	2.98	1,000	1400.49	744314200
	3.30	11.6	9	732-1160-1-ND	4.19	3.51	2.98	1,000	1400.49	744314330
	4.90	17.00	6.5	732-1161-1-ND	4.19	3.51	2.98	1,000	1400.49	744314490
	6.5	25.00	6	732-1162-1-ND	4.19	3.51	2.98	1,000	1400.49	744314650
	0.40	0.77	24	732-1164-1-ND	5.27	4.40	3.74	700	1536.60	744325040
4	0.72	1.65	22	732-1165-1-ND	5.27	4.40	3.74	700	1536.60	744325072
	1.20	2.00	20	732-1166-1-ND	5.27	4.40	3.74	700	1536.60	744325120
	1.80	4.00	16	732-1167-1-ND	5.27	4.40	3.74	—	—	744325180
	2.40	5.00	14	732-1168-1-ND	5.27	4.40	3.74	700	1536.60	744325240
	3.30	6.60	12	732-1169-1-ND	5.27	4.40	3.74	—	—	744325330
	4.20	8.00	11	732-1170-1-ND	5.27	4.40	3.74	700	1536.60	744325420
5	5.50	14.00	10	732-1171-1-ND	5.27	4.40	3.74	700	1536.60	744325550
	7.60	30.20	4.2	732-2181-1-ND	4.66	3.89	3.31	1,000	1553.45	744314760
	8.50	32.50	4.0	732-2182-1-ND	4.66	3.89	3.31	1,000	1553.45	744314850
5	10.00	33.00	3.5	732-2180-1-ND	4.30	3.59	3.05	1,000	1433.95	744314101

✓ **NEW!** † For Tape and Reel part number, change 1-ND to 2-ND.

### Kit

732-1923-ND (744721) Kit Chokes for EXAR (See Digi-Key website for contents of kit) - **RoHS Compliant** ..... **\$152.36**

## NEW! Trilogy of Magnetics — 4th Edition The Design Guide

The design guide for EMI Filter Design and SMPS and RF Design Circuit is completely revised, newly structured, and covers a multitude of new components and applications. The design guide is divided into the following chapters: Basic Principles, Components, and Applications. A keyword index, as well as a formula, complete the book. The objective of the design guide, "Trilogy of Magnetics", is to practically familiarize customers and users with the characteristics and applications of inductive components. The design guide was published 8 years ago for the first time and is now a standard work for lots of development departments and universities. In the 4th edition, the explanation of old techniques and components has been set aside to have more room for new components and applications. Notably, a multitude of external authors from our customer base and our well known manufactures passed on their experiences and solutions in the Basic Principles and Applications section.

732-2511-ND (744006) ..... **\$80.80**

Digi-Reel® Most SMT cutdown parts are available on a Digi-Reel®. For Digi-Reel part number, change 1-ND to 6-ND or CT-ND to DKR-ND. See Digi-Key® Services on page 2 for additional information.

**Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.**  
 1588 (CA2011) 1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380