




## 1500 Watt TVS Diode DO-214AB (SMC) Package — SMCJ Series



**FEATURES:**

- Glass passivated junction
- J lead construction

**SPECIFICATIONS:**

- Voltage Tolerance: 5%
- Operating Temperature: -65°C ~ 150°C
- High Temperature Soldering: 260°C for 40 seconds at terminals
- Plastic Package: UL94V-0
- Electrical Specification: Tested at 25°C

(Value) Nominal Breakdown Voltage	Reverse Stand Off Voltage VR (V)	Breakdown Voltage VBR (V) @ IT		Maximum Reverse Leakage IR @ VR (µA)
		Min.	Max.	
5.0	5.0	6.40	7.00	800
6.0	6.0	6.67	7.37	800
6.5	6.5	7.22	7.98	500

(Value) Nominal Breakdown Voltage	Reverse Stand Off Voltage VR (V)	Breakdown Voltage VBR (V) @ IT		Maximum Reverse Leakage IR @ VR (µA)
		Min.	Max.	
7.0	7.0	7.78	8.60	200
7.5	7.5	8.33	9.21	100
8.0	8.0	8.89	9.83	50
8.5	8.5	9.44	10.40	20
9.0	9.0	10.00	11.10	10
10	10	11.10	12.30	5
11	11	12.20	13.50	1
12	12	13.30	14.70	1
13	13	14.40	15.90	1
14	14	15.60	17.20	1
15	15	16.70	18.50	1
16	16	17.80	19.70	1
17	17	18.90	20.90	1
18	18	20.00	22.10	1
20	20	22.20	24.50	1
22	22	24.40	26.90	1
24	24	26.70	29.50	1
26	26	29.00	31.90	1
28	28	31.10	34.40	1
30	30	33.30	36.80	1
33	33	36.70	40.60	1
36	36	40.00	44.20	1
40	40	44.40	49.10	1
45	45	50.00	55.30	1
48	48	53.30	58.90	1


(Value) Nominal Breakdown Voltage	Reverse Stand Off Voltage VR (V)	Breakdown Voltage VBR (V) @ IT		Maximum Reverse Leakage IR @ VR (µA)
		Min.	Max.	
51	51.0	56.70	62.70	1
54	54.0	60.00	66.30	1
58	58.0	64.40	71.20	1
60	60.0	68.70	75.70	1
64	64.0	71.10	78.60	1
70	70.0	77.80	86.00	1
75	75.0	83.30	92.10	1
78	78.0	86.70	95.80	1
85	85.0	94.40	104.00	1
90	90.0	100.00	111.00	1
100	100.0	111.00	123.00	1
110	110.0	122.00	135.00	1
120	120.0	133.00	147.00	1
130	130.0	144.00	159.00	1
150	150.0	167.00	185.00	1
160	160.0	178.00	197.00	1
170	170.0	189.00	209.00	1
180	180.0	201.00	222.00	1
200	200.0	224.00	247.00	1
220	220.0	246.00	272.00	1
250	250.0	279.00	309.00	1
300	300.0	335.00	371.00	1
350	350.0	391.00	432.00	1
400	400.0	447.00	494.00	1
440	440.0	492.00	543.00	1

Description	Voltage Range (Value) See Chart	Digi-Key Part No.†	Cut Tape Pricing			Digi-Key Part No.†	Tape and Reel Pricing 3,000
			1	10	100		
Uni-directional	5.0 – 200	SMCJ(Value)ALFCT-ND	.76	7.02	59.00	SMCJ(Value)ALFTR-ND	278.73/M
	220 – 440	SMCJ(Value)ALFCT-ND	1.07	9.85	82.81	SMCJ(Value)ALFTR-ND	391.94/M
Bi-directional	5.0 – 8.0, 9.0 – 10, 12 – 200	SMCJ(Value)CALFCT-ND	.83	7.67	64.52	SMCJ(Value)CALFTR-ND	304.81/M
	220 – 440	SMCJ(Value)CALFCT-ND	1.17	10.76	90.40	SMCJ(Value)CALFTR-ND	427.06/M

† For complete part number, substitute (Value) from the Value Chart. **Note:** Bidirectional type having Vr of 10V and less, the Ir limit is double.

‡ SMCJ-A-KIT-ND **NEW!** 36 values, 5 each of parts indicated (180 pieces) .....\$51.11 ▲ SMCJ-CA-KIT-ND **NEW!** 36 values, 5 each of parts indicated (180 pieces) .....\$53.68

## 1500 Watt TVS Diode DO-214AB (SMC) Package — 1.5SMC Series



**FEATURES:**

- Glass passivated chip junction
- J lead construction
- High temperature soldering: 260°C/40 seconds at terminals
- Matte tin lead-free plated

**SPECIFICATIONS:**


- Operating Junction and Storage Temperature Range: -65°C ~ 150°C
- Voltage tolerance: 5%
- Electrical specification tested at 25°C

(Value) Nominal Breakdown Voltage	Marking Code		Reverse Stand Off Voltage VR (V)	Breakdown Voltage VBR (V) @ IT		Maximum Reverse Leakage IR @ VR (µA)
	Uni	Bi		Min.	Max.	
6.8	6V8A	6V8C	5.80	6.45	7.14	1000
12	12A	12C	10.20	11.40	12.60	5
24	24A	24C	20.50	22.80	25.20	1
27	27A	27C	23.10	25.70	28.40	1
33	33A	33C	28.20	31.40	34.70	1
36	36A	36C	30.80	34.20	37.80	1
39	39A	39C	33.30	37.10	41.00	1

Description	Voltage Range (Value) See Chart	Digi-Key Part No.†	Cut Tape Pricing			Digi-Key Part No.†	Tape and Reel Pricing 3,000
			1	10	100		
Uni-directional	6.8 – 39	1.5SMC(Value)ACT-ND	.76	7.02	59.00	1.5SMC(Value)ATR-ND	278.73/M
Bi-directional	6.8 – 39	1.5SMC(Value)CACT-ND	.83	7.67	64.52	1.5SMC(Value)CATR-ND	304.81/M

† For complete part number, substitute (Value) from the Value Chart. **Note:** Bidirectional type having Vr of 10V and less, the Ir limit is double.

## 3000 Watt TVS Diode DO-214AB (SMC) Package — SMDJ Series



**FEATURES:**

- Glass passivated chip junction
- J lead construction
- High temperature soldering: 260°C/40 seconds at terminals
- Matte tin lead-free plated

**SPECIFICATIONS:**

- Operating Junction and Storage Temperature Range: -65°C ~ 150°C
- Voltage tolerance: 5%

(Value) Nominal Breakdown Voltage	Marking Code		Reverse Stand Off Voltage VR (V)	Breakdown Voltage VBR (V) @ IT		Maximum Reverse Leakage IR @ VR (µA)	(Value) Nominal Breakdown Voltage	Marking Code		Reverse Stand Off Voltage VR (V)	Breakdown Voltage VBR (V) @ IT		Maximum Reverse Leakage IR @ VR (µA)
	Uni	Bi		Min.	Max.			Uni	Bi		Min.	Max.	
10	PDX	DDX	10.0	11.10	12.30	5	45	PFV	DFV	45.0	50.00	55.30	2
12	PEE	DEE	12.0	13.30	14.70	2	48	PFX	DFX	48.0	53.30	58.90	2
15	PEM	DEM	15.0	16.70	18.50	2	51	PFZ	DFZ	51.0	56.70	62.70	2
17	PER	DER	17.0	18.90	20.90	2	54	RGE	DGE	54.0	60.00	66.30	2
18	PET	DET	18.0	20.00	22.10	2	58	PGG	DGG	58.0	64.40	71.20	2
20	PEV	DEV	20.0	22.20	24.50	2	60	PGK	DGK	60.0	66.70	73.70	2
24	PEZ	DEZ	24.0	26.70	29.50	2	64	PGM	DGM	64.0	71.10	78.60	2
28	PEF	DEF	28.0	31.10	34.40	2	70	PGP	DGP	70.0	77.80	86.00	2
30	PFK	DFK	30.0	33.30	36.80	2	75	PGR	DGR	75.0	83.30	92.10	2
33	PFM	DFM	33.0	36.70	40.60	2	78	PGT	DGT	78.0	86.70	95.80	2
36	PFV	DFV	36.0	40.00	44.20	2	85	PGV	DGV	85.0	94.40	104.00	2
40	PFR	DFR	40.0	44.40	49.10	2	90	PGX	DGX	90.0	100.00	111.00	2
43	PFT	DFT	43.0	47.80	52.80	2							

Description	Voltage Range (Value) See Chart	Digi-Key Part No.†	Cut Tape Pricing			Digi-Key Part No.†	Tape and Reel Pricing 3,000
			1	10	100		
Uni-directional	10 – 40	SMDJ(Value)ACT-ND	1.25	11.46	96.26	SMDJ(Value)ATR-ND	454.77/M
	43 – 90	SMDJ(Value)ACT-ND <b>NEW!</b>	1.45	13.38	112.48	SMDJ(Value)ATR-ND <b>NEW!</b>	531.37/M
Bi-directional	10 – 17	SMDJ(Value)CACT-ND	1.34	12.35	103.85	SMDJ(Value)CATR-ND	490.62/M
	18 – 43	SMDJ(Value)CACT-ND	1.59	14.66	123.18	SMDJ(Value)CATR-ND	581.90/M
	45 – 90	SMDJ(Value)CACT-ND <b>NEW!</b>	2.52	23.19	194.94	SMDJ(Value)CATR-ND <b>NEW!</b>	920.94/M

† For complete part number, substitute (Value) from the Value Chart. **Note:** Bidirectional type having Vr of 10V and less, the Ir limit is double.

‡ SMDJ-A-KIT-ND **NEW!** 18 values, 5 each of parts indicated (90 pieces) .....\$62.00 ▲ SMDJ-CA-KIT-ND **NEW!** 18 values, 5 each of parts indicated (90 pieces) .....\$82.66

Digi-Reel® Most SMT cutdown parts are available on a Digi-Reel®. For Digi-Reel part number, change 1-ND to 6-ND or CT-ND to DKR-ND. See Digi-Key® Services on page 2 for additional information.

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

2162 (CA2011)

1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380