



Surface Mount Ceramic Multilayer Chip Capacitors – 0402, 0603, 0805, 1206, 1812 (Cont.)



Case Size	Type	WV DC	Capacitance	Tolerance	Dim. T Nom. (mm)	Digi-Key Part No.	Cut Tape Pricing			Digi-Key Part No.	Tape and Reel		Yageo Part No.	
							10	100	500		Qty.	Pricing		
0603	NPO	50	.5pF	±0.25pF	0.8	311-1048-1-ND	.64	3.79	10.94	311-1048-2-ND	4,000	10.51/M	CC0603CRNPO9BNR50	
	NPO	50	1.0pF	±0.25pF	0.8	311-1049-1-ND	.50	2.95	8.52	311-1049-2-ND	4,000	8.18/M	CC0603CRNPO9BN1R0	
	NPO	50	1.5pF	±0.25pF	0.8	311-1050-1-ND	.50	2.95	8.52	311-1050-2-ND	4,000	8.18/M	CC0603CRNPO9BN1R5	
	NPO	50	2.0pF	±0.25pF	0.8	311-1051-1-ND	.62	3.62	10.46	311-1051-2-ND	4,000	10.04/M	CC0603CRNPO9BN2R0	
	NPO	50	3.0pF	±0.25pF	0.8	311-1052-1-ND	.62	3.62	10.46	311-1052-2-ND	4,000	10.04/M	CC0603CRNPO9BN3R0	
	NPO	50	4.0pF	±0.25pF	0.8	311-1053-1-ND	.64	3.79	10.94	311-1053-2-ND	4,000	10.51/M	CC0603CRNPO9BN4R0	
	NPO	50	5.0pF	±0.25pF	0.8	311-1054-1-ND	.62	3.62	10.46	311-1054-2-ND	4,000	10.04/M	CC0603CRNPO9BN5R0	
	NPO	50	6.0pF	±0.5pF	0.8	311-1055-1-ND	.56	3.34	9.66	311-1055-2-ND	4,000	9.28/M	CC0603DRNPO9BN6R0	
	NPO	50	7.0pF	±0.5pF	0.8	311-1056-1-ND	.64	3.79	10.94	311-1056-2-ND	4,000	10.51/M	CC0603DRNPO9BN7R0	
	NPO	50	8.0pF	±0.5pF	0.8	311-1057-1-ND	.64	3.79	10.94	311-1057-2-ND	4,000	10.51/M	CC0603DRNPO9BN8R0	
	NPO	50	10pF	±5%	0.8	311-1058-1-ND	.55	3.25	9.38	311-1058-2-ND	4,000	9.01/M	CC0603JRNPO9BN100	
	NPO	50	12pF	±5%	0.8	311-1059-1-ND	.47	2.76	7.96	311-1059-2-ND	4,000	7.64/M	CC0603JRNPO9BN120	
	NPO	50	15pF	±5%	0.8	311-1060-1-ND	.55	3.25	9.38	311-1060-2-ND	4,000	9.01/M	CC0603JRNPO9BN150	
	NPO	50	18pF	±5%	0.8	311-1061-1-ND	.55	3.25	9.38	311-1061-2-ND	4,000	9.01/M	CC0603JRNPO9BN180	
	NPO	50	22pF	±5%	0.8	311-1062-1-ND	.55	3.25	9.38	311-1062-2-ND	4,000	9.01/M	CC0603JRNPO9BN220	
	NPO	50	27pF	±5%	0.8	311-1063-1-ND	.55	3.25	9.38	311-1063-2-ND	4,000	9.01/M	CC0603JRNPO9BN270	
	NPO	50	33pF	±5%	0.8	311-1064-1-ND	.55	3.25	9.38	311-1064-2-ND	4,000	9.01/M	CC0603JRNPO9BN330	
	NPO	50	47pF	±5%	0.8	311-1065-1-ND	.55	3.25	9.38	311-1065-2-ND	4,000	9.01/M	CC0603JRNPO9BN470	
	NPO	50	56pF	±5%	0.8	311-1066-1-ND	.55	3.25	9.38	311-1066-2-ND	4,000	9.01/M	CC0603JRNPO9BN560	
	NPO	50	68pF	±5%	0.8	311-1067-1-ND	.19	1.13	3.29	311-1067-2-ND	4,000	3.15/M	CC0603JRNPO9BN680	
	NPO	50	82pF	±5%	0.8	311-1068-1-ND	.19	1.13	3.29	311-1068-2-ND	4,000	3.15/M	CC0603JRNPO9BN820	
	NPO	50	100pF	±5%	0.8	311-1069-1-ND	.55	3.25	9.38	311-1069-2-ND	4,000	9.01/M	CC0603JRNPO9BN101	
	NPO	50	120pF	±5%	0.8	311-1070-1-ND	.59	3.55	10.22	311-1070-2-ND	4,000	9.82/M	CC0603JRNPO9BN121	
	NPO	50	150pF	±5%	0.8	311-1071-1-ND	.79	4.63	13.36	311-1071-2-ND	4,000	12.83/M	CC0603JRNPO9BN151	
	NPO	50	180pF	±5%	0.8	311-1072-1-ND	.28	1.66	4.78	311-1072-2-ND	4,000	4.59/M	CC0603JRNPO9BN181	
	NPO	50	220pF	±5%	0.8	311-1073-1-ND	.86	5.12	14.77	311-1073-2-ND	4,000	14.18/M	CC0603JRNPO9BN221	
	NPO	50	270pF	±5%	0.8	311-1074-1-ND	.86	5.12	14.77	311-1074-2-ND	4,000	14.18/M	CC0603JRNPO9BN271	
	NPO	50	330pF	±5%	0.8	311-1075-1-ND	.86	5.12	14.77	311-1075-2-ND	4,000	14.18/M	CC0603JRNPO9BN331	
	NPO	50	390pF	±5%	0.8	311-1076-1-ND	.86	5.12	14.77	311-1076-2-ND	4,000	14.18/M	CC0603JRNPO9BN391	
	NPO	25	1000pF	±5%	0.8	311-1342-1-ND NEW!	.36	2.10	6.04	311-1342-2-ND NEW!	4,000	5.80/M	CC0603JRNPO8BN102	
	X7R	50	220pF	±10%	0.8	311-1077-1-ND	.47	2.76	7.96	311-1077-2-ND	4,000	7.64/M	CC0603KRX7R9BB221	
	X7R	50	270pF	±10%	0.8	311-1185-1-ND	.47	2.76	7.96	311-1185-2-ND	4,000	7.64/M	CC0603KRX7R9BB271	
	X7R	50	330pF	±10%	0.8	311-1186-1-ND	.47	2.76	7.96	311-1186-2-ND	4,000	7.64/M	CC0603KRX7R9BB331	
	X7R	50	390pF	±10%	0.8	311-1187-1-ND	.47	2.76	7.96	311-1187-2-ND	4,000	7.64/M	CC0603KRX7R9BB391	
	X7R	50	470pF	±10%	0.8	311-1078-1-ND	.47	2.76	7.96	311-1078-2-ND	4,000	7.64/M	CC0603KRX7R9BB471	
	X7R	50	560pF	±10%	0.8	311-1079-1-ND	.47	2.79	8.06	311-1079-2-ND	4,000	7.74/M	CC0603KRX7R9BB561	
	X7R	50	680pF	±10%	0.8	311-1188-1-ND	.47	2.79	8.06	311-1188-2-ND	4,000	7.74/M	CC0603KRX7R9BB681	
	X7R	50	820pF	±10%	0.8	311-1189-1-ND	.47	2.79	8.06	311-1189-2-ND	4,000	7.74/M	CC0603KRX7R9BB821	
	X7R	50	1000pF	±10%	0.8	311-1080-1-ND	.45	2.66	7.68	311-1080-2-ND	4,000	7.38/M	CC0603KRX7R9BB102	
	X7R	50	1500pF	±10%	0.8	311-1184-1-ND	.47	2.76	7.96	311-1184-2-ND	4,000	7.64/M	CC0603KRX7R9BB152	
	X7R	50	2200pF	±10%	0.8	311-1081-1-ND	.47	2.76	7.96	311-1081-2-ND	4,000	7.64/M	CC0603KRX7R9BB222	
	X7R	50	3300pF	±10%	0.8	311-1082-1-ND	.47	2.76	7.96	311-1082-2-ND	4,000	7.64/M	CC0603KRX7R9BB332	
	X7R	50	4700pF	±10%	0.8	311-1083-1-ND	.47	2.76	7.96	311-1083-2-ND	4,000	7.64/M	CC0603KRX7R9BB472	
	X7R	50	6800pF	±10%	0.8	311-1084-1-ND	.50	2.95	8.52	311-1084-2-ND	4,000	8.18/M	CC0603KRX7R9BB682	
	X7R	50	10000pF	±10%	0.8	311-1085-1-ND	.31	1.87	5.41	311-1085-2-ND	4,000	5.19/M	CC0603KRX7R9BB103	
	X7R	50	22000pF	±10%	0.8	311-1370-1-ND NEW!	.75	4.47	12.88	311-1370-2-ND NEW!	4,000	12.36/M	CC0603KRX7R9BB223	
	X7R	50	.10µF	±10%	0.8	311-1344-1-ND NEW!	.29	1.69	4.88	311-1344-2-ND NEW!	4,000	4.69/M	CC0603KRX7R9BB104	
	X7R	25	10000pF	±10%	0.8	311-1360-1-ND NEW!	.19	1.13	3.29	311-1360-2-ND NEW!	4,000	3.15/M	CC0603KRX7R8BB103	
	X7R	25	22000pF	±10%	0.8	311-1086-1-ND	.75	4.47	12.88	311-1086-2-ND	4,000	12.36/M	CC0603KRX7R8BB223	
	X7R	25	47000pF	±10%	0.8	311-1373-1-ND NEW!	.31	1.84	5.31	311-1373-2-ND NEW!	4,000	5.09/M	CC0603KRX7R8BB473	
	X7R	25	.10µF	±10%	0.8	311-1341-1-ND NEW!	.22	1.32	3.80	311-1341-2-ND NEW!	4,000	3.66/M	CC0603KRX7R8BB104	
	X7R	16	68000pF	±10%	0.8	311-1379-1-ND NEW!	.53	3.12	9.01	311-1379-2-ND NEW!	4,000	8.65/M	CC0603KRX7R7BB683	
	X7R	16	.10µF	±10%	0.8	311-1088-1-ND	.28	1.68	4.86	311-1088-2-ND	4,000	4.67/M	CC0603KRX7R7BB104	
	X7R	10	.22µF	±10%	0.8	311-1346-1-ND NEW!	.36	2.10	6.04	311-1346-2-ND NEW!	4,000	5.80/M	CC0603KRX7R6BB224	
	Y5V	50	.10µF	±20%	0.8	311-1366-1-ND NEW!	.22	1.32	3.80	311-1366-2-ND NEW!	4,000	3.66/M	CC0603MRYSV9BB104	
	Y5V	50	.10µF	-20%/+80%	0.8	311-1343-1-ND NEW!	.17	1.01	2.93	311-1343-2-ND NEW!	4,000	2.81/M	CC0603ZRY5V9BB104	
	Y5V	25	.10µF	±20%	0.8	311-1363-1-ND NEW!	.22	1.32	3.80	311-1363-2-ND NEW!	4,000	3.66/M	CC0603MRYSV8BB104	
	Y5V	25	.10µF	-20%/+80%	0.8	311-1087-1-ND	.54	3.15	9.09	311-1087-2-ND	4,000	8.73/M	CC0603ZRY5V8BB104	
	Y5V	16	.10µF	-20%/+80%	0.8	311-1369-1-ND NEW!	.17	1.01	2.93	311-1369-2-ND NEW!	4,000	2.81/M	CC0603ZRY5V7BB104	
	Y5V	16	.22µF	-20%/+80%	0.8	311-1339-1-ND NEW!	.67	3.95	11.38	311-1339-2-ND NEW!	4,000	10.93/M	CC0603ZRY5V7BB224	
	Y5V	16	1.0µF	-20%/+80%	0.8	311-1372-1-ND NEW!	.31	1.89	5.45	311-1372-2-ND NEW!	4,000	5.24/M	CC0603ZRY5V7BB105	
	Y5V	10	1.0µF	-20%/+80%	0.8	311-1357-1-ND NEW!	.52	3.04	8.78	311-1357-2-ND NEW!	4,000	8.43/M	CC0603ZRY5V6BB105	
	0805	NPO	50	.5pF	±0.25pF	0.6	311-1094-1-ND	.74	4.35	12.56	311-1094-2-ND	4,000	12.06/M	CC0805CRNPO9BNR50
		NPO	50	1.0pF	±0.25pF	0.6	311-1089-1-ND	.64	3.79	10.94	311-1089-2-ND	4,000	10.51/M	CC0805CRNPO9BN1R0
		NPO	50	1.5pF	±0.25pF	0.6	311-1090-1-ND	.64	3.79	10.94	311-1090-2-ND	4,000	10.51/M	CC0805CRNPO9BN1R5
		NPO	50	2.0pF	±0.25pF	0.6	311-1091-1-ND	.70	4.13	11.91	311-1091-2-ND	4,000	11.44/M	CC0805CRNPO9BN2R0
		NPO	50	3.0pF	±0.25pF	0.6	311-1092-1-ND	.70	4.13	11.91	311-1092-2-ND	4,000	11.44/M	CC0805CRNPO9BN3R0
		NPO	50	4.0pF	±0.25pF	0.6	311-1093-1-ND	.70	4.13	11.91	311-1093-2-ND	4,000	11.44/M	CC0805CRNPO9BN4R0
		NPO	50	6.0pF	±0.5pF	0.6	311-1095-1-ND	.70	4.13	11.91	311-1095-2-ND	4,000	11.44/M	CC0805DRNPO9BN6R0
		NPO	50	7.0pF	±0.5pF	0.6	311-1096-1-ND	.70	4.13	11.91	311-1096-2-ND	4,000	11.44/M	CC0805DRNPO9BN7R0
		NPO	50	8.0pF	±0.5pF	0.6	311-1097-1-ND	.70	4.13	11.91	311-1097-2-ND	4,000	11.44/M	CC0805DRNPO9BN8R0
		NPO	50	9.0pF	±0.5pF	0.6	311-1098-1-ND	.70	4.13	11.91	311-1098-2-ND	4,000	11.44/M	CC0805DRNPO9BN9R0
		NPO	50	10pF	±5%	0.6	311-1099-1-ND	.56	3.34	9.66	311-1099-2-ND	4,000	9.28/M	CC0805JRNPO9BN100
		NPO	50	12pF	±5%	0.6	311-1100-1-ND	.64	3.79	10.94	311-1100-2-ND	4,000		