

Pomona Test Equipment (Cont.)

Oscilloscope Probes

Features:

- All Probes meet IEC1010-2-031, 300V, CAT 1

Probes Include:

- Retractable Hook Tip • BNC Adapter • IC Adapter • Insulating Tip • Trimmer Tool • 6" (152.40mm) Ground Lead with Alligator Clip

Probe Ratio	System Bandwidth MHz (-3db)	Cable Length Meters	Digi-Key Part No.	Price Each			Pomona Part No.
				1	10	100	
1:1 10:1	Up - 203 60	1.2	501-1012-ND	48.95	44.24	6266	
1:1 10:1	Up - 153 100	1.2	501-1007-ND	69.43	62.74	4550B	
1:1 10:1	Up - 203 200	1.2	501-1008-ND	77.90	70.40	5806A	
100:1	200	2.0	501-1010-ND	125.18	113.12	5827A	
10:1	250	1.2	501-1011-ND	72.23	65.28	6069A	
10:1	300	1.2	501-1009-ND	132.71	119.92	5812A	

◆ RoHS Compliant

Wire Test Leads

Description	Length (feet)	Color	Digi-Key Part No.	Price Each			Pomona Part No.
				1	10	100	
Model 6733 with Silicone Insulation	50	Black	501-1281-ND	23.00	20.79	19.41	6733-0
Model 6733 with Silicone Insulation	50	Red	501-1282-ND	23.00	20.79	19.41	6733-2

NEW! Jumper Test Lead Sets

Features:


- Each jumper test lead set includes one sheathed 4mm banana plug to sheathed 4mm banana plug test lead, and one sheathed 4mm banana plug to sheathed 4mm banana jack patch cord.
- Flexible jumper test lead sets are perfect for conducting peer-checking system tests with test point check before final connection.
- Plug and housing are molded directly to the cable in an integral one piece design and wire is double crimped for a long lasting connection.
- Multi-leaf banana spring is beryllium copper, nickel-plated for extended insertion cycle life and low contact resistance.
- High strand count silicone insulated wire offers excellent flexibility and high temperature resistance.

Materials:

- Plug: Brass, Nickel plated
- Spring: Beryllium Copper, Nickel plated
- Insulator: Polypropylene
- Wire: 18AWG
- Wire Insulation: Silicone, O.D. 0.146" (3.7mm)

Specifications:

- Operating Temperature: -20°C ~ 55°C
- Operating Voltage: CAT I, 1000Vrms
- Current: 10A Maximum



Length Inch (mm)	Color	Digi-Key Part No.	Price Each			Pomona Part No.
			1	10	100	
6 (152)	Black	501-1305-ND	20.40	18.44	17.21	73087-6-0
6 (152)	Red	501-1306-ND	20.40	18.44	17.21	73087-6-2
12 (305)	Black	501-1299-ND	21.25	19.21	17.93	73087-12-0
12 (305)	Red	501-1300-ND	21.25	19.21	17.93	73087-12-2
24 (610)	Black	501-1301-ND	22.77	20.57	19.20	73087-24-0
24 (610)	Red	501-1302-ND	22.77	20.57	19.20	73087-24-2
36 (914)	Black	501-1303-ND	24.29	21.95	20.49	73087-36-0
36 (914)	Red	501-1304-ND	24.29	21.95	20.49	73087-36-2
72 (1829)	Black	501-1307-ND	28.84	26.06	24.32	73087-72-0
72 (1829)	Red	501-1308-ND	28.84	26.06	24.32	73087-72-2

NEW! Terminal Jacks

Features:


- Adapter provides an easy and quick banana jack connection by replacing the screw in a terminal strip or control panel.
- Allows a standard sheathed or unsheathed banana plug/patch cord to securely connect to a terminal strip.
- Helps to avoid accidental arc-over by eliminating the usage of alligator clips, or test probe "slip offs" during measurement applications.

Materials:

- Banana Jack: Nickel plated Brass
- Insulation: Polypropylene V-2

Specifications:


- Voltage: 600 Vrms Maximum
- Current: 20A
- Operating Temperature: -10°C ~ 80°C



Thread	Torque (In/Lb.)	Color	Digi-Key Part No.	Price Each			Pomona Part No.
				1	10	100	
6-32 Male	7	Black	501-1283-ND	2.93	2.65	2.47	73084-0
	7	Red	501-1284-ND	2.93	2.65	2.47	73084-2
	7	Yellow	501-1285-ND	2.93	2.65	2.47	73084-4
	7	Blue	501-1286-ND	2.93	2.65	2.47	73084-6
8-32 Male	16	Black	501-1295-ND	2.93	2.65	2.47	73088-0
	16	Red	501-1296-ND	2.93	2.65	2.47	73088-2
	16	Yellow	501-1297-ND	2.93	2.65	2.47	73088-4
	16	Blue	501-1298-ND	2.93	2.65	2.47	73088-6
10-32 Male	20	Black	501-1287-ND	2.93	2.65	2.47	73085-0
	20	Red	501-1288-ND	2.93	2.65	2.47	73085-2
	20	Yellow	501-1289-ND	2.93	2.65	2.47	73085-4
	20	Blue	501-1290-ND	2.93	2.65	2.47	73085-6
10-32 Female	20	Black	501-1291-ND	2.93	2.65	2.47	73086-0
	20	Red	501-1292-ND	2.93	2.65	2.47	73086-2
	20	Yellow	501-1293-ND	2.93	2.65	2.47	73086-4
	20	Blue	501-1294-ND	2.93	2.65	2.47	73086-6

Adapter Kits

Universal Adapter Kit (Model 5698)



- Includes:**
- Type "N" Male and Female
 - BNC Male and Female
 - TNC Male and Female
 - SMA Male and Female
 - Coupling Adapter
 - Double Banana Plug
 - Double Binding Post

501-1034-ND.....\$217.13

Maxi Universal Adapter Kit (Model 5748)


- Includes:**
- Type "N" Male and Female
 - BNC Male and Female
 - TNC Male and Female
 - SMA Male and Female
 - Coupling Nut
 - Double Banana Plug
 - UHF Male and Female
 - Mini UHF Male and Female
 - RCA Phono Male and Female
 - Type "F" Male and Female
 - Unidapt Signal Sampler

501-1035-ND.....\$354.71

SMA Adapter Kit (Model 72931)

- Includes:**
- Right Angle SMA Female to SMA Male
 - Inline SMA Male to SMA Male
 - Inline SMA Female to SMA Female
 - SMA Male Terminator Plug
 - SMA Female to BNC Male
 - SMA Male to BNC Female
 - SMA Female to BNC Female
 - SMA Male to TNC Male
 - SMA Female to TNC Male
 - SMA Male to TNC Female
 - SMA Female to TNC Female
 - SMA Male to Type "N" Male
 - SMA Female to Type "N" Male
 - SMA Male to Type "N" Female
 - SMA Female to Type "N" Female


501-1235-ND.....\$291.77



Multi-RF Direct Adapter Kit (Model 72934)

- Includes:**
- BNC Male to Type "N" Female
 - BNC Female to Type "N" Male
 - TNC Male to BNC Female
 - SMA Male to BNC Male
 - SMA Male to BNC Female
 - SMA Female to BNC Male
 - SMA Female to BNC Female
 - SMA Male to Type "N" Female
 - SMA Female to Type "N" Male
 - SMA Male to Type "N" Female
 - SMA Female to TNC Male
 - SMA Male to TNC Female
 - SMA Female to TNC Female
 - SMA Male to Type "N" Male
 - BNC Female to Female to Female TEE
 - BNC Female to Female to Female TEE
 - TNC Female to Female Adapter
 - Type "N" Female to Female
 - Type "N" Male to Male
 - SMA Male to Female Right Angle
 - SMA Male to Male
 - SMA Female to Female
 - SMA Termination, 50Ω Male

501-1238-ND.....\$449.58



(Continued)

Free shipping on orders over \$200 CAD! All prices in Canadian dollars and include duty and brokerage fees.

2550 (CA2011)

1-800-344-4539 • www.digikey.ca • 218-681-6674 • Fax: 218-681-3380