

Digi-Key 零件编号	描述	封装	1	25	100	
COP8CCR9IMT7-ND	8位微控制器, 带 32K 闪存和 10 位模数转换器*	8-Bit Microcontroller with 32K Flash, 10-Bit A/D*	48-TSSOP	16.80	15.68	14.56
COP8CDE9IMT9-ND	8位微控制器, 带 8K 闪存和 10 位模数转换器*	8-Bit Microcontroller with 8K Flash, 10-Bit A/D*	48-TSSOP	5.73	4.54	3.64
COP8CFE9HVA9-ND	8位微控制器, 带 8K 闪存和 10 位模数转换器*	8-Bit Microcontroller with 8K Flash, 10-Bit A/D*	44-PLCC	5.29	4.19	3.36
COP8CFE9IMT9-ND	8位微控制器, 带 8K 闪存和 10 位模数转换器*	8-Bit Microcontroller with 8K Flash, 10-Bit A/D*	48-TSSOP	5.48	4.34	3.48
COP8SDE9IMT9-ND	8位微控制器, 带 8K 闪存*	8-Bit Microcontroller with 8K Flash*	48-TSSOP	5.40	4.27	3.42
COP8SGE7VEJ8-ND	8位 OTP 微控制器, 8K 内存, 2 个比较器 USART*	8-Bit OTP Microcontroller, 8K Memory, 2 Comparators USART*	44-LQFP	12.65	10.85	9.62
COP8SGE7Z8M8-ND	8位 OTP 微控制器, 8K 内存, 2 个比较器 USART*	8-Bit OTP Microcontroller, 8K Memory, 2 Comparators USART*	28-SOIC	10.06	7.96	6.38
COP8SGE7Z8N8-ND	8位 OTP 微控制器, 8K 内存, 2 个比较器 USART*	8-Bit OTP Microcontroller, 8K Memory, 2 Comparators USART*	28-Dip	9.05	7.76	6.88
COP8SGE744V8-ND	8位 OTP 微控制器, 8K 内存, 2 个比较器 USART*	8-Bit OTP Microcontroller, 8K Memory, 2 Comparators USART*	44-PLCC	10.89	9.33	8.28
COP8SGR7Z8M8-ND	8位 OTP 微控制器, 32K 内存, 2 个比较器 USART*	8-Bit OTP Microcontroller, 32K Memory, 2 Comparators USART*	28-SOIC	8.84	6.99	5.60
COP8SGR7Z8N8-ND	8位 OTP 微控制器, 32K 内存, 2 个比较器 USART*	8-Bit OTP Microcontroller, 32K Memory, 2 Comparators USART*	28-Dip	9.05	7.76	6.88
COP8SGR744V8-ND	8位 OTP 微控制器, 32K 内存, 2 个比较器 USART*	8-Bit OTP Microcontroller, 32K Memory, 2 Comparators USART*	44-PLCC	10.08	8.64	7.67
CR16MAS9VJE9-ND	16 位 CAN CompactRISC™ 闪存微控制器*	16-Bit, CAN CompactRISC™ Flash Microcontroller*	80-PQFP	20.25	18.90	17.55
CR16MCS9VJE9-ND	16 位 CAN CompactRISC™ 闪存微控制器*	16-Bit, CAN CompactRISC™ Flash Microcontroller*	80-PQFP	20.25	18.90	17.55
LF156H-ND	单片 JFET 输入运算放大器*	Mono JFET In Op Amp*	TO-5	5.67	4.49	3.60
LF256H-ND	宽带 JFET 运算放大器*	Wideband JFET Op Amp*	TO-5	5.67	4.49	3.60
LF298M-ND	单片式采样和保持电路*	Monolithic Sample and Hold Circuit*	14-SOIC	3.10	2.36	1.80
LF347BN-ND	四路 Bi-FET 运算放大器*	Quad Bi-FET Op Amp*	14-Dip	2.51	1.87	1.38
LF347M-ND	四路 Bi-FET 运算放大器*	Quad Bi-FET Op Amp*	14-SOIC	2.64	1.96	1.45
LF347MXTR-ND	四路 Bi-FET 运算放大器*	Quad Bi-FET Op Amp*	14-SOIC	2656.25/2,500		
LF347NNS-ND	四路 Bi-FET 运算放大器*	Quad Bi-FET Op Amp*	14-Dip	2.26	1.68	1.25
LF353M-ND	宽带双路 JFET 运算放大器*	Wideband Dual JFET Op Amp*	8-SOIC	1.24	.91	.66
LF353MXCT-ND	宽带双路 JFET 运算放大器*	Wideband Dual JFET Op Amp*	8-SOIC	1.24	.91	.66
LF353MXTR-ND	宽带双路 JFET 运算放大器*	Wideband Dual JFET Op Amp*	8-SOIC	1051.88/2,500		
LF353NNS-ND	宽带双路 JFET 输入运算放大器*	Wideband Dual JFET Input Op Amp*	8-Dip	1.35	.99	.72
LF356H-ND	单片式 JFET 输入运算放大器*	Monolithic JFET Input Op Amp*	TO-5	6.53	5.17	4.14
LF356M-ND	单片式 JFET 输入运算放大器*	Monolithic JFET Input Op Amp*	8-SOIC	1.13	.83	.60
LF356N-ND	单片式 JFET 输入运算放大器*	Monolithic JFET Input Op Amp*	8-Dip	1.16	.86	.62
LF398AN-ND	单片式采样和保持电路*	Monolithic Sample and Hold Circuit*	8-Dip	3.03	2.30	1.76
LF398H-ND	单片式采样和保持电路*	Monolithic Sample and Hold Circuit*	TO-5	5.88	4.65	3.73
LF398M-ND	单片式采样和保持电路*	Monolithic Sample and Hold Circuit*	14-SOIC	1.80	1.34	.99
LF398N-ND	单片式采样和保持电路*	Monolithic Sample and Hold Circuit*	8-Dip	1.74	1.29	.96
LF411ACH-ND	低偏移低漂移 JFET 输入运算放大器*	Low Offset Low Drift JFET Input Op Amp*	TO-5	8.82	6.98	5.59
LF411ACN-ND	低偏移低漂移 JFET 输入运算放大器*	Low Offset Low Drift JFET Input Op Amp*	8-Dip	6.05	4.60	3.51
LF411CN-ND	低偏移低漂移 JFET 输入运算放大器*	Low Offset Low Drift JFET Input Op Amp*	8-Dip	1.65	1.21	.88
LF412ACN-ND	低偏移低漂移 JFET 双路运算放大器*	Low Offset Low Drift JFET Dual Op Amp*	8-Dip	4.98	3.79	2.89
LF412CN-ND	低偏移低漂移 JFET 双路运算放大器*	Low Offset Low Drift JFET Dual Op Amp*	8-Dip	1.67	1.25	.92
LF412MH-ND	低偏移低漂移 JFET 双路运算放大器*	Low Offset Low Drift JFET Dual Op Amp*	TO-5	9.07	7.18	5.75
LF442ACN-ND	双路低功率 JFET 运算放大器*	Dual Low Power JFET Op Amp*	8-Dip	5.73	4.36	3.33
LF442AMH-ND	双路低功率 JFET 运算放大器*	Dual Low Power JFET Op Amp*	TO-5	17.40	16.24	15.08
LF442CN-ND	双路低功率 JFET 运算放大器*	Dual Low Power JFET Op Amp*	8-Dip	1.55	1.15	.85
LF444ACN-ND	四路低功率 JFET 运算放大器*	Quad Low Power JFET Op Amp*	14-Dip	3.30	2.51	1.92
LF444CN-ND	四路低功率 JFET 运算放大器*	Quad Low Power JFET Op Amp*	14-SOIC	1.98	1.48	1.09
LF444CN-ND	四路低功率 JFET 运算放大器*	Quad Low Power JFET Op Amp*	14-Dip	2.02	1.50	1.11
LM100CH-ND	运算放大器和基准电压*	Op Amp and Voltage Reference*	TO-5	6.72	5.32	4.26
LM100CLN-ND	运算放大器和基准电压*	Op Amp and Voltage Reference*	8-Dip	3.18	2.42	1.85
LM100CN-ND	运算放大器和基准电压*	Op Amp and Voltage Reference*	8-Dip	2.98	2.27	1.73
LM100CWM-ND	运算放大器和基准电压*	Op Amp and Voltage Reference*	14-SOIC	2.80	2.13	1.63
LM120CLN-ND	80W 功率运算放大器 4 个引脚*	80W Power Op Amp 4-Pin*	TO-3	55.20	51.52	47.84
LM12H458CIV-ND	12 位正标志 DAS, 带自校准功能*	12-Bit + Sign DAS with Self-Calibration*	44-PQFP	20.55	19.18	17.81
LM12H458CIVF-ND	12 位正标志 DAS, 带自校准功能*	12-Bit + Sign DAS with Self-Calibration*	44-PQFP	20.55	19.18	17.81
LM12L458CIV-ND	12 位正标志 DAS, 带自校准功能*	12-Bit + Sign DAS with Self-Calibration*	44-PQFP	20.55	19.18	17.81
LM190CZ-ND	2.4V 10µA 温度传感器, -55° 至 130°C*	2.4V, 10µA Temperature Sensor, -55° to 130°C*	TO-92	1.08	.78	.57
LM20BIM7CT-ND	微 SMD 温度传感器, ±2.5°C	Micro SMD Temperature Sensor, ±2.5°C	SC-70-5	1.24	.91	.66
LM20BIM7TR-ND	微 SMD 温度传感器, ±2.5°C	Micro SMD Temperature Sensor, ±2.5°C	SC-70-5	429.00/1,000		
LM20CIM7CT-ND	微 SMD 温度传感器, ±5°C	Micro SMD Temperature Sensor, ±5°C*	SC-70-5	1.05	.77	.56
LM20CIM7TR-ND	微 SMD 温度传感器, ±5°C	Micro SMD Temperature Sensor, ±5°C*	SC-70-5	364.00/1,000		
LM20SIBPCT-ND	微 SMD 温度传感器	Micro SMD Temperature Sensor	4-microSMD	1.05	.77	.56
LM20SIBPTR-ND	微 SMD 温度传感器	Micro SMD Temperature Sensor	4-microSMD	105.00/250		
LM26CIM5-HHDCT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.43	1.05	.76
LM26CIM5-HHDTR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	494.00/1,000		
LM26CIM5-NPACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.54	1.13	.82
LM26CIM5-NPATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	533.00/1,000		
LM26CIM5-PHACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.54	1.13	.82
LM26CIM5-PHATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	533.00/1,000		
LM26CIM5-RPACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.43	1.05	.76
LM26CIM5-RPATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	533.00/1,000		
LM26CIM5-SHACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.54	1.13	.82
LM26CIM5-SHATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	533.00/1,000		
LM26CIM5-SPACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.54	1.13	.82
LM26CIM5-SPATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	533.00/1,000		
LM26CIM5-TPACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.54	1.13	.82
LM26CIM5-TPATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	533.00/1,000		
LM26CIM5-VHACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.54	1.13	.82
LM26CIM5-VHATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	533.00/1,000		
LM26CIM5-VPACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.54	1.13	.82
LM26CIM5-VPATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	533.00/1,000		
LM26CIM5-XHACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.54	1.13	.82
LM26CIM5-XHATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	533.00/1,000		
LM26CIM5-XPACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.54	1.13	.82
LM26CIM5-XPATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	533.00/1,000		
LM26CIM5-YHACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.54	1.13	.82
LM26CIM5-YHATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	533.00/1,000		
LM26CIM5-YPACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.43	1.05	.76
LM26CIM5-YPATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	494.00/1,000		
LM26CIM5-ZHACT-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	1.54	1.13	.82
LM26CIM5-ZHATR-ND	±3°C 精度工厂预设恒温器*	±3°C Accurate, Factory Preset Thermostat*	SOT-23-5	533.00/1,000		
LM26LVCISDCT-ND	1.6V 预设温度开关和温度传感器*	1.6V Preset Temperature Switch and Temperature Sensor*	6-LLP	1.78	1.31	.95
LM26LVCISDTR-ND	1.6V 预设温度开关和温度传感器*	1.6V Preset Temperature Switch and Temperature Sensor*	6-LLP	617.50/1,000		
LM27CIM5-1HJCT-ND	±3°C 精度 120°C 至 150°C 工厂预设恒温器	±3°C Accurate, 120°C-150°C Factory Preset Thermostat	SOT-23-5	2.33	1.73	1.28
LM27CIM5-1HJTR-ND	±3°C 精度 120°C 至 150°C 工厂预设恒温器	±3°C Accurate, 120°C-150°C Factory Preset Thermostat	SOT-23-5	961.28/1,000		
LM27CIM5-2HJCT-ND	±3°C 精度 120°C 至 150°C 工厂预设恒温器	±3°C Accurate, 120°C-150°C Factory Preset Thermostat	SOT-23-5	2.33	1.73	1.28
LM27CIM5-2HJTR-ND	±3°C 精度 120°C 至 150°C 工厂预设恒温器	±3°C Accurate, 120°C-150°C Factory Preset Thermostat	SOT-23-5	961.28/1,000		
LM27CIM5-3HJCT-ND	±3°C 精度 120°C 至 150°C 工厂预设恒温器*	±3°C Accurate, 120°C-150°C Factory Preset Thermostat*	SOT-23-5	2.33	1.73	1.28
LM27CIM5-3HJTR-ND	±3°C 精度 120°C 至 150°C 工厂预设恒温器*	±3°C Accurate, 120°C-150°C Factory Preset Thermostat*	SOT-23-5	961.28/1,000		
LM32CIMT-ND	双路热敏二极管温度传感器*	Dual Thermal Diode Temperature Sensor*	14-TSSOP	3.10	2.36	1.80
LM34AH-ND	精密型华氏温度传感器, -50°F 至 300°F*	Precision Fahrenheit Temperature Sensor, -50°F to 300°F*	TO-46	13.86	11.88	10.54
LM34CAH-ND	精密型华氏温度传感器, -40°F 至 230°F*	Precision Fahrenheit Temperature Sensor, -40°F to 230°F*	TO-46	11.55	9.90	8.78
LM34CAZ-ND	精密型华氏温度传感器, -40°F 至 230°F*	Precision Fahrenheit Temperature Sensor, -40°F to 230°F*	TO-92	7.14	5.65	4.53
LM34CH-ND	精密型华氏温度传感器, -40°F 至 230°F*	Precision Fahrenheit Temperature Sensor, -40°F to 230°F*	TO-46	9.52	8.16	7.24

* 符合 RoHS 规范要求

(转下页)

★ 欢迎来电查询, 大批量订购, 价格优惠! ★

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)

digikey.com.cn — 电话: (852) 3104 0500 — 传真: (852) 3104 0686

(CN082-09) 1111