

电感 (μH)	电感 容差	测试 频率 (kHz)	标称直流 电阻 (Ω)	额定 电流 (A)	Digi-Key 零件编号	剪切带 单价			Digi-Key 零件编号	带卷		TDK 零件编号
						1	10	100		数量	价格	
图 9 - VLCF4020 系列												
1.8	±30%	100	0.046	1.97	445-3181-1-ND	.77	.68	.60	445-3181-2-ND	1,000	298.00	VLCF4020T-1R8N1R9
2.2	±30%	100	0.054	1.72	445-3182-1-ND	.77	.68	.60	445-3182-2-ND	1,000	298.00	VLCF4020T-2R2N1R7
3.3	±30%	100	0.071	1.52	445-3183-1-ND	.77	.68	.60	445-3183-2-ND	1,000	298.00	VLCF4020T-3R3N1R5
4.7	±30%	100	0.089	1.24	445-3184-1-ND	.77	.68	.60	445-3184-2-ND	1,000	298.00	VLCF4020T-4R7N1R2
6.8	±30%	100	0.119	1.05	445-3185-1-ND	.77	.68	.60	445-3185-2-ND	1,000	298.00	VLCF4020T-6R8N1R0
10	±20%	100	0.168	0.85	445-3186-1-ND	.77	.68	.60	445-3186-2-ND	1,000	298.00	VLCF4020T-100MR85
15	±20%	100	0.275	0.68	445-3187-1-ND	.77	.68	.60	445-3187-2-ND	1,000	298.00	VLCF4020T-150MR68
22	±20%	100	0.391	0.56	445-3188-1-ND	.77	.68	.60	445-3188-2-ND	1,000	298.00	VLCF4020T-220MR56
27	±20%	100	0.451	0.48	445-3189-1-ND	.77	.68	.60	445-3189-2-ND	1,000	298.00	VLCF4020T-270MR48
33	±20%	100	0.571	0.47	445-3190-1-ND	.77	.68	.60	445-3190-2-ND	1,000	298.00	VLCF4020T-330MR47
47	±20%	100	0.849	0.39	445-3191-1-ND	.77	.68	.60	445-3191-2-ND	1,000	298.00	VLCF4020T-470MR39
100	±20%	100	1.308	0.26	445-3192-1-ND	.77	.68	.60	445-3192-2-ND	1,000	298.00	VLCF4020T-101MR26
图 10 - VLCF5020 系列												
1.8	±30%	100	0.049	2.07	445-3193-1-ND	.81	.72	.63	445-3193-2-ND	500	157.50	VLCF5020T-1R8N2R0
2.7	±30%	100	0.058	1.76	445-3194-1-ND	.81	.72	.63	445-3194-2-ND	500	157.50	VLCF5020T-2R7N1R7
3.3	±30%	100	0.069	1.6	445-3195-1-ND	.81	.72	.63	445-3195-2-ND	500	157.50	VLCF5020T-3R3N1R6
4.7	±30%	100	0.079	1.4	445-3196-1-ND	.81	.72	.63	445-3196-2-ND	500	157.50	VLCF5020T-4R7N1R4
6.8	±30%	100	0.102	1.11	445-3197-1-ND	.81	.72	.63	445-3197-2-ND	500	157.50	VLCF5020T-6R8N1R1
10	±20%	100	0.151	0.87	445-3198-1-ND	.81	.72	.63	445-3198-2-ND	500	157.50	VLCF5020T-100MR87
15	±20%	100	0.214	0.71	445-3199-1-ND	.81	.72	.63	445-3199-2-ND	500	157.50	VLCF5020T-150MR71
22	±20%	100	0.311	0.58	445-3200-1-ND	.81	.72	.63	445-3200-2-ND	500	157.50	VLCF5020T-220MR58
33	±20%	100	0.435	0.48	445-3201-1-ND	.81	.72	.63	445-3201-2-ND	500	157.50	VLCF5020T-330MR48
47	±20%	100	0.623	0.40	445-3202-1-ND	.81	.72	.63	445-3202-2-ND	500	157.50	VLCF5020T-470MR40
100	±20%	100	1.375	0.27	445-3203-1-ND	.81	.72	.63	445-3203-2-ND	500	157.50	VLCF5020T-101MR27
图 10 - VLCF5020-1 系列												
2.2	±30%	100	0.058	2.62	445-3204-1-ND	.81	.72	.63	445-3204-2-ND	500	157.50	VLCF5020T-2R2N2R6-1
2.7	±30%	100	0.069	2.28	445-3205-1-ND	.81	.72	.63	445-3205-2-ND	500	157.50	VLCF5020T-2R7N2R2-1
3.3	±30%	100	0.079	2.02	445-3206-1-ND	.81	.72	.63	445-3206-2-ND	500	157.50	VLCF5020T-3R3N2R0-1
4.7	±30%	100	0.102	1.7	445-3207-1-ND	.81	.72	.63	445-3207-2-ND	500	157.50	VLCF5020T-4R7N1R7-1
6.8	±30%	100	0.138	1.39	445-3208-1-ND	.81	.72	.63	445-3208-2-ND	500	157.50	VLCF5020T-6R8N1R3-1
10	±20%	100	0.198	1.13	445-3209-1-ND	.81	.72	.63	445-3209-2-ND	500	157.50	VLCF5020T-100M1R1-1
15	±20%	100	0.292	0.90	445-3210-1-ND	.81	.72	.63	445-3210-2-ND	500	157.50	VLCF5020T-150MR90-1
22	±20%	100	0.413	0.75	445-3211-1-ND	.81	.72	.63	445-3211-2-ND	500	157.50	VLCF5020T-220MR75-1
33	±20%	100	0.597	1.62	445-3212-1-ND	.81	.72	.63	445-3212-2-ND	500	157.50	VLCF5020T-330MR62-1
47	±20%	100	0.875	0.51	445-3213-1-ND	.81	.72	.63	445-3213-2-ND	500	157.50	VLCF5020T-470MR51-1
图 11 - VLF3010A 系列												
1.5	±30%	100	0.068	1.2	445-3214-1-ND	.90	.80	.70	445-3214-2-ND	2,000	350.00/M	VLF3010AT-1R5N1R2
2.2	±20%	100	0.10	1.0	445-3215-1-ND	.90	.80	.70	445-3215-2-ND	2,000	350.00/M	VLF3010AT-2R2M1R0
3.3	±20%	100	0.15	0.87	445-3216-1-ND	.90	.80	.70	445-3216-2-ND	2,000	350.00/M	VLF3010AT-3R3MR87
4.7	±20%	100	0.24	0.70	445-3217-1-ND	.90	.80	.70	445-3217-2-ND	2,000	350.00/M	VLF3010AT-4R7MR70
6.8	±20%	100	0.34	0.61	445-3218-1-ND	.90	.80	.70	445-3218-2-ND	2,000	350.00/M	VLF3010AT-6R8MR61
10	±20%	100	0.58	0.49	445-3219-1-ND	.90	.80	.70	445-3219-2-ND	2,000	350.00/M	VLF3010AT-100MR49
15	±20%	100	0.75	0.40	445-3220-1-ND	.90	.80	.70	445-3220-2-ND	2,000	350.00/M	VLF3010AT-150MR40
22	±20%	100	1.3	0.33	445-3221-1-ND	.90	.80	.70	445-3221-2-ND	2,000	350.00/M	VLF3010AT-220MR33
图 11 - VLF3012A 系列												
1.5	±30%	100	0.059	1.2	445-3222-1-ND	.86	.76	.67	445-3222-2-ND	2,000	333.00/M	VLF3012AT-1R5N1R2
2.2	±20%	100	0.088	1.0	445-3223-1-ND	.86	.76	.67	445-3223-2-ND	2,000	333.00/M	VLF3012AT-2R2M1R0
3.3	±20%	100	0.11	0.87	445-3224-1-ND	.86	.76	.67	445-3224-2-ND	2,000	333.00/M	VLF3012AT-3R3MR87
4.7	±20%	100	0.16	0.74	445-3225-1-ND	.86	.76	.67	445-3225-2-ND	2,000	333.00/M	VLF3012AT-4R7MR74
6.8	±20%	100	0.23	0.59	445-3226-1-ND	.86	.76	.67	445-3226-2-ND	2,000	333.00/M	VLF3012AT-6R8MR59
10	±20%	100	0.36	0.49	445-3227-1-ND	.86	.76	.67	445-3227-2-ND	2,000	333.00/M	VLF3012AT-100MR49
15	±20%	100	0.54	0.41	445-3228-1-ND	.86	.76	.67	445-3228-2-ND	2,000	333.00/M	VLF3012AT-150MR41
22	±20%	100	0.66	0.33	445-3229-1-ND	.86	.76	.67	445-3229-2-ND	2,000	333.00/M	VLF3012AT-220MR33
33	±20%	100	1.1	0.27	445-3230-1-ND	.86	.76	.67	445-3230-2-ND	2,000	333.00/M	VLF3012AT-330MR27
47	±20%	100	1.9	0.22	445-3231-1-ND	.86	.76	.67	445-3231-2-ND	2,000	333.00/M	VLF3012AT-470MR22
图 12 - VLF4012A 系列												
1.5	±20%	100	0.069	1.8	445-3232-1-ND	.81	.72	.63	445-3232-2-ND	1,000	315.00	VLF4012AT-1R5M1R6
2.2	±20%	100	0.076	1.5	445-3233-1-ND	.81	.72	.63	445-3233-2-ND	1,000	315.00	VLF4012AT-2R2M1R5
3.3	±20%	100	0.1	1.3	445-3234-1-ND	.81	.72	.63	445-3234-2-ND	1,000	315.00	VLF4012AT-3R3M1R3
4.7	±20%	100	0.14	1.1	445-3235-1-ND	.81	.72	.63	445-3235-2-ND	1,000	315.00	VLF4012AT-4R7M1R1
6.8	±20%	100	0.2	0.96	445-3236-1-ND	.81	.72	.63	445-3236-2-ND	1,000	315.00	VLF4012AT-6R8MR96
10	±20%	100	0.3	0.80	445-3237-1-ND	.81	.72	.63	445-3237-2-ND	1,000	315.00	VLF4012AT-100MR79
15	±20%	100	0.46	0.63	445-3238-1-ND	.81	.72	.63	445-3238-2-ND	1,000	315.00	VLF4012AT-150MR63
22	±20%	100	0.71	0.52	445-3239-1-ND	.81	.72	.63	445-3239-2-ND	1,000	315.00	VLF4012AT-220MR51
33	±20%	100	1.2	0.44	445-3240-1-ND	.81	.72	.63	445-3240-2-ND	1,000	315.00	VLF4012AT-330MR39
47	±20%	100	2.0	0.36	445-3241-1-ND	.81	.72	.63	445-3241-2-ND	1,000	315.00	VLF4012AT-470MR30
图 13 - VLF5014A 系列												
4.7	±20%	100	0.12	1.7	445-3242-1-ND	1.26	1.12	.98	445-3242-2-ND	1,000	490.00	VLF5014AT-4R7M1R1
6.8	±20%	100	0.16	1.4	445-3243-1-ND	1.26	1.12	.98	445-3243-2-ND	1,000	490.00	VLF5014AT-6R8MR99
10	±20%	100	0.19	1.1	445-3244-1-ND	1.26	1.12	.98	445-3244-2-ND	1,000	490.00	VLF5014AT-100MR92
15	±20%	100	0.28	0.97	445-3245-1-ND	1.26	1.12	.98	445-3245-2-ND	1,000	490.00	VLF5014AT-150MR76

E

全部产品均以美元计价。 免费电话: 10800-1527031 (China Telecom - 中国电讯) — 10800-8527031 (CNCG - 中国网通)