



直角 (接上页)

Table with columns: 触点数, 镀金触点, 柱长度, Digi-Key 零件编号, 单价, AMP 零件编号. Includes RoHS requirements and part numbers like ALSN01-ND.

小尺寸 - 4 面
保护接头 -
0.100x0.100 中心

技术规格:

- .025" (0.64mm) 方形柱, 0.240" (6.10mm) 配接柱长度。
• 材料和表面处理: 外壳和锁销 - 黑色热塑性塑料, 定级 94V-0。
• 触点表面处理: 接线柱/引脚配接端镀 15μ 或 30μ 金, 接线端镀 100μ-200μ 亮锡铅, 整个触点底层镀 50μ 镍。

Diagram of a 4-face protection connector with dimensions and a table of pin counts and dimensions.

Main table for 4-face protection connectors with columns for pin count, gold plating, Digi-Key part number, price, and AMP part number.

Table for 4-face protection connectors with columns for pin count, gold plating, Digi-Key part number, price, and AMP part number.

†蓝色 ‡灰色

Diagram of a 4-face protection connector with dimensions and a table of pin counts and dimensions.

Main table for 4-face protection connectors with columns for pin count, gold plating, Digi-Key part number, price, and AMP part number.

†蓝色

Diagram of a connector with dimensions and a table of pin counts and dimensions.

Table for connectors with columns for pin count, gold plating, lock height, Digi-Key part number, price, and AMP part number.

Diagram of a connector with dimensions and a table of pin counts and dimensions.

Table for connectors with columns for pin count, gold plating, lock height, Digi-Key part number, price, and AMP part number.