

TEXAS INSTRUMENTS Digi-Reel ® (Forts.)		DIGITALLOGIK					
RoHS-konforme Teilenummern sind erhältlich							
TI Teile-Nr.	Digi-Key Teile-Nr.	Beschreibung		Gehäuse	Stückpreis ★		
					1	25	100
SN74ALVCH16240DLR	296-5186-1-ND	16-Bit-Tri-State-Puffer/Treiber	Tri-State 16-Bit Buffer/Driver	48-SSOP	1.94	1.49	1.36
SN74ALVCH16240DLR	296-5186-2-ND	16-Bit-Tri-State-Puffer/Treiber	Tri-State 16-Bit Buffer/Driver	48-SSOP	800.46/1,000		
SN74ALVCH16244DGGRR	296-1139-1-ND	16-Bit-Tri-State-Puffer/Treiber	Tri-State 16-Bit Buffer/Driver	48-TSSOP	1.40	1.09	.99
SN74ALVCH16244DGGRR	296-1139-2-ND	16-Bit-Tri-State-Puffer/Treiber	Tri-State 16-Bit Buffer/Driver	48-TSSOP	1081.08/2,000		
SN74ALVCH16244DGVR	296-5187-1-ND	16-Bit-Tri-State-Puffer/Treiber	Tri-State 16-Bit Buffer/Driver	48-TVSOIP	1.40	1.09	.99
SN74ALVCH16244DGVR	296-5187-2-ND	16-Bit-Tri-State-Puffer/Treiber	Tri-State 16-Bit Buffer/Driver	48-TVSOIP	1081.08/2,000		
SN74ALVCH16244DLR	296-5188-5-ND	16-Bit-Tri-State-Puffer/Treiber	Tri-State 16-Bit Buffer/Driver	48-SSOP	1.62	1.31	1.18
SN74ALVCH16244DLR	296-5188-1-ND	16-Bit-Tri-State-Puffer/Treiber	Tri-State 16-Bit Buffer/Driver	48-SSOP	1.55	1.19	1.08
SN74ALVCH16244KR	296-5189-1-ND	16-Bit-Tri-State-Puffer/Treiber	Tri-State 16-Bit Buffer/Driver	56-BGA	2.11	1.63	1.48
SN74ALVCH16244KR	296-5189-2-ND	16-Bit-Tri-State-Puffer/Treiber	Tri-State 16-Bit Buffer/Driver	56-BGA	870.87/1,000		
SN74ALVCH16245DGGRR	296-5190-1-ND	16-Bit-Tri-State-Bus-Transceiver	Tri-State 16-Bit Bus Transceiver	48-TSSOP	1.40	1.09	.99
SN74ALVCH16245DGGRR	296-5190-2-ND	16-Bit-Tri-State-Bus-Transceiver	Tri-State 16-Bit Bus Transceiver	48-TSSOP	1081.08/2,000		
SN74ALVCH16245DGVR	296-5191-1-ND	16-Bit-Tri-State-Bus-Transceiver	Tri-State 16-Bit Bus Transceiver	48-TVSOIP	1.40	1.09	.99
SN74ALVCH16245DGVR	296-5191-2-ND	16-Bit-Tri-State-Bus-Transceiver	Tri-State 16-Bit Bus Transceiver	48-TVSOIP	1081.08/2,000		
SN74ALVCH16245DL	296-5192-5-ND	16-Bit-Tri-State-Bus-Transceiver	Tri-State 16-Bit Bus Transceiver	48-SSOP	1.62	1.31	1.18
SN74ALVCH16245DLR	296-5192-1-ND	16-Bit-Tri-State-Bus-Transceiver	Tri-State 16-Bit Bus Transceiver	48-SSOP	1.55	1.19	1.08
SN74ALVCH16245DLR	296-5192-2-ND	16-Bit-Tri-State-Bus-Transceiver	Tri-State 16-Bit Bus Transceiver	48-SSOP	639.04/1,000		
SN74ALVCH16245KR	296-5193-1-ND	16-Bit-Tri-State-Bus-Transceiver	Tri-State 16-Bit Bus Transceiver	56-BGA	2.11	1.63	1.48
SN74ALVCH16245KR	296-5193-2-ND	16-Bit-Tri-State-Bus-Transceiver	Tri-State 16-Bit Bus Transceiver	56-BGA	870.87/1,000		
SN74ALVCH16260DGGRR	296-1140-1-ND	12-24-Bit-Tri-State-Mux-D-Latch	Tri-State 12-24-Bit Mux D-Type Latch	56-TSSOP	1.78	1.37	1.25
SN74ALVCH16260DGGRR	296-1140-2-ND	12-24-Bit-Tri-State-Mux-D-Latch	Tri-State 12-24-Bit Mux D-Type Latch	56-TSSOP	1368.49/2,000		
SN74ALVCH16260DLR	296-1141-1-ND	12-24-Bit-Tri-State-Mux-D-Latch	Tri-State 12-24-Bit Mux D-Type Latch	56-SSOP	2.10	1.62	1.47
SN74ALVCH16260DLR	296-1141-2-ND	12-24-Bit-Tri-State-Mux-D-Latch	Tri-State 12-24-Bit Mux D-Type Latch	56-SSOP	868.43/1,000		
SN74ALVCH16269DGGRR	296-5198-1-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24-Bit Registered Bus Exchanger	56-TSSOP	1.83	1.41	1.28
SN74ALVCH16269DGGRR	296-5198-2-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24-Bit Registered Bus Exchanger	56-TSSOP	1406.20/2,000		
SN74ALVCH16269DL	296-5199-5-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24-Bit Registered Bus Exchanger	56-SSOP	2.11	1.71	1.54
SN74ALVCH16269KR	296-9775-1-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24 Bit Registered Bus Exchanger	56-BGA	2.40	1.97	1.77
SN74ALVCH16269KR	296-9775-2-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24 Bit Registered Bus Exchanger	56-BGA	1121.12/1,000		
SN74ALVCH16270DGGRR	296-5200-1-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24 Bit Registered Bus Exchanger	56-TSSOP	2.55	1.97	1.79
SN74ALVCH16270DGGRR	296-5200-2-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24 Bit Registered Bus Exchanger	56-TSSOP	1967.57/2,000		
SN74ALVCH16270DL	296-5201-5-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24 Bit Registered Bus Exchanger	56-SSOP	2.26	1.83	1.64
SN74ALVCH16270DLR	296-5201-1-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24 Bit Registered Bus Exchanger	56-SSOP	2.55	1.97	1.79
SN74ALVCH16270DLR	296-5201-2-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24 Bit Registered Bus Exchanger	56-SSOP	1056.66/1,000		
SN74ALVCH16271DGGRR	296-5202-1-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24 Bit Registered Bus Exchanger	56-TSSOP	4.20	3.44	3.09
SN74ALVCH16271DGGRR	296-5202-2-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24 Bit Registered Bus Exchanger	56-TSSOP	3728.52/2,000		
SN74ALVCH16271DL	296-5203-5-ND	12-24-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 12-24 Bit Registered Bus Exchanger	56-SSOP	4.26	3.43	3.12
SN74ALVCH16282DBRR	296-5210-1-ND	18-36-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 18-36-Bit Registered Bus Exchanger	80-TSSOP	7.96	6.61	6.01
SN74ALVCH16282DBRR	296-5210-2-ND	18-36-Bit-Tri-State-Register-Bus-Exchanger	Tri-State 18-36-Bit Registered Bus Exchanger	80-TSSOP	7807.80/2,000		
SN74ALVCH16334DL	296-5221-5-ND	Universeller 16-Bit-Tri-State-Bustreiber	Tri-State 16-Bit Universal Bus Driver	48-SSOP	3.70	2.98	2.71
SN74ALVCH16334DL	296-5222-1-ND	1-4-Bit-Tri-State-Adressstreiber	Tri-State 1-4 Bit Address Driver	56-TSSOP	3.96	3.24	2.91
SN74ALVCH16344DGGRR	296-5222-2-ND	1-4-Bit-Tri-State-Adressstreiber	Tri-State 1-4 Bit Address Driver	56-TSSOP	3514.71/2,000		
SN74ALVCH16373DGGRR	296-5224-1-ND	16-Bit-Tri-State-D-Latch	Tri-State 16-Bit Transp. D-Type Latch	48-TSSOP	1.40	1.09	.99
SN74ALVCH16373DGGRR	296-5224-2-ND	16-Bit-Tri-State-D-Latch	Tri-State 16-Bit Transp. D-Type Latch	48-TSSOP	1081.08/2,000		
SN74ALVCH16373DL	296-5225-5-ND	16-Bit-Tri-State-D-Latch	Tri-State 16-Bit Transp. D-Type Latch	48-SSOP	1.62	1.31	1.18
SN74ALVCH16373DLR	296-14784-1-ND	16-Bit-Tri-State-D-Latch	Tri-State 16-Bit Transp. D-Type Latch	48-SSOP	1.55	1.19	1.08
SN74ALVCH16374DGGRR	296-1144-1-ND	16-Bit-Tri-State-D-Flip-Flop, flankengetriggert	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-TSSOP	1.40	1.09	.99
SN74ALVCH16374DGGRR	296-1144-2-ND	16-Bit-Tri-State-D-Flip-Flop, flankengetriggert	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-TSSOP	1081.08/2,000		
SN74ALVCH16374DGVR	296-23238-1-ND	16-Bit-Tri-State-D-Flip-Flop, flankengetriggert	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-TVSOIP	1.40	1.09	.99
SN74ALVCH16374DGVR	296-23238-2-ND	16-Bit-Tri-State-D-Flip-Flop, flankengetriggert	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-TVSOIP	1081.08/2,000		
SN74ALVCH16374DL	296-5226-5-ND	16-Bit-Tri-State-D-Flip-Flop, flankengetriggert	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	48-SSOP	1.62	1.31	1.18
SN74ALVCH16374KR	296-9777-1-ND	16-Bit-Tri-State-D-Flip-Flop, flankengetriggert	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	56-BGA	2.11	1.63	1.48
SN74ALVCH16374KR	296-9777-2-ND	16-Bit-Tri-State-D-Flip-Flop, flankengetriggert	Tri-State 16-Bit Edge-Triggered D-Type Flip-Flop	56-BGA	871.27/1,000		
SN74ALVCH16409DL	296-5228-5-ND	Universeller 9-Bit-Tri-State-Bus-Exchanger, 4 Ports	Tri-State 9-Bit 4-Port Universal Bus Exchanger	56-SSOP	1.45	1.17	1.06
SN74ALVCH16500DGGRR	296-5229-1-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-TSSOP	1.81	1.40	1.27
SN74ALVCH16500DGGRR	296-5229-2-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-TSSOP	1391.35/2,000		
SN74ALVCH16500DLR	296-5230-1-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-SSOP	1.81	1.40	1.27
SN74ALVCH16500DLR	296-5230-2-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-SSOP	747.21/1,000		
SN74ALVCH16501DGGRR	296-1145-1-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-TSSOP	2.57	1.99	1.80
SN74ALVCH16501DGGRR	296-1145-2-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-TSSOP	1982.75/2,000		
SN74ALVCH16501DL	296-5231-5-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-SSOP	1.99	1.61	1.45
SN74ALVCH16501KR	296-9778-1-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-BGA	2.67	2.06	1.87
SN74ALVCH16501KR	296-9778-2-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-BGA	1103.50/1,000		
SN74ALVCH16524DGGRR	296-5232-1-ND	18-Bit-Tri-State-Register-Bus-Transceiver	Tri-State 18-Bit Registered Bus Transceiver	56-TSSOP	8.49	7.05	6.41
SN74ALVCH16524DGGRR	296-5232-2-ND	18-Bit-Tri-State-Register-Bus-Transceiver	Tri-State 18-Bit Registered Bus Transceiver	56-TSSOP	8328.32/2,000		
SN74ALVCH16524DL	296-12870-5-ND	Universeller 16-Bit-Tri-State-Bustreiber	Tri-State 16-Bit Universal Bus Driver	56-SSOP	8.81	7.23	6.52
SN74ALVCH16525DL	296-12871-5-ND	18-Bit-Tri-State-Register-Bus-Transceiver	Tri-State 18-Bit Registered Bus Transceiver	56-SSOP	1.99	1.61	1.45
SN74ALVCH16525DGGRR	296-5233-1-ND	18-Bit-Tri-State-Register-Bus-Transceiver	Tri-St. 18-Bit Registered Bus Transcvr	56-TSSOP	2.25	1.74	1.58
SN74ALVCH16525DGGRR	296-5233-2-ND	18-Bit-Tri-State-Register-Bus-Transceiver	Tri-St. 18-Bit Registered Bus Transcvr	56-TSSOP	1735.13/2,000		
SN74ALVCH16543DL	296-5237-5-ND	16-Bit-Tri-State-Register-Transceiver	Tri-State 16-Bit Registered Transceiver	56-SSOP	1.89	1.53	1.38
SN74ALVCH16543DLR	296-14785-1-ND	16-Bit-Tri-State-Register-Transceiver	Tri-State 16-Bit Registered Transceiver	56-SSOP	2.14	1.65	1.50
SN74ALVCH16601DGGRR	296-1146-1-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-TSSOP	2.08	1.61	1.46
SN74ALVCH16601DGGRR	296-1146-2-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-TSSOP	1604.32/2,000		
SN74ALVCH16601DL	296-5240-5-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-SSOP	2.36	1.91	1.72
SN74ALVCH16601DLR	296-5241-1-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-SSOP	2.38	1.84	1.67
SN74ALVCH16601DLR	296-5241-2-ND	Universeller 18-Bit-Tri-State-Bus-Transceiver	Tri-State 18-Bit Univ. Bus Transceiver	56-SSOP	984.66/1,000		
SN74ALVCH16646DGGRR	296-5242-1-ND	16-Bit-Tri-State-Bus-Transceiver/Regist	Tri-St. 16-Bit Bus Transceiver/Regist	56-TSSOP	2.39	1.84	1.67
SN74ALVCH16646DGGRR	296-5242-2-ND	16-Bit-Tri-State-Bus-Transceiver/Regist	Tri-St. 16-Bit Bus Transceiver/Regist	56-TSSOP	1837.84/2,000		
SN74ALVCH16646DGVR	296-5243-1-ND	16-Bit-Tri-State-Bus-Transceiver/Regist	Tri-St. 16-Bit Bus Transceiver/Regist	56-TVSOIP	2.39	1.84	1.67
SN74ALVCH16646DGVR	296-5243-2-ND	16-Bit-Tri-State-Bus-Transceiver/Regist	Tri-St. 16-Bit Bus Transceiver/Regist	56-TVSOIP	1837.84/2,000		
SN74ALVCH16646DL	296-5244-5-ND	16-Bit-Tri-State-Bus-Transceiver/Regist	Tri-St. 16-Bit Bus Transceiver/Regist	56-SSOP	2.58	2.08	1.89
SN74ALVCH16646DLR	296-5244-1-ND	16-Bit-Tri-State-Bus-Transceiver/Regist	Tri-St. 16-Bit Bus Transceiver/Regist	56-SSOP	2.67	2.06	1.87
SN74ALVCH16646DLR	296-5244-2-ND	16-Bit-Tri-State-Bus-Transceiver/Regist	Tri-St. 16-Bit Bus Transceiver/Regist	56-SSOP	1103.50/1,000		
SN74ALVCH16721DGGRR	296-1147-1-ND	20-Bit-Tri-State-Flip-Flop, 3.3 V	Tri-State 3.3V, 20-Bit Flip-Flop	56-TSSOP	1.83	1.41	1.28
SN74ALVCH16721DGGRR	296-1147-2-ND	20-Bit-Tri-State-Flip-Flop, 3.3 V	Tri-State 3.3V, 20-Bit Flip-Flop	56-TSSOP	1406.20/2,000		
SN74ALVCH16721DGVR	296-5245-1-ND	20-Bit-Tri-State-Flip-Flop, 3.3 V	Tri-State 3.3V, 20-Bit Flip-Flop	56-TVSOIP	1.83	1.41	1.28
SN74ALVCH16721DGVR	296-5245-2-ND	20-Bit-Tri-State-Flip-Flop, 3.3 V	Tri-State 3.3V, 20-Bit Flip-Flop	56-TVSOIP	1405.40/2,000		
SN74ALVCH16721DLR	296-5246-1-ND	20-Bit-Tri-State-Flip-Flop, 3.3 V	Tri-State 3.3V, 20-Bit Flip-Flop	56-SSOP	2.11	1.63	1.48
SN74ALVCH16721DLR	296-5246-2-ND	20-Bit-Tri-State-Flip-Flop, 3.3 V	Tri-State 3.3V, 20-Bit Flip-Flop	56-SSOP	871.27/1,000		
SN74ALVCH16820DGGRR	296-5247-1-ND	10-Bit-Tri-State-Flip-Flop, zweif. Ausgang, 3.3 V	Tri-State Dual Output 3.3V, 10-Bit F/F	56-TSSOP	3.72	3.05	2.74
SN74ALVCH16820DGGRR	296-5247-2-ND	10-Bit-Tri-State-Flip-Flop, zweif. Ausgang, 3.3 V	Tri-State Dual Output 3.3V, 10-Bit F/F	56-TSSOP	3301.70/2,000		
SN74ALVCH16820DLR	296-5248-1-ND	10-Bit-Tri-State-Flip-Flop, zweif. Ausgang, 3.3 V	Tri-State Dual Output 3.3V, 10-Bit F/F	56-SSOP	4.20	3.44	3.09
SN74ALVCH16820DLR	296-5248-2-ND	10-Bit-Tri-State-Flip-Flop, zweif. Ausgang, 3.3 V	Tri-State Dual Output 3.3V, 10-Bit F/F	56-SSOP	1961.96/1,000		
SN74ALVCH16821DGGRR	296-5249-1-ND	20-Bit-Tri-State-Busschnittstellen-Flip-Flop, 3.3 V	Tri-State 3.3V, 20-Bit Bus-Interface Flip-Flop	56-TSSOP	3.72	3.05	2.74
SN74ALVCH16821DGGRR	296-5249-2-ND	20-Bit-Tri-State-Busschnittstellen-Flip-Flop, 3.3 V	Tri-State 3.3V, 20-Bit Bus-Interface Flip-Flop	56-TSSOP	3301.70/2,000		
SN74ALVCH16821DL	296-5250-5-ND	20-Bit-Tri-State-Busschnittstellen-Flip-Flop, 3.3 V	Tri-St. 3.3V, 20-Bit Bus-Interface F/F	56-SSOP	5.38	4.33	3.94
SN74ALVCH16823DGGRR	296-1148-1-ND	18-Bit-Tri-State-Busschnittstellen-Flip-Flop	Tri-State 18-Bit Bus Interface Flip-Flop	56-TSSOP	2.52	2.06	1.85
SN74ALVCH16823DGGRR	296-1148-2-ND	18-Bit-Tri-State-Busschnittstellen-Flip-Flop	Tri-State 18-Bit Bus Interface Flip-Flop	56-TSSOP	2237.44/2		