

ANALOG DEVICES		POWER MANAGEMENT		Price Each*	
Digi-Key Part No.	Description	Pkg.	1	25	100
ADP3309ARTZ-3.3-R7CT-ND	Regulator LDO 3.3V, 100mA	SOT-23-5	1.21	1.02	.81
ADP3309ARTZ-3.3-R7TR-ND	Regulator LDO 3.3V, 100mA	SOT-23-5	1578.68/3,000		
ADP3309ARTZ-2.5-R7CT-ND	Regulator LDO 2.5V, 200mA	SOT-23-6	1.28	1.03	.77
ADP3309ARTZ-2.5-R7TR-ND	Regulator LDO 2.5V, 200mA	SOT-23-6	1966.78/3,000		
ADP3309ARTZ-3-RL7CT-ND	Regulator LDO 3.3V, 200mA	SOT-23-6	1.28	1.03	.77
ADP3309ARTZ-3-RL7TR-ND	Regulator LDO 3.3V, 200mA	SOT-23-6	1966.78/3,000		
ADP3311ARTZ-REEL7CT-ND	Regulator LDO Adj. 200mA	SOT-23-6	1.28	1.03	.77
ADP3311ARTZ-REEL7TR-ND	Regulator LDO Adj. 200mA	SOT-23-6	1966.78/3,000		
ADP3333ARMZ-5-R7CT-ND	Regulator LDO 5.0V, 300mA	8-MSOP	1.72	1.38	1.03
ADP3333ARMZ-5-R7TR-ND	Regulator LDO 5.0V, 300mA	8-MSOP	891.36/1,000		
ADP3334ARZ-ND	Regulator LDO Adj. 500mA	8-SOIC	1.80	1.44	1.08
ADP3335ACPZ-3.3-R7CT-ND	Regulator LDO 3.3V, 500mA	8-LFSCP	1.88	1.51	1.13
ADP3335ACPZ-3.3-R7TR-ND	Regulator LDO 3.3V, 500mA	8-LFSCP	1465.91/1,500		
ADP3335ARMZ-2.5-RLCT-ND	Regulator LDO 2.5V, 500mA	8-MSOP	1.90	1.52	1.14
ADP3335ARMZ-3.3-RLCT-ND	Regulator LDO 3.3V, 500mA	8-MSOP	1.90	1.52	1.14
ADP3335ARMZ-3.3-RLTR-ND	Regulator LDO 3.3V, 500mA	8-MSOP	1918.45/3,000		
ADP3335ARMZ-REEL7CT-ND	Regulator LDO 500mA, Adj.	8-MSOP	1.90	1.52	1.14
ADP3335ARMZ-REEL7TR-ND	Regulator LDO 500mA, Adj.	8-MSOP	988.02/1,000		
ADP3338AKCZ-1.5-R7CT-ND	Regulator LDO 1A Precision 1.5V	SOT-223	2.05	1.64	1.28
ADP3338AKCZ-1.5-R7TR-ND	Regulator LDO 1A Precision 1.5V	SOT-223	590.66/500		
ADP3338AKCZ-1.8-R7CT-ND	Regulator LDO 1A Precision 1.8V	SOT-223	2.05	1.64	1.28
ADP3338AKCZ-1.8-R7TR-ND	Regulator LDO 1A Precision 1.8V	SOT-223	590.66/500		
ADP3338AKCZ-2.5-RL7CT-ND	Regulator LDO 1A Precision 2.5V	SOT-223	2.05	1.64	1.28
ADP3338AKCZ-2.5-RL7TR-ND	Regulator LDO 1A Precision 2.5V	SOT-223	590.66/500		
ADP3338AKCZ-3.3-RL7CT-ND	Regulator LDO 1A Precision 3.3V	SOT-223	2.05	1.64	1.28
ADP3338AKCZ-3.3-RL7TR-ND	Regulator LDO 1A Precision 3.3V	SOT-223	590.66/500		
ADP3338AKCZ-5-R7CT-ND	Regulator LDO 1A Precision 5V	SOT-223	2.05	1.64	1.28
ADP3338AKCZ-5-R7TR-ND	Regulator LDO 1A Precision 5V	SOT-223	590.66/500		
ADP3339AKCZ-1.5-R7CT-ND	Regulator LDO 1.5A, 1.5V	SOT-223	2.20	1.76	1.37
ADP3339AKCZ-1.5-R7TR-ND	Regulator LDO 1.5A, 1.5V	SOT-223	633.62/500		
ADP3339AKCZ-1.8-R7CT-ND	Regulator LDO 1.5A, 1.8V	SOT-223	2.20	1.76	1.37
ADP3339AKCZ-1.8-R7TR-ND	Regulator LDO 1.5A, 1.8V	SOT-223	633.62/500		
ADP3339AKCZ-2.5-R7CT-ND	Regulator LDO 1.5A, 2.5V	SOT-223	2.20	1.76	1.37
ADP3339AKCZ-2.5-R7TR-ND	Regulator LDO 1.5A, 2.5V	SOT-223	633.62/500		
ADP3339AKCZ-3-RL7CT-ND	Regulator LDO 1.5A, 3V	SOT-223	2.20	1.76	1.37
ADP3339AKCZ-3-RL7TR-ND	Regulator LDO 1.5A, 3V	SOT-223	633.62/500		
ADP3339AKCZ-3.3-R7CT-ND	Regulator LDO 1.5A, 3.3V	SOT-223	2.20	1.76	1.37
ADP3339AKCZ-3.3-R7TR-ND	Regulator LDO 1.5A, 3.3V	SOT-223	633.62/500		
ADP3339AKCZ-5-R7CT-ND	Regulator LDO 1.5A, 5V	SOT-223	2.20	1.76	1.37
ADP3339AKCZ-5-R7TR-ND	Regulator LDO 1.5A, 5V	SOT-223	633.62/500		
ADP3367ARZ-ND	Regulator LDO Adjustable 5V	8-SOIC	3.36	2.70	2.10
ADP5020ACPZ-R7CT-ND	Regulator LDO Dual, Step-Down	20-LFSCP	2.79	2.24	1.74
ADP5020ACPZ-R7TR-ND	Regulator LDO Dual, Step-Down	20-LFSCP	2369.87/1,500		
Voltage Reference					
AD580LH-ND	Precision Voltage Reference 2.5V*	TO-52-3	4.99	4.00	3.37
AD580LH-ND	Precision Voltage Reference 2.5V*	TO-52-3	11.55	10.40	9.22
AD580TH-ND	Precision Voltage Reference 2.5V*	TO-52-3	19.89	18.57	17.24
AD581JH-ND	Precision Voltage Reference 10V*	TO-5-3	7.63	6.11	5.16
AD581KH-ND	Precision Voltage Reference 10V*	TO-5-3	9.98	8.99	7.97
AD581LH-ND	Precision Voltage Reference 10V*	TO-5-3	18.29	17.08	15.86
AD584JH-ND	Precision Voltage Reference Programmable	TO-99-8	7.50	6.76	5.99
AD584JH-ND	Precision Voltage Reference Programmable	8-Dip	5.25	4.21	3.55
AD584KHZ-ND	Precision Voltage Reference Programmable*	8-Dip	8.60	7.75	6.87
AD584LH-ND	Precision Voltage Reference Programmable	TO-99-8	27.70	25.85	24.01
AD586ARZ-REELCT-ND	Precision Voltage Reference 5V*	8-SOIC	6.94	6.25	5.54
AD586ARZ-REELTR-ND	Precision Voltage Reference 5V*	8-SOIC	12646.76/2,500		
AD586BRZ-ND	Precision Voltage Reference 5V*	8-SOIC	9.65	8.69	7.71
AD586BRZ-REELCT-ND	Precision Voltage Reference 5V*	8-SOIC	9.65	8.69	7.71
AD586JHZ-ND	Precision Voltage Reference 5V*	8-SOIC	5.02	4.02	3.40
AD586KHZ-ND	Precision Voltage Reference 5V*	8-Dip	1.60	4.88	4.12
AD586KHZ-ND	Precision Voltage Reference 5V*	8-SOIC	6.63	5.31	4.48
AD586LHZ-ND	Precision Voltage Reference 5V*	8-SOIC	7.57	6.82	6.05
AD586MZH-ND	Precision Voltage Reference 5V*	8-Dip	8.16	7.35	6.52
AD587JHZ-ND	Precision Voltage Reference 10V*	8-Dip	4.41	3.53	2.98
AD587JHZ-ND	Precision Voltage Reference 10V*	8-SOIC	5.02	4.12	3.40
AD587KHZ-ND	Precision Voltage Reference 10V*	8-SOIC	5.70	4.56	3.85
AD588AQ-ND	Precision Voltage Reference Programmable	16-Dip	22.20	20.72	19.24
AD588JQ-ND	Precision Voltage Reference Programmable	16-Dip	19.03	17.77	16.50
AD588JQ-ND	Voltage Reference 1.235V, 2-Terminal*	TO-51-2	7.07	5.66	4.78
AD588JHZ-ND	Voltage Reference 1.235V, 2-Terminal*	8-SOIC	3.16	2.53	1.97
AD589KH-ND	Voltage Reference 1.235V, 2-Terminal	TO-51-2	7.68	6.15	5.19
AD680AMZ-ND	Voltage Reference 2.5V, Low Power*	8-Dip	5.39	4.31	3.64
AD680JR-REEL7CT-ND	Voltage Reference 2.5V Low Power	8-SOIC	4.15	3.32	2.58
AD680JZ-ND	Voltage Reference 2.5V Low Power*	8-SOIC	3.44	2.76	2.14
AD680JZ-ND	Voltage Reference 2.5V Low Power*	TO-92-3	3.44	2.76	2.14
AD688AQ-ND	Precision Voltage Reference +/-10V	16-Dip	20.32	18.97	17.62
AD688BQ-ND	Precision Voltage Reference +/-10V	16-Dip	34.27	31.99	29.71
AD780AMZ-ND	Precision Voltage Reference 2.5V/3.0V*	8-Dip	6.61	5.29	4.47
AD780ARZ-ND	Precision Voltage Reference 2.5V/3.0V*	8-SOIC	6.61	5.29	4.47
AD780BZ-ND	Precision Voltage Reference 2.5V/3.0V*	8-Dip	7.96	7.17	6.36
AD780BRZ-ND	Precision Voltage Reference 2.5V/3.0V*	8-SOIC	7.96	7.17	6.36
AD1580ARTZ-REEL7CT-ND	Voltage Reference 1.225V*	SOT-23	1.39	1.11	.84
AD1580ARTZ-REEL7TR-ND	Voltage Reference 1.225V*	SOT-23	2125.39/3,000		
AD1580BRTZ-REEL7CT-ND	Voltage Reference 1.225V*	SOT-23	1.49	1.19	.90
AD1580BRTZ-REEL7TR-ND	Voltage Reference 1.225V*	SOT-23	2284.00/3,000		
AD1582ARTZREEL7CT-ND	Voltage Reference 2.5V*	SOT-23	1.12	.90	.67
AD1582ARTZREEL7TR-ND	Voltage Reference 2.5V*	SOT-23	1713.00/3,000		
AD1582BRTZREEL7CT-ND	Voltage Reference 2.5V*	SOT-23-3	1.55	1.24	.93
AD1582BRTZREEL7TR-ND	Voltage Reference 2.5V*	SOT-23-3	2379.17/3,000		
AD1583ARTZ-REEL7CT-ND	Voltage Reference 3V*	SOT-23-3	1.12	.90	.67
AD1583ARTZ-REEL7TR-ND	Voltage Reference 3V*	SOT-23-3	1713.00/3,000		
AD1583BRTZ-REEL7CT-ND	Voltage Reference 3V*	SOT-23	1.55	1.24	.93
AD1583BRTZ-REEL7TR-ND	Voltage Reference 3V*	SOT-23	2379.17/3,000		
AD1584ARTZ-REEL7CT-ND	Voltage Reference 4.096V*	SOT-23-3	1.12	.90	.67
AD1584ARTZ-REEL7TR-ND	Voltage Reference 4.096V*	SOT-23-3	1713.00/3,000		
AD1584BRTZ-REEL7CT-ND	Voltage Reference 4.096V*	SOT-23	1.55	1.24	.93
AD1584BRTZ-REEL7TR-ND	Voltage Reference 4.096V*	SOT-23	2379.17/3,000		
AD101ARZ-ND	Precision Voltage Reference 10V, 10mA*	8-SOIC	2.01	1.61	1.21
AD101AUJZ-REEL7CT-ND	Precision Voltage Reference 10V, 10mA*	TSOT-23-5	2.02	1.62	1.22
AD101AUJZ-REEL7TR-ND	Precision Voltage Reference 10V, 10mA*	TSOT-23-5	3108.78/3,000		
AD101BRZ-ND	Precision Voltage Reference 10V, 10mA*	8-SOIC	4.20	3.37	2.62
AD102AKSZ-REEL7CT-ND	Precision Voltage Reference 5V, 10mA*	SC70-5	2.05	1.64	1.28
AD102AKSZ-REEL7TR-ND	Precision Voltage Reference 5V, 10mA*	SC70-5	3434.92/3,000		
AD102ARZ-ND	Precision Voltage Reference 5V, 10mA*	8-SOIC	2.01	1.61	1.21
AD102AUJZ-REEL7CT-ND	Precision Voltage Reference 5V, 10mA*	TSOT-23-5	2.02	1.62	1.22
AD102AUJZ-REEL7TR-ND	Precision Voltage Reference 5V, 10mA*	TSOT-23-5	3108.78/3,000		
AD102BKSZ-REEL7CT-ND	Precision Voltage Reference 5V, 10mA*	SC70-5	3.79	3.04	2.36

ANALOG DEVICES		POWER MANAGEMENT		Price Each*	
Digi-Key Part No.	Description	Pkg.	1	25	100
AD102BKSZ-REEL7TR-ND	Precision Voltage Reference 5V, 10mA*	SC70-5	6370.22/3,000		
AD102BRZ-ND	Precision Voltage Reference 5V, 10mA*	8-SOIC	2.01	1.61	1.21
AD102BUJZ-REEL7CT-ND	Precision Voltage Reference 5V, 10mA*	TSOT-23-5	3.79	3.04	2.36
AD102BUJZ-REEL7TR-ND	Precision Voltage Reference 5V, 10mA*	TSOT-23-5	6370.22/3,000		
AD103AKSZ-REEL7CT-ND	Precision Voltage Reference 2.5V, 10mA*	SC70-5	2.05	1.64	1.28
AD103AKSZ-REEL7TR-ND	Precision Voltage Reference 2.5V, 10mA*	SC70-5	3434.92/3,000		
AD103ARZ-ND	Precision Voltage Reference 2.5V, 10mA*	8-SOIC	2.01	1.61	1.21
AD103AUJZ-REEL7CT-ND	Precision Voltage Reference 2.5V, 10mA*	TSOT-23-5	2.02	1.62	1.22
AD103AUJZ-REEL7TR-ND	Precision Voltage Reference 2.5V, 10mA*	TSOT-23-5	3108.78/3,000		
AD103BKSZ-REEL7CT-ND	Precision Voltage Reference 2.5V, 10mA*	SC70-5	3.79	3.04	2.36
AD103BKSZ-REEL7TR-ND	Precision Voltage Reference 2.5V, 10mA*	SC70-5	6370.22/3,000		
AD103BRZ-ND	Precision Voltage Reference 2.5V, 10mA*	8-SOIC	2.01	1.61	1.21
AD103BUJZ-REEL7CT-ND	Precision Voltage Reference 2.5V, 10mA*	TSOT-23-5	3.79	3.04	2.36
AD103BUJZ-REEL7TR-ND	Precision Voltage Reference 2.5V, 10mA*	TSOT-23-5	6370.22/3,000		
AD106AKSZ-REEL7CT-ND	Precision Voltage Reference 3V, 10mA*	SC70-5	2.05	1.64	1.28
AD106AKSZ-REEL7TR-ND	Precision Voltage Reference 3V, 10mA*	SC70-5	3434.92/3,000		
AD106ARZ-ND	Precision Voltage Reference 3V, 10mA*	8-SOIC	2.01	1.61	1.21
AD106AUJZ-REEL7CT-ND	Precision Voltage Reference 3V, 10mA*	TSOT-23-5	3.79	3.04	2.36
AD106AUJZ-REEL7TR-ND	Precision Voltage Reference 3V, 10mA*	TSOT-23-5	6370.22/3,000		
AD106BRZ-ND	Precision Voltage Reference 3V, 10mA*	8-SOIC	2.01	1.61	1.21
AD106BUJZ-REEL7CT-ND	Precision Voltage Reference 3V, 10mA*	TSOT-23-6	1.65	1.33	1.00
AD106BUJZ-REEL7TR-ND	Precision Voltage Reference 3V, 10mA*	TSOT-23-6	2537.78/3,000		
AD121AUJZ-REEL7CT-ND	Precision Voltage Reference 2.5V*	TSOT-23-6	1.65	1.33	1.00
AD121AUJZ-REEL7TR-ND	Precision Voltage Reference 2.5V*	TSOT-23-6	2537.78/3,000		
AD125AUJZ-REEL7CT-ND	Precision Voltage Reference 5V*	TSOT-23-6	1.65	1.33	1.00
AD125AUJZ-REEL7TR-ND	Precision Voltage Reference 5V*	TSOT-23-6	2537.78/3,000		
AD127AUJZ-REEL7CT-ND	Precision Voltage Reference 1.25V*	TSOT-23-6	1.65	1.33	1.00
AD127AUJZ-REEL7TR-ND	Precision Voltage Reference 1.25V*	TSOT-23-6	2537.78/3,000		
AD130AUJZ-REEL7CT-ND	Precision Voltage Reference Sub-Band Gap*	TSOT-6	1.65	1.33	1.00
AD130AUJZ-REEL7TR-ND	Precision Voltage Reference Sub-Band Gap*	TSOT-6	2537.78/3,000		
AD130BUJZ-REEL7CT-ND	Precision Voltage Reference Sub-Band Gap*	TSOT-6	2.44	1.95	1.52
AD130BUJZ-REEL7TR-ND	Precision Voltage Reference Sub-Band Gap*	TSOT-6	4090.68/3,000		
AD1820AKSZ-REEL7CT-ND	Voltage Reference High PSRR 1.2V*	SC70	1.40	1.13	.85
AD1820AKSZ-REEL7TR-ND	Voltage Reference High PSRR 1.2V*	SC70	2157.11/3,000		
AD1820ARTZ-REEL7CT-ND	Voltage Reference High PSRR 1.2V*	SOT-23	1.40	1.13	.85
AD1820ARTZ-REEL7TR-ND	Voltage Reference High PSRR 1.2V*	SOT-23	2157.11/3,000		
ADR291ERZ-ND	Precision Voltage Reference 2.5V, 5mA Out*	8-SOIC	7.42	6.68	5.93
ADR291FRZ-ND	Precision Voltage Reference 2.5V, 5mA Out*	8-SOIC	4.18	3.35	2.83
ADR291GRZ-ND	Precision Voltage Reference 2.5V, 5mA Out*	8-TSSOP	4.16	3.34	2.60
ADR291GRZ-ND					