

TEXAS INSTRUMENTS		Digital Reel® (Cont.)		DIGITAL LOGIC			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
SN74LV004ADGVR	296-8435-2-ND	Hex Inverter	14-TVSOP	176.79/2,000					
SN74LV004ANSR	296-26572-1-ND	Hex Inverter*	14-SOP	.43	.29	.24			
SN74LV004ANSR	296-26572-2-ND	Hex Inverter*	14-SOP	196.61/2,000					
SN74LV004APWR	296-1219-1-ND	Hex Inverter	14-TSSOP	.39	.26	.21			
SN74LV004APWR	296-1219-2-ND	Hex Inverter	14-TSSOP	176.79/2,000					
SN74LV004ADREP	296-18126-1-ND	Hex Inverter	14-SOIC	.80	.62	.55			
SN74LV004ADREP	296-18126-2-ND	Hex Inverter	14-SOIC	658.81/2,500					
SN74LV004AQPWREP	296-22326-1-ND	Hex Inverter	14-TSSOP	.80	.62	.55			
SN74LV004AQPWREP	296-22326-2-ND	Hex Inverter	14-TSSOP	527.05/2,000					
SN74LV004AR9YR	296-13956-1-ND	Hex Inverter	14-QFN	.43	.29	.24			
SN74LV004AR9YR	296-13956-2-ND	Hex Inverter	14-QFN	294.92/3,000					
SN74LV006ADB	296-1696-5-ND	Hex Inverter Buffer/Driver with OD	14-SOIC	.43	.29	.24			
SN74LV006ADB	296-14399-1-ND	Hex Inverter Buffer/Driver with OD	14-SSOP	.45	.30	.24			
SN74LV006ADB	296-14399-2-ND	Hex Inverter Buffer/Driver with OD	14-SSOP	201.57/2,000					
SN74LV006ADBR	296-14905-1-ND	Hex Inverter Buffer/Driver with OD	14-SOIC	.40	.27	.22			
SN74LV006ADBR	296-14905-2-ND	Hex Inverter Buffer/Driver with OD	14-SOIC	229.24/2,500					
SN74LV006ADGVR	296-8436-1-ND	Hex Inverter Buffer/Driver with OD	14-TVSOP	.40	.27	.22			
SN74LV006ADGVR	296-8436-2-ND	Hex Inverter Buffer/Driver with OD	14-TVSOP	183.39/2,000					
SN74LV006ADMPREP	296-22327-1-ND	Hex Inverter Buffer/Driver with OD	14-SOIC	.83	.65	.57			
SN74LV006ADMPREP	296-22327-2-ND	Hex Inverter Buffer/Driver with OD	14-SOIC	688.76/2,500					
SN74LV006APWR	296-8437-1-ND	Hex Inverter Buffer/Driver with OD	14-TSSOP	.40	.27	.22			
SN74LV006APWR	296-8437-2-ND	Hex Inverter Buffer/Driver with OD	14-TSSOP	183.39/2,000					
SN74LV006ARGYR	296-13957-1-ND	Hex Inverter Buffer/Driver with OD	14-QFN	.45	.30	.24			
SN74LV006ARGYR	296-13957-2-ND	Hex Inverter Buffer/Driver with OD	14-QFN	302.35/3,000					
SN74LV007AD	296-8441-5-ND	Hex Buffer/Driver with OD	14-SOIC	.43	.29	.24			
SN74LV007AD	296-8441-1-ND	Hex Buffer/Driver with OD	14-SOIC	.40	.27	.22			
SN74LV007ADR	296-8441-2-ND	Hex Buffer/Driver with OD	14-SOIC	229.24/2,500					
SN74LV007ADBR	296-8439-1-ND	Hex Buffer/Driver with OD	14-SSOP	.45	.30	.24			
SN74LV007ADBR	296-8439-2-ND	Hex Buffer/Driver with OD	14-SSOP	201.57/2,000					
SN74LV007ADGVR	296-8440-1-ND	Hex Buffer/Driver with OD	14-TVSOP	.40	.27	.22			
SN74LV007ADGVR	296-8440-2-ND	Hex Buffer/Driver with OD	14-TVSOP	183.39/2,000					
SN74LV007AIPWREP	296-22328-1-ND	Hex Buffer/Driver with OD	14-TSSOP	.62	.48	.43			
SN74LV007AIPWREP	296-22328-2-ND	Hex Buffer/Driver with OD	14-TSSOP	407.27/2,000					
SN74LV007AMPWREP	296-22329-1-ND	Hex Buffer/Driver with OD	14-TSSOP	1.50	1.19	1.08			
SN74LV007AMPWREP	296-22329-2-ND	Hex Buffer/Driver with OD	14-TSSOP	1110.29/2,000					
SN74LV007APWR	296-8442-1-ND	Hex Buffer/Driver with OD	14-TSSOP	.40	.27	.22			
SN74LV007APWR	296-8442-2-ND	Hex Buffer/Driver with OD	14-TSSOP	183.39/2,000					
SN74LV007AQPWRQ1	296-20707-1-ND	Hex Buffer/Driver with OD	14-TSSOP	.45	.30	.25			
SN74LV007AQPWRQ1	296-20707-2-ND	Hex Buffer/Driver with OD	14-TSSOP	204.87/2,000					
SN74LV007ARGYR	296-13958-1-ND	Hex Buffer/Driver with OD	14-QFN	.45	.30	.24			
SN74LV007ARGYR	296-13958-2-ND	Hex Buffer/Driver with OD	14-QFN	302.35/3,000					
SN74LV008AD	296-1697-5-ND	Quad 2-Input Positive AND Gate	14-SOIC	.42	.28	.23			
SN74LV008AD	296-1697-1-ND	Quad 2-Input Positive AND Gate	14-SOIC	.39	.26	.21			
SN74LV008ADR	296-1697-2-ND	Quad 2-Input Positive AND Gate	14-SOIC	220.98/2,500					
SN74LV008ADBR	296-1220-1-ND	Quad 2-Input Positive AND Gate	14-SSOP	.43	.29	.24			
SN74LV008ADBR	296-1220-2-ND	Quad 2-Input Positive AND Gate	14-SSOP	196.61/2,000					
SN74LV008AMPWREP	296-22330-1-ND	Quad 2-Input Positive AND Gate	14-TSSOP	.82	.64	.56			
SN74LV008AMPWREP	296-22330-2-ND	Quad 2-Input Positive AND Gate	14-TSSOP	539.03/2,000					
SN74LV008ANSR	296-26576-1-ND	Quad 2-Input Pos. AND Gate*	14-SOP	.43	.29	.24			
SN74LV008ANSR	296-26576-2-ND	Quad 2-Input Pos. AND Gate*	14-SOP	196.61/2,000					
SN74LV008APWR	296-1221-1-ND	Quad 2-Input Positive AND Gate	14-TSSOP	.39	.26	.21			
SN74LV008APWR	296-1221-2-ND	Quad 2-Input Positive AND Gate	14-TSSOP	176.79/2,000					
SN74LV008AQPWRQ1	296-21812-1-ND	Quad 2-Input Positive AND Gate	14-TSSOP	.45	.30	.25			
SN74LV008AQPWRQ1	296-21812-2-ND	Quad 2-Input Positive AND Gate	14-TSSOP	204.87/2,000					
SN74LV008ARGYR	296-13959-1-ND	Quad 2-Input Positive AND Gate	14-QFN	.43	.29	.24			
SN74LV008ARGYR	296-13959-2-ND	Quad 2-Input Positive AND Gate	14-QFN	294.92/3,000					
SN74LV010AD	296-8443-5-ND	Triple 3-Input NAND Gate	14-SOIC	.42	.28	.23			
SN74LV010AD	296-8443-1-ND	Triple 3-Input NAND Gate	14-SOIC	.43	.29	.24			
SN74LV010ADBR	296-8444-1-ND	Triple 3-Input NAND Gate	14-SSOP	.43	.29	.24			
SN74LV010ADBR	296-8444-2-ND	Triple 3-Input NAND Gate	14-SSOP	196.61/2,000					
SN74LV010APW	296-26578-5-ND	Triple 3-Input Pos. NAND Gate*	14-TSSOP	.42	.28	.23			
SN74LV010APWR	296-8445-1-ND	Triple 3-Input NAND Gate	14-TSSOP	.39	.26	.21			
SN74LV010APWR	296-8445-2-ND	Triple 3-Input NAND Gate	14-TSSOP	176.79/2,000					
SN74LV010ARGYR	296-13960-1-ND	Triple 3-Input NAND Gate	14-QFN	.43	.29	.24			
SN74LV010ARGYR	296-13960-2-ND	Triple 3-Input NAND Gate	14-QFN	294.92/3,000					
SN74LV14AD	296-1699-5-ND	Hex Schmitt-Trigger Inverter	14-SOIC	.42	.28	.23			
SN74LV14AD	296-1699-1-ND	Hex Schmitt-Trigger Inverter	14-SOIC	.39	.26	.21			
SN74LV14ADR	296-1699-2-ND	Hex Schmitt-Trigger Inverter	14-SOIC	220.98/2,500					
SN74LV14ADBR	296-8463-1-ND	Hex Schmitt-Trigger Inverter	14-SSOP	.43	.29	.24			
SN74LV14ADBR	296-8463-2-ND	Hex Schmitt-Trigger Inverter	14-SSOP	196.61/2,000					
SN74LV14ADGVR	296-8464-1-ND	Hex Schmitt-Trigger Inverter	14-TVSOP	.39	.26	.21			
SN74LV14ADGVR	296-8464-2-ND	Hex Schmitt-Trigger Inverter	14-TVSOP	176.79/2,000					
SN74LV14ANSR	296-26583-1-ND	Hex Schmitt-Trigger Inverter*	14-SOP	.43	.29	.24			
SN74LV14ANSR	296-26583-2-ND	Hex Schmitt-Trigger Inverter*	14-SOP	196.61/2,000					
SN74LV14APWR	296-1224-1-ND	Hex Schmitt-Trigger Inverter	14-TSSOP	.39	.26	.21			
SN74LV14APWR	296-1224-2-ND	Hex Schmitt-Trigger Inverter	14-TSSOP	176.79/2,000					
SN74LV14AQDREP	296-19596-1-ND	Hex Schmitt-Trigger Inverter	14-SOIC	.80	.62	.55			
SN74LV14AQDREP	296-19596-2-ND	Hex Schmitt-Trigger Inverter	14-SOIC	658.81/2,500					
SN74LV14AQDREG401	296-23270-1-ND	Hex Schmitt-Trigger Inverter	14-SOIC	.45	.30	.25			
SN74LV14AQDREG401	296-23270-2-ND	Hex Schmitt-Trigger Inverter	14-SOIC	256.09/2,500					
SN74LV14AQPWREP	296-20666-1-ND	Hex Schmitt-Trigger Inverter	14-TSSOP	.80	.62	.55			
SN74LV14AQPWREP	296-20666-2-ND	Hex Schmitt-Trigger Inverter	14-TSSOP	476.79/2,000					
SN74LV14ARGYR	296-13965-1-ND	Hex Schmitt-Trigger Inverter	14-QFN	.43	.29	.24			
SN74LV14ARGYR	296-13965-2-ND	Hex Schmitt-Trigger Inverter	14-QFN	294.92/3,000					
SN74LV32AD	296-1235-5-ND	Quad 2-Input OR Gate	14-SOIC	.42	.28	.23			
SN74LV32AD	296-1235-1-ND	Quad 2-Input OR Gate	14-SOIC	.39	.26	.21			
SN74LV32ADR	296-1235-2-ND	Quad 2-Input OR Gate	14-SOIC	220.98/2,500					
SN74LV32ADBR	296-1234-1-ND	Quad 2-Input OR Gate	14-SSOP	.43	.29	.24			
SN74LV32ADBR	296-1234-2-ND	Quad 2-Input OR Gate	14-SSOP	196.61/2,000					
SN74LV32ADMPREP	296-22361-1-ND	Quad 2-Input OR Gate	14-SOIC	.83	.65	.57			
SN74LV32ADMPREP	296-22361-2-ND	Quad 2-Input OR Gate	14-SOIC	688.76/2,500					
SN74LV32AMPWREP	296-22362-1-ND	Quad 2-Input OR Gate	14-TSSOP	1.50	1.19	1.08			
SN74LV32AMPWREP	296-22362-2-ND	Quad 2-Input OR Gate	14-TSSOP	1110.28/2,000					
SN74LV32ANSR	296-26624-1-ND	Quad 2-Input OR Gate*	14-SOP	.43	.29	.24			
SN74LV32ANSR	296-26624-2-ND	Quad 2-Input OR Gate*	14-SOP	196.61/2,000					
SN74LV32APWR	296-1236-1-ND	Quad 2-Input OR Gate	14-TSSOP	.39	.26	.21			
SN74LV32APWR	296-1236-2-ND	Quad 2-Input OR Gate	14-TSSOP	176.79/2,000					
SN74LV32AQDREP	296-22363-1-ND	Quad 2-Input OR Gate	14-SOIC	.80	.62	.55			
SN74LV32AQDREP	296-22363-2-ND	Quad 2-Input OR Gate	14-SOIC	658.81/2,500					
SN74LV32AQPWREP	296-18127-1-ND	Quad 2-Input OR Gate	14-TSSOP	.80	.62	.55			
SN74LV32AQPWREP	296-18127-2-ND	Quad 2-Input OR Gate	14-TSSOP	527.05/2,000					
SN74LV32ARGYR	296-13819-1-ND	Quad 2-Input OR Gate	14-QFN	.43	.29	.24			
SN74LV32ARGYR	296-13819-2-ND	Quad 2-Input OR Gate	14-QFN	294.92/3,000					
SN74LV74AD	296-1240-5-ND	Tri-State Dual D-Type Flip-Flop	14-SOIC	.45	.30	.25			
SN74LV74AD	296-1240-1-ND	Tri-State Dual D-Type Flip-Flop	14-SOIC	.42	.28	.23			
SN74LV74ADR	296-1240-2-ND	Tri-State Dual D-Type Flip-Flop	14-SOIC	239.57/2,500					
SN74LV74ADBR	296-1239-1-ND	Tri-State Dual D-Type Flip-Flop	14-SSOP	.46	.31	.25			
SN74LV74ADBR	296-1239-2-ND	Tri-State Dual D-Type Flip-Flop	14-SSOP	209.83/2,000					

TEXAS INSTRUMENTS		Digital Reel® (Cont.)		DIGITAL LOGIC			RoHS Compliant Parts Available		
T.I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*					
				1	25	100			
SN74LVCT4AMPWREP	296-22378-1-ND	Tri-State Dual D-Type Flip-Flop	14-TSSOP	83	65	57			
SN74LVCT4AMPWREP	296-22378-2-ND	Tri-State Dual D-Type Flip-Flop	14-TSSOP	551.01/2,000					
SN74LVCT4APWR	296-1241-1-ND	Tri-State Dual D-Type Flip-Flop	14-TSSOP	.42	.28	.23			
SN74LVCT4APWR	296-1241-2-ND	Tri-State Dual D-Type Flip-Flop	14-TSSOP	191.66/2,000					
SN74LVCT4ADREP	296-22379-1-ND	Tri-State Dual D-Type Flip-Flop	14-SOIC	.81					