



Pluggable Terminal Blocks and Pin Headers

Terminal Blocks: • Hole Diameter: 1.3mm • Voltage: 250V • Current: 16A • Temperature: -30°C ~ 120°C • Plating: BeCu
 • Wire Size: 14-22AWG • Flame Class: 94V-0 **Pin Headers:** • Spacing: 5mm • Rated Voltage: 300V (250V for ED2673-ND and ED2674-ND) • Rated Current: 10A • Terminal Plating: Tin




Fig.	No. of Pos.	Digi-Key Part No.	Pricing		
			1	10	100
Pluggable Terminal Blocks					
1	2	ED1613-ND	.61	5.49	48.85
	3	ED1614-ND	.91	8.20	72.87
	4	ED2214-ND	1.23	11.03	98.02
	5	ED2215-ND	1.53	13.75	122.20
	6	ED2216-ND	1.83	16.50	146.71
	7	ED2217-ND	2.14	19.26	171.21
2	10	ED2218-ND	3.06	27.53	244.72
	12	ED2219-ND	3.68	33.05	293.73
	2	ED2655-ND	.27	2.42	21.46
	3	ED2656-ND	.41	3.64	32.35
	4	ED2657-ND	.54	4.84	43.08
	5	ED2658-ND	.67	6.05	53.81
3	6	ED2659-ND	.81	7.26	64.54
	7	ED2660-ND	.94	8.47	75.28
	8	ED2661-ND	1.08	9.70	86.17
	10	ED2662-ND	1.35	12.11	107.63
	12	ED2663-ND	1.68	15.14	134.53
	Pin Headers				
3	2	ED1660-ND	.29	2.58	21.25
	3	ED1661-ND	.42	3.72	30.69
	4	ED1662-ND	.54	4.87	40.13

Fig.	No. of Pos.	Digi-Key Part No.	Pricing		
			1	10	100
3	5	ED1663-ND	.67	6.02	49.57
	6	ED1664-ND	.80	7.17	59.00
	7	ED1665-ND	.93	8.31	68.44
	8	ED1666-ND	1.06	9.46	77.89
	9	ED1667-ND	1.19	10.60	87.33
	10	ED1668-ND	1.31	11.75	96.77
	11	ED1669-ND	1.44	12.90	106.21
	12	ED1670-ND	1.57	14.05	115.65
	13	ED1671-ND	1.70	15.19	125.09
	14	ED1672-ND	1.83	16.34	134.53
	15	ED1673-ND	1.95	17.48	143.98
	16	ED1674-ND	2.08	18.63	153.42
	17	ED1675-ND	2.21	19.77	162.86
	18	ED1676-ND	2.34	20.92	172.30
	19	ED1677-ND	2.47	22.07	181.74
	20	ED1678-ND	2.59	23.22	191.18
	21	ED1679-ND	2.72	24.36	200.62
	22	ED1680-ND	2.85	25.51	210.07
	23	ED1681-ND	2.98	26.65	219.50
24	ED1682-ND	2.47	22.20	197.32	
24	24	ED2673-ND	.82	7.39	65.73
	24	ED2674-ND	1.08	9.73	86.49



Terminal Blocks

UL# E101811, 86ME2081 CSA# 068503X000

Specifications: • Rated Currents: 10A/15A/16A • Insulator: PA 6 GV/PBTP and PBT • Temperature Range: -30°C ~ 105°C • Flame Class: 94V-0

These On-Shore Technology Terminal Blocks are Stackable for any number of contacts. 4.5mm Lead Length.




Fig.	No. of Pos.	Lead Spacing (mm)	Rated Volt. (V) VDE 0110	Terminal Plating	Block Length (mm)	Digi-Key Part No.	Pricing			
							1	10	100	
1	2	5.0	250	Nickel	10.16	ED1631-ND	.70	6.34	56.38	
	3	5.0	300	Tin	10.16	ED1643-ND	.60	5.37	47.73	
	2	7.5	380	Tin	15	ED1605-ND	.52	4.67	41.48	
	2	10.0	500	Tin	15	ED1615-ND	.52	4.67	41.48	
	2	10.0	250	Tin	15	ED1627-ND	.52	4.67	41.48	
	2	10.0	500	Nickel	15	ED1633-ND	.79	7.10	63.10	
	3	5.0	250	Nickel	15	ED1632-ND	1.06	9.53	84.72	
	3	5.0	300	Tin	15.24	ED1644-ND	.90	8.07	71.75	
	3	7.5	380	Tin	22.5	ED1606-ND	.78	6.99	62.14	
	3	10.0	500	Tin	25	ED1616-ND	.78	6.99	62.14	
	3	10.0	500	Nickel	25	ED1628-ND	.78	6.99	62.14	
	3	10.0	500	Nickel	25	ED1634-ND	1.19	10.67	94.81	
2	2	5.0	250	Tin	10	ED1603-ND	.52	4.67	41.48	
	2	5.0	125	Tin	10	ED1625-ND	.52	4.67	41.48	
	2	5.0	250	Tin	10.16	ED1611-ND	.52	4.67	41.48	
	2	7.5	380	Tin	15	ED1607-ND	.59	5.33	47.41	
	2	10.0	250	Tin	15	ED1617-ND	.59	5.33	47.41	
	2	10.0	250	Tin	15	ED1629-ND	.59	5.33	47.41	
	3	5.0	250	Tin	15	ED1604-ND	.78	6.99	62.14	
	3	5.0	125	Tin	15	ED1626-ND	.78	6.99	62.14	
	3	5.0	250	Tin	15.25	ED1612-ND	.78	6.99	62.14	
	3	7.5	380	Tin	22.5	ED1608-ND	.89	7.98	70.95	
	3	10.0	250	Tin	25	ED1618-ND	.89	7.98	70.95	
	3	10.0	250	Tin	25	ED1630-ND	.89	7.98	70.95	
3	2	5.0	250	Nickel	10	ED1619-ND	.58	5.19	46.13	
	2	10.0	250	Nickel	15	ED1621-ND	.74	6.67	59.26	
	3	5.0	250	Nickel	15	ED1620-ND	.86	7.77	69.03	
	3	10.0	250	Nickel	25	ED1622-ND	1.11	9.99	88.73	
	4	2	5.0	300	Tin	10	ED1653-ND	1.44	12.97	115.32
		3	5.0	300	Tin	15	ED1654-ND	2.16	19.46	172.97
		2	5.0	250	Tin	10	ED2561-ND	.19	1.75	15.57
		3	5.0	250	Tin	15	ED2562-ND	.29	2.63	23.35
		4	5.0	250	Tin	20	ED2563-ND	.39	3.50	31.14
		5	5.0	250	Tin	25	ED2565-ND	.49	4.38	38.92
	5	6	5.0	250	Tin	30	ED2566-ND	.58	5.25	46.70
		8	5.0	250	Tin	40	ED2567-ND	.78	7.01	62.27
10		5.0	250	Tin	50	ED2568-ND	.98	8.76	77.84	
12		5.0	250	Tin	60	ED2569-ND	1.17	10.51	93.41	
6		2	5.0	250	Brass	10	ED2570-ND	.33	2.92	25.95
		3	5.0	250	Brass	15	ED2571-ND	.49	4.38	38.92
	4	5.0	250	Brass	20	ED2572-ND	.65	5.84	51.89	
	5	5.0	250	Brass	25	ED2573-ND	.81	7.30	64.86	
	6	5.0	250	Brass	30	ED2574-ND	.98	8.76	77.84	
	8	5.0	250	Brass	40	ED2575-ND	1.30	11.68	103.78	
7	10	5.0	250	Brass	50	ED2576-ND	1.63	14.60	129.73	
	12	5.0	250	Brass	60	ED2577-ND	1.95	17.51	155.68	
	2	7.5	250	CuZn	15	ED2578-ND	.21	1.88	16.72	
	3	7.5	250	CuZn	22.5	ED2579-ND	.31	2.82	25.08	
	8	2	5.0	250	Brass	10.16	ED2580-ND	.22	1.91	17.01
		3	5.0	250	Brass	15.24	ED2581-ND	.32	2.87	25.51
4		5.0	250	Brass	20.32	ED2582-ND	.42	3.83	34.02	
5		5.0	250	Brass	25.4	ED2583-ND	.53	4.78	42.52	
6		5.0	250	Brass	30.48	ED2584-ND	.64	5.74	51.03	
7		5.0	250	Brass	35.56	ED2585-ND	.74	6.69	59.53	
9	8	5.0	250	Brass	40.64	ED2586-ND	.85	7.66	68.04	
	10	5.0	250	Brass	45.72	ED2587-ND	1.07	9.57	85.04	
	12	5.0	250	Brass	50.8	ED2588-ND	1.27	11.48	102.05	
	2	5.0	250	Brass	10.16	ED2589-ND	.33	2.92	25.95	
	3	5.0	250	Brass	15.24	ED2590-ND	.49	4.38	38.92	
	4	5.0	250	Brass	20.32	ED2591-ND	.65	5.84	51.89	
10	6	5.0	250	Brass	30.48	ED2592-ND	.98	8.76	77.84	
	8	5.0	250	Brass	40.64	ED2593-ND	1.30	11.68	103.78	
	10	5.0	250	Brass	50.8	ED2594-ND	1.63	14.60	129.73	
	12	5.0	250	Brass	60.96	ED2595-ND	1.95	17.51	155.68	
	2	10.0	250	Tin	15	ED2596-ND	.30	2.63	23.38	
	3	10.0	250	Tin	25	ED2597-ND	.44	3.93	34.91	

Fig.	No. of Pos.	Lead Spacing (mm)	Rated Volt. (V) VDE 0110	Terminal Plating	Block Length (mm)	Digi-Key Part No.	Pricing		
							1	10	100
11	2	10.0	250	Brass	15	ED2598-ND	.36	3.24	28.83
	3	10.0	250	Brass	25	ED2599-ND	.54	4.87	43.24
	2	5.0	250	Brass	10	ED2600-ND	.16	1.43	12.68
	3	5.0	250	Brass	15	ED2601-ND	.24	2.14	19.03
	4	5.0	250	Brass	20	ED2602-ND	.32	2.85	25.37
	5	5.0	250	Brass	25	ED2603-ND	.40	3.57	31.71
	6	5.0	250	Brass	30	ED2604-ND	.47	4.28	38.05
	7	5.0	250	Brass	35	ED2605-ND	.55	5.00	44.40
	8	5.0	250	Brass	40	ED2606-ND	.63	5.71	50.74
	10	5.0	250	Brass	50	ED2607-ND	.79	7.14	63.42
	12	5.0	250	Brass	60	ED2608-ND	.95	8.56	76.11
	13	2	5.0	300	Brass	10.16	ED2609-ND	.17	1.49
3		5.0	300	Brass	15.24	ED2610-ND	.25	2.23	19.89
4		5.0	300	Brass	20.32	ED2611-ND	.33	2.99	26.52
5		5.0	300	Brass	25.4	ED2612-ND	.42	3.73	33.15
6		5.0	300	Brass	30.48	ED2613-ND	.50	4.48	39.78
7		5.0	300	Brass	35.56	ED2614-ND	.58	5.22	46.41
8		5.0	300	Brass	40.64	ED2615-ND	.66	5.97	53.04
10		5.0	300	Brass	50.8	ED2616-ND	.83	7.46	66.31
12		5.0	300	Brass	60.96	ED2617-ND	.99	8.95	79.57
14		2	5.0	2					