

ANALOG DEVICES		Digi+Reel® (Cont.)		AMPLIFIERS		
Digi-Key Part No.	Description	Pkg.	Price Each*			
			1	25	100	
AD8033ARZ-ND	Voltage-Feedback Amp with FastFET™**	8-SOIC	2.05	1.64	1.28	
AD8034ARTZ-REEL7CT-ND	Voltage-Feedback Amp Dual with FastFET™**	SOT-23-8	2.99	2.40	1.87	
AD8034ARTZ-REEL7TR-ND	Voltage-Feedback Amp Dual with FastFET™**	SOT-23-8	5027.48	3,000		
AD8034ARZ-ND	Voltage-Feedback Amp Dual with FastFET™**	8-SOIC	3.05	2.44	1.90	
AD8036ANZ-ND	Voltage-Feedback Clamp Amp*	8-Dip	7.34	5.87	4.36	
AD8036ARZ-ND	Voltage-Feedback Clamp Amp*	8-SOIC	7.34	5.87	4.36	
AD8037ANZ-ND	Voltage-Feedback Amp Output Clamping*	8-Dip	7.05	5.65	4.77	
AD8037ARZ-ND	Voltage-Feedback Amp Output Clamping*	8-SOIC	7.05	5.65	4.77	
AD8038AKSZ-REEL7CT-ND	Voltage-Feedback Amp 350MHz Low Power*	SC70-5	1.78	1.43	1.07	
AD8038AKSZ-REEL7TR-ND	Voltage-Feedback Amp 350MHz Low Power*	SC70-5	2728.11	3,000		
AD8038ARZ-ND	Voltage-Feedback Amp 350MHz Low Power*	8-SOIC	1.82	1.46	1.10	
AD8039ARZ-ND	Voltage-Feedback Amp 350MHz Low Power*	8-SOIC	2.30	1.85	1.44	
AD8039ARTZ-REEL7CT-ND	Voltage-Feedback Amp 350MHz Low Power*	SOT-23-8	2.25	1.80	1.40	
AD8039ARTZ-REEL7TR-ND	Voltage-Feedback Amp 350MHz Low Power*	SOT-23-8	3778.42	3,000		
AD8040ARZ-ND	Low Power, High Speed, Rail-to-Rail In/Out Amp*	14-SOIC	3.06	2.46	1.91	
AD8041ANZ-ND	Voltage-Feedback Amp with Disable*	8-Dip	3.49	2.80	2.18	
AD8041ARZ-ND	Voltage-Feedback Amp with Disable*	8-SOIC	3.49	2.80	2.18	
AD8042ARZ-ND	Voltage-Feedback Amp Dual Rail-to-Rail*	8-SOIC	4.33	3.47	2.70	
AD8044ANZ-ND	Voltage-Feedback Amp Rail-to-Rail Quad*	14-Dip	6.77	5.42	4.58	
AD8044ARZ-14-ND	Voltage-Feedback Amp Rail-to-Rail Quad*	14-SOIC	6.77	5.42	4.58	
AD8045ACPZ-REEL7CT-ND	Voltage-Feedback Amp Ultralow Distortion*	8-LFSCP	2.62	2.10	1.64	
AD8045ACPZ-REEL7TR-ND	Voltage-Feedback Amp Ultralow Distortion*	8-LFSCP	2227.69	1,500		
AD8045ARZ-ND	Voltage-Feedback Amp Ultralow Distortion*	8-SOIC	2.68	2.15	1.67	
AD8047ANZ-ND	Voltage-Feedback Amp 250MHz*	8-Dip	4.52	3.62	2.82	
AD8047ARZ-ND	Voltage-Feedback Amp 250MHz*	8-SOIC	4.52	3.62	2.82	
AD8048ARZ-ND	Voltage-Feedback Amp General Purpose*	8-SOIC	4.11	3.29	2.56	
AD8051ARZ-ND	Voltage-Feedback Amp Single High Speed*	8-SOIC	1.80	1.44	1.08	
AD8051ARTZ-REEL7CT-ND	Voltage-Feedback Amp Single High Speed*	SOT-23-5	1.80	1.44	1.08	
AD8051ARTZ-REEL7TR-ND	Voltage-Feedback Amp Single High Speed*	SOT-23-5	2759.83	3,000		
AD8052ARZ-ND	Voltage-Feedback Amp Dual High Speed*	8-SOIC	3.06	2.46	1.91	
AD8052ARMZ-ND	Voltage-Feedback Amp Dual High Speed*	8-MSOP	3.06	2.46	1.91	
AD8054AR-REEL7CT-ND	Voltage-Feedback Amp Quad High Speed*	14-SOIC	5.63	4.51	3.81	
AD8054ARZ-ND	Voltage-Feedback Amp Quad High Speed*	14-SOIC	4.87	3.90	3.29	
AD8054ARUZ-ND	Voltage-Feedback Amp Quad High Speed*	14-TSSOP	5.12	4.10	3.46	
AD8055ANZ-ND	Voltage-Feedback Amp Single*	8-Dip	1.82	1.46	1.10	
AD8055ARZ-ND	Voltage-Feedback Amp Single*	8-SOIC	1.82	1.46	1.10	
AD8055ARTZ-REEL7CT-ND	Voltage-Feedback Amp Single*	SOT-23-5	1.55	1.24	.93	
AD8055ARTZ-REEL7TR-ND	Voltage-Feedback Amp Single*	SOT-23-5	2379.17	3,000		
AD8056AR-REEL7TR-ND	Voltage-Feedback Amp Dual	8-SOIC	1538.40	750		
AD8056ARMZ-ND	Voltage-Feedback Amp Dual*	8-MSOP	3.06	2.46	1.91	
AD8056ARZ-ND	Voltage-Feedback Amp Dual*	8-SOIC	3.06	2.46	1.91	
AD8057ARTZ-REEL7CT-ND	Voltage-Feedback Amp Single*	SOT-23-5	1.55	1.24	.93	
AD8057ARTZ-REEL7TR-ND	Voltage-Feedback Amp Single*	SOT-23-5	2379.17	3,000		
AD8057ARZ-ND	Voltage-Feedback Amp Single*	8-SOIC	1.82	1.46	1.10	
AD8058ARMZ-ND	Voltage-Feedback Amp Dual*	8-MSOP	3.06	2.46	1.91	
AD8058ARZ-ND	Voltage-Feedback Amp Dual*	8-SOIC	3.06	2.46	1.91	
AD8061ARTZ-REEL7CT-ND	Voltage-Feedback Amp Rail-to-Rail*	SOT-23-5	1.55	1.24	.93	
AD8061ARTZ-REEL7TR-ND	Voltage-Feedback Amp Rail-to-Rail*	SOT-23-5	2379.17	3,000		
AD8062ARZ-ND	Voltage-Feedback Amp Rail-to-Rail*	8-SOIC	3.06	2.46	1.91	
AD8062ARMZ-R7CT-ND	Voltage-Feedback Amp Rail-to-Rail*	8-MSOP	3.06	2.46	1.91	
AD8062ARMZ-R7TR-ND	Voltage-Feedback Amp Rail-to-Rail*	8-MSOP	1737.91	1,000		
AD8063ARZ-ND	Voltage-Feedback Amp Rail-to-Rail*	8-SOIC	1.80	1.44	1.08	
AD8065ARZ-ND	Voltage-Feedback Amp Single High Speed*	8-SOIC	3.05	2.44	1.90	
AD8065ARTZ-REEL7CT-ND	Voltage-Feedback Amp Single High Speed*	SOT-23-5	2.99	2.40	1.87	
AD8065ARTZ-REEL7TR-ND	Voltage-Feedback Amp Single High Speed*	SOT-23-5	5027.48	3,000		
AD8066ARZ-ND	Voltage-Feedback Amp Dual High Speed*	8-SOIC	4.04	3.53	2.75	
AD8066ARMZ-ND	Voltage-Feedback Amp Dual High Speed*	8-MSOP	4.04	3.53	2.75	
AD8067ARTZ-REEL7CT-ND	Precision FastFET™ Op Amp*	SOT-23-5	4.31	3.45	2.69	
AD8067ARTZ-REEL7TR-ND	Precision FastFET™ Op Amp*	SOT-23-5	7244.23	3,000		
AD8091ARTZ-R7CT-ND	Voltage-Feedback Amp Single Rail-to-Rail*	SOT-23-5	1.45	1.16	.87	
AD8091ARTZ-R7TR-ND	Voltage-Feedback Amp Single Rail-to-Rail*	SOT-23-5	2220.56	3,000		
AD8091ARZ-ND	Voltage-Feedback Amp Single Rail-to-Rail*	8-SOIC	1.47	1.18	.88	
AD8092ARMZ-ND	Voltage-Feedback Amp Dual Rail-to-Rail*	8-MSOP	1.90	1.52	1.14	
AD8092ARZ-ND	Voltage-Feedback Amp Dual Rail-to-Rail*	8-SOIC	1.90	1.52	1.14	
AD8099ACPZ-REEL7CT-ND	Voltage-Feedback High Speed Op Amp*	8-LFSCP	3.72	2.98	2.32	
AD8099ACPZ-REEL7TR-ND	Voltage-Feedback High Speed Op Amp*	8-LFSCP	3159.83	1,500		
AD8099ARZ-ND	Voltage-Feedback High Speed Op Amp*	8-SOIC	3.81	3.05	2.38	
AD8132ARZ-ND	Differential Amp 350MHz High Speed*	8-SOIC	3.18	2.55	1.98	
AD8132ARMZ-ND	Differential Amp 350MHz High Speed*	8-MSOP	3.18	2.55	1.98	
AD8132WARMZ-R7CT-ND	Differential Amp 350MHz High Speed*	8-MSOP	3.40	2.73	2.12	
AD8132WARMZ-R7TR-ND	Differential Amp 350MHz High Speed*	8-MSOP	1927.50	1,000		
AD8137YCPZ-REEL7CT-ND	Differential 12-Bit ADC Driver*	8-LFSCP	2.05	1.64	1.28	
AD8137YCPZ-REEL7TR-ND	Differential 12-Bit ADC Driver*	8-LFSCP	1737.91	1,500		
AD8137YRZ-ND	Differential 12-Bit ADC Driver*	8-SOIC	2.10	1.69	1.31	
AD8138ARZ-ND	Differential ADC Driver Low Distortion*	8-SOIC	6.20	4.96	4.19	
AD8138ARMZ-ND	Differential ADC Driver Low Distortion*	8-MSOP	6.20	4.96	4.19	
AD8139ACPZ-REEL7CT-ND	Differential Low Noise Rail-to-Rail ADC Driver*	8-LFSCP	6.20	4.96	4.19	
AD8139ACPZ-REEL7TR-ND	Differential Low Noise Rail-to-Rail ADC Driver*	8-LFSCP	5808.52	1,500		
AD8139ARZ-ND	Differential Low Noise Rail-to-Rail ADC Driver*	8-SOIC	6.20	4.96	4.19	
AD8397ARZ-ND	Voltage-Feedback Amp Dual Rail-to-Rail*	8-SOIC	4.40	3.53	2.75	
AD8644ARZ-ND	Op Amp 18V Quad 5.5MHz*	14-SOIC	4.54	3.63	2.83	
AD8646ARMZ-REELCT-ND	24MHz Rail-to-Rail Dual Amp*	8-MSOP	1.32	1.06	.80	
AD8646ARZ-ND	24MHz Rail-to-Rail Dual Amp*	8-SOIC	1.32	1.06	.80	
AD9631ARZ-ND	Voltage-Feedback Op Amp Wide Bandwidth*	8-SOIC	8.06	6.45	5.45	
ADA4850-1YCPZ-R2CT-ND	Op Amp High Speed Rail-to-Rail Out*	8-LFSCP	1.45	1.16	.87	
ADA4850-1YCPZ-R2TR-ND	Op Amp High Speed Rail-to-Rail Out*	8-LFSCP	202.39	250		
ADA4850-2YCPZ-R2CT-ND	Op Amp High Speed Rail-to-Rail Out*	16-LFSCP	1.80	1.44	1.08	
ADA4850-2YCPZ-R2TR-ND	Op Amp High Speed Rail-to-Rail Out*	16-LFSCP	251.55	250		
OP42FZ-ND	Op Amp Precision High Speed Fast Set*	8-CDip	6.01	4.82	4.06	
OP42GPZ-ND	Op Amp Precision High Speed Fast Set*	8-Dip	4.06	3.25	2.53	
OP42GSZ-ND	Op Amp Precision High Speed Fast Set*	8-SOIC	4.06	3.25	2.53	
OP162S2Z-ND	Op Amp 15MHz Rail-to-Rail*	8-SOIC	3.05	2.44	1.90	
OP249GPZ-ND	Op Amp Dual JFET Precision High Speed*	8-Dip	3.33	2.67	2.08	
OP249GSZ-ND	Op Amp Dual JFET Precision High Speed*	8-SOIC	3.33	2.67	2.08	
OP462GSZ-ND	Op Amp Quad Rail-to-Rail High Speed*	14-SOIC	6.56	5.25	4.43	
OP467GPZ-ND	Op Amp Quad Precision High Speed*	14-Dip	9.91	8.93	7.92	
OP467GSZ-ND	Op Amp Quad Precision High Speed*	16-SOIC	10.68	9.62	8.53	
OP482GPZ-ND	Op Amp Quad JFET High Speed Low Power*	14-Dip	4.00	3.20	2.49	
OP482GSZ-ND	Op Amp Quad JFET High Speed Low Power*	14-SOIC	3.59	2.87	2.24	

**Instrumentation**

AD521J0Z-ND	Instrumentation Amp Precision*	14-CDip	28.15	26.27	24.39
AD524ADZ-ND	Instrumentation Amp Precision*	16-CDip	16.05	14.98	13.91
AD524ARZ-16-ND	Instrumentation Amp Precision*	16-SOIC	11.63	10.48	9.29
AD524BDZ-ND	Instrumentation Amp Precision*	16-CDip	25.22	23.54	21.86
AD524CDZ-ND	Instrumentation Amp Precision*	16-CDip	38.53	35.96	33.39

ANALOG DEVICES		Digi+Reel® (Cont.)		AMPLIFIERS		
Digi-Key Part No.	Description	Pkg.	Price Each*			
			1	25	100	
AD526ADZ-ND	Gain Amp Software Programmable*	16-Dip	14.69	13.71	12.73	
AD526BDZ-ND	Gain Amp Software Programmable*	16-Dip	17.69	16.51	15.33	
AD526CDZ-ND	Gain Amp Software Programmable*	16-Dip	32.96	30.77	28.57	
AD526J0Z-ND	Gain Amp Software Programmable*	16-Dip	8.63	7.77	6.89	
AD594ADZ-ND	Mono Thermocouple Amp*	TO-116	17.81	16.62	15.44	
AD594CDZ-ND	Mono Thermocouple Amp*	TO-116	25.84	24.12	22.40	
AD595ADZ-ND	Thermocouple Instrumentation Amp*	14-CDip	19.53	18.23	16.93	
AD595CDZ-ND	Thermocouple Instrumentation Amp*	14-CDip	25.84	24.12	22.40	
AD620ANZ-ND	Instrumentation Amp Low Power*	8-Dip	5.72	4.58	3.86	
AD620ARZ-ND	Instrumentation Amp Low Power*	8-SOIC	5.72	4.58	3.86	
AD620ARZ-REEL7CT-ND	Instrumentation Amp Low Power*	8-SOIC	5.72	4.58	3.86	
AD620ARZ-REEL7TR-ND	Instrumentation Amp Low Power*	8-SOIC	2722.54	750		
AD620BNZ-ND	Instrumentation Amp Low Power*	8-Dip	7.15	6.44	5.71	
AD620BRZ-ND	Instrumentation Amp Low Power*	8-SOIC	7.15	6.44	5.71	
AD621ANZ-ND	Instrumentation Amp Low Power Low Drift*	8-Dip	7.35	5.89	4.97	
AD621ARZ-ND	Instrumentation Amp Low Power Low Drift*	8-SOIC	7.35	5.89	4.97	
AD621BNZ-ND	Instrumentation Amp Low Power Low Drift*	8-Dip	9.18	8.27	7.33	
AD621BRZ-ND	Instrumentation Amp Low Power Low Drift*	8-SOIC	9.18	8.27	7.33	
AD622ARZ-ND	Instrumentation Amp*	8-Dip	4.35	3.48	2.94	
AD623ANZ-ND	Instrumentation Amp Rail-to-Rail Out*	8-SOIC	3.33	2.67	2.08	
AD623ARZ-ND	Instrumentation Amp Rail-to-Rail Out*	8-SOIC	2.84	2.28	1.77	
AD623ARZ-REEL7TR-ND	Instrumentation Amp Rail-to-Rail Out*	8-SOIC	1832.70	1,000		
AD623ARMZ-ND	Instrumentation Amp Rail-to-Rail Out*	8-MSOP	2.84	2.28	1.77	
AD623BRZ-ND	Instrumentation Amp Rail-to-Rail Out*	8-SOIC	4.59	3.68	3.11	
AD624ADZ-ND	Instrumentation Amp Precision Low Noise*	16-CDip	19.31	18.02	16.74	
AD624BDZ-ND	Instrumentation Amp Precision Low Noise*	16-CDip	30.04	28.04	26.04	
AD624CDZ-ND	Instrumentation Amp Precision Low Noise*	16-CDip	45.00	42.00	39.00	
AD625ADZ-ND	Instrumentation Amp Programmable Gain*	16-CDip	17.76	16.58	15.39	
AD625J0Z-ND	Instrumentation Amp Programmable Gain*	16-Dip	11.88	10.70	9.49	
AD625KNZ-ND	Instrumentation Amp Programmable Gain*	16-Dip	15.17	14.16	13.15	
AD626ANZ-ND	Differential Amp True Single Supply*	8-Dip	6.03	4.83	4.08	
AD627ANZ-ND	Instrumentation Amp Rail-to-Rail*	8-Dip	4.43	3.55	2.99	
AD627ARZ-ND	Instrumentation Amp Rail-to-Rail*	8-SOIC	4.43	3.55	2.99	
AD627ARZ-R7CT-ND	Instrumentation Amp Rail-to-Rail*	8-SOIC	2767.44	1,000		
AD627ARZ-R7TR-ND	Instrumentation Amp Rail-to-Rail*	8-SOIC	2767.44	1,000		
AD627BNZ-ND	Instrumentation Amp Rail-to-Rail*	8-Dip	6.18	4.95	4.18	
AD627BRZ-ND	Instrumentation Amp Rail-to-Rail*	8-SOIC	6.18	4.95	4.18	
AD628ARZ-ND	Diff. Amp High-Common Mode Voltage Prog.*	8-SOIC	3.55	2.84	2.21	
AD628ARMZ-ND	Diff. Amp High-Common Mode Voltage Prog.*	8-MSOP	3.55	2.84	2.21	
AD629ANZ-ND	Differential Amp High-Common Mode Voltage*	8-Dip	4.92	3.94	3.33	
AD629ARZ-ND	Differential Amp High-Common Mode Voltage*	8-SOIC	4.92	3.94	3.33	
AD629BNZ-ND	Differential Amp High-Common Mode Voltage*	8-Dip	7.58	6.07	5.12	
AD629BRZ-ND	Differential Amp High-Common Mode Voltage*	8-SOIC	7.58	6.07	5.12	
AD5750-1ACPZ-ND	Ind. Current/Voltage Output Driver*	32-LFSCP	4.30	3.44	2.90	
AD5750-1BCPZ-ND	Ind. Current/Voltage Output Driver*	32-LFSCP	5.77	4.62	3.90	
AD5751ACPZ-ND	Ind. Current/Voltage Output Driver*	32-LFSCP	5.27	4.22	3.56	
AD5751BCPZ-ND	Ind. Current/Voltage Output Driver*	32-LFSCP	8.15	6.52	5.50	
AD8220ARMZ-ND	JFET Input Instrumentation Amp*	8-MSOP	4.55	3.65	2.84	
AD8220ARMZ-R7CT-ND	JFET Input Instrumentation Amp*	8-MSOP	4.55	3.65	2.84	
AD8220ARMZ-R7TR-ND	JFET Input Instrumentation Amp*	8-MSOP	2560.53	1,000		
AD8220						