

STMicroelectronics		Digi+Reel (Cont.)		AMPLIFIERS AND LINEAR RoHS Compliant Parts Available		
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
LM346N	497-2980-5-ND	Programmable Quad Bipolar Op Amp	16-Dip	1.26	1.12	.88
LM348DT	497-4049-1-ND	Four UA741 Quad Bipolar Op Amp	14-SOIC	.83	.73	.57
LM348N	497-2981-5-ND	Four UA741 Quad Bipolar Op Amp	14-Dip	1.12	1.00	.79
LM358ADT	497-1590-1-ND	Low Power Dual Op Amp	8-SOIC	.44	.36	.27
LM358ADT	497-1590-2-ND	Low Power Dual Op Amp	8-SOIC	310.31/2,500		
LM358AN	497-2983-5-ND	Low Power Dual Op Amp	8-Dip	.40	.34	.26
LM358APT	497-5367-1-ND	Low Power Dual Op Amp*	8-TSSOP	.54	.43	.32
LM358APT	497-5367-2-ND	Low Power Dual Op Amp*	8-TSSOP	602.20/4,000		
LM358AST	497-7332-1-ND	Low Power Dual Op Amp*	8-Mini SOIC	.46	.37	.28
LM358AST	497-7332-2-ND	Low Power Dual Op Amp*	8-Mini SOIC	522.12/4,000		
LM358DT	497-1591-1-ND	Low Power Dual Op Amp	8-SOIC	.42	.33	.23
LM358DT	497-1591-2-ND	Low Power Dual Op Amp	8-SOIC	238.24/2,500		
LM358N	497-1592-5-ND	Low Power Dual Op Amp	8-Dip	.40	.34	.26
LM358PT	497-6455-1-ND	Low Power Dual Op Amp*	8-TSSOP	.42	.34	.26
LM358PT	497-6455-2-ND	Low Power Dual Op Amp*	8-TSSOP	470.87/4,000		
LM358ST	497-6456-1-ND	Low Power Dual Op Amp*	8-Mini SOIC	.46	.37	.28
LM358ST	497-6456-2-ND	Low Power Dual Op Amp*	8-Mini SOIC	522.12/4,000		
LM358YDT	497-10177-1-ND	Low Power Dual Op Amp*	8-SOIC	.46	.37	.28
LM358YDT	497-10177-2-ND	Low Power Dual Op Amp*	8-SOIC	326.33/2,500		
LM393ADT	497-4267-1-ND	Low Power Dual Voltage Comparator	8-SOIC	.50	.41	.31
LM393ADT	497-4267-2-ND	Low Power Dual Voltage Comparator	8-SOIC	356.36/2,500		
LM393AN	497-6881-5-ND	Low Power Dual Voltage Comparator*	8-Dip	.52	.44	.33
LM393DT	497-1593-1-ND	Low Power Dual Voltage Comparator	8-SOIC	.42	.33	.23
LM393DT	497-1593-2-ND	Low Power Dual Voltage Comparator	8-SOIC	238.24/2,500		
LM393N	497-1594-5-ND	Low Power Dual Voltage Comparator	8-Dip	.40	.34	.26
LM393PT	497-7333-1-ND	Low Power Dual Voltage Comparator*	8-TSSOP	.49	.39	.30
LM393PT	497-7333-2-ND	Low Power Dual Voltage Comparator*	8-TSSOP	547.75/4,000		
LM393ST	497-7334-1-ND	Low Power Dual Voltage Comparator*	8-Mini SOIC	.49	.39	.30
LM393ST	497-7334-2-ND	Low Power Dual Voltage Comparator*	8-Mini SOIC	547.75/4,000		
LM833DT	497-1597-1-ND	Low Noise Dual Op Amp	8-SOIC	528.53/2,500		
LM833N	497-1598-5-ND	Low Noise Dual Op Amp	8-Dip	.62	.55	.43
LM833YDT	497-10220-1-ND	Low Noise Dual Op Amp*	8-SOIC	.52	.46	.36
LM2901DT	497-1555-1-ND	Low Power Quad Voltage Comparator	14-SOIC	.51	.41	.31
LM2901DT	497-1555-2-ND	Low Power Quad Voltage Comparator	14-SOIC	360.36/2,500		
LM2901N	497-1556-5-ND	Low Power Quad Voltage Comparator	14-Dip	.44	.38	.28
LM2901PT	497-6454-1-ND	Low Power Quad Voltage Comparator*	14-TSSOP	.59	.48	.36
LM2901PT	497-6454-2-ND	Low Power Quad Voltage Comparator*	14-TSSOP	416.42/2,500		
LM2901YDT	497-10211-1-ND	Low Power Quad Voltage Comparator*	14-SOIC	.74	.64	.51
LM2901YDT	497-10211-2-ND	Low Power Quad Voltage Comparator*	14-SOIC	610.61/2,500		
LM2901YPT	497-10212-1-ND	Low Power Quad Voltage Comparator*	14-TSSOP	.74	.64	.51
LM2901YPT	497-10212-2-ND	Low Power Quad Voltage Comparator*	14-TSSOP	610.61/2,500		
LM2902AWYDT	497-10426-1-ND	Low Power Quad Op Amp*	14-SOIC	.46	.37	.28
LM2902AWYDT	497-10426-2-ND	Low Power Quad Op Amp*	14-SOIC	326.33/2,500		
LM2902AWYPT	497-10427-1-ND	Low Power Quad Op Amp*	14-TSSOP	.46	.37	.28
LM2902AWYPT	497-10427-2-ND	Low Power Quad Op Amp*	14-TSSOP	326.33/2,500		
LM2902DT	497-1557-1-ND	Low Power Quad Op Amp	14-SOIC	.51	.41	.31
LM2902DT	497-1557-2-ND	Low Power Quad Op Amp	14-SOIC	360.36/2,500		
LM2902N	497-1558-5-ND	Low Power Quad Op Amp	14-Dip	.44	.38	.28
LM2902PT	497-4045-1-ND	Low Power Quad Op Amp	14-TSSOP	.64	.52	.39
LM2902PT	497-4045-2-ND	Low Power Quad Op Amp	14-TSSOP	450.45/2,500		
LM2902WYDT	497-10428-1-ND	Low Power Quad Op Amp*	14-SOIC	.46	.37	.28
LM2902WYDT	497-10428-2-ND	Low Power Quad Op Amp*	14-SOIC	326.33/2,500		
LM2902WYPT	497-10429-1-ND	Low Power Quad Op Amp*	14-TSSOP	.46	.37	.28
LM2902WYPT	497-10429-2-ND	Low Power Quad Op Amp*	14-TSSOP	326.33/2,500		
LM2902YDT	497-10213-1-ND	Low Power Quad Op Amp*	14-SOIC	.67	.59	.46
LM2902YDT	497-10213-2-ND	Low Power Quad Op Amp*	14-SOIC	610.61/2,500		
LM2902YPT	497-10214-1-ND	Low Power Quad Op Amp*	14-TSSOP	.74	.64	.51
LM2902YPT	497-10214-2-ND	Low Power Quad Op Amp*	14-TSSOP	610.61/2,500		
LM2903DT	497-1559-1-ND	Low Power Dual Voltage Comparator	8-SOIC	.51	.41	.31
LM2903DT	497-1559-2-ND	Low Power Dual Voltage Comparator	8-SOIC	360.36/2,500		
LM2903HDT	497-4260-1-ND	Low Power Dual Voltage Comparator	8-SOIC	1.06	.95	.76
LM2903HDT	497-4260-2-ND	Low Power Dual Voltage Comparator	8-SOIC	972.97/2,500		
LM2903H	497-1560-5-ND	Low Power Dual Voltage Comparator	8-Dip	.44	.38	.28
LM2903PT	497-7328-2-ND	Low Power Dual Voltage Comparator*	8-TSSOP	624.62/4,000		
LM2903YDT	497-10215-1-ND	Low Power Dual Voltage Comparator*	8-SOIC	.74	.64	.51
LM2903YDT	497-10215-2-ND	Low Power Dual Voltage Comparator*	8-SOIC	610.61/2,500		
LM2903YPT	497-10216-1-ND	Low Power Dual Voltage Comparator*	8-TSSOP	.74	.64	.51
LM2903YPT	497-10216-2-ND	Low Power Dual Voltage Comparator*	8-TSSOP	976.98/4,000		
LM2904DT	497-1561-1-ND	Low Power Dual Op Amp	8-SOIC	.51	.41	.31
LM2904DT	497-1561-2-ND	Low Power Dual Op Amp	8-SOIC	360.36/2,500		
LM2904N	497-1562-5-ND	Low Power Dual Op Amp	8-Dip	.44	.38	.28
LM2904PT	497-4046-1-ND	Low Power Dual Op Amp	8-TSSOP	.49	.39	.30
LM2904PT	497-4046-2-ND	Low Power Dual Op Amp	8-TSSOP	547.75/4,000		
LM2904ST	497-7816-1-ND	Low Power Dual Op Amp*	8-Mini SOIC	.66	.58	.46
LM2904ST	497-7816-2-ND	Low Power Dual Op Amp*	8-Mini SOIC	877.68/4,000		
LM2904WHDT	497-4261-1-ND	Low Power Dual Op Amp	8-SOIC	1.15	1.03	.82
LM2904WHDT	497-4261-2-ND	Low Power Dual Op Amp	8-SOIC	1059.06/2,500		
LM2904YDT	497-10217-1-ND	Low Power Dual Op Amp*	8-SOIC	.74	.64	.51
LM2904YDT	497-10217-2-ND	Low Power Dual Op Amp*	8-SOIC	610.61/2,500		
LM2904YPT	497-10218-1-ND	Low Power Dual Op Amp*	8-TSSOP	.74	.64	.51
LM2904YPT	497-10218-2-ND	Low Power Dual Op Amp*	8-TSSOP	976.98/4,000		
LM2904YST	497-10219-1-ND	Low Power Dual Op Amp*	8-MSOP	.74	.64	.51
LM2904YST	497-10219-2-ND	Low Power Dual Op Amp*	8-MSOP	976.98/4,000		
LMV3211LT	497-4941-1-ND	Low Power In/Out R/R Op Amp	SOT-23-5	.85	.74	.59
LMV3211LT	497-4941-2-ND	Low Power In/Out R/R Op Amp	SOT-23-5	843.24/3,000		
LMV3211YLT	497-10221-1-ND	Low Power In/Out R/R Op Amp*	SOT-23-5	.74	.65	.50
LMV3211YLT	497-10221-2-ND	Low Power In/Out R/R Op Amp*	SOT-23-5	804.80/3,000		
LMV3211R1LT	497-4942-1-ND	Low Power In/Out R/R Op Amp	SOT-23-5	.85	.74	.59
LMV3211R1LT	497-4942-2-ND	Low Power In/Out R/R Op Amp	SOT-23-5	843.24/3,000		
LMV3241DT	497-4943-1-ND	Low Power Quad In/Out R/R Op Amp	14-SOIC	.88	.79	.63
LMV3241DT	497-4943-2-ND	Low Power Quad In/Out R/R Op Amp	14-SOIC	812.81/2,500		
LMV3241PT	497-4944-1-ND	Low Power Quad In/Out R/R Op Amp	14-TSSOP	.88	.79	.63
LMV3241PT	497-4944-2-ND	Low Power Quad In/Out R/R Op Amp	14-TSSOP	812.81/2,500		
LMV3241YDT	497-10222-1-ND	Low Power Quad In/Out R/R Op Amp*	14-SOIC	.78	.70	.55
LMV3241YDT	497-10222-2-ND	Low Power Quad In/Out R/R Op Amp*	14-SOIC	782.78/2,500		
LMV3241YPT	497-10356-1-ND	Low Power Quad In/Out R/R Op Amp*	14-TSSOP	.74	.65	.50
LMV3241YPT	497-10356-2-ND	Low Power Quad In/Out R/R Op Amp*	14-TSSOP	670.67/2,500		
LMV3311CT	497-10355-1-ND	Low Voltage Comparator*	SC70-5	.61	.53	.41
LMV3311CT	497-10355-2-ND	Low Voltage Comparator*	SC70-5	658.26/3,000		
LMV3311LT	497-10433-1-ND	Low Voltage Comparator*	SOT-23-5	.61	.53	.41
LMV3311LT	497-10433-2-ND	Low Voltage Comparator*	SOT-23-5	658.26/3,000		
LMV3581DT	497-4945-1-ND	Low Power Dual In/Out R/R Op Amp	8-SOIC	.85	.74	.59

STMicroelectronics		Digi+Reel (Cont.)		AMPLIFIERS AND LINEAR RoHS Compliant Parts Available		
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
LMV3581DT	497-4945-2-ND	Low Power Dual In/Out R/R Op Amp	8-SOIC	702.70/2,500		
LMV3581PT	497-4946-1-ND	Low Power Dual In/Out R/R Op Amp	8-TSSOP	.68	.59	.47
LMV3581PT	497-4946-2-ND	Low Power Dual In/Out R/R Op Amp	8-TSSOP	900.10/4,000		
LS2040CDT	497-7823-1-ND	High Performance Dual Op Amp*	8-SOIC	1.62	1.39	1.14
LS2040CDT	497-7823-2-ND	High Performance Dual Op Amp*	8-SOIC	1561.56/2,500		
LS2040CN	497-7335-5-ND	High Performance Dual Op Amp*	8-Dip	1.17	1.06	.85
LS2040DT	497-7824-1-ND	High Performance Dual Op Amp*	8-SOIC	1.62	1.39	1.14
LS2040DT	497-7824-2-ND	High Performance Dual Op Amp*	8-SOIC	1561.56/2,500		
LS2040YDT	497-10223-1-ND	High Performance Dual Op Amp*	8-SOIC	1.72	1.56	1.25
LS2040YDT	497-10223-2-ND	High Performance Dual Op Amp*	8-SOIC	1873.87/2,500		
LS4040CDT	497-7825-1-ND	High Performance Quad Op Amp*	14-SOIC	1.66	1.50	1.21
LS4040CDT	497-7825-2-ND	High Performance Quad Op Amp*	14-SOIC	2214.21/2,500		
LS4040CN	497-7336-5-ND	High Performance Quad Op Amp*	14-Dip	1.66	1.50	1.21
LS4040DT	497-7826-1-ND	High Performance Quad Op Amp*	14-SOIC	2.51	2.15	1.76
LS4040DT	497-7826-2-ND	High Performance Quad Op Amp*	14-SOIC	2414.41/2,500		
LS4040IN	497-7337-5-ND	High Performance Quad Op Amp*	14-Dip	1.06	.94	.74
MC1458DT	497-1948-1-ND	High Performance Dual Op Amp	8-SOIC	.65	.52	.39
MC1458DT	497-1948-2-ND	High Performance Dual Op Amp	8-SOIC	456.46/2,500		
MC1458IDT	497-7405-5-ND	High Performance Dual Op Amp*	8-SOIC	.58	.51	.39
MC1458IN	497-1949-5-ND	High Performance Dual Op Amp	8-Dip	54	48	37
MC1458N	497-7406-5-ND	High Performance Dual Op Amp*	8-Dip	52	44	33
MC1558N	497-7407-5-ND	High Performance Dual Op Amp*	8-Dip	54	48	37
MC3303DT	497-4050-1-ND	Low Power Quad Bipolar Op Amp	14-SOIC	92	83	66
MC3303DT	497-4050-2-ND	Low Power Quad Bipolar Op Amp	14-SOIC	848.85/2,500		
MC3303PT	497-7848-1-ND	Low Power Quad Bipolar Op Amp*	14-TSSOP	.77	.69	.55
MC3303PT	497-7848-2-ND	Low Power Quad Bipolar Op Amp*	14-TSSOP	706.71/2,500		
MC3403D	497-1959-5-ND	Low Power Quad Bipolar Op Amp	14-SOIC	88	79	62
MC3403DT	497-1959-1-ND	Low Power Quad Bipolar Op Amp	14-SOIC	57	50	40
MC3403N	497-7411-5-ND	Low Power Quad Bipolar Op Amp*	14-Dip	72	64	51
MC4558CDT	497-4051-1-ND	Wide Bandwidth Dual Bipolar Op Amp	8-SOIC	.55	.45	.34
MC4558CDT	497-4051-2-ND	Wide Bandwidth Dual Bipolar Op Amp	8-SOIC	390.39/2,500		
MC4558CN	497-1960-5-ND	Wide Bandwidth Dual Bipolar Op Amp	8-Dip	50	45	35
MC4558CPT	497-7853-1-ND	Wide Bandwidth Dual Bipolar Op Amp*	8-TSSOP	70	61	49
MC4558CPT	497-7853-2-ND	Wide Bandwidth Dual Bipolar Op Amp*	8-TSSOP	928.93/4,000		
MC4558IDT	497-1961-1-ND	Wide Bandwidth Dual Bipolar Op Amp	8-SOIC	.82	.71	.56
MC4558IDT	497-1961-2-ND	Wide Bandwidth Dual Bipolar Op Amp	8-SOIC	670.67/2,500		
MC33078DT	497-1952-1-ND	Low Noise Dual Op Amp	8-SOIC	.82	.71	.56
MC33078DT	497-1952-2-ND	Low Noise Dual Op Amp	8-SOIC	670.67/2,500		
MC33078N	497-1953-5-ND	Low Noise Dual Op Amp	8-Dip	.78	.68	.53
MC33078YDT	497-10224-1-ND	Low Noise Dual Op Amp*	8-SOIC	.85	.76	.61
MC33078YDT	497-10224-2-ND	Low Noise Dual Op Amp*	8-SOIC	782.78/2,500		
MC33079DT	497-1954-1-ND	Low Noise Quad Op Amp	14-SOIC	.86	.78	.62
MC33079DT	497-1954-2-ND	Low Noise Quad Op Amp	14-SOIC	796.80/2,500		
MC33079YDT	497-10225-1-ND	Low Noise Quad Op Amp*	14-SOIC	1.03	.92	.73
MC33079YDT	497-10225-2-ND	Low Noise Quad Op Amp*	14-SOIC	940.94/2,500		
MC33171DT	497-1956-5-ND	Low Power Single Bipolar Op Amp	8-SOIC	.86	.76	.60
MC33171DT	497-1956-1-ND	Low Power Single Bipolar Op Amp	8-SOIC	93	83	66
MC33171DT	497-1956-2-ND	Low Power Single Bipolar Op Amp	8-SOIC	854.85/2,500		
MC33171N	497-7408-5-ND	Low Power Single Bipolar Op Amp*	8-Dip	70	62	49
MC33172DT	497-1957-1-ND	Low Power Dual Bipolar Op Amp	8-SOIC	.83	.75	.60
MC33172DT	497-1957-2-ND	Low Power Dual Bipolar Op Amp	8-SOIC	764.76/2,500		
MC33172N	497-7409-5-ND	Low Power Dual Bipolar Op Amp*	8-Dip	1.23	1.10	.87
MC33174DT	49					