

Input Voltage Range (VDC)	Output Voltage @ Maximum Current (VDC @ A)		Output Power Maximum (W)	Mounting Type	Modular Orientation	Digi-Key Part No.	Price Each			Texas Instruments Part No.
	Output #1	Output #2					1	25	100	
8.0 - 18.0	-13.6 - 9.0 @ 2.0	—	18.0	TH	Vertical	PT6643P-ND	36.95	31.96	29.97	PT6643P
8.0 - 21.0	-10.2 - 6.0 @ 2.5	—	15.0	TH	Horizontal	296-20194-ND	36.95	31.96	29.97	PT6644D
8.0 - 21.0	-10.2 - 6.0 @ 2.5	—	15.0	SMT	Horizontal	296-20195-ND	36.95	31.96	29.97	PT6644E
8.0 - 15.0	-17.0 - -10.0 @ 1.5	—	15.0	SMT	Horizontal	296-20197-ND	36.95	31.96	29.97	PT6645E
8.0 - 15.0	-17.0 - -10.0 @ 1.5	—	15.0	TH	Vertical	296-20198-ND	36.95	31.96	29.97	PT6645P
10.8 - 13.2	1.3 - 3.5 @ 14.0	—	49.0	TH	Horizontal	PT6721A-ND	41.19	35.63	33.40	PT6721A
10.8 - 13.2	1.3 - 3.5 @ 14.0	—	49.0	TH	Vertical	296-20205-ND	41.19	35.63	33.40	PT6721N
10.8 - 13.2	1.1 - 1.85 @ 14.0	—	25.9	TH	Horizontal	296-20206-ND	41.19	35.63	33.40	PT6722A
10.8 - 13.2	2.5 @ 10.5	1.8 @ 2.50	30.8	SMT	Horizontal	296-20240-ND	55.27	48.77	46.33	PT6981C
10.8 - 13.2	3.3 @ 10.5	2.5 @ 2.25	40.3	SMT	Horizontal	296-20241-ND	44.24	39.04	37.09	PT6982C
10.8 - 13.2	3.3 @ 10.5	2.5 @ 2.25	40.3	TH	Vertical	296-20242-ND	44.24	39.04	37.09	PT6982N
10.8 - 13.2	3.3 @ 9.5	1.8 @ 2.0	35.0	TH	Horizontal	296-20243-ND	44.24	39.04	37.09	PT6983A
10.8 - 13.2	3.3 @ 9.5	1.8 @ 2.0	35.0	SMT	Horizontal	296-20244-ND	55.75	49.84	47.31	PT6983C
9.0 - 15.0	-12.0 @ 1.0	—	12.0	TH	Horizontal	296-20269-ND	31.10	26.90	25.22	PT78NR212H
9.0 - 15.0	-12.0 @ 1.0	—	12.0	SMT	Horizontal	296-20270-ND	31.10	26.90	25.22	PT78NR212S
9.0 - 15.0	-12.0 @ 1.0	—	12.0	TH	Vertical	296-20271-ND	31.10	26.90	25.22	PT78NR212V
9.0 - 15.0	-15.0 @ 0.80	—	12.0	TH	Horizontal	296-20272-ND	26.93	22.90	21.21	PT78NR215H
9.0 - 15.0	-15.0 @ 0.80	—	12.0	SMT	Horizontal	296-20273-ND	26.93	22.90	21.21	PT78NR215S
9.0 - 15.0	-15.0 @ 0.80	—	12.0	TH	Vertical	296-20274-ND	26.93	22.90	21.21	PT78NR215V
9.0 - 15.0	-5.2 @ 2.0	—	10.4	SMT	Horizontal	296-20275-ND	26.93	22.90	21.21	PT78NR252S
9.0 - 15.0	-5.2 @ 2.0	—	10.4	TH	Vertical	296-20276-ND	26.93	22.90	21.21	PT78NR252V
10.8 - 13.2	1.3 - 3.5 @ 30.0	—	105.0	TH	Horizontal	PT8121A-ND	70.11	62.45	59.17	PTH1200LAH
10.8 - 13.2	1.075 - 1.85 @ 30.0	—	55.5	TH	Horizontal	296-20304-ND	80.21	71.45	67.69	PTH1212A
10.8 - 13.2	1.05 - 1.825 @ 30.0	—	54.8	TH	Horizontal	296-20305-ND	80.21	71.45	67.69	PTH1244A
10.8 - 13.2	0.8 - 1.8 @ 6.0	—	10.8	TH	Horizontal	296-20446-ND	15.72	13.22	12.15	PTH1200LAH
10.8 - 13.2	0.8 - 1.8 @ 6.0	—	10.8	SMT	Horizontal	296-20447-ND	15.72	13.22	12.15	PTH1200LAS
10.8 - 13.2	0.8 - 1.8 @ 6.0	—	10.8	SMT	Horizontal	296-20448-ND	15.72	13.22	12.15	PTH1200LAZ
10.8 - 13.2	1.2 - 5.5 @ 6.0	—	33.0	TH	Horizontal	296-20449-ND	12.54	10.55	9.70	PTH1200WAH
10.8 - 13.2	1.2 - 5.5 @ 6.0	—	33.0	SMT	Horizontal	296-20450-ND	12.54	10.55	9.70	PTH1200WAS
10.8 - 13.2	0.8 - 1.8 @ 12.0	—	21.6	TH	Horizontal	296-20451-ND	22.77	19.36	17.93	PTH1201LAH
10.8 - 13.2	0.8 - 1.8 @ 12.0	—	21.6	SMT	Horizontal	296-20452-ND	22.77	19.36	17.93	PTH1201LAS
10.8 - 13.2	0.8 - 1.8 @ 12.0	—	21.6	SMT	Horizontal	296-20453-ND	22.77	19.36	17.93	PTH1201LAZ
10.8 - 13.2	1.2 - 5.5 @ 12.0	—	66.0	TH	Horizontal	296-20454-ND	18.21	15.48	14.34	PTH1201WAH
10.8 - 13.2	1.2 - 5.5 @ 12.0	—	66.0	SMT	Horizontal	296-20455-ND	18.21	15.48	14.34	PTH1201WAS
10.8 - 13.2	1.2 - 5.5 @ 12.0	—	66.0	SMT	Horizontal	296-20456-ND	18.21	15.48	14.34	PTH1201WAZ
10.8 - 13.2	0.55 - 1.8 @ 12.0	—	21.6	TH	Horizontal	296-20457-ND	22.77	19.36	17.93	PTH1201OAH
10.8 - 13.2	0.55 - 1.8 @ 12.0	—	21.6	SMT	Horizontal	296-20458-ND	22.77	19.36	17.93	PTH1201OAS
10.8 - 13.2	0.55 - 1.8 @ 12.0	—	21.6	SMT	Horizontal	296-20459-ND	22.77	19.36	17.93	PTH1201OAZ
10.8 - 13.2	0.8 - 1.8 @ 18.0	—	32.4	TH	Horizontal	296-20460-ND	23.54	20.02	18.55	PTH1202LAH
10.8 - 13.2	0.8 - 1.8 @ 18.0	—	32.4	SMT	Horizontal	296-20461-ND	23.54	20.02	18.55	PTH1202LAS
10.8 - 13.2	0.8 - 1.8 @ 18.0	—	32.4	SMT	Horizontal	296-20462-ND	23.54	20.02	18.55	PTH1202LAZ
10.8 - 13.2	1.2 - 5.5 @ 18.0	—	99.0	TH	Horizontal	296-20463-ND	23.54	20.02	18.55	PTH1202WAH
10.8 - 13.2	1.2 - 5.5 @ 18.0	—	99.0	SMT	Horizontal	296-20464-ND	23.54	20.02	18.55	PTH1202WAS
10.8 - 13.2	1.2 - 5.5 @ 18.0	—	99.0	SMT	Horizontal	296-20465-ND	23.54	20.02	18.55	PTH1202WAZ
10.2 - 13.8	0.8 - 1.8 @ 26.0	—	46.8	TH	Horizontal	296-20466-ND	30.85	26.69	25.02	PTH1203LAH
10.2 - 13.8	0.8 - 1.8 @ 26.0	—	46.8	SMT	Horizontal	296-20467-ND	30.85	26.69	25.02	PTH1203LAS
10.2 - 13.8	0.8 - 1.8 @ 26.0	—	46.8	SMT	Horizontal	296-20468-ND	30.85	26.69	25.02	PTH1203LAZ
10.2 - 13.8	1.2 - 5.5 @ 26.0	—	143.0	TH	Horizontal	296-20469-ND	30.85	26.69	25.02	PTH1203WAH
10.2 - 13.8	1.2 - 5.5 @ 26.0	—	143.0	SMT	Horizontal	296-20470-ND	30.85	26.69	25.02	PTH1203WAS
10.2 - 13.8	1.2 - 5.5 @ 26.0	—	143.0	SMT	Horizontal	296-20471-ND	30.85	26.69	25.02	PTH1203WAZ
8.0 - 14.0	0.8 - 5.5 @ 50.0	—	275.0	TH	Horizontal	296-26313-ND	46.70	41.21	39.15	PTH1204WAD
8.0 - 14.0	0.8 - 5.5 @ 50.0	—	275.0	TH	Horizontal	296-20472-ND	46.70	41.21	39.15	PTH1204WAH
8.0 - 14.0	0.8 - 5.5 @ 50.0	—	275.0	SMT	Horizontal	296-20473-ND	46.70	41.21	39.15	PTH1204WAS
8.0 - 14.0	0.8 - 5.5 @ 50.0	—	275.0	SMT	Horizontal	296-20985-ND	46.70	41.21	39.15	PTH1204WAZ
10.8 - 13.2	0.8 - 1.8 @ 6.0	—	10.8	TH	Horizontal	296-20474-ND	11.92	10.03	9.22	PTH1205LAH
10.8 - 13.2	0.8 - 1.8 @ 6.0	—	10.8	SMT	Horizontal	296-20475-ND	11.92	10.03	9.22	PTH1205LAS
10.8 - 13.2	0.8 - 1.8 @ 6.0	—	10.8	SMT	Horizontal	296-20476-ND	11.92	10.03	9.22	PTH1205LAZ
10.8 - 13.2	0.8 - 1.8 @ 6.0	—	10.8	SMT	Horizontal	296-26314-ND	11.92	10.03	9.22	PTH1205WAD
10.8 - 13.2	1.2 - 5.5 @ 6.0	—	33.0	TH	Horizontal	296-20477-ND	11.92	10.03	9.22	PTH1205WAH
10.8 - 13.2	1.2 - 5.5 @ 6.0	—	33.0	SMT	Horizontal	296-20478-ND	11.92	10.03	9.22	PTH1205WAS
10.8 - 13.2	1.2 - 5.5 @ 6.0	—	33.0	SMT	Horizontal	296-20479-ND	11.92	10.03	9.22	PTH1205WAZ
10.8 - 13.2	0.55 - 1.8 @ 6.0	—	10.8	TH	Horizontal	296-20480-ND	14.94	12.57	11.55	PTH1205OAH
10.8 - 13.2	0.55 - 1.8 @ 6.0	—	10.8	SMT	Horizontal	296-20481-ND	14.94	12.57	11.55	PTH1205OAS
10.8 - 13.2	0.55 - 1.8 @ 6.0	—	10.8	SMT	Horizontal	296-20482-ND	14.94	12.57	11.55	PTH1205OAZ
10.8 - 13.2	0.8 - 1.8 @ 10.0	—	18.0	TH	Horizontal	296-20483-ND	16.92	14.23	13.08	PTH1206LAH
10.8 - 13.2	0.8 - 1.8 @ 10.0	—	18.0	SMT	Horizontal	296-20484-ND	16.92	14.23	13.08	PTH1206LAS
10.8 - 13.2	0.8 - 1.8 @ 10.0	—	18.0	SMT	Horizontal	296-20485-ND	16.92	14.23	13.08	PTH1206LAZ
10.8 - 13.2	1.2 - 5.5 @ 10.0	—	55.0	TH	Horizontal	296-26316-ND	16.92	14.23	13.08	PTH1206WAD
10.8 - 13.2	1.2 - 5.5 @ 10.0	—	55.0	TH	Horizontal	296-20486-ND	16.92	14.23	13.08	PTH1206WAH
10.8 - 13.2	1.2 - 5.5 @ 10.0	—	55.0	SMT	Horizontal	296-20487-ND	16.92	14.23	13.08	PTH1206WAS
10.8 - 13.2	1.2 - 5.5 @ 10.0	—	55.0	SMT	Horizontal	296-20488-ND	16.92	14.23	13.08	PTH1206WAZ
10.8 - 13.2	0.55 - 1.8 @ 10.0	—	18.0	TH	Horizontal	296-20489-ND	19.23	16.35	15.15	PTH1206OAH
10.8 - 13.2	0.55 - 1.8 @ 10.0	—	18.0	SMT	Horizontal	296-20490-ND	19.23	16.35	15.15	PTH1206OAS
10.8 - 13.2	0.55 - 1.8 @ 10.0	—	18.0	SMT	Horizontal	296-20491-ND	19.23	16.35	15.15	PTH1206OAZ
7.0 - 28.7	-15.0 - -3.0 @ 1.5	—	9.0	TH	Horizontal	296-20501-ND	14.54	12.23	11.24	PTN78000AAH
7.0 - 28.7	-15.0 - -3.0 @ 1.5	—	9.0	SMT	Horizontal	296-20502-ND	14.54	12.23	11.24	PTN78000AAZ
7.0 - 36.0	2.5 - 12.6 @ 1.5	—	18.9	TH	Horizontal	296-20506-ND	14.54	12.23	11.24	PTN78000WAH
7.0 - 36.0	2.5 - 12.6 @ 1.5	—	18.9	SMT	Horizontal	296-20507-ND	14.54	12.23	11.24	PTN78000WAS
7.0 - 36.0	2.5 - 12.6 @ 1.5	—	18.9	SMT	Horizontal	296-20508-ND	14.54	12.23	11.24	PTN78000WAZ
9.0 - 29.0	-15.0 - -3.0 @ 4.0	—	25.0	TH	Horizontal	296-20509-ND	30.98	26.34	24.40	PTN78020AAH
9.0 - 29.0	-15.0 - -3.0 @ 4.0	—	25.0	SMT	Horizontal	296-20510-ND	30.98	26.34	24.40	PTN78020AAZ
7.0 - 36.0	2.5 - 12.6 @ 6.0	—	90.0	TH	Horizontal	296-20515-ND	24.78	21.07	19.52	PTN78020WAH
7.0 - 36.0	2.5 - 12.6 @ 6.0	—	90.0	SMT	Horizontal	296-20516-ND	24.78	21.07	19.52	PTN78020WAS
7.0 - 36.0	2.5 - 12.6 @ 6.0	—	90.0	SMT	Horizontal	296-20517-ND	24.78	21.07	19.52	PTN78020WAZ
9.0 - 28.7	-15.0 - -3.0 @ 3.0	—	15.0	TH	Horizontal	296-20518-ND	22.72	19.32	17.90	PTN78060AAH
9.0 - 28.7	-15.0 - -3.0 @ 3.0	—	15.0	SMT	Horizontal	296-20519-ND	22.72	19.32	17.90	PTN78060AAS
9.0 - 28.7	-15.0 - -3.0 @ 3.0	—	15.0	SMT	Horizontal	296-20520-ND	22.72	19.32	17.90	PTN78060AAZ
7.0 - 36.0	2.5 - 12.6 @ 3.0	—	45.0	TH	Horizontal	296-20523-ND	18.17	15.45	14.32	PTN78060WAH
7.0 - 36.0	2.5 - 12.6 @ 3.0	—	45.0	SMT	Horizontal	296-20524-ND	18.17	15.45	14.32	PTN78060WAS
7.0 - 36.0	2.5 - 12.6 @ 3.0	—	45.0	SMT	Horizontal	296-20525-ND	18.17	15.45	14.32	PTN78060WAZ
7.0 - 36.0	2.5 - 12.6 @ 3.0	—	37.8	SMT	Horizontal	296-26317-1-ND	18.17	16.36	15.00	PTN78060WAZT
7.0 - 36.0	2.5 - 12.6 @ 3.0	—	37.8	SMT	Horizontal	296-26317-2-ND	18.17	16.36	15.00	PTN78060WAZT
8.0 - 14.0	0.8 - 3.6 @ 50.0	—	180.0	TH	Vertical	296-20527-ND	56.65	50.65	48.07	PTV08040WAD
8.0 - 14.0	0.8 - 3.6 @ 50.0	—	180.0	TH	Vertical	296-20528-ND	56.65	50.65	48.07	PTV08040WAH
10.8 - 13.2	0.8 - 1.8 @ 8.0	—	14.4	TH	Vertical	296-20989-ND	14.94	12.57	11.55	PTV12010LAD
10.8 - 13.2	1.2 - 5.5 @ 8.0	—	44.0	TH	Vertical	296-20531-ND	14.94	12.57	11.55	PTV12010WAH
10.8 - 13.2	0.8 - 1.8 @ 16.0	—	28.8	TH	Vertical	296-20532-ND	18.21	15.48	14.34	PTV12020LAH