

TS (V c.c.)	Cap. (µF)	Courant de fuite (µA)	Tan δ max	Courant ondulé (mA) eff	Dimensions (mm)				N° de référence Digi-Key	Prix					N° de référence Panasonic	
					øD	L	P	ød		1	10	100	500	1 000		5 000
35	10	3.5	0.14	60	5	11	2.0	0.5	P5161-ND	.13	.65	4.41	14.94	22.87	19.49/M	ECA-1VM100
	22	7.7	0.14	95	5	11	2.0	0.5	P5162-ND	.13	.65	4.41	14.94	22.87	19.49/M	ECA-1VM220
	33	11.5	0.14	110	5	11	2.0	0.5	P5163-ND	.15	.74	4.96	16.81	25.41	22.03/M	ECA-1VM330
	47	16.4	0.14	130	5	11	2.0	0.5	P5164-ND	.15	.74	4.96	16.81	25.41	22.03/M	ECA-1VM470
	100	35.0	0.14	210	6.3	11.2	2.5	0.5	P5165-ND	.17	.86	6.11	21.08	33.03	28.80/M	ECA-1VM101
	220	77.0	0.14	350	8	11.5	3.5	0.6	P5166-ND	.22	1.25	8.96	32.25	49.97	46.59/M	ECA-1VM221
	330	115.5	0.14	440	10	12.5	5.0	0.6	P5167-ND	.30	1.95	13.89	50.01	77.92	72.00/M	ECA-1VM331
	470	164.5	0.14	550	10	16	5.0	0.6	P5168-ND	.36	2.24	16.05	57.78	89.78	83.86/M	ECA-1VM471
	1000	350.0	0.14	900	12.5	20	5.0	0.6	P5169-ND	.63	4.35	31.91	115.41	182.95	176.18/M	ECA-1VM102
	2200	770.0	0.16	1250	16	25	7.5	0.8	P5170-ND	1.07	7.04	52.77	187.63	311.70	299.84/M	ECA-1VM222
3300	1155.0	0.18	1400	16	31.5	7.5	0.8	P5171-ND	1.25	8.50	64.19	240.70	417.57	404.02/M	ECA-1VM332	
4700	1645.0	0.20	1600	18	35.5	7.5	0.8	P5172-ND	2.05	12.43	93.80	351.74	609.84	591.21/M	ECA-1VM472	
50	0.33	3.0	0.12	4.4	5	11	2.0	0.5	P5349-ND†	.18	1.13	7.61	25.79	38.96	33.04/M	ECA-1HMR33
	0.47	3.0	0.12	5	5	11	2.0	0.5	P5173-ND†	.13	.65	4.41	14.94	22.87	19.49/M	ECA-1HMR47
	1.0	3.0	0.12	10	5	11	2.0	0.5	P5174-ND†	.13	.65	4.41	14.94	22.87	19.49/M	ECA-1HM010
	2.2	3.0	0.12	20	5	11	2.0	0.5	P5175-ND†	.13	.65	4.41	14.94	22.87	19.49/M	ECA-1HM2R2
	3.3	3.0	0.12	35	5	11	2.0	0.5	P5176-ND†	.13	.65	4.41	14.94	22.87	19.49/M	ECA-1HM3R3
	4.7	3.0	0.12	45	5	11	2.0	0.5	P5177-ND†	.13	.65	4.41	14.94	22.87	19.49/M	ECA-1HM4R7
	10	5.0	0.12	65	5	11	2.0	0.5	P5178-ND†	.13	.65	4.41	14.94	22.87	19.49/M	ECA-1HM100
	22	11.0	0.12	100	5	11	2.0	0.5	P5179-ND†	.15	.74	4.96	16.81	25.41	22.03/M	ECA-1HM220
	33	16.5	0.12	110	5	11	2.0	0.5	P5180-ND†	.15	.74	4.96	16.81	25.41	22.03/M	ECA-1HM330
	47	23.5	0.12	130	6.3	11.2	2.5	0.5	P5181-ND†	.21	1.02	6.88	23.30	35.57	29.65/M	ECA-1HM470
	100	50.0	0.12	250	8	11.5	3.5	0.6	P5182-ND†	.25	1.40	9.85	34.04	53.36	46.59/M	ECA-1HM101
	220	110.0	0.12	400	10	12.5	5.0	0.6	P5183-ND†	.31	2.08	14.81	53.28	83.01	77.08/M	ECA-1HM221
	330	165.0	0.12	500	10	16	5.0	0.6	P5184-ND†	.36	2.17	15.94	57.67	91.48	88.09/M	ECA-1HM331
	470	235.0	0.12	650	10	20	5.0	0.6	P5185-ND†	.44	2.96	21.76	78.69	125.36	120.28/M	ECA-1HM471
	1000	500.0	0.12	1050	12.5	25	5.0	0.6	P5186-ND†	.87	5.18	38.88	138.23	229.54	221.07/M	ECA-1HM102
	2200	1100.0	0.14	1300	16	31.5	7.5	0.8	P5187-ND†	1.57	9.16	69.12	259.18	448.91	435.36/M	ECA-1HM222
	3300	1650.0	0.16	1500	18	35.5	7.5	0.8	P5188-ND†	2.13	12.43	93.80	351.74	609.84	591.21/M	ECA-1HM332
	63	10	6.3	0.11	70	5	11	2.0	0.5	P5189-ND	.14	.74	4.96	16.81	25.41	22.03/M
22		13.8	0.11	105	5	11	2.0	0.5	P5190-ND	.15	.74	4.96	16.81	25.41	22.03/M	ECA-1JM220
33		20.7	0.11	130	6.3	11.2	2.5	0.5	P5191-ND	.16	.86	6.11	21.08	33.03	28.80/M	ECA-1JM330
47		29.6	0.11	160	6.3	11.2	2.5	0.5	P5192-ND	.18	.94	6.62	22.85	36.42	31.34/M	ECA-1JM470
100		63.0	0.11	270	8	11.5	3.5	0.6	P5193-ND	.26	1.52	10.80	38.88	60.14	55.91/M	ECA-1JM101
220		138.6	0.11	450	10	16	5.0	0.6	P5194-ND	.38	2.17	15.94	57.67	91.48	88.09/M	ECA-1JM221
330		207.9	0.11	550	10	20	5.0	0.6	P5195-ND	.53	3.08	22.63	81.86	129.59	125.36/M	ECA-1JM331
470		296.1	0.11	750	12.5	20	5.0	0.6	P5196-ND	.78	4.45	33.33	118.51	197.35	189.73/M	ECA-1JM471
1000		630.0	0.11	1100	16	25	7.5	0.8	P5197-ND	1.19	7.04	52.77	187.63	311.70	299.84/M	ECA-1JM102
2200		1386.0	0.13	1400	18	35.5	7.5	0.8	P5198-ND	2.24	13.09	98.74	370.29	642.03	621.70/M	ECA-1JM222
100	0.47	3.0	0.10	10	5	11	2.0	0.5	P5199-ND	.15	.77	5.18	17.52	27.10	22.87/M	ECA-2AMR47
	1.0	3.0	0.10	20	5	11	2.0	0.5	P5305-ND	.15	.77	5.18	17.52	27.10	22.87/M	ECA-2AM010
	2.2	3.0	0.10	30	5	11	2.0	0.5	P5306-ND	.16	.77	5.18	17.52	27.10	22.87/M	ECA-2AM2R2
	3.3	3.3	0.10	40	5	11	2.0	0.5	P5307-ND	.16	.77	5.18	17.52	27.10	22.87/M	ECA-2AM3R3
	4.7	4.7	0.10	50	5	11	2.0	0.5	P5308-ND	.16	.77	5.18	17.52	27.10	22.87/M	ECA-2AM4R7
	10	10.0	0.10	70	5	11	2.0	0.5	P5309-ND	.16	.80	5.35	18.14	27.95	23.72/M	ECA-2AM100
	22	22.0	0.10	115	6.3	11.2	2.5	0.5	P5310-ND	.18	.94	6.62	22.85	36.42	31.34/M	ECA-2AM220
	33	33.0	0.10	145	8	11.5	3.5	0.6	P5311-ND	.32	1.69	11.88	41.04	65.22	55.91/M	ECA-2AM330
	47	47.0	0.10	180	8	11.5	3.5	0.6	P5312-ND	.27	1.60	11.42	41.09	63.53	59.29/M	ECA-2AM470
	100	100.0	0.10	350	10	16	5.0	0.6	P5313-ND	.41	2.45	17.97	65.02	103.33	99.10/M	ECA-2AM101
	220	220.0	0.10	550	12.5	20	5.0	0.6	P5314-ND	.80	4.62	34.70	123.39	204.97	193.36/M	ECA-2AM221
	330	330.0	0.10	700	12.5	25	5.0	0.6	P5315-ND	1.02	5.92	44.43	157.95	262.57	252.41/M	ECA-2AM331
	470	470.0	0.10	900	16	25	7.5	0.8	P5316-ND	1.35	7.85	59.24	222.15	385.39	373.53/M	ECA-2AM471
	1000	1000.0	0.10	1300	18	35.5	7.5	0.8	P5317-ND	2.46	15.04	113.55	425.81	737.74	715.72/M	ECA-2AM102
160	1.0	19.6	0.16	36	6.3	11.2	2.5	0.5	P5318-ND	.27	1.16	8.16	28.16	44.89	38.97/M	ECA-2CM010
	2.2	31.1	0.16	53	6.3	11.2	2.5	0.5	P5319-ND	.28	1.16	8.16	28.16	44.89	38.97/M	ECA-2CM2R2
	3.3	41.6	0.16	66	6.3	11.2	2.5	0.5	P5320-ND	.25	1.04	7.41	26.68	41.50	38.97/M	ECA-2CM3R3
	4.7	55.1	0.16	78	6.3	11.2	2.5	0.5	P5321-ND	.26	1.04	7.41	26.68	41.50	38.97/M	ECA-2CM4R7
	10	103.0	0.16	105	10	12.5	5.0	0.6	P5322-ND	.36	1.95	13.89	50.01	77.92	72.00/M	ECA-2CM100
	22	221.0	0.16	175	10	16	5.0	0.6	P5323-ND	.43	2.17	15.94	57.67	91.48	88.09/M	ECA-2CM220
	33	326.0	0.16	235	10	20	5.0	0.6	P5324-ND	.58	2.57	18.85	68.18	108.42	104.19/M	ECA-2CM330
	47	461.0	0.16	320	12.5	20	5.0	0.6	P5325-ND	.84	4.07	30.55	108.62	180.41	173.64/M	ECA-2CM470
	100	970.0	0.16	515	12.5	25	5.0	0.6	P5326-ND	1.05	5.18	38.88	138.23	229.54	221.07/M	ECA-2CM101
	220	2122.0	0.16	830	16	31.5	7.5	0.8	P5327-ND	1.52	8.17	61.71	231.43	401.48	388.78/M	ECA-2CM221
330	3178.0	0.16	1090	18	31.5	7.5	0.8	P5328-ND	2.60	15.69	118.48	444.29	769.92	746.21/M	ECA-2CM331	
470	4522.0	0.16	1440	18	40	7.5	0.8	P5329-ND	3.52	20.61	155.51	583.16	1010.47	979.98/M	ECA-2CM471	
250	1.0	25.0	0.18	34	6.3	11.2	2.5	0.5	P5330-ND	.25	1.04	7.41	26.68	41.50	38.97/M	ECA-2EM010
	2.2	43.0	0.18	50	6.3	11.2	2.5	0.5	P5331-ND	.25	1.04	7.41	26.68	41.50	38.97/M	ECA-2EM2R2
	3.3	59.5	0.18	72	8	11.5	3.5	0.6	P5332-ND	.30	1.52	10.80	38.88	60.14	55.91/M	ECA-2EM3R3
	4.7	80.5	0.18	86	8	11.5	3.5	0.6	P5333-ND	.35	1.52	10.80	38.88	60.14	55.91/M	ECA-2EM4R7
	10	160.0	0.18	110	10	16	5.0	0.6	P5334-ND	.43	2.17	15.94	57.67	91.48	88.09/M	ECA-2EM100
	22	340.0	0.18	180	10	20	5.0	0.6	P5335-ND	.69	2.85	2				