



TS (V c.c.)	Cap. µF	D.C.L. (+20 °C) (µA) max.	tan δ max.	Courant ondulé (mA) eff.	Dimensions (mm)				N° de référence Digi-Key	Prix					N° de référence Panasonic	
					øD	L	P	ød		1	10	100	500	1 000		5 000
50	0.1	3.0	0.12	1.1	5	11	2.0	0.5	P5559-ND†	.20	.97	6.51	22.06	33.88	27.96/M	ECA-1HHG0R1
	0.22	3.0	0.12	2.3	5	11	2.0	0.5	P5560-ND†	.20	.97	6.51	22.06	33.88	27.96/M	ECA-1HHGR22
	0.33	3.0	0.12	3.5	5	11	2.0	0.5	P5561-ND†	.20	.97	6.51	22.06	33.88	27.96/M	ECA-1HHGR33
	0.47	3.0	0.12	5	5	11	2.0	0.5	P5562-ND†	.20	.97	6.51	22.06	33.88	27.96/M	ECA-1HHGR47
	1.0	3.0	0.12	10	5	11	2.0	0.5	P5563-ND†	.20	.97	6.51	22.06	33.88	27.96/M	ECA-1HHG010
	2.2	3.0	0.12	18	5	11	2.0	0.5	P5564-ND†	.20	.97	6.51	22.06	33.88	27.96/M	ECA-1HHG2R2
	3.3	3.0	0.12	22	5	11	2.0	0.5	P5565-ND†	.20	.97	6.51	22.06	33.88	27.96/M	ECA-1HHG3R3
	4.7	3.0	0.12	26	5	11	2.0	0.5	P5566-ND†	.20	.97	6.51	22.06	33.88	27.96/M	ECA-1HHG4R7
	10	5.0	0.12	39	5	11	2.0	0.5	P5567-ND†	.19	.97	6.51	22.06	33.88	27.96/M	ECA-1HHG100
	22	11.0	0.12	65	5	11	2.0	0.5	P5568-ND†	.15	.82	5.78	19.96	31.34	27.11/M	ECA-1HHG220
	33	16.5	0.12	90	5	11	2.0	0.5	P5569-ND†	.16	.82	5.78	19.96	31.34	27.11/M	ECA-1HHG330
	47	23.5	0.12	110	6.3	11.2	2.5	0.5	P5570-ND†	.25	1.30	9.16	31.63	49.97	43.20/M	ECA-1HHG470
	100	50.0	0.12	180	8	11.5	3.5	0.6	P5571-ND†	.33	1.81	12.96	46.65	72.84	67.76/M	ECA-1HHG101
	220	110.0	0.12	330	10	12.5	5.0	0.6	P5572-ND†	.42	2.49	18.27	66.09	105.03	100.80/M	ECA-1HHG221
	330	165.0	0.12	410	10	16	5.0	0.6	P5573-ND†	.48	3.00	22.03	79.70	126.20	121.97/M	ECA-1HHG331
	470	235.0	0.12	530	10	20	5.0	0.6	P5574-ND†	.59	3.95	29.00	104.90	166.86	160.09/M	ECA-1HHG471
	1000	500.0	0.12	950	12.5	25	5.0	0.6	P5575-ND†	1.01	6.48	48.60	172.79	287.13	276.13/M	ECA-1HHG102
	2200	1100.0	0.14	1470	16	31.5	7.5	0.8	P5576-ND†	1.47	10.47	78.99	296.22	513.28	498.04/M	ECA-1HHG222
	3300	1650.0	0.16	1770	18	35.5	7.5	0.8	P5577-ND	2.57	15.37	116.02	435.09	753.83	730.97/M	ECA-1HHG332
	63	10	6.3	0.10	46	5	11	2.0	0.5	P5578-ND	.17	.86	6.11	21.08	33.03	28.80/M
22		13.8	0.10	71	5	11	2.0	0.5	P5579-ND	.17	.86	6.11	21.08	33.03	28.80/M	ECA-1JHG220
33		20.7	0.10	100	6.3	11.2	2.5	0.5	P5580-ND	.26	1.35	9.50	32.83	51.67	44.90/M	ECA-1JHG330
47		29.6	0.10	120	6.3	11.2	2.5	0.5	P5581-ND	.21	1.21	8.64	31.10	48.28	44.90/M	ECA-1JHG470
100		63.0	0.10	215	10	12.5	5.0	0.6	P5582-ND	.41	2.72	19.44	69.98	109.26	100.80/M	ECA-1JHG101
220		138.6	0.10	335	10	16	5.0	0.6	P5583-ND	.58	3.28	24.06	87.05	138.06	132.98/M	ECA-1JHG221
330		207.9	0.10	510	10	20	5.0	0.6	P5584-ND	.77	4.35	31.91	115.41	182.95	176.18/M	ECA-1JHG331
470		296.1	0.10	640	12.5	20	5.0	0.6	P5585-ND	.97	5.56	41.66	148.12	246.48	237.16/M	ECA-1JHG471
1000		630.0	0.10	930	16	25	7.5	0.8	P5586-ND	1.51	8.66	65.41	245.27	425.19	411.65/M	ECA-1JHG102
2200		1386.0	0.12	1610	18	35.5	7.5	0.8	P5587-ND	2.96	17.01	128.35	481.33	834.30	808.89/M	ECA-1JHG222
100	0.47	3.0	0.08	9	5	11	2.0	0.5	P5588-ND	.17	.86	6.11	21.08	33.03	28.80/M	ECA-2AHGR47
	1.0	3.0	0.08	14	5	11	2.0	0.5	P5589-ND	.17	.86	6.11	21.08	33.03	28.80/M	ECA-2AHG010
	2.2	3.0	0.08	21	5	11	2.0	0.5	P5590-ND	.17	.86	6.11	21.08	33.03	28.80/M	ECA-2AHG2R2
	3.3	3.3	0.08	31	5	11	2.0	0.5	P5591-ND	.17	.86	6.11	21.08	33.03	28.80/M	ECA-2AHG3R3
	4.7	4.7	0.08	38	5	11	2.0	0.5	P5592-ND	.17	.86	6.11	21.08	33.03	28.80/M	ECA-2AHG4R7
	10	10.0	0.08	54	6.3	11.2	2.5	0.5	P5593-ND	.25	1.35	9.50	32.83	51.67	44.90/M	ECA-2AHG100
	22	22.0	0.08	93	6.3	11.2	2.5	0.5	P5594-ND	.21	1.21	8.64	31.10	48.28	44.90/M	ECA-2AHG220
	33	33.0	0.08	130	8	11.5	3.5	0.6	P5595-ND	.37	2.08	14.81	53.28	83.01	77.08/M	ECA-2AHG330
	47	47.0	0.08	165	10	12.5	5.0	0.6	P5596-ND	.45	2.51	17.96	64.41	99.95	93.17/M	ECA-2AHG470
	100	100.0	0.08	265	10	20	5.0	0.6	P5597-ND	.77	4.35	31.91	115.41	182.95	176.18/M	ECA-2AHG101
	220	220.0	0.08	440	12.5	25	5.0	0.6	P5598-ND	1.15	6.59	49.44	175.77	292.22	281.21/M	ECA-2AHG221
	330	330.0	0.08	540	16	25	7.5	0.8	P5599-ND	1.63	9.26	69.43	246.85	410.80	394.71/M	ECA-2AHG331
	470	470.0	0.08	715	16	25	7.5	0.8	P5850-ND	1.71	9.81	74.04	277.67	481.10	466.70/M	ECA-2AHG471
	1000	1000.0	0.08	985	18	35.5	7.5	0.8	P5851-ND	2.96	17.01	128.35	481.33	834.30	808.89/M	ECA-2AHG102
160	1.0	19.6	0.15	17	6.3	11.2	2.5	0.5	P5852-ND	.29	1.30	9.26	33.31	51.67	48.28/M	ECA-2CHG010
	2.2	31.1	0.15	25	6.3	11.2	2.5	0.5	P5853-ND	.32	1.30	9.26	33.31	51.67	48.28/M	ECA-2CHG2R2
	3.3	41.6	0.15	36	6.3	11.2	2.5	0.5	P5854-ND	.35	1.30	9.26	33.31	51.67	48.28/M	ECA-2CHG3R3
	4.7	55.1	0.15	43	6.3	11.2	2.5	0.5	P5855-ND	.38	1.30	9.26	33.31	51.67	48.28/M	ECA-2CHG4R7
	10	106.0	0.15	70	10	12.5	5.0	0.6	P5856-ND	.45	2.29	16.82	60.84	96.56	93.17/M	ECA-2CHG100
	22	221.0	0.15	130	10	20	5.0	0.6	P5857-ND	.60	3.08	22.63	81.86	129.59	125.36/M	ECA-2CHG220
	33	326.0	0.15	180	10	20	5.0	0.6	P5858-ND	.69	2.89	21.67	77.04	127.90	123.67/M	ECA-2CHG330
	47	461.0	0.15	220	12.5	20	5.0	0.6	P5859-ND	.86	4.07	30.55	108.62	180.41	173.64/M	ECA-2CHG470
	100	970.0	0.15	335	16	25	7.5	0.8	P5860-ND	1.27	6.67	49.99	177.73	295.60	284.60/M	ECA-2CHG101
	220	2122.0	0.15	540	16	31.5	7.5	0.8	P5861-ND	1.93	9.16	69.12	259.18	448.91	435.36/M	ECA-2CHG221
330	3178.0	0.15	705	18	31.5	7.5	0.8	P5862-ND	2.76	16.36	123.42	462.84	802.11	777.55/M	ECA-2CHG331	
250	1.0	25.0	0.15	17	6.3	11.2	2.5	0.5	P5863-ND	.34	1.30	9.26	33.31	51.67	48.28/M	ECA-2EHG010
	2.2	43.0	0.15	29	6.3	11.2	2.5	0.5	P5864-ND	.36	1.30	9.26	33.31	51.67	48.28/M	ECA-2EHG2R2
	3.3	59.5	0.15	42	8	11.5	3.5	0.6	P5865-ND	.38	1.58	11.60	41.98	66.91	64.38/M	ECA-2EHG3R3
	4.7	80.5	0.15	50	8	11.5	3.5	0.6	P5866-ND	.44	1.78	13.06	47.23	75.38	72.00/M	ECA-2EHG4R7
	10	160.0	0.15	88	10	16	5.0	0.6	P5867-ND	.66	3.00	22.03	79.70	126.20	121.97/M	ECA-2EHG100
	22	340.0	0.15	155	12.5	20	5.0	0.6	P5868-ND	.80	4.26	31.94	113.57	188.88	182.11/M	ECA-2EHG220
	33	505.0	0.15	190	12.5	20	5.0	0.6	P5869-ND	.95	4.62	34.70	123.39	204.97	197.36/M	ECA-2EHG330
	47	715.0	0.15	230	12.5	25	5.0	0.6	P5870-ND	1.23	5.92	44.43	157.95	262.57	252.41/M	ECA-2EHG470
	100	1510.0	0.15	365	16	31.5	7.5	0.8	P5871-ND	1.88	9.16	69.12	259.18	448.91	435.36/M	ECA-2EHG101
	450	1.0	37.0	0.20	18	8	11.5	3.5	0.6	P5872-ND	.47	1.97	14.51	52.49	83.01	80.47/M
2.2		69.4	0.20	29	10	12.5	5.0	0.6	P5873-ND	.51	2.37	17.40	62.92	99.95	96.56/M	ECA-2WHG2R2
3.3		99.1	0.20	41	10	16	5.0	0.6	P5874-ND	.71	3.08	22.63	81.86	129.59	125.36/M	ECA-2WHG3R3
4.7		136.0	0.20	49	10	20	5.0	0.6	P5875-ND	.75	3.15	23.61	83.95	139.76	134.68/M	ECA-2WHG4R7
10		280.0	0.20	75	12.5	20	5.0	0.6	P5876-ND	1.27	5.56	41.66	148.12	246.48	237.16/M	ECA-2WHG100
22		604.0	0.20	115	16	25	7.5	0.8	P5877-ND	1.69	7.85	59.24	222.15	385.39	373.53/M	ECA-2WHG220
33		901.0	0.20	155	16	31.5	7.5	0.8	P5878-ND	2.08	9.81	74.04	277.67	481.10	466.70/M	ECA-2WHG330