



Fig.	Tension de sortie	I sortie (A)	Tension d'entrée	N° de référence Digi-Key	Prix unitaire	1	10	100	N° de référence Digi-Key	Prix de bande et bobine	N° de référence Lineage Power
Convertisseurs											
1	3.0 - 6.0	10.0	18 - 30	555-1106-1-ND†	19.48	17.11	15.36	—	555-1106-2-ND	3230.25/250	AXB030X43-SRZ
2	3.3	20.0	36 - 75	555-1100-ND	44.11	38.95	35.09	—	—	—	EQW020A0F1Z
3	3.3	15.0	36 - 75	555-1104-1-ND†	46.75	41.26	37.13	—	555-1104-2-ND	4562.37/140	KW015A0F41-SRZ
4	3.3	15.0	36 - 75	555-1105-ND	46.75	41.26	37.13	—	—	—	KW015A0F41Z
5	48.0	2.4	38 - 75	555-1108-ND	57.60	50.82	45.74	—	—	—	PIM200FZ
6	3.3	50.0	36 - 75	555-1110-ND	89.78	81.32	72.85	—	—	—	QPW050A0F1Z
7	3.3	25.0	36 - 75	555-1113-ND	60.30	53.24	47.91	—	—	—	QRW025A0F1Z
7	3.3	35.0	36 - 75	555-1114-ND	73.77	65.14	58.62	—	—	—	QRW035A0F1Z
8	3.3	3.5	36 - 75	555-1118-1-ND†	21.94	18.98	17.20	—	555-1118-2-ND	2246.88/150	SW003A5F91-SRZ
9	3.3	3.5	36 - 75	555-1119-ND	21.94	18.98	17.20	—	—	—	SW003A5F91Z
1	5.0 - 15.0	8.0	20 - 30	555-1107-1-ND†	19.74	17.37	15.59	—	555-1107-2-ND	3316.01/250	AXB050X43-SRZ
7	5.0	25.0	36 - 75	555-1112-ND	73.77	65.14	58.62	—	—	—	QRW025A0A1Z
8	5.0	3.0	36 - 75	555-1116-1-ND†	21.94	18.98	17.20	—	555-1116-2-ND	2246.88/150	SW003A0A91-SRZ
9	5.0	3.0	36 - 75	555-1117-ND	21.94	18.98	17.20	—	—	—	SW003A0A91Z
2	12.0	6.0	36 - 75	555-1098-ND	44.11	38.95	35.09	—	—	—	EQW006A0B1Z
6	12.0	18.0	36 - 75	555-1109-ND	39.44	37.25	34.86	—	—	—	QBW018A0B1Z
7	12.0	10.0	36 - 75	555-1111-ND	73.77	65.14	58.62	—	—	—	QRW010A0B1Z
9	12.0	1.2	36 - 75	555-1115-ND	21.94	18.98	17.20	—	—	—	SW001A2B91Z
Filtres											
10	—	10	100	555-1101-ND	15.92	14.02	12.20	—	—	—	FLTR100V10Z
11	—	20	100	555-1102-ND	23.80	21.35	18.60	—	—	—	FLTR100V20Z
12	—	5.0	75	555-1103-ND	14.40	12.71	11.27	—	—	—	FLTR75V05Z

† Bande coupée

