

Case Size	Type	WV DC	Capacitance	Tolerance	Dim. T (mm)	Digi-Key Part No.	Cut Tape Pricing			Digi-Key Part No.	Tape and Reel		Kemet Part No.
							10	100	500		Qty.	Pricing	
0402	X7R	10	18000pF	±10%	0.5	399-4882-1-ND	34.60	204.47	589.87	399-4882-2-ND	10,000	569.64/M	C0402C183K8RACTU
		10	22000pF	±10%	0.5	399-4884-1-ND	34.60	204.47	589.87	399-4884-2-ND	10,000	569.64/M	C0402C223K8RACTU
		10	27000pF	±10%	0.5	399-4889-1-ND	34.60	204.47	589.87	399-4889-2-ND	10,000	569.64/M	C0402C273K8RACTU
		10	33000pF	±10%	0.5	399-4892-1-ND	34.60	204.47	589.87	399-4892-2-ND	10,000	569.64/M	C0402C333K8RACTU
		10	39000pF	±10%	0.5	399-4895-1-ND	34.60	204.47	589.87	399-4895-2-ND	10,000	569.64/M	C0402C393K8RACTU
		10	47000pF	±10%	0.5	399-4897-1-ND	34.60	204.47	589.87	399-4897-2-ND	10,000	569.64/M	C0402C473K8RACTU
		10	56000pF	±10%	0.5	399-4902-1-ND	34.60	204.47	589.87	399-4902-2-ND	10,000	569.64/M	C0402C563K8RACTU
		10	68000pF	±10%	0.5	399-4905-1-ND	34.60	204.47	589.87	399-4905-2-ND	10,000	569.64/M	C0402C683K8RACTU
		10	82000pF	±10%	0.5	399-4908-1-ND	34.60	204.47	589.87	399-4908-2-ND	10,000	569.64/M	C0402C823K8RACTU
		10	.1µF	±10%	0.5	399-3520-1-ND	2.21	13.26	38.26	399-3520-2-ND	10,000	51.02/M	C0402C104K8RACTU
		6.3	12000pF	±10%	0.5	399-4877-1-ND	34.60	204.47	589.87	399-4877-2-ND	10,000	569.64/M	C0402C123K9RACTU
		6.3	15000pF	±10%	0.5	399-4880-1-ND	34.60	204.47	589.87	399-4880-2-ND	10,000	569.64/M	C0402C153K9RACTU
		6.3	18000pF	±10%	0.5	399-4883-1-ND	34.60	204.47	589.87	399-4883-2-ND	10,000	569.64/M	C0402C183K9RACTU
		6.3	22000pF	±10%	0.5	399-4885-1-ND	34.60	204.47	589.87	399-4885-2-ND	10,000	569.64/M	C0402C223K9RACTU
		6.3	27000pF	±10%	0.5	399-4890-1-ND	34.60	204.47	589.87	399-4890-2-ND	10,000	569.64/M	C0402C273K9RACTU
		6.3	33000pF	±10%	0.5	399-4893-1-ND	34.60	204.47	589.87	399-4893-2-ND	10,000	569.64/M	C0402C333K9RACTU
		6.3	39000pF	±10%	0.5	399-4896-1-ND	34.60	204.47	589.87	399-4896-2-ND	10,000	569.64/M	C0402C393K9RACTU
		6.3	47000pF	±10%	0.5	399-4898-1-ND	34.60	204.47	589.87	399-4898-2-ND	10,000	569.64/M	C0402C473K9RACTU
		6.3	56000pF	±10%	0.5	399-4903-1-ND	34.60	204.47	589.87	399-4903-2-ND	10,000	569.64/M	C0402C563K9RACTU
		6.3	68000pF	±10%	0.5	399-4906-1-ND	34.60	204.47	589.87	399-4906-2-ND	10,000	569.64/M	C0402C683K9RACTU
	6.3	82000pF	±10%	0.5	399-4909-1-ND	34.60	204.47	589.87	399-4909-2-ND	10,000	569.64/M	C0402C823K9RACTU	
	6.3	.1µF	±10%	0.5	399-4872-1-ND	4.25	24.91	71.76	399-4872-2-ND	10,000	93.53/M	C0402C104K9RACTU	
	10	12000pF	±10%	0.5	399-3009-1-ND	19.64	116.05	334.81	399-3009-2-ND	10,000	323.08/M	C0402C123K8PACTU	
	10	15000pF	±10%	0.5	399-3011-1-ND	19.64	116.05	334.81	399-3011-2-ND	10,000	323.08/M	C0402C153K8PACTU	
	10	18000pF	±10%	0.5	399-3013-1-ND	19.64	116.05	334.81	399-3013-2-ND	10,000	323.08/M	C0402C183K8PACTU	
	10	22000pF	±10%	0.5	399-3015-1-ND	20.57	121.58	350.71	399-3015-2-ND	10,000	340.08/M	C0402C223K8PACTU	
	10	27000pF	±10%	0.5	399-3017-1-ND	20.57	121.58	350.71	399-3017-2-ND	10,000	340.08/M	C0402C273K8PACTU	
	10	33000pF	±10%	0.5	399-3019-1-ND	21.51	127.10	366.69	399-3019-2-ND	10,000	348.59/M	C0402C333K8PACTU	
	10	47000pF	±10%	0.5	399-3021-1-ND	22.45	132.63	382.59	399-3021-2-ND	10,000	365.59/M	C0402C473K8PACTU	
	10	68000pF	±10%	0.5	399-3023-1-ND	23.38	138.16	398.57	399-3023-2-ND	10,000	382.59/M	C0402C683K8PACTU	
	10	.1µF	±10%	0.5	399-3027-1-ND	2.04	12.16	35.11	399-3027-2-ND	10,000	51.02/M	C0402C104K8PACTU	
	6.3	12000pF	±10%	0.5	399-3008-1-ND	19.64	116.05	334.81	399-3008-2-ND	10,000	323.08/M	C0402C123K9PACTU	
	6.3	15000pF	±10%	0.5	399-3010-1-ND	19.64	116.05	334.81	399-3010-2-ND	10,000	323.08/M	C0402C153K9PACTU	
	6.3	18000pF	±10%	0.5	399-3012-1-ND	19.64	116.05	334.81	399-3012-2-ND	10,000	323.08/M	C0402C183K9PACTU	
	6.3	22000pF	±10%	0.5	399-3014-1-ND	20.57	121.58	350.71	399-3014-2-ND	10,000	340.08/M	C0402C223K9PACTU	
	6.3	27000pF	±10%	0.5	399-3016-1-ND	20.57	121.58	350.71	399-3016-2-ND	10,000	340.08/M	C0402C273K9PACTU	
	6.3	33000pF	±10%	0.5	399-3018-1-ND	21.51	127.10	366.69	399-3018-2-ND	10,000	348.59/M	C0402C333K9PACTU	
	6.3	47000pF	±10%	0.5	399-3020-1-ND	22.45	132.63	382.59	399-3020-2-ND	10,000	365.59/M	C0402C473K9PACTU	
	6.3	68000pF	±10%	0.5	399-3022-1-ND	23.38	138.16	398.57	399-3022-2-ND	10,000	382.59/M	C0402C683K9PACTU	
	6.3	.1µF	±10%	0.5	399-3026-1-ND	3.74	22.11	63.77	399-3026-2-ND	10,000	85.02/M	C0402C104K9PACTU	
6.3	.22µF	±10%	0.5	399-4886-1-ND	37.41	221.05	637.65	399-4886-2-ND	10,000	612.15/M	C0402C224K9PACTU		
6.3	.22µF	±20%	0.5	399-4887-1-ND	36.47	215.53	621.75	399-4887-2-ND	10,000	595.14/M	C0402C224M9PACTU		
6.3	1µF	±10%	0.5	399-4873-1-ND	4.25	24.91	71.76	399-4873-2-ND	10,000	68.02/M	C0402C105K9PACTU		
6.3	1µF	±20%	0.5	399-4874-1-ND	17.34	109.28	294.93	399-4874-2-ND	10,000	280.57/M	C0402C105M9PACTU		
0603	COG (NPO)	100	220pF	±5%	0.8	399-4910-1-ND	25.25	149.21	430.46	399-4910-2-ND	4,000	416.60/M	C0603C221J1GACTU
		50	.5pF	±0.25pF	0.8	399-1044-1-ND	41.49	245.37	707.79	399-1044-2-ND	4,000	680.16/M	C0603C508C5GACTU
		50	1pF	±0.25pF	0.8	399-1045-1-ND	34.60	204.47	589.87	399-1045-2-ND	4,000	569.64/M	C0603C109C5GACTU
		50	1.5pF	±0.25pF	0.8	399-1046-1-ND	34.60	204.47	589.87	399-1046-2-ND	4,000	569.64/M	C0603C159C5GACTU
		50	2pF	±0.25pF	0.8	399-1047-1-ND	41.49	245.37	707.79	399-1047-2-ND	4,000	680.16/M	C0603C209C5GACTU
		50	3pF	±0.25pF	0.8	399-1048-1-ND	41.49	245.37	707.79	399-1048-2-ND	4,000	680.16/M	C0603C309C5GACTU
		50	10pF	±5%	0.8	399-1049-1-ND	2.38	13.86	39.87	399-1049-2-ND	4,000	51.02/M	C0603C100J5GACTU
		50	12pF	±5%	0.8	399-1050-1-ND	3.32	19.38	55.77	399-1050-2-ND	4,000	76.52/M	C0603C120J5GACTU
		50	15pF	±5%	0.8	399-1051-1-ND	3.06	18.28	52.63	399-1051-2-ND	4,000	68.02/M	C0603C150J5GACTU
		50	18pF	±5%	0.8	399-1052-1-ND	3.06	18.28	52.63	399-1052-2-ND	4,000	68.02/M	C0603C180J5GACTU
		50	22pF	±5%	0.8	399-1053-1-ND	3.06	18.28	52.63	399-1053-2-ND	4,000	68.02/M	C0603C220J5GACTU
		50	27pF	±5%	0.8	399-1054-1-ND	3.06	18.28	52.63	399-1054-2-ND	4,000	68.02/M	C0603C270J5GACTU
		50	33pF	±5%	0.8	399-1055-1-ND	2.81	16.58	47.87	399-1055-2-ND	4,000	68.02/M	C0603C330J5GACTU
		50	47pF	±5%	0.8	399-1056-1-ND	3.32	19.38	55.77	399-1056-2-ND	4,000	76.52/M	C0603C470J5GACTU
		50	56pF	±5%	0.8	399-1057-1-ND	2.47	14.37	41.49	399-1057-2-ND	4,000	59.52/M	C0603C560J5GACTU
		50	68pF	±5%	0.8	399-1058-1-ND	3.15	18.79	54.24	399-1058-2-ND	4,000	76.52/M	C0603C680J5GACTU
		50	82pF	±5%	0.8	399-1060-1-ND	3.32	19.38	55.77	399-1060-2-ND	4,000	76.52/M	C0603C820J5GACTU
		50	82pF	±10%	0.8	399-1059-1-ND	18.70	110.53	318.83	399-1059-2-ND	4,000	306.08/M	C0603C820K5GACTU
		50	100pF	±5%	0.8	399-1061-1-ND	2.21	13.26	38.26	399-1061-2-ND	4,000	51.02/M	C0603C101J5GACTU
		50	120pF	±5%	0.8	399-1062-1-ND	3.32	19.38	55.77	399-1062-2-ND	4,000	76.52/M	C0603C121J5GACTU
	50	150pF	±5%	0.8	399-1063-1-ND	3.74	22.11	63.77	399-1063-2-ND	4,000	85.02/M	C0603C151J5GACTU	
	50	180pF	±5%	0.8	399-1064-1-ND	8.25	48.63	140.28	399-1064-2-ND	4,000	187.05/M	C0603C181J5GACTU	
	50	220pF	±5%	0.8	399-1066-1-ND	4.08	24.32	70.14	399-1066-2-ND	4,000	93.53/M	C0603C221J5GACTU	
	50	220pF	±10%	0.8	399-1065-1-ND	22.45	132.63	382.59	399-1065-2-ND	4,000	365.59/M	C0603C221K5GACTU	
	50	270pF	±5%	0.8	399-1067-1-ND	4.00	23.81	68.53	399-1067-2-ND	4,000	93.53/M	C0603C271J5GACTU	
	50	330pF	±5%	0.8	399-1068-1-ND	4.59	27.12	78.13	399-1068-2-ND	4,000	102.03/M	C0603C331J5GACTU	
	50	390pF	±5%	0.8	399-1069-1-ND	5.36	31.54	90.89	399-1069-2-ND	4,000	119.03/M	C0603C391J5GACTU	
	50	560pF	±5%	0.8	399-3287-1-ND	6.12	35.96	103.64	399-3287-2-ND	4,000	136.04/M	C0603C561J5GACTU	
	50	620pF	±5%	0.8	399-3288-1-ND	32.73	193.42	557.99	399-3288-2-ND	4,000	535.63/M	C0603C621J5GACTU	
	50	680pF	±5%	0.8	399-3289-1-ND	5.19	30.44	87.66	399-3289-2-ND	4,000	119.03/M	C0603C681J5GACTU	
	50	750pF	±5%	0.8	399-3290-1-ND	33.67	198.95	573.89	399-3290-2-ND	4,000	552.63/M	C0603C751J5GACTU	
	50	820pF	±5%	0.8	399-3291-1-ND	8.42	49.74						