

Fig.	Boitier	Rapport de transfert de courant				Claquage du collecteur V (BR)	Tension d'isolement (V eff.)	N° de référence Digi-Key	Prix unitaire			N° de référence Digi-Key	Bande et bobine	
		Min. (%)	Max. (%)	à If (mA)	VCE (V)				1	10	100		Qté	Prix
1	Dip	100	1,200	1	0.5	55	5,000	TLP331F-ND	.91	.77	.61	—	—	—
	Dip	50	600	5	5	55	5,000	TLP631F-ND	.64	.53	.43	—	—	—
	Dip	100	600	5	5	55	5,000	TLP631GBF-ND	.64	.53	.43	—	—	—
	Dip	50	600	5	5	55	4,000	TLP731D4-GRF-ND	.73	.61	.49	—	—	—
	SMD	20	—	10	10	30	2,500	4N25ASHORTF-ND	.51	.39	.29	—	—	—
	Dip	20	—	10	10	30	2,500	4N25SHORTFT-ND	.41	.31	.23	—	—	—
2	Dip	50	600	5	5	55	5,000	TLP632F-ND	.91	.76	.61	—	—	—
	Dip	100	600	5	5	55	5,000	TLP632GBF-ND	.91	.76	.61	—	—	—
	Dip	50	600	5	5	80	4,000	TLP732D4-GR-LF2-ND	.97	.81	.65	—	—	—
	Dip	50	600	5	5	55	4,000	TLP732D4-GR-LF2F-ND	.97	.81	.65	—	—	—
	Dip	100	—	10	10	30	2,500	4N35SHORTF-ND	.51	.41	.31	—	—	—
	Dip	100	—	10	10	80	2,500	4N38SHORTF-ND	.54	.41	.31	—	—	—
3	Dip	100	600	5	5	55	5,000	TLP630GBF-ND	.64	.53	.43	—	—	—
	SMD	100	1,200	1	0.5	80	3,750	TLP124F-ND	.75	.56	.42	—	—	—
	SMD	100	1,200	1	0.5	80	3,750	TLP124FCT-ND	.75	.56	.42	TLP124FTR-ND	3,000	242.25/M
	SMD	200	1,200	1	0.5	80	3,750	TLP124BVCT-ND	.78	.59	.44	TLP124BVTR-ND	3,000	253.26/M
	SMD	50	600	5	5	80	3,750	TLP181FT-ND	.41	.31	.23	—	—	—
	SMD	100	600	5	5	80	3,750	TLP181GBF-ND	.41	.31	.23	—	—	—
4	SMD	100	600	5	5	80	3,750	TLP181GBFCT-ND	.41	.31	.23	TLP181GBFTR-ND	3,000	132.14/M
	SMD	100	300	5	5	80	3,750	TLP181GRFCT-ND	.41	.31	.23	TLP181GRFTR-ND	3,000	132.14/M
	SMD	50	600	5	5	80	3,750	TLP131F-ND	.76	.64	.51	—	—	—
	SMD	100	600	5	5	80	3,750	TLP131GBF-ND	.76	.64	.51	—	—	—
	SMD	100	600	5	5	80	3,750	TLP131GBFCT-ND	.76	.64	.51	TLP131GBFTR-ND	3,000	330.33/M
	SMD	100	1,200	1	0.5	80	3,750	TLP137F-ND	.71	.60	.48	—	—	—
5	Dip	50	600	5	5	55	5,000	TLP621FT-ND	.58	.44	.33	—	—	—
	Dip	200	600	5	5	55	5,000	TLP621BLTF-ND	.47	.36	.27	—	—	—
	Dip(,4)	50	150	5	5	55	5,000	TLP621D4-Y-LF2-ND	.51	.39	.29	—	—	—
	Dip(,4)	50	150	5	5	55	5,000	TLP621D4-Y-LF2T-ND	.47	.36	.27	—	—	—
	Dip	100	600	5	5	55	5,000	TLP621GBT-ND	.44	.33	.25	—	—	—
	Dip	100	600	5	5	55	5,000	TLP621GBT-ND	.44	.33	.25	—	—	—
6	Dip	100	300	5	5	55	5,000	TLP621GRT-ND	.44	.33	.25	—	—	—
	Dip	100	300	5	5	55	5,000	TLP621GRFT-ND	.44	.33	.25	—	—	—
	Dip	50	600	5	5	55	5,000	TLP621-2FT-ND	.66	.56	.45	—	—	—
	Dip	100	600	5	5	55	5,000	TLP621-2GBF-ND	.89	.75	.60	—	—	—
	Dip	100	300	5	5	55	5,000	TLP621-2GRFT-ND	.89	.75	.60	—	—	—
	Dip	50	600	5	5	55	5,000	TLP621-4F-ND	2.16	1.80	1.52	—	—	—
7	Dip	100	600	5	5	55	5,000	TLP621-4GBF-ND	1.80	1.44	1.08	—	—	—
	SMD	100	1,200	1	0.5	55	5,000	TLP624LF1F-ND	.61	.51	.41	—	—	—
	Dip	100	1,200	1	0.5	55	5,000	TLP624F-ND	.81	.61	.46	—	—	—
	Dip	100	1,200	1	0.5	55	5,000	TLP624-2F-ND	1.27	1.06	.89	—	—	—
	Dip	100	1,200	1	0.5	55	5,000	TLP624-4F-ND	1.91	1.53	1.19	—	—	—
	Dip	100	1,200	±1	0.5	55	5,000	TLP626F-ND	.89	.75	.60	—	—	—
8	Dip	100	600	±5	5	55	5,000	TLP626BF-ND	.97	.81	.65	—	—	—
	Dip	100	600	±5	5	55	5,000	TLP620GBF-ND	.61	.46	.35	—	—	—
	Dip	50	600	±5	5	55	5,000	TLP620F-ND	.51	.39	.29	—	—	—
	Dip	100	300	±5	5	55	5,000	TLP620GR-ND	.61	.46	.35	—	—	—
	Dip	100	600	±5	5	55	5,000	TLP620GRFT-ND	.61	.46	.35	—	—	—
	Dip	50	600	±5	5	55	5,000	TLP620-2FT-ND	.91	.77	.61	—	—	—
9	SOP	100	600	±5	5	55	5,000	TLP620-2GBF-ND	.97	.81	.65	—	—	—
	SMD	100	600	±5	5	55	5,000	TLP620-2GBFCT-ND	1.10	.89	.67	TLP620-2GBFTR-ND	1,000	572.57
	Dip	50	600	±5	5	55	5,000	TLP620-4F-ND	1.97	1.57	1.18	—	—	—
	Dip	100	600	±5	5	55	5,000	TLP620-4GBF-ND	1.42	1.14	.86	—	—	—
	Dip	100	600	±5	5	55	5,000	TLP620-4D4-GBF-ND	2.06	1.65	1.24	—	—	—
	Dip	100	1,200	±1	—	55	5,000	TLP626-2-ND	1.48	1.19	.89	—	—	—
10	Dip	100	1,200	±1	—	55	5,000	TLP626-2F-ND	1.48	1.19	.89	—	—	—
	Dip	100	1,200	±1	—	55	5,000	TLP626-4F-ND	2.86	2.29	1.78	—	—	—
	SOP	100	600	5	5	80	2,500	TLP280-4GB-ND	1.80	1.44	1.08	—	—	—
	SOP	100	600	5	5	80	2,500	TLP280-4GBF-ND	1.55	1.24	.93	—	—	—
	SOP	100	600	5	5	80	2,500	TLP280-4GBFCT-ND	1.55	1.24	.93	TLP280-4GBFTR-ND	2,500	791.44/M
	SOP	100	600	5	5	80	2,500	TLP280GBF-ND	.70	.57	.43	—	—	—
11	SOP	100	600	5	5	80	2,500	TLP280GBFCT-ND	.63	.47	.36	TLP280GBFTR-ND	2,500	203.71/M
	SOP	100	600	5	5	80	2,500	TLP281-4GBFCT-ND	1.36	1.09	.82	TLP281-4GBFTR-ND	2,500	693.87/M
	SOP	50	600	5	5	80	2,500	TLP281-4JFCT-ND	1.36	1.09	.82	TLP281-4JFTR-ND	2,500	693.87/M
	SOP	100	600	5	5	80	2,500	TLP281-4GBJF-ND	1.36	1.09	.82	—	—	—
	SOP	100	600	5	5	80	2,500	TLP281GBFCT-ND	.56	.42	.32	TLP281GBFTR-ND	2,500	181.68/M
	SOP	50	600	5	5	80	2,500	TLP281GRF-ND	.58	.44	.33	—	—	—
12	SMD	100	400	1	5	100	2,500	TLP283F-ND	.56	.42	.32	—	—	—
	Dip	100	300	5	5	80	5,000	TLP421GR-ND	.42	.34	.26	—	—	—
	SMD	100	300	5	5	80	5,000	TLP421GRTP1CT-ND	.47	.38	.28	—	—	—
	Dip	50	600	60	—	80	5,000	TLP421-ND	.42	.33	.25	—	—	—
	Dip	200	600	60	—	80	5,000	TLP421BL-ND	.42	.34	.25	—	—	—
	Dip	200	600	5	5	80	5,000	TLP781BLF-ND	.43	.35	.26	—	—	—
13	Dip	100	300	5	5	80	5,000	TLP781D4-GRF-ND	.38	.31	.23	—	—	—
	Dip	50	600	5	5	80	5,000	TLP781F-ND	.38	.31	.23	—	—	—
	Dip	100	600	5	5	80	5,000	TLP781GBF-ND	.42	.34	.26	—	—	—
	SMD	100	600	5	5	80	5,000	TLP781GB-LF6FCT-ND	.43	.35	.26	TLP781GB-LF6FTR-ND	100	25.92
	SMD	100	600	5	5	80	5,000	TLP781GB-TP6FCT-ND	.38	.31	.23	TLP781GB-TP6FTR-ND	2,000	106.72/M
	Dip	100	300	5	5	80	5,000	TLP781GRF-ND	.42	.34	.26	—	—	—
14	Dip	100	200	5	5	80	5,000	TLP781GR-LF6F-ND	.43	.35	.26	—	—	—
	SMD	100	300	5	5	80	5,000	TLP781GR-LF6FCT-ND	.39	.31	.24	—	—	—
	SMD	100	300	5	5	80	5,000	TLP781GR-TP6FCT-ND	.43	.35	.26	TLP781GR-TP6FTR-ND	2,000	119.77/M
	Dip	100	300	5	5	80	5,000	TLP781GRF-ND	.43	.35	.26	—	—	—
	Dip	100	300	5	5	80	5,000	TLP781GRF-ND	.43	.35	.26	—	—	—
	Dip	100	300	5	5	80	5,000	TLP781GRF-ND	.43	.35	.26	—	—	—
15	Dip	50	600	5	5	55	2,500	TLP504AF-ND	1.07	.89	.72	—	—	—
	Dip	50	600	5	5	55	2,500	TLP504AGBF-ND	1.07	.89	.72	—	—	—
	Dip	50	600	5	5	55	2,500	TLP504A-2F-ND	1.78	1.43	1.07	—	—	—
	Dip	100	600	5	5	55	2,500	TLP504A-2GBF-ND	1.78	1.43	1.07	—	—	—
	SMD	50	600	5	5	80	3,750	TLP180FCT-ND	.58	.44	.33	TLP180FTR-ND	3,000	187.19/M
	SMD	100	600	5	5	80	3,750	TLP180GBF-ND	.68	.51	.39	—	—	—
16	SMD	100	600	5	5	80	3,750	TLP180GBTPLFCT-ND	.58	.44	.33	TLP180GBTPLTR-ND	3,000	187.19/M