



多层陶瓷片状电容器 (接上页)



尺寸代码	类型	WV DC	电容		尺寸 T (mm)	Digi-Key 零件编号	剪切带价格			Digi-Key 零件编号	带卷		Murata 零件编号				
			电容	公差			10	100	500		数量	价格					
0402	X7R	50	470pF	±10%	0.5	490-1300-1-ND	.35	2.11	6.07	490-1300-2-ND	10,000	6.16/M	GRM155R71H471KA01D				
			560pF	±10%	0.5	490-1301-1-ND	.35	2.11	6.07	490-1301-2-ND	10,000	6.16/M	GRM155R71H561KA01D				
			680pF	±10%	0.5	490-1302-1-ND	.35	2.11	6.07	490-1302-2-ND	10,000	6.16/M	GRM155R71H681KA01D				
			820pF	±10%	0.5	490-3250-1-ND	.35	2.11	6.07	490-3250-2-ND	10,000	6.16/M	GRM155R71H821KA01D				
			1000pF	±10%	0.5	490-1303-1-ND	.22	1.25	3.60	490-1303-2-ND	10,000	3.08/M	GRM155R71H102KA01D				
			1200pF	±10%	0.5	490-1304-1-ND	.32	1.91	5.48	490-1304-2-ND	10,000	4.62/M	GRM155R71H122KA01D				
			1500pF	±10%	0.5	490-3245-1-ND	.32	1.91	5.48	490-3245-2-ND	10,000	4.62/M	GRM155R71H152KA01D				
			2200pF	±10%	0.5	490-1305-1-ND	.29	1.76	5.05	490-1305-2-ND	10,000	4.62/M	GRM155R71H222KA01D				
			2700pF	±10%	0.5	490-1306-1-ND	.32	1.91	5.48	490-1306-2-ND	10,000	4.62/M	GRM155R71H272KA01D				
			3900pF	±10%	0.5	490-1307-1-ND	.32	1.91	5.48	490-1307-2-ND	10,000	4.62/M	GRM155R71H392KA01D				
		4700pF	±10%	0.5	490-1308-1-ND	.34	2.00	5.78	490-1308-2-ND	10,000	6.16/M	GRM155R71H472KA01D					
		6800pF	±10%	0.5	490-4515-1-ND	.43	2.51	7.22	490-4515-2-ND	10,000	6.16/M	GRM155R71H682KA88D					
		10000pF	±10%	0.5	490-4516-1-ND	.35	2.11	6.07	490-4516-2-ND	10,000	4.62/M	GRM155R71H103KA88D					
		15000pF	±10%	0.5	490-4517-1-ND	.51	3.00	8.67	490-4517-2-ND	10,000	6.16/M	GRM155R71H153KA12D					
		22000pF	±10%	0.5	490-3884-1-ND	.51	3.00	8.67	490-3884-2-ND	10,000	7.70/M	GRM155R71H223KA12D					
		25	4700pF	±10%	0.5	490-1309-1-ND	.29	1.76	5.05	490-1309-2-ND	10,000	4.62/M	GRM155R71E472KA01D				
			6800pF	±10%	0.5	490-1310-1-ND	.32	1.91	5.48	490-1310-2-ND	10,000	4.62/M	GRM155R71E682KA01D				
			8200pF	±10%	0.5	490-1311-1-ND	.32	1.91	5.48	490-1311-2-ND	10,000	4.62/M	GRM155R71E822KA01D				
			10000pF	±10%	0.5	490-1312-1-ND	.20	1.20	3.47	490-1312-2-ND	10,000	3.08/M	GRM155R71E103KA01D				
			15000pF	±10%	0.5	490-3251-1-ND	.46	2.71	7.79	490-3251-2-ND	10,000	7.70/M	GRM155R71E153KA61D				
	22000pF		±10%	0.5	490-3252-1-ND	.48	2.80	8.09	490-3252-2-ND	10,000	7.70/M	GRM155R71E223KA61D					
	33000pF		±10%	0.5	490-3253-1-ND	.68	4.00	11.55	490-3253-2-ND	10,000	10.78/M	GRM155R71E333KA88D					
	47000pF		±10%	0.5	490-3254-1-ND	.52	3.11	8.95	490-3254-2-ND	10,000	9.24/M	GRM155R71E473KA88D					
	16		10000pF	±10%	0.5	490-1313-1-ND	.22	1.25	3.60	490-1313-2-ND	10,000	3.08/M	GRM155R71C103KA01D				
			15000pF	±10%	0.5	490-1314-1-ND	.43	2.53	7.30	490-1314-2-ND	10,000	7.70/M	GRM155R71C153KA01D				
		22000pF	±10%	0.5	490-3256-1-ND	.40	2.39	6.87	490-3256-2-ND	10,000	6.16/M	GRM155R71C223KA01D					
		.1µF	±10%	0.5	490-3261-1-ND	.23	1.40	4.05	490-3261-2-ND	10,000	4.62/M	GRM155R71C104KA88D					
		33000pF	±10%	0.5	490-1315-1-ND	.54	3.22	9.30	490-1315-2-ND	10,000	9.24/M	GRM155R71A333KA01D					
		47000pF	±10%	0.5	490-1316-1-ND	.43	2.53	7.30	490-1316-2-ND	10,000	7.70/M	GRM155R71A473KA01D					
		10	68000pF	±10%	0.5	490-1317-1-ND	.55	3.31	9.53	490-1317-2-ND	10,000	9.24/M	GRM155R61A683KA01D				
			.1µF	±10%	0.5	490-1318-1-ND	.20	1.20	3.47	490-1318-2-ND	10,000	3.08/M	GRM155R61A104KA01D				
			.22µF	±10%	0.5	490-3910-1-ND	.89	5.25	15.15	490-3910-2-ND	10,000	13.86/M	GRM155R61A224KE19D				
			.33µF	±10%	0.5	490-3263-1-ND	1.40	8.32	23.96	490-3263-2-ND	10,000	23.10/M	GRM155R61A334KE15D				
	.47µF		±10%	0.5	490-3264-1-ND	1.36	8.01	23.10	490-3264-2-ND	10,000	21.56/M	GRM155R61A474KE15D					
	.1µF		±10%	0.5	490-3890-1-ND	1.06	6.31	18.19	490-3890-2-ND	10,000	16.94/M	GRM155R61A105KE15D					
	.33µF		±10%	0.5	490-3265-1-ND	1.40	8.32	23.96	490-3265-2-ND	10,000	23.10/M	GRM155R60J334KE01D					
	.47µF		±10%	0.5	490-3266-1-ND	1.00	5.93	17.09	490-3266-2-ND	10,000	16.94/M	GRM155R60J474KE19D					
	1.0µF		±10%	0.5	490-1320-1-ND	.57	3.40	9.83	490-1320-2-ND	10,000	9.24/M	GRM155R60J105KE19D					
	1.0µF		±20%	0.5	490-1319-1-ND	.57	3.40	9.83	490-1319-2-ND	10,000	9.24/M	GRM155R60J105ME19D					
	2.2µF	±20%	0.5	490-4519-1-ND	5.62	33.23	95.87	490-4519-2-ND	10,000	72.38/M	GRM155R60J225ME15D						
	4	2.2µF	±20%	0.5	490-4518-1-ND	3.56	21.02	60.65	490-4518-2-ND	10,000	46.20/M	GRM155R60G225ME15D					
	50	Y5V	25	2200pF	+80, -20%	0.5	490-1321-1-ND	.45	2.60	7.52	490-1321-2-ND	10,000	7.70/M	GRM155F1H222ZA01D			
				4700pF	+80, -20%	0.5	490-1322-1-ND	.45	2.60	7.52	490-1322-2-ND	10,000	7.70/M	GRM155F1H472ZA01D			
				10000pF	+80, -20%	0.5	490-1323-1-ND	.34	2.00	5.78	490-1323-2-ND	10,000	6.16/M	GRM155F1H103ZA01D			
				10000pF	+80, -20%	0.5	490-1324-1-ND	.39	2.31	6.64	490-1324-2-ND	10,000	6.16/M	GRM155F1E103ZA01D			
				22000pF	+80, -20%	0.5	490-1325-1-ND	.34	2.00	5.78	490-1325-2-ND	10,000	6.16/M	GRM155F1E223ZA01D			
				47000pF	+80, -20%	0.5	490-3270-1-ND	.35	2.11	6.07	490-3270-2-ND	10,000	6.16/M	GRM155F1E473ZA01D			
				.1µF	+80, -20%	0.5	490-3271-1-ND	.34	2.00	5.78	490-3271-2-ND	10,000	6.16/M	GRM155F1E104ZA01D			
				22000pF	+80, -20%	0.5	490-3272-1-ND	.39	2.31	6.64	490-3272-2-ND	10,000	6.16/M	GRM155F1C223ZA01D			
				47000pF	+80, -20%	0.5	490-1326-1-ND	.34	2.00	5.78	490-1326-2-ND	10,000	6.16/M	GRM155F1C473ZA01D			
				.1µF	+80, -20%	0.5	490-1327-1-ND	.22	1.31	3.76	490-1327-2-ND	10,000	3.08/M	GRM155F1C104ZA01D			
		.22µF	+80, -20%	0.5	490-3273-1-ND	.67	3.40	9.83	490-3273-2-ND	10,000	9.24/M	GRM155F1C224ZA01D					
		.47µF	+80, -20%	0.5	490-3274-1-ND	.58	4.00	11.55	490-3274-2-ND	10,000	10.78/M	GRM155F1C474ZA01D					
		10	6.3	.33µF	+80, -20%	0.5	490-3275-1-ND	.72	4.31	12.41	490-3275-2-ND	10,000	12.32/M	GRM155F1A334ZE01D			
				.47µF	+80, -20%	0.5	490-3276-1-ND	.77	4.51	13.00	490-3276-2-ND	10,000	12.32/M	GRM155F1A474ZE01D			
				.1µF	+80, -20%	0.5	490-3277-1-ND	.35	2.11	6.07	490-3277-2-ND	10,000	6.16/M	GRM155F50J104ZA01D			
				.68µF	+80, -20%	0.5	490-3278-1-ND	.79	4.60	13.29	490-3278-2-ND	10,000	12.32/M	GRM155F50J684ZE01D			
				0603	COG (NPO)	100	10pF	±25pF	0.8	490-3279-1-ND	.79	4.67	13.46	490-3279-2-ND	4,000	12.32/M	GRM1885C2A100RA01D
							11pF	±5%	0.8	490-1328-1-ND	.99	5.81	16.76	490-1328-2-ND	4,000	15.40/M	GRM1885C2A110JA01D
							12pF	±5%	0.8	490-1329-1-ND	.77	4.51	13.00	490-1329-2-ND	4,000	12.32/M	GRM1885C2A120JA01D
							13pF	±5%	0.8	490-1330-1-ND	.99	5.81	16.76	490-1330-2-ND	4,000	15.40/M	GRM1885C2A130JA01D
	15pF						±5%	0.8	490-1331-1-ND	.72	4.31	12.41	490-1331-2-ND	4,000	12.32/M	GRM1885C2A150JA01D	
	16pF						±5%	0.8	490-1332-1-ND	.99	5.81	16.76	490-1332-2-ND	4,000	15.40/M	GRM1885C2A160JA01D	
	18pF	±5%	0.8				490-1333-1-ND	.77	4.51	13.00	490-1333-2-ND	4,000	12.32/M	GRM1885C2A180JA01D			
	20pF	±5%	0.8				490-1334-1-ND	.99	5.81	16.76	490-1334-2-ND	4,000	15.40/M	GRM1885C2A200JA01D			
	22pF	±5%	0.8				490-1335-1-ND	.72	4.31	12.41	490-1335-2-ND	4,000	12.32/M	GRM1885C2A220JA01D			
	24pF	±5%	0.8				490-1336-1-ND	.99	5.81	16.76	490-1336-2-ND	4,000	15.40/M	GRM1885C2A240JA01D			
	27pF	±5%	0.8	490-1337-1-ND	.77	4.51	13.00	490-1337-2-ND	4,000	12.32/M	GRM1885C2A270JA01D						
	30pF	±5%	0.8	490-1338-1-ND	.99	5.81	16.76	490-1338-2-ND	4,000	15.40/M	GRM1885C2A300JA01D						
	33pF	±5%	0.8	490-1339-1-ND	.72	4.31	12.41	490-1339-2-ND	4,000	12.32/M	GRM1885C2A330JA01D						
	36pF	±5%	0.8	490-1340-1-ND	.99	5.81	16.76	490-1340-2-ND	4,000	16.08/M	GRM1885C2A360JA01D						
	39pF	±5%	0.8	490-1341-1-ND	.77	4.51	13.00	490-1341-2-ND	4,000	12.32/M	GRM1885C2A390JA01D						
	43pF	±5%	0.8	490-1342-1-ND	.99	5.81	16.76	490-1342-2-ND	4,000	15.40/M	GRM1885C2A430JA01D						
	47pF	±5%	0.8	490-1343-1-ND	.72	4.31	12.41	490-1343-2-ND	4,000	12.32/M	GRM1885C2A470JA01D						
	51pF	±5%	0.8	490-1344-1-ND	.99	5.81	16.76	490-1344-2-ND	4,000	16.08/M	GRM1885C2A510JA01D						
	56pF	±5%	0.8	490-1345-1-ND	.77	4.51	13.00	490-1345-2-ND	4,000	12.32/M	GRM1885C2A560JA01D						
	62pF	±5%	0.8	490-1346-1-ND	.91	5.41	15.60	490-1346-2-ND	4,000	15.40/M	GRM1885C2A620JA01D						
	68pF	±5%	0.8	490-1347-1-ND	.72	4.31	12.41	490-1347-2-ND	4,000	12.32/M	GRM1885C2A680JA01D						
	75pF	±5%	0.8	490-1348-1-ND	.99	5.81	16.76	490-1348-2-ND	4,000	15.40/M	GRM1885C2A750JA01D						
	82pF	±5%	0.8	490-1349-1-ND	.77	4.51	13.00	490-1349-2-ND	4,000	12.32/M	GRM1885C2A820JA01D						
	91pF	±5%	0.8	490-1350-1-ND	.99												