

STMicroelectronics		DigiKey (Cont.)		AMPLIFIERS AND LINEAR RoHS Compliant Parts Available		
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
LM346N	497-2980-5-ND	Programmable Quad Bipolar Op Amp	16-Dip	2.21	1.96	1.55
LM348DT	497-4049-1-ND	Four UA741 Quad Bipolar Op Amp	14-SOIC	1.46	1.27	1.01
LM348N	497-2981-5-ND	Four UA741 Quad Bipolar Op Amp	14-Dip	1.24	1.10	.87
LM358ADT	497-1590-1-ND	Low Power Dual Op Amp	8-SOIC	.77	.62	.47
LM358ADT	497-1590-2-ND	Low Power Dual Op Amp	8-SOIC	545.60/2,500		
LM358AN	497-2983-5-ND	Low Power Dual Op Amp	8-Dip	.70	.60	.45
LM358APT	497-5367-1-ND	Low Power Dual Op Amp*	8-TSSOP	.94	.75	.57
LM358APT	497-5367-2-ND	Low Power Dual Op Amp*	8-TSSOP	1058.82/4,000		
LM358AST	497-7332-1-ND	Low Power Dual Op Amp*	8-Mini SOIC	.82	.65	.49
LM358AST	497-7332-2-ND	Low Power Dual Op Amp*	8-Mini SOIC	918.02/4,000		
LM358DT	497-1591-1-ND	Low Power Dual Op Amp	8-SOIC	.73	.58	.40
LM358DT	497-1591-2-ND	Low Power Dual Op Amp	8-SOIC	418.88/2,500		
LM358N	497-1592-5-ND	Low Power Dual Op Amp	8-Dip	.70	.60	.45
LM358PT	497-6455-1-ND	Low Power Dual Op Amp*	8-TSSOP	.73	.59	.45
LM358PT	497-6455-2-ND	Low Power Dual Op Amp*	8-TSSOP	827.90/4,000		
LM358ST	497-6456-1-ND	Low Power Dual Op Amp*	8-Mini SOIC	.82	.65	.49
LM358ST	497-6456-2-ND	Low Power Dual Op Amp*	8-Mini SOIC	918.02/4,000		
LM358YDT	497-10177-1-ND	Low Power Dual Op Amp*	8-SOIC	.82	.65	.49
LM358YDT	497-10177-2-ND	Low Power Dual Op Amp*	8-SOIC	573.76/2,500		
LM393ADT	497-4267-1-ND	Low Power Dual Voltage Comparator	8-SOIC	.89	.72	.54
LM393ADT	497-4267-2-ND	Low Power Dual Voltage Comparator	8-SOIC	626.56/2,500		
LM393AN	497-6881-5-ND	Low Power Dual Voltage Comparator*	8-Dip	.92	.78	.58
LM393DT	497-1593-1-ND	Low Power Dual Voltage Comparator	8-SOIC	.73	.58	.40
LM393DT	497-1593-2-ND	Low Power Dual Voltage Comparator	8-SOIC	418.88/2,500		
LM393N	497-1594-5-ND	Low Power Dual Voltage Comparator	8-Dip	.70	.60	.45
LM393PT	497-7333-1-ND	Low Power Dual Voltage Comparator*	8-TSSOP	.86	.69	.52
LM393PT	497-7333-2-ND	Low Power Dual Voltage Comparator*	8-TSSOP	863.07/4,000		
LM393ST	497-7334-1-ND	Low Power Dual Voltage Comparator*	8-Mini SOIC	.96	.69	.52
LM393ST	497-7334-2-ND	Low Power Dual Voltage Comparator*	8-Mini SOIC	963.07/4,000		
LM833DT	497-1597-1-ND	Low Noise Dual Op Amp	8-SOIC	929.28/2,500		
LM833N	497-1598-5-ND	Low Noise Dual Op Amp	8-Dip	1.10	.97	.75
LM833YDT	497-10220-1-ND	Low Noise Dual Op Amp*	8-SOIC	.92	.80	.62
LM2901DT	497-1555-1-ND	Low Power Quad Voltage Comparator	14-SOIC	.90	.72	.54
LM2901DT	497-1555-2-ND	Low Power Quad Voltage Comparator	14-SOIC	633.60/2,500		
LM2901N	497-1556-5-ND	Low Power Quad Voltage Comparator	14-Dip	.77	.66	.49
LM2901PT	497-6454-1-ND	Low Power Quad Voltage Comparator*	14-TSSOP	1.04	.84	.63
LM2901PT	497-6454-2-ND	Low Power Quad Voltage Comparator*	14-TSSOP	732.16/2,500		
LM2901YDT	497-10211-1-ND	Low Power Quad Voltage Comparator*	14-SOIC	1.30	1.13	.89
LM2901YDT	497-10211-2-ND	Low Power Quad Voltage Comparator*	14-SOIC	1073.60/2,500		
LM2901YPT	497-10212-1-ND	Low Power Quad Voltage Comparator*	14-TSSOP	1.30	1.13	.89
LM2901YPT	497-10212-2-ND	Low Power Quad Voltage Comparator*	14-TSSOP	1073.60/2,500		
LM2902AWYDT	497-10426-1-ND	Low Power Quad Op Amp*	14-SOIC	.82	.65	.49
LM2902AWYDT	497-10426-2-ND	Low Power Quad Op Amp*	14-SOIC	1070.08/5,000		
LM2902AWYPT	497-10427-1-ND	Low Power Quad Op Amp*	14-TSSOP	.82	.65	.49
LM2902AWYPT	497-10427-2-ND	Low Power Quad Op Amp*	14-TSSOP	1070.08/5,000		
LM2902D	497-1557-1-ND	Low Power Quad Op Amp	14-SOIC	.90	.72	.54
LM2902DT	497-1557-2-ND	Low Power Quad Op Amp	14-SOIC	633.60/2,500		
LM2902N	497-1558-5-ND	Low Power Quad Op Amp	14-Dip	.77	.66	.49
LM2902PT	497-4045-1-ND	Low Power Quad Op Amp	14-TSSOP	1.13	.90	.68
LM2902PT	497-4045-2-ND	Low Power Quad Op Amp	14-TSSOP	792.00/2,500		
LM2902WYDT	497-10428-1-ND	Low Power Quad Op Amp*	14-SOIC	.82	.65	.49
LM2902WYDT	497-10428-2-ND	Low Power Quad Op Amp*	14-SOIC	1070.08/5,000		
LM2902WYPT	497-10429-1-ND	Low Power Quad Op Amp*	14-TSSOP	.82	.65	.49
LM2902WYPT	497-10429-2-ND	Low Power Quad Op Amp*	14-TSSOP	573.76/2,500		
LM2902YDT	497-10213-1-ND	Low Power Quad Op Amp*	14-SOIC	1.30	1.13	.89
LM2902YDT	497-10213-2-ND	Low Power Quad Op Amp*	14-SOIC	1073.60/2,500		
LM2902YPT	497-10214-1-ND	Low Power Quad Op Amp*	14-TSSOP	1.30	1.13	.89
LM2902YPT	497-10214-2-ND	Low Power Quad Op Amp*	14-TSSOP	1073.60/2,500		
LM2903DT	497-1559-1-ND	Low Power Dual Voltage Comparator	8-SOIC	.90	.72	.54
LM2903DT	497-1559-2-ND	Low Power Dual Voltage Comparator	8-SOIC	633.60/2,500		
LM2903HDT	497-4260-1-ND	Low Power Dual Voltage Comparator	8-SOIC	1.86	1.67	1.32
LM2903HDT	497-4260-2-ND	Low Power Dual Voltage Comparator	8-SOIC	1710.72/2,500		
LM2903H	497-1560-5-ND	Low Power Dual Voltage Comparator	8-Dip	.77	.66	.49
LM2903PT	497-7332-2-ND	Low Power Dual Voltage Comparator*	8-TSSOP	1098.24/4,000		
LM2903YDT	497-10215-1-ND	Low Power Dual Voltage Comparator*	8-SOIC	1.30	1.13	.89
LM2903YDT	497-10215-2-ND	Low Power Dual Voltage Comparator*	8-SOIC	1073.60/2,500		
LM2903YPT	497-10216-1-ND	Low Power Dual Voltage Comparator*	8-TSSOP	1.30	1.13	.89
LM2903YPT	497-10216-2-ND	Low Power Dual Voltage Comparator*	8-TSSOP	1717.76/4,000		
LM2904DT	497-1561-1-ND	Low Power Dual Op Amp	8-SOIC	.90	.72	.54
LM2904DT	497-1561-2-ND	Low Power Dual Op Amp	8-SOIC	633.60/2,500		
LM2904N	497-1562-5-ND	Low Power Dual Op Amp	8-Dip	.77	.66	.49
LM2904PT	497-4046-1-ND	Low Power Dual Op Amp	8-TSSOP	.86	.69	.52
LM2904PT	497-4046-2-ND	Low Power Dual Op Amp	8-TSSOP	963.07/4,000		
LM2904ST	497-7816-1-ND	Low Power Dual Op Amp*	8-Mini SOIC	1.17	1.02	.80
LM2904ST	497-7816-2-ND	Low Power Dual Op Amp*	8-Mini SOIC	1543.17/4,000		
LM2904WHDT	497-4261-1-ND	Low Power Dual Op Amp	8-SOIC	2.03	1.81	1.44
LM2904WHDT	497-4261-2-ND	Low Power Dual Op Amp	8-SOIC	1862.08/2,500		
LM2904YDT	497-10217-1-ND	Low Power Dual Op Amp*	8-SOIC	1.30	1.13	.89
LM2904YDT	497-10217-2-ND	Low Power Dual Op Amp*	8-SOIC	1073.60/2,500		
LM2904YPT	497-10218-1-ND	Low Power Dual Op Amp*	8-TSSOP	1.30	1.13	.89
LM2904YPT	497-10218-2-ND	Low Power Dual Op Amp*	8-TSSOP	1717.76/4,000		
LM2904YST	497-10219-1-ND	Low Power Dual Op Amp*	8-MSOP	1.30	1.13	.89
LM2904YST	497-10219-2-ND	Low Power Dual Op Amp*	8-MSOP	1717.76/4,000		
LMV321IL	497-4941-1-ND	Low Power In/Out R/R Op Amp	SOT-23-5	1.49	1.30	1.03
LMV321IL	497-4941-2-ND	Low Power In/Out R/R Op Amp	SOT-23-5	1482.62/3,000		
LMV321IYL	497-10221-1-ND	Low Power In/Out R/R Op Amp*	SOT-23-5	1.44	1.24	.98
LMV321IYL	497-10221-2-ND	Low Power In/Out R/R Op Amp*	SOT-23-5	1415.04/3,000		
LMV321RIL	497-4942-1-ND	Low Power In/Out R/R Op Amp	SOT-23-5	1.49	1.30	1.03
LMV321RIL	497-4942-2-ND	Low Power In/Out R/R Op Amp	SOT-23-5	1482.62/3,000		
LMV324IDT	497-4943-1-ND	Low Power Quad In/Out R/R Op Amp	14-SOIC	1.55	1.39	1.11
LMV324IDT	497-4943-2-ND	Low Power Quad In/Out R/R Op Amp	14-SOIC	1429.12/2,500		
LMV324IPT	497-4944-1-ND	Low Power Quad In/Out R/R Op Amp	14-TSSOP	1.55	1.39	1.11
LMV324IPT	497-4944-2-ND	Low Power Quad In/Out R/R Op Amp	14-TSSOP	1429.12/2,500		
LMV324YDT	497-10222-1-ND	Low Power Quad In/Out R/R Op Amp*	14-SOIC	1.49	1.34	1.07
LMV324YDT	497-10222-2-ND	Low Power Quad In/Out R/R Op Amp*	14-SOIC	1376.32/2,500		
LMV324YPT	497-10356-1-ND	Low Power Quad In/Out R/R Op Amp*	14-TSSOP	1.44	1.24	.98
LMV324YPT	497-10356-2-ND	Low Power Quad In/Out R/R Op Amp*	14-TSSOP	1179.20/2,500		
LMV331ICT	497-10355-1-ND	Low Voltage Comparator*	SC70-5	1.17	1.02	.80
LMV331ICT	497-10355-2-ND	Low Voltage Comparator*	SC70-5	1157.38/3,000		
LMV331IL	497-10433-1-ND	Low Voltage Comparator*	SOT-23-5	1.17	1.02	.80
LMV331IL	497-10433-2-ND	Low Voltage Comparator*	SOT-23-5	1157.38/3,000		
LMV358IDT	497-4945-1-ND	Low Power Dual In/Out R/R Op Amp	8-SOIC	1.49	1.30	1.03

STMicroelectronics		DigiKey (Cont.)		AMPLIFIERS AND LINEAR RoHS Compliant Parts Available		
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
LMV358IDT	497-4945-2-ND	Low Power Dual In/Out R/R Op Amp	8-SOIC	1235.52/2,500		
LMV358IPT	497-4946-1-ND	Low Power Dual In/Out R/R Op Amp	8-TSSOP	1.20	1.04	.82
LMV358IPT	497-4946-2-ND	Low Power Dual In/Out R/R Op Amp	8-TSSOP	1582.59/4,000		
LS2040CDT	497-7823-1-ND	High Performance Dual Op Amp*	8-SOIC	2.84	2.45	2.00
LS2040CDT	497-7823-2-ND	High Performance Dual Op Amp*	8-SOIC	2745.60/2,500		
LS2040CN	497-7335-5-ND	High Performance Dual Op Amp*	8-Dip	2.06	1.86	1.50
LS2040DT	497-7824-1-ND	High Performance Dual Op Amp*	8-SOIC	2.84	2.45	2.00
LS2040DT	497-7824-2-ND	High Performance Dual Op Amp*	8-SOIC	2745.60/2,500		
LS2040YDT	497-10223-1-ND	High Performance Dual Op Amp*	8-SOIC	3.42	2.93	2.40
LS2040YDT	497-10223-2-ND	High Performance Dual Op Amp*	8-SOIC	3294.72/2,500		
LS4040CDT	497-7825-1-ND	High Performance Quad Op Amp*	14-SOIC	2.91	2.64	2.12
LS4040CDT	497-7825-2-ND	High Performance Quad Op Amp*	14-SOIC	3893.12/2,500		
LS4040CN	497-7336-5-ND	High Performance Quad Op Amp*	14-Dip	2.91	2.64	2.12
LS4040DT	497-7826-1-ND	High Performance Quad Op Amp*	14-SOIC	4.41	3.78	3.09
LS4040DT	497-7826-2-ND	High Performance Quad Op Amp*	14-SOIC	4245.12/2,500		
LS4040IN	497-7337-5-ND	High Performance Quad Op Amp*	14-Dip	1.86	1.65	1.30
MC1458DT	497-1948-1-ND	High Performance Dual Op Amp	8-SOIC	1.14	.92	.69
MC1458DT	497-1948-2-ND	High Performance Dual Op Amp	8-SOIC	802.56/2,500		
MC1458ID	497-7405-5-ND	High Performance Dual Op Amp*	8-SOIC	1.01	.89	.69
MC1458IN	497-1949-5-ND	High Performance Dual Op Amp	8-Dip	.94	.83	.64
MC1458N	497-7406-5-ND	High Performance Dual Op Amp*	8-Dip	.92	.78	.58
MC1558N	497-7407-5-ND	High Performance Dual Op Amp*	8-Dip	.94	.83	.64
MC3303DT	497-4050-1-ND	Low Power Quad Bipolar Op Amp	14-SOIC	1.62	1.45	1.16
MC3303DT	497-4050-2-ND	Low Power Quad Bipolar Op Amp	14-SOIC	1492.48/2,500		
MC3303PT	497-7848-1-ND	Low Power Quad Bipolar Op Amp*	14-TSSOP	1.35	1.21	.96
MC3303PT	497-7848-2-ND	Low Power Quad Bipolar Op Amp*	14-TSSOP	1242.56/2,500		
MC3403D	497-1959-5-ND	Low Power Quad Bipolar Op Amp	14-SOIC	1.55	1.38	1.09
MC3403DT	497-1959-1-ND	Low Power Quad Bipolar Op Amp	14-SOIC	1.00	.87	.69
MC3403N	497-7411-5-ND	Low Power Quad Bipolar Op Amp*	14-Dip	1.27	1.12	.89
MC4558CDT	497-4051-1-ND	Wide Bandwidth Dual Bipolar Op Amp	8-SOIC	.97	.78	.59
MC4558CDT	497-4051-2-ND	Wide Bandwidth Dual Bipolar Op Amp	8-SOIC	886.40/2,500		
MC4558CN	497-1960-5-ND	Wide Bandwidth Dual Bipolar Op Amp	8-Dip	.89	.78	.61
MC4558CPT	497-7853-1-ND	Wide Bandwidth Dual Bipolar Op Amp*	8-TSSOP	1.24	1.07	.85
MC4558CPT	497-7853-2-ND	Wide Bandwidth Dual Bipolar Op Amp*	8-TSSOP	1633.28/4,000		
MC4558IDT	497-1961-1-ND	Wide Bandwidth Dual Bipolar Op Amp	8-SOIC	1.44	1.24	.98
MC4558IDT	497-1961-2-ND	Wide Bandwidth Dual Bipolar Op Amp	8-SOIC	1179.20/2,500		
MC33078DT	497-1952-1-ND	Low Noise Dual Op Amp	8-SOIC	1.44	1.24	.98
MC33078DT	497-1952-2-ND	Low Noise Dual Op Amp	8-SOIC	1179.20/2,500		
MC33078N	497-1953-5-ND	Low Noise Dual Op Amp	8-Dip	1.37	1.20	.92
MC33078YDT	497-10224-1-ND	Low Noise Dual Op Amp*	8-SOIC	1.49	1.34	1.07
MC33078YDT	497-10224-2-ND	Low Noise Dual Op Amp*	8-SOIC	1376.32/2,500		
MC33079DT	497-1954-1-ND	Low Noise Quad Op Amp	14-SOIC	1.52	1.36	1.08
MC33079DT	497-1954-2-ND	Low Noise Quad Op Amp	14-SOIC	1400.96/2,500		
MC33079YDT	497-10225-1-ND	Low Noise Quad Op Amp*	14-SOIC	1.80	1.61	1.28
MC33079YDT	497-10225-2-ND	Low Noise Quad Op Amp*	14-SOIC	1654.40/2,500		
MC33171DT	497-1956-5-ND	Low Power Single Bipolar Op Amp	8-SOIC	1.51	1.34	1.06
MC33171DT	497-1956-1-ND	Low Power Single Bipolar Op Amp	8-SOIC	163.3	1.46	1.16
MC33171DT	497-1956-2-ND	Low Power Single Bipolar Op Amp	8-SOIC	1503.04/2,500		
MC33171N	497-7408-5-ND	Low Power Single Bipolar Op Amp*	8-Dip	1.22	1.09	.86
MC33172DT	497-1957-1-ND	Low Power Dual Bipolar Op Amp				