

STMicroelectronics		DigiKey (Cont.)		AMPLIFIERS AND LINEAR		
				RoHS Compliant Parts Available		
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
TL074ACD	497-2203-2-ND	Low Noise, JFET Quad Op Amp	14-SOIC	1907.84/2,500		
TL074ACN	497-7660-5-ND	Low Noise, JFET Quad Op Amp*	14-Dip	1.66	1.47	1.16
TL074BCN	497-7041-5-ND	Low Noise, JFET Quad Op Amp*	14-Dip	3.44	3.11	2.50
TL074CDT	497-2204-1-ND	Low Noise, JFET Quad Op Amp	14-SOIC	1.06	.85	.64
TL074CDT	497-2204-2-ND	Low Noise, JFET Quad Op Amp	14-SOIC	746.24/2,500		
TL074CN	497-2205-5-ND	Low Noise, JFET Quad Op Amp	14-Dip	.92	.78	.58
TL074IDT	497-4056-1-ND	Low Noise, JFET Quad Op Amp	14-SOIC	1.30	1.13	.89
TL074IDT	497-4056-2-ND	Low Noise, JFET Quad Op Amp	14-SOIC	1073.60/2,500		
TL074IN	497-2206-5-ND	Low Noise, JFET Quad Op Amp	14-Dip	1.30	1.14	.88
TL074IYDT	497-10228-1-ND	Low Noise, JFET Quad Op Amp*	14-SOIC	1.35	1.21	.96
TL074IYDT	497-10228-2-ND	Low Noise, JFET Quad Op Amp*	14-SOIC	1242.56/2,500		
TL081ACD	497-2207-1-ND	JFET Single Op Amp	8-SOIC	1.41	1.26	1.00
TL081ACD	497-2207-2-ND	JFET Single Op Amp	8-SOIC	1295.36/2,500		
TL081CN	497-2209-5-ND	JFET Single Op Amp	8-Dip	.80	.67	.51
TL081IDT	497-2210-1-ND	JFET Single Op Amp	8-SOIC	1.11	.96	.76
TL081IDT	497-2210-2-ND	JFET Single Op Amp	8-SOIC	915.20/2,500		
TL081IN	497-7661-5-ND	JFET Single Op Amp*	8-Dip	1.03	.90	.70
TL082ACN	497-7662-5-ND	JFET Dual Op Amp*	8-Dip	1.06	.93	.72
TL082AIYDT	497-10229-1-ND	JFET Dual Op Amp*	8-SOIC	2.25	2.02	1.60
TL082AIYDT	497-10229-2-ND	JFET Dual Op Amp*	8-SOIC	2069.76/2,500		
TL082BIYDT	497-10230-1-ND	JFET Dual Op Amp*	8-SOIC	2.37	2.12	1.68
TL082BIYDT	497-10230-2-ND	JFET Dual Op Amp*	8-SOIC	2171.84/2,500		
TL082CDT	497-2212-1-ND	JFET Dual Op Amp	8-SOIC	1.06	.85	.64
TL082CDT	497-2212-2-ND	JFET Dual Op Amp	8-SOIC	746.24/2,500		
TL082CN	497-2213-5-ND	JFET Dual Op Amp	8-Dip	.92	.78	.58
TL082CPT	497-4057-1-ND	JFET Dual Op Amp	8-TSSOP	1.17	1.02	.80
TL082CPT	497-4057-2-ND	JFET Dual Op Amp	8-TSSOP	1543.17/4,000		
TL082IDT	497-2214-1-ND	JFET Dual Op Amp	8-SOIC	1.24	1.07	.85
TL082IDT	497-2214-2-ND	JFET Dual Op Amp	8-SOIC	1020.80/2,500		
TL082IN	497-3032-5-ND	JFET Dual Op Amp	8-Dip	1.14	1.00	.77
TL082IPT	497-8065-1-ND	JFET Dual Op Amp*	8-TSSOP	1.41	1.26	1.00
TL082IPT	497-8065-2-ND	JFET Dual Op Amp*	8-TSSOP	2072.58/4,000		
TL082IYDT	497-10231-1-ND	JFET Dual Op Amp*	8-SOIC	2.14	1.92	1.52
TL082IYDT	497-10231-2-ND	JFET Dual Op Amp*	8-SOIC	1967.68/2,500		
TL084ACD	497-2215-1-ND	JFET Quad Op Amp	14-SOIC	1.52	1.36	1.08
TL084ACD	497-2215-2-ND	JFET Quad Op Amp	14-SOIC	1400.96/2,500		
TL084ACN	497-2216-5-ND	JFET Quad Op Amp	14-Dip	1.39	1.24	.98
TL084AIDT	497-4752-1-ND	JFET Quad Op Amp	14-SOIC	1.77	1.59	1.27
TL084AIDT	497-4752-2-ND	JFET Quad Op Amp	14-SOIC	1636.80/2,500		
TL084BCD	497-8066-1-ND	JFET Quad Op Amp*	14-SOIC	4.66	4.00	3.26
TL084BCD	497-8066-2-ND	JFET Quad Op Amp*	14-SOIC	4491.52/2,500		
TL084BIDT	497-7042-1-ND	JFET Quad Op Amp*	14-SOIC	2.84	2.45	2.00
TL084BIDT	497-7042-2-ND	JFET Quad Op Amp*	14-SOIC	2745.60/2,500		
TL084BIN	497-7043-5-ND	JFET Quad Op Amp*	14-Dip	2.52	2.28	1.84
TL084CD	497-3033-5-ND	JFET Quad Op Amp	14-SOIC	.99	.83	.63
TL084CDT	497-2217-1-ND	JFET Quad Op Amp	14-SOIC	1.14	.92	.69
TL084CDT	497-2217-2-ND	JFET Quad Op Amp	14-SOIC	802.56/2,500		
TL084CN	497-2218-5-ND	JFET Quad Op Amp	14-Dip	1.01	.89	.69
TL084CPT	497-2219-1-ND	JFET Quad Op Amp	14-TSSOP	1.30	1.12	.88
TL084CPT	497-2219-2-ND	JFET Quad Op Amp	14-TSSOP	1063.04/2,500		
TL084IDT	497-2220-1-ND	JFET Quad Op Amp	14-SOIC	1.37	1.19	.94
TL084IDT	497-2220-2-ND	JFET Quad Op Amp	14-SOIC	1126.40/2,500		
TL084IN	497-2221-5-ND	JFET Quad Op Amp	14-Dip	1.30	1.14	.88
TL084IPT	497-8067-1-ND	JFET Quad Op Amp*	14-TSSOP	1.75	1.56	1.24
TL084IPT	497-8067-2-ND	JFET Quad Op Amp*	14-TSSOP	1605.12/2,500		
TL084IYDT	497-10232-1-ND	JFET Quad Op Amp*	14-SOIC	1.41	1.26	1.00
TL084IYDT	497-10232-2-ND	JFET Quad Op Amp*	14-SOIC	1295.36/2,500		
TS27L2ACD	497-7673-1-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1.91	1.71	1.36
TS27L2ACD	497-7673-2-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1760.00/2,500		
TS27L2ACN	497-7674-5-ND	Precision LP, CMOS Dual Op Amp*	8-Dip	1.91	1.71	1.88
TS27L2AID	497-2250-5-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	2.89	2.61	2.10
TS27L2AID	497-2250-6-ND	Precision LP, CMOS Dual Op Amp*	8-Dip	2.89	2.61	2.18
TS27L2BCD	497-8082-1-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1.87	1.69	1.36
TS27L2BCD	497-8082-2-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	2495.68/2,500		
TS27L2BIDT	497-8083-1-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	4.41	3.78	3.09
TS27L2BIDT	497-8083-2-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	4245.12/2,500		
TS27L2CDT	497-6774-1-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1.30	1.12	.88
TS27L2CDT	497-6774-2-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1063.04/2,500		
TS27L2CN	497-7676-5-ND	Precision LP, CMOS Dual Op Amp*	8-Dip	2.98	2.71	2.18
TS27L2CPT	497-8084-1-ND	Precision LP, CMOS Dual Op Amp*	8-TSSOP	2.37	2.12	1.68
TS27L2CPT	497-8084-2-ND	Precision LP, CMOS Dual Op Amp*	8-TSSOP	3474.94/4,000		
TS27L2IDT	497-2251-1-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	1.80	1.61	1.28
TS27L2IDT	497-2251-2-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	1654.40/2,500		
TS27L2IPT	497-8085-1-ND	Precision LP, CMOS Dual Op Amp*	8-TSSOP	2.53	2.18	1.78
TS27L2IPT	497-8085-2-ND	Precision LP, CMOS Dual Op Amp*	8-TSSOP	3914.24/4,000		
TS27L4AID	497-2252-5-ND	Precision LP, CMOS Quad Op Amp	14-SOIC	2.44	2.20	1.77
TS27L4AID	497-2252-6-ND	Precision LP, CMOS Quad Op Amp	14-Dip	2.44	2.20	1.77
TS27L4CDT	497-8086-1-ND	Precision LP, CMOS Quad Op Amp*	14-SOIC	2.53	2.27	1.80
TS27L4CDT	497-8086-2-ND	Precision LP, CMOS Quad Op Amp*	14-SOIC	2330.24/2,500		
TS27L4CN	497-2254-5-ND	Precision LP, CMOS Quad Op Amp	14-Dip	1.49	1.33	1.05
TS27L4IDT	497-2255-1-ND	Precision LP, CMOS Quad Op Amp	14-SOIC	1.97	1.77	1.40
TS27L4IDT	497-2255-2-ND	Precision LP, CMOS Quad Op Amp	14-SOIC	1812.80/2,500		
TS27L4IN	497-2256-5-ND	Precision LP, CMOS Quad Op Amp	14-Dip	1.97	1.75	1.38
TS27L4IPT	497-8087-1-ND	Precision LP, CMOS Quad Op Amp*	14-TSSOP	2.32	2.10	1.69
TS27L4IPT	497-8087-2-ND	Precision LP, CMOS Quad Op Amp*	14-TSSOP	3094.08/2,500		
TS27M2ACD	497-8088-1-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	2.55	2.30	1.85
TS27M2ACD	497-8088-2-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	3393.28/2,500		
TS27M2AIDT	497-2257-1-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	2.03	1.81	1.44
TS27M2AIDT	497-2257-2-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	1862.08/2,500		
TS27M2AIN	497-2258-5-ND	Precision LP, CMOS Dual Op Amp	8-Dip	1.90	1.69	1.33
TS27M2BIDT	497-4445-1-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	4.41	3.78	3.09
TS27M2BIDT	497-4445-2-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	4245.12/2,500		
TS27M2CDT	497-8089-1-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1.44	1.24	.98
TS27M2CDT	497-8089-2-ND	Precision LP, CMOS Dual Op Amp*	8-SOIC	1179.20/2,500		
TS27M2CPT	497-8089-1-ND	Precision LP, CMOS Dual Op Amp*	8-TSSOP	2.37	2.12	1.68
TS27M2CPT	497-8089-2-ND	Precision LP, CMOS Dual Op Amp*	8-TSSOP	3474.94/4,000		
TS27M2IDT	497-2259-1-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	2.07	1.86	1.48
TS27M2IDT	497-2259-2-ND	Precision LP, CMOS Dual Op Amp	8-SOIC	1907.84/2,500		
TS27M2IN	497-2260-5-ND	Precision LP, CMOS Dual Op Amp	8-Dip	1.61	1.43	1.13
TS27M4CDT	497-8090-1-ND	Precision LP, CMOS Quad Op Amp*	14-SOIC	2.53	2.27	1.80
TS27M4CDT	497-8090-2-ND	Precision LP, CMOS Quad Op Amp*	14-SOIC	2330.24/2,500		
TS27M4IN	497-2263-5-ND	Precision LP, CMOS Quad Op Amp	14-Dip	1.82	1.64	1.32

STMicroelectronics		DigiKey (Cont.)		AMPLIFIERS AND LINEAR		
				RoHS Compliant Parts Available		
STMicroelectronics Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	10	100
TS27M4IPT	497-8091-1-ND	Precision LP, CMOS Quad Op Amp*	14-TSSOP	3.15	2.71	2.22
TS27M4IPT	497-8091-2-ND	Precision LP, CMOS Quad Op Amp*	14-TSSOP	3044.80/2,500		
TS271ACD	497-2242-1-ND	CMOS Programmable LP Single Op Amp	8-SOIC	1.51	1.36	1.08
TS271ACD	497-2242-2-ND	CMOS Programmable LP Single Op Amp	8-SOIC	1710.72/2,500		
TS271ACN	497-2243-5-ND	CMOS Programmable LP Single Op Amp	8-Dip	1.39	1.24	.98
TS271BIDT	497-8075-1-ND	CMOS Programmable LP Single Op Amp*	8-SOIC	2.24	2.03	1.63
TS271BIDT	497-8075-2-ND	CMOS Programmable LP Single Op Amp*	8-SOIC	2995.52/2,500		
TS271CDT	497-8076-1-ND	CMOS Programmable LP Single Op Amp*	8-SOIC	1.46	1.31	1.04
TS271CDT	497-8076-2-ND	CMOS Programmable LP Single Op Amp*	8-SOIC	1344.64/2,500		
TS271CN	497-7670-5-ND	CMOS Programmable LP Single Op Amp*	8-Dip	1.06	.94	.74
TS271IDT	497-2244-1-ND	CMOS Programmable LP Single Op Amp	8-SOIC	1.41	1.26	1.00
TS271IDT	497-2244-2-ND	CMOS Programmable LP Single Op Amp	8-SOIC	1295.36/2,500		
TS272ACD	497-8077-1-ND	CMOS Dual Op Amp*	8-SOIC	2.55	2.30	1.85
TS272ACD	497-8077-2-ND	CMOS Dual Op Amp*	8-SOIC	3393.28/2,500		
TS272AID	497-2245-5-ND	CMOS Dual Op Amp	8-SOIC	1.86	1.65	1.31
TS272AIN	497-2246-5-ND	CMOS Dual Op Amp	8-Dip	2.07	1.84	1.45
TS272BIDT	497-8078-1-ND	CMOS Dual Op Amp*	8-SOIC	4.41	3.78	3.09
TS272BIDT	497-8078-2-ND	CMOS Dual Op Amp*	8-SOIC	4245.12/2,500		
TS272CD	497-3037-5-ND	CMOS Dual Op Amp	8-SOIC	1.86	1.65	1.31
TS272CN	497-7671-5-ND	CMOS Dual Op Amp*	8-Dip	1.52	1.35	1.07
TS272CPT	497-8079-1-ND	CMOS Dual Op Amp*	8-TSSOP	1.75	1.56	1.24
TS272CPT	497-8079-2-ND	CMOS Dual Op Amp*	8-TSSOP	2568.19/4,000		
TS272IDT	497-2247-1-ND	CMOS Dual Op Amp	8-SOIC	2.10	1.89	1.50
TS272IDT	497-2247-2-ND	CMOS Dual Op Amp	8-SOIC	2379.52/2,500		
TS272IPT	497-8080-1-ND	CMOS Dual Op Amp*	8-TSSOP	2.59	2.32	1.84
TS272IPT	497-8080-2-ND	CMOS Dual Op Amp*	8-TSSOP	3807.23/4,000		
TS274ACD	497-8081-1-ND	CMOS Quad Op Amp*	14-SOIC	4.41	3.78	3.09
TS274ACD	497-8081-2-ND	CMOS Quad Op Amp*	14-SOIC	4245.12/2,500		
TS2740CD	497-4060-1-ND	CMOS Quad Op Amp	14-SOIC	1.58	1.41	1.12
TS2740CD	497-4060-2-ND	CMOS Quad Op Amp	14-SOIC	1450.24/2,500		
TS274CN	497-7672-5-ND	CMOS Quad Op Amp*	14-Dip	1.82	1.61	1.27
TS274IDT	497-2249-1-ND	CMOS Quad Op Amp	14-SOIC	2.56	2.21	1.80
TS274IDT	497-2249-2-ND	CMOS Quad Op Amp	14-SOIC	2474.56/2,500		
TS274IN	497-5196-ND	CMOS Quad Op Amp*	14-Dip	2.52	2.28	1.84
TS321AILT	497-8093-1-ND	Low Power Single Op Amp*	SOT-23-5	1.46	1.31	1.04
TS321AILT	497-8093-2-ND	Low Power Single Op Amp				