



Fig.	Output Voltage	I Out (A)	Input Voltage	Digi-Key Part No.	Price Each	10	100	Digi-Key Part No.	Tape and Reel Pricing	Lineage Power Part No.
Converters										
1	3.0 - 6.0	10.0	18 - 30	555-1106-1-ND†	23.00	20.19	18.13	555-1106-2-ND	3813.75/250	AXB030X43-SRZ
2	3.3	20.0	36 - 75	555-1100-ND	52.08	45.98	41.43	—	—	EQW020A0F1Z
3	3.3	15.0	36 - 75	555-1104-1-ND†	55.20	48.71	43.84	555-1104-2-ND	5386.50/140	KW015A0F41-SRZ
4	3.3	15.0	36 - 75	555-1105-ND	55.20	48.71	43.84	—	—	KW015A0F41Z
5	48.0	2.4	38 - 75	555-1108-ND	68.00	60.00	54.00	—	—	PIM200FZ
6	3.3	50.0	36 - 75	555-1110-ND	106.00	96.00	86.00	—	—	QPW050A0F1Z
7	3.3	25.0	36 - 75	555-1113-ND	71.19	62.86	56.57	—	—	QRW025A0F1Z
7	3.3	35.0	36 - 75	555-1114-ND	87.10	76.90	69.20	—	—	QRW035A0F1Z
8	3.3	3.5	36 - 75	555-1118-1-ND†	25.90	22.40	20.30	555-1118-2-ND	2652.75/150	SW003A5F91-SRZ
9	3.3	3.5	36 - 75	555-1119-ND	25.90	22.40	20.30	—	—	SW003A5F91Z
1	5.0 - 15.0	8.0	20 - 30	555-1107-1-ND†	23.30	20.50	18.40	555-1107-2-ND	3915.00/250	AXB050X43-SRZ
7	5.0	25.0	36 - 75	555-1112-ND	87.10	76.90	69.20	—	—	QRW025A0A1Z
8	5.0	3.0	36 - 75	555-1116-1-ND†	25.90	22.40	20.30	555-1116-2-ND	2652.75/150	SW003A0A91-SRZ
9	5.0	3.0	36 - 75	555-1117-ND	25.90	22.40	20.30	—	—	SW003A0A91Z
2	12.0	6.0	36 - 75	555-1098-ND	52.08	45.98	41.43	—	—	EQW006A0B1Z
6	12.0	18.0	36 - 75	555-1109-ND	46.56	43.98	41.16	—	—	QBW018A0B1Z
7	12.0	10.0	36 - 75	555-1111-ND	87.10	76.90	69.20	—	—	QRW010A0B1Z
9	12.0	1.2	36 - 75	555-1115-ND	25.90	22.40	20.30	—	—	SW001A2B91Z
Filters										
10	—	10	100	555-1101-ND	18.80	16.55	14.40	—	—	FLTR100V10Z
11	—	20	100	555-1102-ND	28.10	25.20	21.95	—	—	FLTR100V20Z
12	—	5.0	75	555-1103-ND	17.00	15.00	13.30	—	—	FLTR75V05Z

† Cut Tape