

Honeywell

Sensing and Control **Sensors Hall Effect Sensors**

Fig.	Supply Voltage (VDC)	Output Current	Output Type	Terminal Type	Polarity	Digi-Key Part No.	Price Each			T & R Pricing 1,000#	Honeywell Part No.
							1	50	100		
1	3.8 - 30	10mA	Sink	Lead Wires	—	480-1992-ND	5.90	3.70	3.52	—	SR16C-J6
2	4.5 - 24	40mA	Sink	Lead Wires	—	480-1990-ND	24.75	17.95	17.33	—	4AV16F
3	3.8 - 30	20mA	Sink	Lead Wires	Unipolar	480-1991-ND	6.37	4.00	3.80	—	SR13C-A1
4	3.8 - 30	40mA	Sink	Lead Wires	—	480-1993-ND	7.99	5.12	4.80	—	SR17C-J6
5	3.8 - 30	20mA	Sink	SOT89	Bipolar	480-2011-1-ND	3.17	2.72	2.27	695.00	SS511AT
	3.8 - 30	20mA	Sink		Unipolar	480-2012-1-ND	1.41	1.22	1.01	586.00	SS541AT
	3.8 - 30	20mA	Sink		Bipolar Latch	480-2013-1-ND	3.17	2.72	2.27	695.00	SS561AT
	4.5 - 24	20mA	Sink		Bipolar	480-2010-1-ND	2.61	2.24	1.87	1080.00	SS51T
6	4.5 - 24	40mA	Sink	Lead Wires	—	480-2021-ND	22.29	16.17	15.61	—	1GT101DC
7	8 - 16	10mA	Source	PC Board	Ratiometric Linear	480-2007-ND	12.29	8.36	7.92	—	91SS12-2
	6.6 - 12.6	1mA	Sink/Source		Ratiometric	480-2008-ND	16.72	11.40	10.83	—	SS94A1
	6.6 - 12.6	1mA	Sink/Source		Ratiometric	480-2009-ND	17.57	12.56	11.93	—	SS94A1F
	4.5 - 24	20mA	Sink		Bipolar	480-1998-ND	1.12	.96	.84	—	SS40A
8	4.5 - 24	20mA	Sink	PC Board	Bipolar	480-1999-ND	1.35	.68	.63	—	SS41
	3.8 - 30	20mA	Sink		Bipolar	480-2000-ND	2.67	1.51	1.47	—	SS411A
	3.8 - 30	20mA	Sink		Unipolar	480-2001-ND	1.62	.84	.77	—	SS441A
	3.8 - 30	20mA	Sink		Unipolar	480-2002-ND	1.40	.72	.67	—	SS443A
	3.8 - 30	20mA	Sink		Bipolar Latch	480-2003-ND	1.62	.84	.77	—	SS461A
	3.8 - 30	20mA	Sink		Bipolar Latch	480-2004-ND	1.44	.75	.69	—	SS466A
	4.5 - 10.5	1.5mA	Sink/Source		Ratiometric	480-2005-ND	2.10	1.12	1.07	—	SS495A
	3 - 6.5	1.5mA	Source		Analog	480-2006-ND	1.70	.90	.83	—	SS49E
9	4.5 - 24	20mA	Sink	Lead Wires	Unipolar	480-2014-ND	19.03	13.60	12.92	—	103SR13A-1

◆ RoHS Compliant ‡ For Tape and Reel part number, change 1-ND to 2-ND.

Temperature — RoHS Compliant

Fig.	Supply Voltage	Supply Current	Temperature Sensing Range	Length (Inch)	Termination	Packaging Type	Digi-Key Part No.	Price Each			Honeywell Part No.
								1	50	100	
8	10.0 VDC	1mA	-40°C - 150°C	—	SIP	Plastic Case	480-2017-ND	4.34	2.55	2.45	TD5A
9	10.0 VDC	1mA	—	1.5	Lead Wires	3/8-24 UNF-2A	480-2016-ND	23.38	16.96	16.37	TD4A

Magnet — RoHS Compliant

Fig.	Outside Diameter mm (Inch)	Thread Dim.	Length Inch (mm)	Digi-Key Part No.	Price Each			Honeywell Part No.
					1	50	100	
10	7.9 (0.31)	8-32	0.67 (17.0)	480-2015-ND	9.78	6.32	6.12	102MG11

Current Sensor — RoHS Compliant

Fig.	Supply Voltage (VDC)	Output Current	Output Type	Terminal Type	Polarity	Sensor Type	Current Type	Response Time	Digi-Key Part No.	Price Each			Honeywell Part No.
										1	50	100	
11	5.4 - 13.2	—	Voltage	PCB	—	Open Loop Linear	AC or DC	3µs	480-1994-ND	16.91	11.53	10.96	CSLA2CD
12	4.5 - 10.5	1.5mA	Voltage	PCB	Positive	Open Loop	DC	50µs	480-1995-ND	8.88	5.92	5.55	CSLH3A45
13	4.75 - 5.25	12.5mA	Current	PCB	—	Closed Loop Linear	AC or DC	≤0.2µs	480-1996-ND	20.83	14.88	14.14	CSNX25

Switch — RoHS Compliant

Fig.	Supply Voltage (VDC)	Output Current	Output Type	Transistor State	Digi-Key Part No.	Price Each			Honeywell Part No.
						1	50	100	
14	4.5 - 24.0	10mA	Sink	Normally Off	480-2018-ND	8.50	5.67	5.32	VX10

MR — RoHS Compliant


Fig.	Supply Voltage (VDC)	Output Current	Output Type	Polarity	Operate Point	Release Point @25°C	Digi-Key Part No.	Price Each			Honeywell Part No.
								1	50	100	
15	3.8 - 30.0	20mA	Sink	Omnipolar	1.5 mT	1.1 mT	480-1997-ND	3.34	1.93	1.82	2SS52M

Oxygen Sensors and Oxygen Sensor Interface Boards — RoHS Compliant

Fig.	Supply Voltage	Oxygen Sensors Supply Current	Oxygen Range	Gas Flow Rate	Output Signal	Digi-Key Part No.	Price Each			Honeywell Part No.
							1	50	100	
Oxygen Sensors										
17	—	—	2 - 3000 mbar	0 - 10 m/sec.	—	480-2088-ND	166.10	132.47	—	GMS10RVS
16	—	—	2 - 3000 mbar	0 - 20 m/sec.	—	480-2089-ND	265.40	203.15	—	KGZ-10SP
18	—	—	2 - 3000 mbar	0 - 20 m/sec.	—	480-2090-ND	278.79	220.75	—	KGZ-10
19	24.0 VDC ±5%	500mA	0 - 100%	0 - 10 m/sec.	1 - 10 Volt	480-2092-ND	1511.50	1322.56	—	MF010-0-LC2
			0 - 25%	0 - 10 m/sec.	4 - 20mA	480-2093-ND	1511.50	1322.56	—	MF010-0-LC3
			0 - 100%	0 - 10 m/sec.	4 - 20mA	480-2094-ND	1511.50	1322.56	—	MF010-0-LC4
Oxygen Sensor Interface Boards										
—	24.0 VDC ±20%	—	0 - 25%	—	0 - 10 Volt	480-2095-ND	468.57	390.48	—	DE800.V.1
			0 - 100%	—	0 - 10 Volt	480-2096-ND	754.91	650.79	—	DE800.V.2
			0 - 25%	—	4 - 20mA	480-2097-ND	468.58	390.48	—	DE800.A.1
			0 - 100%	—	4 - 20mA	480-2098-ND	468.58	390.48	—	DE800.A.2
—	±15.0 VDC ±10%	—	0 - 25%	—	0 - 10 Volt	480-2099-ND	304.32	242.51	—	ELECDIT.V.1
			0 - 100%	—	0 - 10 Volt	480-2100-ND	348.02	280.67	—	ELECDIT.V.2
—	24.0 VDC ±20%	—	0 - 25%	—	0 - 10 Volt	480-2103-ND	354.98	286.28	—	OXYMAC50.V.1
			0 - 100%	—	0 - 10 Volt	480-2104-ND	354.98	286.28	—	OXYMAC50.V.2
			0 - 25%	—	4 - 20mA	480-2105-ND	354.98	286.28	—	OXYMAC50.A.1
			0 - 100%	—	4 - 20mA	480-2106-ND	354.98	286.28	—	OXYMAC50.A.2

Liquid Level Sensors

Fig.	Operating Temperature	Description	Level Type	Digi-Key Part No.	Price Each			Honeywell Part No.
					1	10	100	
1	-25°C - 80°C -40°C - 125°C	Screw In, M12 Thread, Plastic	1	480-2022-ND	23.75	19.36	16.63	LLE101000
				480-2026-ND	34.32	28.17	24.65	LLE101101
2	-25°C - 80°C -40°C - 125°C	Screw In, M12 Thread, Plastic	2	480-2023-ND	23.75	19.36	16.63	LLE102000
				480-2027-ND	34.32	28.17	24.65	LLE102101
3	-25°C - 80°C -40°C - 125°C	Screw In, M12 Thread, Plastic	3	480-2024-ND	23.75	19.36	16.63	LLE103000
				480-2028-ND	34.32	28.17	24.65	LLE103101
4	-25°C - 80°C -40°C - 125°C	Push In, Plastic	5	480-2025-ND	23.75	19.36	16.63	LLE105000
				480-2029-ND	34.32	28.17	24.65	LLE105101
5	-40°C - 125°C -40°C - 125°C	Industrial High Air, Stainless Industrial Low Air, Stainless	5	480-2030-ND	127.04	108.36	97.15	LLN8651721
				480-2031-ND	127.04	108.36	97.15	LLN865172-2



N

More Product Available Online: www.digikey.com

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380

(T083) 2421