


### TIP Telecom Duty Fuses (Telecom Interface Protector)



#### Electrical Characteristics:

Rated Current	Pre-arcing Rating	
	100%	300%
350mA - 1.50A	2 hr. minimum	300ms...5s

**Approvals:** cULus Recognized: File No. E67006. Complies to EIA-15-98B; Telcordia GR-1089

#### Features:

- For UL60950/1950 3rd Edition applications • Highly defined cutoff times
- Flame resistant encapsulated casing • Low internal resistance • Irreversible physical separation • Stable characteristics under varying temperatures

**Maximum Fault Currents:** ≤50A at 125VAC; ≤35A at 125VDC


#### Material:

- Base and Cap: Brown thermoplastic (polyamide PA 6.6), UL 94-V0; • Round Pins: Copper alloy, tin-plated

Amp Rating	Voltage Rating	Digi-Key Part No.	Price Each	Tape & Ammo-Pk Qty.	Pricing†
<b>TIP 385 Series</b>					
.350	125	WK4560BK-ND	.59 .55	1,400	247.95/M
1.00	125	WK4563BK-ND	.59 .55	1,400	247.95/M
1.25	125	WK4564BK-ND	.59 .55	1,400	247.95/M
1.50	125	WK4565BK-ND	.59 .55	1,400	247.95/M

† For Tape and Ammo Pack number, change BK-ND to TB-ND.

### Picofuse Fast Acting 125V 275 Series



**Applicable Standards:** • UL 248-14 • CSA C22.2 No. 248.14

**Approvals:** • UL Listed: File No. E 67006 (125mA - 7A) • cUL Listed: File No. E 67006 (125mA - 7A) • UL Recognized: File No. E 67006 (10A) • CSA Certified: File No. 51378 (10A)

**Features:** • Subminiature • Axial Leads

**Materials:** • Body: Ceramic tube, Heat Shrink tube • Plug-on Caps: Copper alloy, tin plated

**Operating Temperature:** -25°C - 70°C (consider de-rating)

#### Electrical Characteristics:




Rated Current	Pre-arcing Rating	
	200%	200% Wickmann Tested
125mA - 10.00A	<60s	<5s

Amp Rating (A)	Voltage Rating	Digi-Key Part No.	Cut Tape Price Each	Tape & Reel Pricing†
			1 10	2,500
<b>275 Series</b>				
4.00	125	WK1092CT-ND	.36 .34	168.00/M
10.0	125	WK1095CT-ND	.36 .34	—

† For Tape and Reel part number, change CT-ND to TR-ND.

### TE5 Fuseholder



#### Material:


- Black thermoplastic UL 94-V0
- Terminals: Brass, tin-plated for soldering

#### Rated Values:

250V; 6.3A; UL Recognized

WK0009-ND	.....	\$1.28/1	\$11.82/10	\$88.65/100
-----------	-------	----------	------------	-------------

### TE5 Sub-Miniature Fuses - UL 248-14



#### Approvals (395 and 396 Series):

cUL Listed, UL Listed for .050A - 6.30A. MITI approved for 1.00A - 5.00A

#### Features:

- Fast-acting and time-lag
- Material: Brown thermoplastic UL 94-V0
- Round Pins: Copper alloy, tin-plated
- Soldering Heat Resistance: 260°C, 10 seconds (IEC 60068-2-20)
- Plug-in holders available

#### Electrical Characteristics:

Series	Rated Current	Pre-arcing Rating	
		100%	200%
395	50mA - 6.3A	> 4 hr.	< 5 sec.
396	50mA - 6.3A	> 4 hr.	< 60 sec.

**Breaking Capacity:** 100A at 125VAC

Amp Rating	Voltage Rating	Digi-Key Part No.	Bulk Price Each		
			1	10	100
<b>Fast-Acting 395 Series</b>					
.050	125	WK4322BK-ND	3.99	3.69	2.77
.063	125	WK4325BK-ND	2.56	2.37	1.78
.100	125	WK4327BK-ND	.94	.87	.65
.125	125	WK4328BK-ND	.94	.87	.65
.160	125	WK4330BK-ND	.94	.87	.65
.200	125	WK4334BK-ND	.94	.87	.65
.250	125	WK4335BK-ND	.94	.87	.65
.315	125	WK4337BK-ND	.94	.87	.65
.400	125	WK4340BK-ND	.94	.87	.65
.500	125	WK4341BK-ND	.94	.87	.65
.630	125	WK4343BK-ND	.94	.87	.65
.800	125	WK4346BK-ND	.94	.87	.65
1.00	125	WK4348BK-ND	.94	.87	.65
1.25	125	WK4350BK-ND	.94	.87	.65
1.60	125	WK4353BK-ND	.94	.87	.65
2.00	125	WK4357BK-ND	.94	.87	.65
2.50	125	WK4358BK-ND	.94	.87	.65
3.15	125	WK4324BK-ND	.94	.87	.65
4.00	125	WK4362BK-ND	.94	.87	.65
5.00	125	WK4363BK-ND	.94	.87	.65
6.30	125	WK4366BK-ND	.94	.87	.65
<b>Time-Lag 396 Series</b>					
.063	125	WK4425BK-ND	1.34	1.24	.93
.080	125	WK4426BK-ND	1.34	1.24	.93
.100	125	WK4427BK-ND	1.19	1.10	.83
.125	125	WK4428BK-ND	1.19	1.10	.83
.160	125	WK4430BK-ND	1.19	1.10	.83
.200	125	WK4434BK-ND	.99	.92	.69
.250	125	WK4435BK-ND	.99	.92	.69
.315	125	WK4437BK-ND	.99	.92	.69
.400	125	WK4440BK-ND	.99	.92	.69
.500	125	WK4441BK-ND	.99	.92	.69
.630	125	WK4443BK-ND	.99	.92	.69
.800	125	WK4446BK-ND	.99	.92	.69
1.00	125	WK4448BK-ND	.99	.92	.69


Amp Rating	Voltage Rating	Digi-Key Part No.	Bulk Price Each		
			1	10	100
1.25	125	WK4450BK-ND	.99	.92	.69
1.60	125	WK4453BK-ND	.99	.92	.69
2.00	125	WK4457BK-ND	.99	.92	.69
2.50	125	WK4458BK-ND	.99	.92	.69
3.15	125	WK4424BK-ND	.99	.92	.69
4.00	125	WK4462BK-ND	.99	.92	.69
5.00	125	WK4463BK-ND	.99	.92	.69
6.30	125	WK4466BK-ND	.99	.92	.69

#### RoHS Compliant

• WK0117-KIT-ND Digi-Key® TE5 Sub-Miniature Fuse Kit  
10 each of TE5 Sub-Miniature Fuses indicated and 20 each of TE5 Fuseholders (WK0009-ND) ..... \$143.81

### Wickmann® Brand Product

### TR5 Sub-Miniature Fuses - IEC 60127-3



#### Approvals:

• 370 Series: SEMKO Approved, cULus Recognized, CCC Approved (.050A - 5.00A), VDE Approved (.050A - 5.00A) Expert Report (6.30A), METI Approved (1.00A - 4.00A)

• 372 Series: SEMKO Approved, cULus Recognized, CCC Approved (.050A - 6.30A), VDE Approved (.050A - 4.00A) Expert Report (5.00A, 6.30A), METI Approved (1.00A - 4.00A), Korean Approved (.050A - 6.30A)

• 382 Series: SEMKO Approved and cULus Recognized (1.00A - 6.30A), CCC Approved (1.00A - 4.00A), VDE Approved (1.00A - 4.00A) Expert Report (5.00A, 6.30A), METI Approved (1.00A - 5.00A), Koren Approval (1.00A - 4.00A)

**Material:** • Base and Cap: Brown thermoplastic, Polyamide PA 6.6, UL 94V-0 • Round Pins: Copper alloy, tin-plated

**Features:** • Fast-acting and Time-lag • Soldering Heat Resistance: 260°C, 10 seconds (IEC 60068-2-20) • Plug-in holders available

#### Electrical Characteristics:



Pre-arcing Rating				
150%	210%	275%	400%	1000%
<b>Series 370 - 50mA - 6.30A</b>				
>1 hr.	<30 min.	10ms - 3sec.	3 - 300ms	<20ms
<b>Series 372 - 50mA - 6.30A</b>				
>1 hr.	<2 min.	400ms - 10sec.	150ms - 3sec.	20 - 150ms
<b>Series 382 - 1.00A - 6.30A</b>				
>1 hr.	<2 min.	400ms - 10sec.	150ms - 3sec.	20 - 150ms

**BREAKING CAPACITY:** 370 and 372 Series: 35A at 250VAC for (.050A - 3.15A), 40A for (4.00A), 50A for (5.00A, 6.30A) 382 Series: 100A at 250VAC (1.00A - 6.30A)

Amp Rating	Voltage Rating	Digi-Key Part No.	Bulk Price Each		
			1	10	100
<b>Fast-Acting 370 Series (IEC 60127-3/III)</b>					
.050	250	WK4922BK-ND	3.38	3.13	2.35
.063	250	WK4925BK-ND	3.38	3.13	2.35
.080	250	WK4926BK-ND	3.38	3.13	2.35
.100	250	WK4927BK-ND	.71	.66	.49
.125	250	WK4928BK-ND	.71	.66	.49
.160	250	WK4930BK-ND	.71	.66	.49
.200	250	WK4934BK-ND	.71	.66	.49
.250	250	WK4935BK-ND	.71	.66	.49
.315	250	WK4937BK-ND	.71	.66	.49
.400	250	WK4940BK-ND	.71	.66	.49
.500	250	WK4941BK-ND	.71	.66	.49
.630	250	WK4943BK-ND	.71	.66	.49
.800	250	WK4946BK-ND	.71	.66	.49
1.00	250	WK4948BK-ND	.71	.66	.49
1.25	250	WK4950BK-ND	.71	.66	.49
1.60	250	WK4953BK-ND	.71	.66	.49
2.00	250	WK4957BK-ND	.71	.66	.49
2.50	250	WK4958BK-ND	.71	.66	.49
3.15	250	WK4924BK-ND	.71	.66	.49
4.00	250	WK4962BK-ND	.71	.66	.49
5.00	250	WK4963BK-ND	.71	.66	.49
6.30	250	WK4964BK-ND	.71	.66	.49
<b>Time-Lag 372 Series (IEC 60127-3/IV)</b>					
.050	250	WK4222BK-ND	.95	.88	.66
.063	250	WK4225BK-ND	.95	.88	.66
.080	250	WK4226BK-ND	.77	.72	.54
.100	250	WK4227BK-ND	.77	.72	.54
.125	250	WK4228BK-ND	.77	.72	.54
.160	250	WK4230BK-ND	.77	.72	.54
.200	250	WK4234BK-ND	.77	.72	.54

#### RoHS Compliant

† Conducting Path minimum: 2mm<sup>2</sup> (Continued)

**TR5 Sub-Minature Fuses – IEC 60127-3 (Cont.)**

Amp Rating	Voltage Rating	Digi-Key Part No.	Bulk Price Each		
			1	10	100
.250	250	WK4235BK-ND	.77	.72	.54
.315	250	WK4237BK-ND	.68	.63	.48
.400	250	WK4240BK-ND	.68	.63	.48
.500	250	WK4241BK-ND	.68	.63	.48
.630	250	WK4243BK-ND	.68	.63	.48
.800	250	WK4246BK-ND	.68	.63	.48
1.00	250	WK4248BK-ND	.68	.63	.48
1.25	250	WK4250BK-ND	.68	.63	.48
1.60	250	WK4253BK-ND	.68	.63	.48
2.00	250	WK4257BK-ND	.68	.63	.48
2.50	250	WK4258BK-ND	.68	.63	.48
3.15	250	WK4224BK-ND	.68	.63	.48
4.00	250	WK4262BK-ND	.68	.63	.48
5.00	250	WK4263BK-ND	.68	.63	.48
6.30	250	WK4264BK-ND	.68	.63	.48

**Time-Lag High Breaking 382 Series (IEC 60127-3/IV) – RoHS Compliant**

Amp Rating	Voltage Rating	Digi-Key Part No.	RoHS	Compliant	
1.00	250	WK6207BK-ND	.80	.75	.56
2.00	250	WK6208BK-ND	.80	.75	.56
2.50	250	WK6209BK-ND	.80	.75	.56
3.15	250	WK6210BK-ND	.80	.75	.56
4.00	250	WK6211BK-ND	.80	.75	.56
5.00	250	WK6212BK-ND	.80	.75	.56
6.30	250	WK6213BK-ND	.80	.75	.56

◆ **RoHS Compliant** † Conducting Path minimum: 2mm<sup>2</sup>  
 • **Digi-Key® TR5 Sub-Minature Fuse IEC 60127-3 Kit** 10 each of **TR5 Sub-Minature Fuses** indicated and 15 each of **TR5 Fuseholders (WK0001-ND)**  
**WK0113-KIT-ND – RoHS Compliant** .....\$124.76

**TR5 Sub-Minature Fuses – UL 248-14**

**Approvals:**  
**373 and 374 Series:** UL Listed, CSA Certified Approved (.050A – 10A)


**Material:** • Base and cap: Brown thermoplastic UL 94-V0, insulated • Round Pins: Copper alloy, tin-plated

**Features:** • Fast-acting and Time-lag • Soldering Heat Resistance: 260°C, 10 seconds, IEC-60068-2-20 • Plug-in holders available

**Electrical Characteristics:**

Series	Rated Current	Pre-arcing Rating	
		100%	200%
373	50mA – 10.A	4 hr. minimum	5 sec. maximum
374	50mA – 10.00A	4 hr. minimum	60 sec. maximum

Amp Rating	Voltage Rating	Digi-Key Part No.	Bulk Price Each		
			1	10	100
<b>Fast-Acting 373 Series</b>					
.050	250	WK3022BK-ND	4.03	3.72	2.79
.063	250	WK3025BK-ND	4.03	3.72	2.79
.080	250	WK3026BK-ND	4.03	3.72	2.79
.100	250	WK3027BK-ND	.89	.83	.62
.125	250	WK3028BK-ND	.89	.83	.62
.160	250	WK3030BK-ND	.89	.83	.62
.200	250	WK3034BK-ND	.89	.83	.62
.250	250	WK3035BK-ND	.89	.83	.62
.315	250	WK3037BK-ND	.89	.83	.62
.400	250	WK3040BK-ND	.89	.83	.62
.500	250	WK3041BK-ND	.89	.83	.62
.630	250	WK3043BK-ND	.89	.83	.62
.800	250	WK3046BK-ND	.89	.83	.62
1.00	250	WK3048BK-ND	.89	.83	.62
1.25	250	WK3050BK-ND	.89	.83	.62
1.60	250	WK3053BK-ND	.89	.83	.62
2.00	250	WK3057BK-ND	.89	.83	.62
2.50	250	WK3058BK-ND	.89	.83	.62
3.15	250	WK3024BK-ND	.89	.83	.62
4.00	250	WK3062BK-ND	.89	.83	.62
5.00	250	WK3063BK-ND	.89	.83	.62
6.30	250	WK3066BK-ND	.89	.83	.62
10.00	250	WK3071BK-ND	.89	.83	.62




Amp Rating	Voltage Rating	Digi-Key Part No.	Bulk Price Each		
<b>Time-Lag 374 Series – RoHS Compliant</b>					
1 10 100					
.050	250	WK4022BK-ND	1.38	1.28	.96
.063	250	WK4025BK-ND	1.38	1.28	.96
.080	250	WK4026BK-ND	1.29	1.19	.90
.100	250	WK4027BK-ND	1.29	1.19	.90
.125	250	WK4028BK-ND	1.09	1.01	.76
.160	250	WK4030BK-ND	1.09	1.01	.76
.200	250	WK4034BK-ND	1.09	1.01	.76
.250	250	WK4035BK-ND	.99	.92	.69
.315	250	WK4037BK-ND	.99	.92	.69
.400	250	WK4040BK-ND	.89	.83	.62
.500	250	WK4041BK-ND	.89	.83	.62
.630	250	WK4043BK-ND	.89	.83	.62
.800	250	WK4046BK-ND	.89	.83	.62
1.00	250	WK4048BK-ND	.89	.83	.62
1.25	250	WK4050BK-ND	.89	.83	.62
1.60	250	WK4053BK-ND	.89	.83	.62
2.00	250	WK4057BK-ND	.89	.83	.62
2.50	250	WK4058BK-ND	.89	.83	.62
3.15	250	WK4024BK-ND	.89	.83	.62
4.00	250	WK4062BK-ND	.89	.83	.62
5.00	250	WK4063BK-ND	.89	.83	.62
6.30	250	WK4066BK-ND	.89	.83	.62
10.00	250	WK4071BK-ND	.99	.92	.69

◆ **RoHS Compliant**  
 • **Digi-Key® TR5 Sub-Minature Fuse UL-248-14 Kit** 10 each of **TR5 Sub-Minature Fuses** indicated and 15 each of **TR5 Fuseholders (WK0001-ND)**  
**WK0116-KIT-ND – RoHS Compliant** .....\$142.91

**TR5 Panel Mount Fuseholder**

**Material:**  
 • Holder: Black thermoplastic UL 94V-0  
 • Polyamide PA  
 • Metal Parts: Copper alloy, solderable tinned  
 • Cap: Transparent thermoplastic polycarbonate PC, UL 94V-0



Description	Digi-Key Part No.	Price Each		Wickmann Part No.
1 10				
Panel Mount Holder	WK6224-ND	1.21	1.12	5700000000
PC Mount Holder	WK6225-ND	.99	.92	5710000000
Transparent Cap	WK6226-ND	.46	.42	5750000000

**TR5 / TE5 SMT Fuseholder**


**Material:** • Black thermoplastic UL 94-V0 • Terminals: Brass, tin-plated • UL Recognized

Amp Rating	Voltage Rating	Digi-Key Part No.	Cut Tape Price Each		Tape & Reel Pricing†
1 10					
6.3	250	WK0010CT-ND	1.61	1.49	719.20/M

† For Tape and Reel Part Number, change CT-ND to TR-ND.

**TR5 Fuseholder**

**Material:** • Thermoplastic, UL 94V-0  
 • Polyester PCT • Terminals: brass, tin-plated  
**Rated Values:** 250V; 6.3A



Height (A) mm	Digi-Key Part No.	Price Each		Wickmann Part No.
		1	10	
3.0	WK0001-ND	.81	.75	5600000131
4.3	WK6235-ND	.66	.61	5600000100

**UL / CSA Fuses Metric (5x20mm) – UL 248-14**

Equivalent to:  
  
 198 Series – Glass

Wickmann	Littelfuse	Bussmann
198 Series	239	GMD

**Approvals:**  
**198 Series:**  
 UL listed, CSA certified, .250A – 3.50A

**Electrical Characteristics:**

Series	Rated Current	Pre-arcing Rating	
		135%	200%
198	.250A – 2.50A	< 1 hr	5-120 sec.
	3.50A	< 1 hr	12-120 sec.

**Breaking Capacity:**

**198 Series:** 35A at 250VAC (.250A – .800A); 100A at 250VAC (2.50A); 10,000A at 125VAC (.250A)

Amp Rating	Voltage Rating	Digi-Key Part No.	Price Each		
1 10 100					
<b>Time-Lag 198 Series</b>					
.250	250	WK4835-ND	.42	.39	.30

**Wickmann® Brand Product**

**IEC 60127-2 Metric (5x20mm) Fuses**



**Approvals:**

**194 Series:** SEMKO Approved, VDE Approved (0.200A – 6.30A), cULus Recognized (0.315A – 16A), CCC Approved (1.00A – 6.30A)  
**195 Series:** SEMKO Approved, VDE Approved, BSI Approved, IMQ Approved, CCC Approved (0.032A – 6.30A), cULus Recognized (0.032A – 12.50A), METI Approved (1.00A – 5.00A)

**Electrical Characteristics:**

Series	Rated Current	Pre-arcing Rating			
		150%	210%	275%	400%
194	0.200 ~ 2.50A	> 1 hr.	< 30 min.	10ms ~ 2 sec.	3 ~ 300 ms
	0.040 ~ .080A	> 1 hr.	< 2 min.	200ms ~ 10 sec.	40ms ~ 3 sec.
195	.125 ~ 2.50A	> 1 hr.	< 2 min.	600ms ~ 10 sec.	150 ms ~ 3 sec.
					20 ~ 300 ms

**BREAKING CAPACITY:** 194 Series: 1500A at 250VAC 195 Series: 35A at 250VAC for (.040 – 2.50A)

Amp Rating	Voltage Rating	Digi-Key Part No.	Price Each		
1 10 100					
<b>Fast Acting, High Breaking Capacity 194 Series</b>					
.315	250	WK2037-ND	.96	.89	.67
1.60	250	WK2053-ND	.54	.50	.38
<b>Time-Lag 195 Series</b>					
.080	250	WK5026-ND	.84	.78	.59
<b>PC Board Mount (5x20mm) – RoHS Compliant</b>					
–	–	WK0011-ND	.37	.35	.26

Shock-Safe fuseholders for 1/4 x 1-1/4" (3AG) or 5 x 20mm fuses built according to UL 512 and IEC 60127-6 and CSA C22.2 No. 39 • VDE, SEMKO rated for use up to 250 Volts. • Casing made of black thermoplastic with UL 94V-0 ratings. Injection-molded terminals prevent intermittent connections. • PC Mount versions include additional pin(s) for added stability from torsional forces seen during fuse removal. • Panel Mount versions have combination 3/16" quick-connect/solderable tabs. • Body Material: White thermoplastic, UL 94V-0 rated (Wickmann Part No. 6490001009 only)

include additional pin(s) for added stability from torsional forces seen during fuse removal. • Panel Mount versions have combination 3/16" quick-connect/solderable tabs. • Body Material: White thermoplastic, UL 94V-0 rated (Wickmann Part No. 6490001009 only)





Fig.	Description	Dimensions - mm			Rated Current Amps VDE	UL/CSA (Amps)	Digi-Key Part No.	Price Each			Wickmann Part No.
		A	B	C				1	10	100	
1	Vertical 3AG (6.3 x 32mm) Holder	46.3	—	—	6.3	16	WK6229-ND*	1.50	1.39	1.04	8110000005
2	Vertical (5 x 20mm) Holder	32.6	—	—	6.3	16	WK6233-ND*	1.16	1.08	.81	8310000005
3	Horizontal 3AG (6.3 x 32mm) Holder	45.7	27.94	1.90	6.3	16	WK6228-ND*	1.95	1.81	1.36	8100000005
4	Horizontal (5 x 20mm) Holder	32.0	12.7	1.80	6.3	16	WK6232-ND*	1.12	1.04	.78	8300000005
5	Panel Mount 3AG (6.3 x 32mm) Holder	45.7	—	—	10	16	WK6227-ND*	1.61	1.49	1.12	8000000005
6	Panel Mount (5 x 20mm) Holder	32.0	—	—	6.3	16	WK6231-ND*	1.29	1.19	.90	8200000005
7	3AG (6.3 x 32mm) Fuse Cap	33.8	9.20	—	—	—	WK6230-ND*	1.18	1.09	.82	8160000005
8	(5 x 20mm) Fuse Cap	20.6	9.20	—	—	—	WK6234-ND*	.82	.76	.57	8350000005
9	PC Mount (5 x 20mm) Holder	—	—	—	6.3	—	WK0011-ND	.37	.35	.26	6490001009
<b>Digi-Key® Fuseholder Kit</b> 1 each of WK6233-ND and WK6234-ND combined in a single bag								—	—	—	—
* Fuse Cap and Holder are sold separate								2.89	2.66	2.24	—

**VISHAY Beyschlag MFU Series Thin Film Chip Fuses**  
0402, 0603, 0805 and 1206 Sizes

**Applications:** • Information technology • Telecommunications • Industrial electronics • Audio/video electronics • Automotive electronics  
**Features:** • Advanced thin film technology • Very quick acting fuse characteristics • Outstanding stability of fusing characteristics • Precise repeatability of fusing characteristics • Compatible with lead-free and lead containing soldering processes



Type	Dimensions - mm		
	H	L	W
MFU 0402	0.32 ± 0.05	1.0 ± 0.05	0.5 ± 0.05
MFU 0603	0.45 ± 0.1/-0.05	1.55 ± 0.05	0.85 ± 0.1
MFU 0805	0.45 ± 0.1/-0.05	2.0 ± 0.1	1.25 ± 0.15
MFU 1206	0.55 ± 0.1	3.2 ± 0.1/-0.2	1.6 ± 0.15

Voltage Rating (V)	Amp Rating (A)	Digi-Key Part No.	Cut Tape Price Each			Tape & Reel Pricing 1,000	Vishay Part No.	
			1	10	100			
0402	32	.5 MFU0402.50CT-ND	.65	.60	.46	289.00	MFU0402FF00500E100	
		.63 MFU0402.63CT-ND	.65	.60	.46	289.00	MFU0402FF00630E100	
		.75 MFU0402.75CT-ND	.65	.60	.46	289.00	MFU0402FF00750E100	
		.8 MFU0402.80CT-ND	.65	.60	.46	289.00	MFU0402FF00800E100	
		1 MFU0402.1.00CT-ND	.49	.46	.34	216.00	MFU0402FF01000E100	
		1.25 MFU0402.1.25CT-ND	.49	.46	.34	216.00	MFU0402FF01250E100	
	0603	32	1.5 MFU0402.1.50CT-ND	.49	.46	.34	216.00	MFU0402FF01500E100
			1.6 MFU0402.1.60CT-ND	.49	.46	.34	216.00	MFU0402FF01600E100
			1.75 MFU0402.1.75CT-ND	.49	.46	.34	216.00	MFU0402FF01750E100
			2 MFU0402.2.00CT-ND	.49	.46	.34	216.00	MFU0402FF02000E100
			.5 MFU0603.50CT-ND	.47	.44	.33	211.00	MFU0603FF00500P100
			.63 MFU0603.63CT-ND	.47	.44	.33	208.00	MFU0603FF00630P100
0805		32	.75 MFU0603.75CT-ND	.47	.44	.33	208.00	MFU0603FF00750P100
			.8 MFU0603.80CT-ND	.47	.44	.33	208.00	MFU0603FF00800P100
			1 MFU0603.1.00CT-ND	.35	.33	.25	156.00	MFU0603FF01000P100
			1.25 MFU0603.1.25CT-ND	.35	.33	.25	156.00	MFU0603FF01250P100
			1.5 MFU0603.1.50CT-ND	.35	.33	.25	156.00	MFU0603FF01500P100
			1.6 MFU0603.1.60CT-ND	.35	.33	.25	156.00	MFU0603FF01600P100
	1206	63	1.75 MFU0603.1.75CT-ND	.35	.33	.25	156.00	MFU0603FF01750P100
			2 MFU0603.2.00CT-ND	.35	.33	.25	156.00	MFU0603FF02000P100
			2.5 MFU0603.2.50CT-ND	.35	.33	.25	156.00	MFU0603FF02500P100
			3 MFU0603.3.00CT-ND	.35	.33	.25	156.00	MFU0603FF03000P100
			3.15 MFU0603.3.15CT-ND	.35	.33	.25	156.00	MFU0603FF03150P100
			3.5 MFU0603.3.50CT-ND	.35	.33	.25	156.00	MFU0603FF03500P100
32		4 MFU0603.4.00CT-ND	.35	.33	.25	156.00	MFU0603FF04000P100	
		5 MFU0603.5.00CT-ND*	.47	.44	.33	216.00	MFU0603FF05000P100	
		.5 MFU0805.50CT-ND	.63	.59	.45	281.00	MFU0805FF00500P100	
		.63 MFU0805.63CT-ND	.63	.59	.45	281.00	MFU0805FF00630P100	
		.75 MFU0805.75CT-ND	.63	.59	.45	281.00	MFU0805FF00750P100	
		.8 MFU0805.80CT-ND	.63	.59	.45	281.00	MFU0805FF00800P100	

Voltage Rating (V)	Amp Rating (A)	Digi-Key Part No.	Cut Tape Price Each			Tape & Reel Pricing 1,000	Vishay Part No.
			1	10	100		
0805	32	1 MFU0805.1.00CT-ND	.47	.45	.34	211.00	MFU0805FF01000P100
		1.25 MFU0805.1.25CT-ND	.47	.45	.34	211.00	MFU0805FF01250P100
		1.5 MFU0805.1.50CT-ND	.47	.45	.34	211.00	MFU0805FF01500P100
		1.6 MFU0805.1.60CT-ND	.47	.45	.34	211.00	MFU0805FF01600P100
		1.75 MFU0805.1.75CT-ND	.47	.45	.34	211.00	MFU0805FF01750P100
		2 MFU0805.2.00CT-ND	.47	.45	.34	211.00	MFU0805FF02000P100
	63	2.5 MFU0805.2.50CT-ND	.47	.45	.34	211.00	MFU0805FF02500P100
		3 MFU0805.3.00CT-ND	.47	.45	.34	211.00	MFU0805FF03000P100
		3.15 MFU0805.3.15CT-ND	.47	.45	.34	211.00	MFU0805FF03150P100
		3.5 MFU0805.3.50CT-ND	.47	.45	.34	211.00	MFU0805FF03500P100
		4 MFU0805.4.00CT-ND	.47	.45	.34	211.00	MFU0805FF04000P100
		5 MFU0805.5.00CT-ND*	.64	.59	.45	291.00	MFU0805FF05000P100
1206	63	.5 MFU1206.50CT-ND	.77	.72	.54	344.00	MFU1206FF00500P100
		.63 MFU1206.63CT-ND	.77	.72	.54	344.00	MFU1206FF00630P100
		.75 MFU1206.75CT-ND	.77	.72	.54	344.00	MFU1206FF00750P100
		.8 MFU1206.80CT-ND	.77	.72	.54	344.00	MFU1206FF00800P100
		1 MFU1206.1.00CT-ND	.58	.54	.41	257.00	MFU1206FF01000P100
		1.25 MFU1206.1.25CT-ND	.58	.54	.41	257.00	MFU1206FF01250P100
	32	1.5 MFU1206.1.50CT-ND	.58	.54	.41	257.00	MFU1206FF01500P100
		1.6 MFU1206.1.60CT-ND	.58	.54	.41	257.00	MFU1206FF01600P100
		1.75 MFU1206.1.75CT-ND	.58	.54	.41	257.00	MFU1206FF01750P100
		2 MFU1206.2.00CT-ND	.58	.54	.41	257.00	MFU1206FF02000P100
		2.5 MFU1206.2.50CT-ND	.58	.54	.41	257.00	MFU1206FF02500P100
		3 MFU1206.3.00CT-ND	.58	.54	.41	257.00	MFU1206FF03000P100
63	3.15 MFU1206.3.15CT-ND	.58	.54	.41	257.00	MFU1206FF03150P100	
	3.5 MFU1206.3.50CT-ND	.58	.54	.41	257.00	MFU1206FF03500P100	
	4 MFU1206.4.00CT-ND	.58	.54	.41	257.00	MFU1206FF04000P100	
	5 MFU1206.5.00CT-ND	.58	.54	.41	257.00	MFU1206FF05000P100	
	6.3 MFU1206.6.30CT-ND*	.78	.73	.55	357.00	MFU1206FF06300P100	

\* For Tape and Reel part number, change CT-ND to TR-ND. \* NEW!

Digi-Reel® Most SMT cutdown parts are available on a Digi-Reel®. For Digi-Reel part number, change 1-ND to 6-ND or CT-ND to DKR-ND. See Digi-Key® Services on page 2 for additional information.

**More Product Available Online: www.digikey.com**

Toll-Free: 1-800-344-4539 • Phone 218-681-6674 • Fax: 218-681-3380

(T091) 2019