



Fig.	Description	Dim. A Inch	Digi-Key Part No.	Pricing 10	100
PC Quick-Fit Tab Terminal					
1	.110" Female, Horizontal	—	3545K-ND	4.57	44.00
1	.110" Female, Horizontal	—	3549K-ND	4.57	44.00
1	.205" Female, Horizontal	—	3546K-ND	4.76	45.55
1	.205" Female, Horizontal	—	3550K-ND	4.76	45.55
1	.250" Female, Horizontal	—	3547K-ND	4.99	48.05
2	.110" Female, Vertical	—	3534K-ND	2.16	17.20
2	.110" Female, Vertical	—	3544K-ND	2.16	17.20
2	.205" Female, Vertical	—	3525K-ND	2.16	17.20
2	.250" Female, Vertical	—	3528K-ND	2.16	17.20
2	.187" Female, Vertical	—	3548K-ND	2.16	17.20
2	.187" Female, Vertical	—	3551K-ND	2.16	17.20
2	.205" Quick-Fit Vertical Terminal	—	3522K-ND	1.46	10.35
3	.110" Female, 18-22 Gage	—	1252K-ND	1.66	15.85
3	.187" Female, 16-22 Gage	—	1264K-ND	3.99	38.15
3	.205" Female, 16-20 Gage	—	4469K-ND	5.82	52.75
3	.250" Female, 16-20 Gage	—	4470K-ND	3.03	29.05
4	.205" Male, .020 Brass, Tin Plate, .046 Diameter	—	1286K-ND	1.00	7.10
4	.205" Male, .032 Brass, Tin Plate, .052 Diameter	—	1213K-ND	1.13	11.05
5	.205" Male, .020 Brass, Tin Plate, .046 Diameter	—	1286-STK-ND	.94	9.10
5	.205" Male, .032 Brass, Tin Plate, .052 Diameter	—	1213-STK-ND	1.13	8.10
6	.187" Male, .020 Brass, Tin Plate, .046 Diameter	—	4900K-ND	1.52	14.75
4	.187" Male, .020 Brass, Tin Plate, .046 Diameter	—	1285K-ND	.89	8.80
4	.187" Male, .032 Brass, Tin Plate, .052 Diameter	—	1212K-ND	1.03	7.30
5	.187" Male, .020 Brass, Tin Plate, .046 Diameter	—	1285-STK-ND	.93	6.65
5	.187" Male, .032 Brass, Tin Plate, .052 Diameter	—	1212-STK-ND	1.03	7.30
7	.110" Male, .020 Brass, Tin Plate, .046 Diameter	—	1267K-ND	1.14	11.05
7	.110" Male, .032 Brass, Tin Plate, .052 Diameter	—	1211K-ND	1.35	12.50
8	.110" Male, .020 Brass, Tin Plate, .046 Diameter	—	4903K-ND	2.38	22.60
8	.110" Male, .032 Brass, Tin Plate, .052 Diameter	—	4906K-ND	2.44	23.30
8	.187" Male, .020 Brass, Tin Plate, .046 Diameter	—	4904K-ND	2.28	21.85
8	.187" Male, .032 Brass, Tin Plate, .052 Diameter	—	4907K-ND	2.34	22.15
8	.250" Male, .032 Brass, Tin Plate, .056 Diameter	—	4966K-ND	1.72	12.70
8	.250" Male, .032 Brass, Tin Plate, .052 Diameter	—	1266K-ND	2.52	17.80
9	.250" Male, .032 Brass, Tin Plate, .106 Diameter	—	1265K-ND	2.46	17.35
4	.250" Male, .032 Brass, Tin Plate, .052 Diameter	—	1287K-ND	1.10	10.70
5	.250" Male, .032 Brass, Tin Plate, .052 Diameter	—	1287-STK-ND	1.10	10.70
10	.110"/.250" Male, .032 Brass, Tin Plate, .052 Diameter	—	1282K-ND	1.10	10.70
6	.250" Male, .032 Brass, Tin Plate, .067 Diameter	—	4901K-ND	2.25	15.75
11	.250" Male, .032 Brass, Tin Plate, .067 Diameter	—	4902K-ND	1.52	14.75
12	.250" Male, .032 Brass, Tin Plate, .052 Diameter	—	4908K-ND	3.23	31.05
13	.250" Male, .032 Brass, Tin Plate, .052 Diameter	—	1289K-ND	1.70	12.50
13	.250" Male, .032 Brass, Tin Plate, .052 Diameter	—	1289-STK-ND	1.65	11.70
14	.250" Male, .032 Brass, Tin Plate, .052 Diameter	—	1281K-ND	2.75	19.45
15	.250" Quick-Fit Vinyl Boot, Clear	—	4471K-ND	1.21	11.70
15	.250" Quick-Fit Vinyl Boot, Red	—	4472K-ND	1.21	11.70
15	.250" Quick-Fit Vinyl Boot, Blue	—	4473K-ND	1.21	11.70
15	.250" Quick-Fit Vinyl Boot, Yellow	—	4474K-ND	1.21	11.70
—	Terminal Hand Insertion Tool	—	1288K-ND	39.42/1	
MT Screw Terminal — RoHS Compliant					
16	Snap-In PC Horizontal	—	7690K-ND	5.09	37.80
17	Snap-In PC Horizontal, Captivated	—	7692K-ND†	5.09	41.30
17	PC Horizontal	—	8190K-ND	3.98	34.90
17	PC Horizontal, Captivated	—	7700K-ND†	4.80	39.15
18	Snap-In PC Vertical	—	7691K-ND	4.01	36.45
18	Snap-In PC Vertical, Captivated	—	7693K-ND†	4.86	39.60
19	PC Vertical	—	8191K-ND	3.67	33.85
19	PC Vertical, Captivated	—	7701K-ND†	4.57	37.00
20	Terminal PC Vertical, Heavy Duty	—	8196K-ND	7.87	63.45
21	Terminal Insert 10/32 Thread, Captivated	—	1202K-ND	10.82	103.95

Fig.	Description	Dim. A Inch	Digi-Key Part No.	Pricing 10	100
21	Screw Terminal Insert 10/32	—	1299K-ND	10.82	103.95
22	Screw Supplied Unassembled	—	8189K-ND	9.17	81.70
22	Screw Installed and Captivated	—	7702K-ND	10.45	85.75
Lockwasher Terminal Lugs — RoHS Compliant					
23	.018 Brass, Tin Plate	.120	908K-ND	1.33	12.70
23	.018 Brass, Tin Plate	.140	914K-ND	1.33	12.70
23	.018 Brass, Tin Plate	.171	915K-ND	1.33	12.70
24	.018 Brass, Tin Plate	.120	910K-ND	1.39	13.15
24	.018 Brass, Tin Plate	.140	918K-ND	1.39	13.15
24	.018 Brass, Tin Plate	.171	906K-ND	1.51	13.15
25	.018 Brass, Tin Plate	.120	903K-ND	1.43	13.75
25	.018 Brass, Tin Plate	.140	904K-ND	1.43	13.75
25	.018 Brass, Tin Plate	.171	905K-ND	1.43	13.75
26	.018 Brass, Tin Plate	.120	909K-ND	1.46	13.75
26	.018 Brass, Tin Plate	.140	916K-ND	1.46	13.75
26	.018 Brass, Tin Plate	.171	917K-ND	1.46	13.75
27	.013 Brass, Tin Plate	—	907K-ND	2.33	22.40
28	.018 Brass, Tin Plate	.120	7311K-ND	1.39	13.15
28	.018 Brass, Tin Plate	.140	7312K-ND	1.39	13.15
28	.018 Brass, Tin Plate	.171	7313K-ND	1.39	13.15
29	.018 Brass, Tin Plate	.120	7317K-ND	1.43	13.75
29	.018 Brass, Tin Plate	.140	7318K-ND	1.43	13.75
29	.018 Brass, Tin Plate	.171	7319K-ND	1.43	13.75
30	.018 Brass, Tin Plate	.120	7314K-ND	1.46	13.75
30	.018 Brass, Tin Plate	.140	7315K-ND	1.46	13.75
30	.018 Brass, Tin Plate	.171	7316K-ND	1.46	13.75
Solder Terminal Lugs — RoHS Compliant					
31	.015 Brass, Tin Plate	.120	7328K-ND	1.26	12.05
31	.015 Brass, Tin Plate	.140	7329K-ND	1.26	12.05
31	.015 Brass, Tin Plate	.171	7330K-ND	1.26	12.05
32	.016 Brass, Tin Plate	—	4004K-ND	1.12	10.70
33	.020 Brass, Tin Plate	.120	7331K-ND	1.36	12.85
33	.020 Brass, Tin Plate	.140	7332K-ND	1.36	12.85
33	.020 Brass, Tin Plate	.171	7333K-ND	1.32	12.40
34	.020 Brass, Tin Plate	.120	7325K-ND	1.32	12.40
34	.020 Brass, Tin Plate	.140	7326K-ND	1.36	12.85
34	.020 Brass, Tin Plate	.171	7327K-ND	1.32	12.40
Terminal Lugs — RoHS Compliant					
35	.015 Brass, Tin Plate	—	680K-ND	1.47	13.85
36	.020 Brass, Tin Plate	.500	4000K-ND	1.16	8.10
36	.020 Brass, Tin Plate	.562	4001K-ND	1.16	8.45
36	.020 Brass, Tin Plate	.750	4002K-ND	1.28	12.50
36	.020 Brass, Tin Plate	1.000	4003K-ND	1.39	13.50
Double Turret Series — RoHS Compliant					
—	TL-1 Brass, Tin Plate, .084" Length	—	1593-2K-ND	1.99	14.30
—	TL-1 Brass, Tin Plate, .082" Length	—	1573-2K-ND	2.16	19.35
—	TL-2 Brass, Tin Plate, .109" Length	—	1502-2K-ND	2.63	24.85
Tubular (Hollow) Turret Series — RoHS Compliant					
—	TL-2 Brass, Tin Plate, .084" Length	—	1562-2K-ND	3.93	35.90
PC Test Point Terminals — RoHS Compliant					
—	.020 Brass, Tin Plate, Slotted, .032" Diameter	—	1031K-ND	1.70	8.80
—	.025 Brass, Tin Plate, Slotted, .118" Diameter	—	1040K-ND	1.49	7.55
—	.025 Brass, Tin Plate, Loop, .040" Diameter	—	1249K-ND	1.73	8.90
—	.025 Brass, Tin Plate, Loop, .050" Diameter	—	1045K-ND	3.44	17.60
—	.025 Brass, Tin Plate, Loop, .098" Diameter	—	4952K-ND	1.55	10.90
90° Quick-Fit Rivet Terminal — RoHS Compliant					
—	.250" Tab, .032 Brass, 3 Pairs, .130" Diameter	—	1006K-ND	5.39	43.85

◆ RoHS Compliant † Screw Installed and Captivated

More Product Available Online: www.digikey.com