

TEXAS INSTRUMENTS		Digi-Key®		DIGITAL LOGIC (Continued)		
T. I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	25	100
SN74HC393D	296-8317-5-ND	Dual 4-Bit Binary Counter	14-SOIC	55	44	33
SN74HC393DBR	296-8318-1-ND	Dual 4-Bit Binary Counter	14-SSOP	50	40	30
SN74HC393DR	296-8318-2-ND	Dual 4-Bit Binary Counter	14-SSOP	280.00/2,000		
SN74HC393DR	296-14851-1-ND	Dual 4-Bit Binary Counter	14-SOIC	50	40	30
SN74HC393DR	296-14851-2-ND	Dual 4-Bit Binary Counter	14-SOIC	337.50/2,500		
SN74HC4000WR	296-8319-5-ND	Dual 4-Bit Binary Counter	14-Dip	48	36	27
SN74HC4000WR	296-8333-1-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	48	36	27
SN74HC4000WR	296-8333-2-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	320.00/2,000		
SN74HC540N	296-8334-5-ND	Tri-State Octal Buffer/Line Driver	20-Dip	62	47	35
SN74HC541DR	296-14855-1-ND	Tri-State Octal Buffer/Line Driver	20-SSOP	56	42	32
SN74HC541DR	296-14855-2-ND	Tri-State Octal Buffer/Line Driver	20-SSOP	372.00/2,000		
SN74HC541DWR	296-1202-5-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	52	39	30
SN74HC541DWR	296-1202-1-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	48	36	27
SN74HC541DWR	296-1202-2-ND	Tri-State Octal Buffer/Line Driver	20-SOIC	320.00/2,000		
SN74HC541N	296-1594-5-ND	Tri-State Octal Buffer/Line Driver	20-Dip	62	47	35
SN74HC541NSR	296-13218-1-ND	Tri-State Octal Buffer/Line Driver	20-SOP	56	42	32
SN74HC541NSR	296-13218-2-ND	Tri-State Octal Buffer/Line Driver	20-SOP	372.00/2,000		
SN74HC541PWR	296-8335-1-ND	Tri-State Octal Buffer/Line Driver	20-TSSOP	48	36	27
SN74HC541PWR	296-8335-2-ND	Tri-State Octal Buffer/Line Driver	20-TSSOP	320.00/2,000		
SN74HC573ADBDR	296-23257-1-ND	Tri-St. Octal Transparent D-Type Latch	20-SSOP	60	45	34
SN74HC573ADBDR	296-23257-2-ND	Tri-St. Octal Transparent D-Type Latch	20-SSOP	400.00/2,000		
SN74HC573ADWR	296-1203-5-ND	Tri-St. Octal Transparent D-Type Latch	20-SOIC	52	39	30
SN74HC573ADWR	296-1203-1-ND	Tri-St. Octal Transparent D-Type Latch	20-SOIC	48	36	27
SN74HC573ADWR	296-1203-2-ND	Tri-St. Octal Transparent D-Type Latch	20-SOIC	320.00/2,000		
SN74HC573AN	296-1596-5-ND	Tri-St. Octal Transparent D-Type Latch	20-Dip	66	50	38
SN74HC573APWR	296-8338-1-ND	Tri-St. Octal Transparent D-Type Latch	20-TSSOP	48	36	27
SN74HC573APWR	296-8338-2-ND	Tri-St. Octal Transparent D-Type Latch	20-TSSOP	320.00/2,000		
SN74HC574DWR	296-1597-5-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	52	39	30
SN74HC574DWR	296-1597-1-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	48	36	27
SN74HC574DWR	296-1597-2-ND	Tri-State Octal D-Type Flip-Flop	20-SOIC	320.00/2,000		
SN74HC574N	296-1598-5-ND	Tri-State Octal D-Type Flip-Flop	20-Dip	66	50	38
SN74HC574PWR	296-8339-1-ND	Tri-State Octal D-Type Flip-Flop	20-TSSOP	48	36	27
SN74HC574PWR	296-8339-2-ND	Tri-State Octal D-Type Flip-Flop	20-TSSOP	320.00/2,000		
SN74HC590AD	296-8340-5-ND	Tri-State 8-Bit Binary Counter	16-SOIC	68	51	39
SN74HC590AD	296-17132-1-ND	Tri-State 8-Bit Binary Counter	16-SOIC	60	45	34
SN74HC590AD	296-17132-2-ND	Tri-State 8-Bit Binary Counter	16-SOIC	487.50/2,500		
SN74HC590ADWR	296-8341-5-ND	Tri-State 8-Bit Binary Counter	16-SOIC	68	51	39
SN74HC590ADWR	296-14856-1-ND	Tri-State 8-Bit Binary Counter	16-SOIC	60	45	34
SN74HC590ADWR	296-14856-2-ND	Tri-State 8-Bit Binary Counter	16-SOIC	400.00/2,000		
SN74HC590AN	296-1599-5-ND	Tri-State 8-Bit Binary Counter	16-Dip	66	50	38
SN74HC594DWR	296-8342-5-ND	8-Bit Shift Register with Output Register	16-SOIC	72	54	41
SN74HC594N	296-8343-5-ND	8-Bit Shift Register with Output Register	16-Dip	75	63	50
SN74HC595D	296-8344-5-ND	Tri-State 8-Bit Shift Register	16-SOIC	48	36	27
SN74HC595DR	296-14857-1-ND	Tri-State 8-Bit Shift Register	16-SOIC	55	44	33
SN74HC595DR	296-14857-2-ND	Tri-State 8-Bit Shift Register	16-SOIC	372.50/2,500		
SN74HC595DWR	296-8345-5-ND	Tri-State 8-Bit Shift Register	16-SOIC	52	39	30
SN74HC595DWR	296-14858-1-ND	Tri-State 8-Bit Shift Register	16-SOIC	48	36	27
SN74HC595DWR	296-14858-2-ND	Tri-State 8-Bit Shift Register	16-SOIC	320.00/2,000		
SN74HC595N	296-1600-5-ND	Tri-State 8-Bit Shift Register	16-Dip	66	50	38
SN74HC595PWR	296-23258-1-ND	Tri-State 8-Bit Shift Register	16-TSSOP	48	36	27
SN74HC595PWR	296-23258-2-ND	Tri-State 8-Bit Shift Register	16-TSSOP	320.00/2,000		
SN74HC623DWR	296-8346-5-ND	Tri-State Octal Bus Transceiver	20-SOIC	5.20	4.16	3.51
SN74HC623N	296-8347-5-ND	Tri-State Octal Bus Transceiver	20-Dip	5.20	4.16	3.51
SN74HC640DWR	296-8348-5-ND	Tri-State Octal Bus Transceiver	20-SOIC	1.25	1.00	0.75
SN74HC640N	296-8349-5-ND	Tri-State Octal Bus Transceiver	20-Dip	1.35	1.13	0.90
SN74HC645DWR	296-8350-5-ND	Tri-State Octal Bus Transceiver	20-SOIC	1.32	1.10	0.88
SN74HC645N	296-8351-5-ND	Tri-State Octal Bus Transceiver	20-Dip	1.20	1.00	0.80
SN74HC646DWR	296-8352-5-ND	Tri-State Octal Bus Transceiver/Register	24-SOIC	1.32	1.10	0.88
SN74HC646N	296-8353-5-ND	Tri-State Octal Bus Transceiver/Register	24-Dip	1.20	1.00	0.80
SN74HC652DWR	296-8354-5-ND	Tri-State Octal Bus Transceiver/Register	24-SOIC	1.50	1.20	0.90
SN74HC652N	296-8355-5-ND	Tri-State Octal Bus Transceiver/Register	24-Dip	1.88	1.50	1.13
SN74HC682DWR	296-8356-1-ND	8-Bit Magnitude Comparator	20-SOIC	3.31	2.65	2.06
SN74HC682DWR	296-8356-2-ND	8-Bit Magnitude Comparator	20-SOIC	3748.00/2,000		
SN74HC682N	296-8357-5-ND	8-Bit Magnitude Comparator	20-Dip	3.31	2.65	2.06
SN74HC684DWR	296-8358-5-ND	8-Bit Magnitude Comparator	20-SOIC	5.80	4.64	3.92
SN74HC684N	296-8359-5-ND	8-Bit Magnitude Comparator	20-Dip	6.00	4.80	4.05
SN74HC688DWR	296-8360-5-ND	8-Bit Identity Comparator	20-SOIC	90	75	60
SN74HC688N	296-8361-5-ND	8-Bit Identity Comparator	20-Dip	81	68	54
SN74HC688PWR	296-8362-1-ND	8-Bit Identity Comparator	20-TSSOP	81	68	54
SN74HC688PWR	296-8362-2-ND	8-Bit Identity Comparator	20-TSSOP	718.00/2,000		
SN74HC4020D	296-8320-5-ND	14-Bit Async. Binary Counter	16-SOIC	60	45	34
SN74HC4020N	296-8321-5-ND	14-Bit Async. Binary Counter	16-Dip	54	41	31
SN74HC4040D	296-8322-5-ND	12-Bit Async. Binary Counter	16-SOIC	60	45	34
SN74HC4040DR	296-8323-1-ND	12-Bit Async. Binary Counter	16-SSOP	54	41	31
SN74HC4040DR	296-8323-2-ND	12-Bit Async. Binary Counter	16-SSOP	360.00/2,000		
SN74HC4040DR	296-14852-1-ND	12-Bit Async. Binary Counter	16-SOIC	54	41	31
SN74HC4040DR	296-14852-2-ND	12-Bit Async. Binary Counter	16-SOIC	440.00/2,500		
SN74HC4040N	296-8324-5-ND	12-Bit Async. Binary Counter	16-Dip	54	41	31
SN74HC4040PWR	296-8325-1-ND	12-Bit Async. Binary Counter	16-TSSOP	54	41	31
SN74HC4040PWR	296-8325-2-ND	12-Bit Async. Binary Counter	16-TSSOP	360.00/2,000		
SN74HC4060D	296-8326-5-ND	14-Stage Async. Binary Counter and Oscillator	16-SOIC	60	45	34
SN74HC4060DR	296-14853-1-ND	14-Stage Async. Binary Counter and Oscillator	16-SOIC	56	42	32
SN74HC4060DR	296-14853-2-ND	14-Stage Async. Binary Counter and Oscillator	16-SOIC	455.00/2,500		
SN74HC4060N	296-8209-5-ND	14-Stage Async. Binary Counter and Oscillator	16-Dip	56	42	32
SN74HC4066D	296-8327-5-ND	Quad Bilateral Analog Switch	14-SOIC	55	44	33
SN74HC4066DBR	296-8328-1-ND	Quad Bilateral Analog Switch	14-SSOP	50	40	30
SN74HC4066DBR	296-8328-2-ND	Quad Bilateral Analog Switch	14-SSOP	280.00/2,000		
SN74HC4066DR	296-14854-1-ND	Quad Bilateral Analog Switch	14-SOIC	50	40	30
SN74HC4066DR	296-14854-2-ND	Quad Bilateral Analog Switch	14-SOIC	337.50/2,500		
SN74HC4066PWR	296-8329-5-ND	Quad Bilateral Analog Switch	14-Dip	50	40	30
SN74HC4066PWR	296-8330-1-ND	Quad Bilateral Analog Switch	14-TSSOP	50	40	30
SN74HC4066PWR	296-8330-2-ND	Quad Bilateral Analog Switch	14-TSSOP	280.00/2,000		
SN74HC4851DGVDR	296-19251-1-ND	8-Channel Analog Mux/Demux	16-TVSOIP	70	53	40
SN74HC4851DGVDR	296-19251-2-ND	8-Channel Analog Mux/Demux	16-TVSOIP	468.00/2,000		
SN74HC4851DR	296-15740-1-ND	8-Channel Analog Mux/Demux	16-SOIC	64	48	36
SN74HC4851DR	296-15740-2-ND	8-Channel Analog Mux/Demux	16-SOIC	520.00/2,500		
SN74HC4851N	296-15741-5-ND	8-Channel Analog Mux/Demux	16-Dip	64	48	36
SN74HC4851PWR	296-16983-1-ND	8-Channel Analog Mux/Demux	16-TSSOP	64	48	36
SN74HC4851PWR	296-16983-2-ND	8-Channel Analog Mux/Demux	16-TSSOP	426.00/2,000		
SN74HC4851QDRQ1	296-17266-1-ND	8-Channel Analog Mux/Demux	16-SOIC	75	57	43
SN74HC4851QDRQ1	296-17266-2-ND	8-Channel Analog Mux/Demux	16-SOIC	610.00/2,500		
SN74HC4851QPWRQ1	296-19551-1-ND	8-Channel Analog Mux/Demux	16-TSSOP	75	57	43

T. I. Part No.	Digi-Key Part No.	Description	Pkg.	Price Each*		
				1	25	100
SN74HC4851QPWRQ1	296-19551-2-ND	8-Channel Analog Mux/Demux	16-TSSOP	500.00/2,000		
SN74HC4852DGVDR	296-19252-1-ND	Dual 4-1 Channel Analog Mux/Demux	16-TVSOIP	64	48	36
SN74HC4852DGVDR	296-19252-2-ND	Dual 4-1 Channel Analog Mux/Demux	16-TVSOIP	426.00/2,000		
SN74HC4852DR	296-19253-1-ND	Dual 4-1 Channel Analog Mux/Demux	16-SOIC	64	48	36
SN74HC4852DR	296-19253-2-ND	Dual 4-1 Channel Analog Mux/Demux	16-SOIC	520.00/2,500		
SN74HC4852N	296-17301-5-ND	Dual 4-1 Channel Analog Mux/Demux	16-Dip	64	48	36
SN74HC4852PWR	296-19254-1-ND	Dual 4-1 Channel Analog Mux/Demux	16-TSSOP	64	48	36
SN74HC4852PWR	296-19254-2-ND	Dual 4-1 Channel Analog Mux/Demux	16-TSSOP	426.00/2,000		
SN74HC7001D	296-8363-5-ND	Quad AND Gate w/Schmitt-Trigger Input	14-SOIC	1.30	1.04	0.78
SN74HC7001N	296-8364-5-ND	Quad AND Gate w/Schmitt-Trigger Input	14-Dip	1.41	1.18	0.94
SN74HC7002D	296-8365-5-ND	Quad NOR Gate w/Schmitt-Trigger Input	14-SOIC	2.00	1.60	1.20
SN74HC7002N	296-8366-5-ND	Quad NOR Gate w/Schmitt-Trigger Input	14-Dip	2.00	1.60	1.20
SN74HC7003D	296-8367-5-ND	Quad OR Gate w/Schmitt-Trigger Input	14-SOIC	2.48	1.98	1.54
SN74HC7003N	296-8368-5-ND	Quad OR Gate w/Schmitt-Trigger Input	14-Dip	2.25	1.80	1.40
HCT Family						
CD74HCT00E	296-2081-5-ND	Quad 2-Input NAND Gate	14-Dip	64	48	36
CD74HCT00M	296-9244-5-ND	Quad 2-Input NAND Gate	14-SOIC	52	39	30
CD74HCT00M96	296-14542-1-ND	Quad 2-Input NAND Gate	14-SOIC	48	36	27
CD74HCT00M96	296-14542-2-ND	Quad 2-Input NAND Gate	14-SOIC	390.00/2,500		
CD74HCT02E	296-2082-5-ND	Quad 2-Input NOR Gate	14-Dip	64	48	36
CD74HCT02M	296-12825-5-ND	Quad 2-Input NOR Gate	14-SOIC	52	39	30
CD74HCT03E	296-2134-5-ND	Quad 2-Input NAND Gate with OD	14-Dip	53	42	32
CD74HCT03M96	296-9245-1-ND	Quad 2-Input NAND Gate with OD	14-SOIC	46	37	26
CD74HCT03M96	296-9245-2-ND	Quad 2-Input NAND Gate with OD	14-SOIC	297.50/2,500		
CD74HCT04E	296-2083-5-ND	Hex Inverter/Buffer	14-Dip	64	48	36
CD74HCT04M	296-9246-5-ND	Hex Inverter/Buffer	14-SOIC	52	39	30
CD74HCT04M96	296-14543-1-ND	Hex Inverter/Buffer	14-SOIC	48	36	27
CD74HCT04M96	296-14543-2-ND	Hex Inverter/Buffer	14-SOIC	390.00/2,500		
CD74HCT04PWR	296-17123-1-ND	Hex Inverter/Buffer	14-TSSOP	48	36	27
CD74HCT04PWR	296-17123-2-ND	Hex Inverter/Buffer	14-TSSOP	320.00/2,000		
CD74HCT08E	296-2084-5-ND	Quad 2-Input AND Gate	14-Dip	64	48	36
CD74HCT08M	296-12828-5-ND	Quad 2-Input AND Gate	14-SOIC	52	39	30
CD74HCT08M96	296-14544-1-ND	Quad 2-Input AND Gate	1			