



Multilayer Ceramic Chip Capacitors (Cont.)



Case Size	Type	WV DC	Capacitance	Tolerance	Dim. T (mm)	Digi-Key Part No.	Cut Tape Pricing			Digi-Key Part No.	Tape and Reel		TDK Part No.
							10	100	500		Qty.	Pricing	
0603	COG (NPO)	50	10pF	±0.5pF	0.8	445-1269-1-ND	.17	.99	2.86	445-1269-2-ND	4,000	2.75/M	C1608COG1H100D
	COG (NPO)	50	11pF	±5%	0.8	445-5049-1-ND	.25	1.49	4.29	445-5049-2-ND	4,000	4.12/M	C1608COG1H110J
	COG (NPO)	50	12pF	±5%	0.8	445-1270-1-ND	.17	1.04	2.99	445-1270-2-ND	4,000	2.87/M	C1608COG1H120J
	COG (NPO)	50	13pF	±5%	0.8	445-5050-1-ND	.25	1.49	4.29	445-5050-2-ND	4,000	4.12/M	C1608COG1H130J
	COG (NPO)	50	15pF	±5%	0.8	445-1271-1-ND	.17	.99	2.86	445-1271-2-ND	4,000	2.75/M	C1608COG1H150J
	COG (NPO)	50	16pF	±5%	0.8	445-5051-1-ND	.25	1.49	4.29	445-5051-2-ND	4,000	4.12/M	C1608COG1H160J
	COG (NPO)	50	18pF	±5%	0.8	445-1272-1-ND	.17	.99	2.86	445-1272-2-ND	4,000	2.75/M	C1608COG1H180J
	COG (NPO)	50	20pF	±5%	0.8	445-5052-1-ND	.25	1.49	4.29	445-5052-2-ND	4,000	4.12/M	C1608COG1H200J
	COG (NPO)	50	22pF	±1%	0.8	445-5366-1-ND	2.67	15.77	45.48	445-5366-2-ND	4,000	43.66/M	C1608COG1H220F
	COG (NPO)	50	22pF	±2%	0.8	445-5372-1-ND	2.29	13.51	38.98	445-5372-2-ND	4,000	37.43/M	C1608COG1H220G
	COG (NPO)	50	22pF	±5%	0.8	445-1273-1-ND	.19	1.13	3.25	445-1273-2-ND	4,000	3.12/M	C1608COG1H220J
	COG (NPO)	50	24pF	±5%	0.8	445-5053-1-ND	.25	1.49	4.29	445-5053-2-ND	4,000	4.12/M	C1608COG1H240J
	COG (NPO)	50	27pF	±5%	0.8	445-1274-1-ND	.17	.99	2.86	445-1274-2-ND	4,000	2.75/M	C1608COG1H270J
	COG (NPO)	50	30pF	±5%	0.8	445-5054-1-ND	.25	1.49	4.29	445-5054-2-ND	4,000	4.12/M	C1608COG1H300J
	COG (NPO)	50	33pF	±5%	0.8	445-1275-1-ND	.19	1.13	3.25	445-1275-2-ND	4,000	3.12/M	C1608COG1H330J
	COG (NPO)	50	36pF	±5%	0.8	445-5055-1-ND	.25	1.49	4.29	445-5055-2-ND	4,000	4.12/M	C1608COG1H360J
	COG (NPO)	50	39pF	±5%	0.8	445-1276-1-ND	.17	1.04	2.99	445-1276-2-ND	4,000	2.87/M	C1608COG1H390J
	COG (NPO)	50	43pF	±5%	0.8	445-5056-1-ND	.25	1.49	4.29	445-5056-2-ND	4,000	4.12/M	C1608COG1H430J
	COG (NPO)	50	47pF	±1%	0.8	445-5367-1-ND	2.67	15.77	45.48	445-5367-2-ND	4,000	43.66/M	C1608COG1H470F
	COG (NPO)	50	47pF	±2%	0.8	445-5373-1-ND	2.29	13.51	38.98	445-5373-2-ND	4,000	37.43/M	C1608COG1H470G
	COG (NPO)	50	47pF	±5%	0.8	445-1277-1-ND	.16	.95	2.73	445-1277-2-ND	4,000	2.62/M	C1608COG1H470J
	COG (NPO)	50	51pF	±5%	0.8	445-5057-1-ND	.25	1.49	4.29	445-5057-2-ND	4,000	4.12/M	C1608COG1H510J
	COG (NPO)	50	56pF	±5%	0.8	445-1278-1-ND	.16	.95	2.73	445-1278-2-ND	4,000	2.62/M	C1608COG1H560J
	COG (NPO)	50	62pF	±5%	0.8	445-5058-1-ND	.25	1.49	4.29	445-5058-2-ND	4,000	4.12/M	C1608COG1H620J
	COG (NPO)	50	68pF	±5%	0.8	445-1279-1-ND	.17	.99	2.86	445-1279-2-ND	4,000	2.75/M	C1608COG1H680J
	COG (NPO)	50	75pF	±5%	0.8	445-5059-1-ND	.25	1.49	4.29	445-5059-2-ND	4,000	4.12/M	C1608COG1H750J
	COG (NPO)	50	82pF	±5%	0.8	445-1280-1-ND	.17	1.04	2.99	445-1280-2-ND	4,000	2.87/M	C1608COG1H820J
	COG (NPO)	50	91pF	±5%	0.8	445-5060-1-ND	.25	1.49	4.29	445-5060-2-ND	4,000	4.12/M	C1608COG1H910J
	COG (NPO)	50	100pF	±1%	0.8	445-5368-1-ND	2.67	15.77	45.48	445-5368-2-ND	4,000	43.66/M	C1608COG1H101F
	COG (NPO)	50	100pF	±2%	0.8	445-5374-1-ND	2.29	13.51	38.98	445-5374-2-ND	4,000	37.43/M	C1608COG1H101G
	COG (NPO)	50	100pF	±5%	0.8	445-1281-1-ND	.15	.90	2.60	445-1281-2-ND	4,000	2.50/M	C1608COG1H101J
	COG (NPO)	50	110pF	±5%	0.8	445-5061-1-ND	.53	3.15	9.10	445-5061-2-ND	4,000	8.74/M	C1608COG1H111J
	COG (NPO)	50	120pF	±5%	0.8	445-1282-1-ND	.27	1.58	4.55	445-1282-2-ND	4,000	4.37/M	C1608COG1H121J
	COG (NPO)	50	130pF	±5%	0.8	445-5062-1-ND	.53	3.15	9.10	445-5062-2-ND	4,000	8.74/M	C1608COG1H131J
	COG (NPO)	50	150pF	±5%	0.8	445-1283-1-ND	.23	1.35	3.90	445-1283-2-ND	4,000	3.75/M	C1608COG1H151J
	COG (NPO)	50	160pF	±5%	0.8	445-5063-1-ND	.53	3.15	9.10	445-5063-2-ND	4,000	8.74/M	C1608COG1H161J
	COG (NPO)	50	180pF	±5%	0.8	445-1284-1-ND	.28	1.62	4.68	445-1284-2-ND	4,000	4.49/M	C1608COG1H181J
	COG (NPO)	50	200pF	±5%	0.8	445-5064-1-ND	.53	3.15	9.10	445-5064-2-ND	4,000	8.74/M	C1608COG1H201J
	COG (NPO)	50	220pF	±1%	0.8	445-5369-1-ND	3.66	21.62	62.37	445-5369-2-ND	4,000	59.60/M	C1608COG1H221F
	COG (NPO)	50	220pF	±2%	0.8	445-5375-1-ND	3.28	19.37	55.88	445-5375-2-ND	4,000	53.36/M	C1608COG1H221G
	COG (NPO)	50	220pF	±5%	0.8	445-1285-1-ND	.23	1.35	3.90	445-1285-2-ND	4,000	3.75/M	C1608COG1H221J
	COG (NPO)	50	240pF	±5%	0.8	445-5065-1-ND	.53	3.15	9.10	445-5065-2-ND	4,000	8.74/M	C1608COG1H241J
	COG (NPO)	50	270pF	±5%	0.8	445-1286-1-ND	.30	1.76	5.07	445-1286-2-ND	4,000	4.87/M	C1608COG1H271J
	COG (NPO)	50	300pF	±5%	0.8	445-5066-1-ND	.53	3.15	9.10	445-5066-2-ND	4,000	8.74/M	C1608COG1H301J
	COG (NPO)	50	330pF	±5%	0.8	445-1287-1-ND	.28	1.67	4.81	445-1287-2-ND	4,000	4.62/M	C1608COG1H331J
	COG (NPO)	50	360pF	±5%	0.8	445-5067-1-ND	.53	3.15	9.10	445-5067-2-ND	4,000	8.74/M	C1608COG1H361J
	COG (NPO)	50	390pF	±5%	0.8	445-1288-1-ND	.35	2.07	5.98	445-1288-2-ND	4,000	5.74/M	C1608COG1H391J
	COG (NPO)	50	430pF	±5%	0.8	445-5068-1-ND	.53	3.15	9.10	445-5068-2-ND	4,000	8.74/M	C1608COG1H431J
	COG (NPO)	50	470pF	±1%	0.8	445-5370-1-ND	6.10	36.04	103.95	445-5370-2-ND	4,000	99.80/M	C1608COG1H471F
	COG (NPO)	50	470pF	±2%	0.8	445-5376-1-ND	3.35	19.82	57.17	445-5376-2-ND	4,000	54.75/M	C1608COG1H471G
	COG (NPO)	50	470pF	±5%	0.8	445-1289-1-ND	.33	1.98	5.72	445-1289-2-ND	4,000	5.49/M	C1608COG1H471J
	COG (NPO)	50	510pF	±5%	0.8	445-5069-1-ND	.61	3.60	10.40	445-5069-2-ND	4,000	9.98/M	C1608COG1H511J
	COG (NPO)	50	560pF	±5%	0.8	445-1290-1-ND	.40	2.39	6.89	445-1290-2-ND	4,000	6.61/M	C1608COG1H561J
	COG (NPO)	50	620pF	±5%	0.8	445-5070-1-ND	.61	3.60	10.40	445-5070-2-ND	4,000	9.98/M	C1608COG1H621J
	COG (NPO)	50	680pF	±5%	0.8	445-1291-1-ND	.40	2.34	6.76	445-1291-2-ND	4,000	6.49/M	C1608COG1H681J
	COG (NPO)	50	750pF	±5%	0.8	445-5071-1-ND	.69	4.05	11.70	445-5071-2-ND	4,000	11.23/M	C1608COG1H751J
	COG (NPO)	50	820pF	±5%	0.8	445-1292-1-ND	.45	2.66	7.66	445-1292-2-ND	4,000	7.36/M	C1608COG1H821J
	COG (NPO)	50	910pF	±5%	0.8	445-5072-1-ND	.69	4.05	11.70	445-5072-2-ND	4,000	11.23/M	C1608COG1H911J
	COG (NPO)	50	1000pF	±1%	0.8	445-5371-1-ND	12.20	72.07	207.90	445-5371-2-ND	4,000	199.59/M	C1608COG1H102F
	COG (NPO)	50	1000pF	±2%	0.8	445-5377-1-ND	10.67	63.06	181.91	445-5377-2-ND	4,000	174.64/M	C1608COG1H102G
	COG (NPO)	50	1000pF	±5%	0.8	445-1293-1-ND	.38	2.25	6.50	445-1293-2-ND	4,000	6.24/M	C1608COG1H102J
	COG (NPO)	50	1200pF	±5%	0.8	445-1294-1-ND	.91	5.41	15.59	445-1294-2-ND	4,000	14.97/M	C1608COG1H122J
	COG (NPO)	50	1500pF	±5%	0.8	445-1295-1-ND	.76	4.50	12.99	445-1295-2-ND	4,000	12.48/M	C1608COG1H152J
	COG (NPO)	50	1800pF	±5%	0.8	445-1296-1-ND	.76	4.50	12.99	445-1296-2-ND	4,000	12.48/M	C1608COG1H182J
	COG (NPO)	50	2200pF	±5%	0.8	445-1297-1-ND	.76	4.50	12.99	445-1297-2-ND	4,000	12.48/M	C1608COG1H222J
	COG (NPO)	50	2700pF	±5%	0.8	445-2669-1-ND	.99	5.86	16.90	445-2669-2-ND	4,000	15.94/M	C1608COG1H272J
	COG (NPO)	50	3300pF	±5%	0.8	445-1599-1-ND	1.37	8.11	23.39	445-1599-2-ND	4,000	22.46/M	C1608COG1H332J
	COG (NPO)	25	3900pF	±5%	0.8	445-2665-1-ND	1.91	11.26	32.49	445-2665-2-ND	4,000	31.19/M	C1608COG1E392J
	COG (NPO)	25	4700pF	±5%	0.8	445-2712-1-ND	1.91	11.26	32.49	445-2712-2-ND	4,000	31.19/M	C1608COG1E472J
	COG (NPO)	25	5600pF	±5%	0.8	445-2666-1-ND	2.29	13.51	38.98	445-2666-2-ND	4,000	37.43/M	C1608COG1E562J
	COG (NPO)	25	6800pF	±5%	0.8	445-2667-1-ND	2.29	13.51	38.98	445-2667-2-ND	4,000	37.43/M	C1608COG1E682J
	COG (NPO)	25	8200pF	±5%	0.8	445-2668-1-ND	2.67	15.77	45.48	445-2668-2-ND	4,000	43.66/M	C1608COG1E822J
	COG (NPO)	25	10000pF	±5%	0.8	445-2664-1-ND	2.67	15.77	45.48	445-2664-2-ND	4,000	43.66/M	C1608COG1E103J
	X7R	100	1000pF	±10%	0.8	445-1298-1-ND	.30	1.80	5.20	445-1298-2-ND	4,000	4.99/M	C1608X7R2A102K
	X7R	100	1000pF	±20%	0.8	445-1299-1-ND	.30	1.80	5.20	445-1299-2-ND	4,000		