



Multilayer Ceramic Chip Capacitors (Cont.)



Size Code	Type	WV DC	Capacitance	Tolerance	Dimension T (mm)	Digi-Key Part No.	Cut Tape Pricing			Digi-Key Part No.	Tape and Reel		Murata Part No.
							10	100	500		Qty.	Pricing	
0603	COG (NP0)	50	5pF	±.25pF	0.8	490-1370-1-ND	.26	1.53	4.42	490-1370-2-ND	4,000	4.16M	GRM1885C1HR50CZ01D
	COG (NP0)	50	7.5pF	±.25pF	0.8	490-1371-1-ND	.35	2.03	5.85	490-1371-2-ND	4,000	5.55M	GRM1885C1HR75CZ01D
	COG (NP0)	50	1.0pF	±.25pF	0.8	490-1372-1-ND	.26	1.53	4.42	490-1372-2-ND	4,000	4.16M	GRM1885C1H1R0CZ01D
	COG (NP0)	50	1.1pF	±.25pF	0.8	490-1373-1-ND	.35	2.03	5.85	490-1373-2-ND	4,000	5.62M	GRM1885C1H1R1CZ01D
	COG (NP0)	50	1.2pF	±.25pF	0.8	490-1374-1-ND	.35	2.03	5.85	490-1374-2-ND	4,000	5.55M	GRM1885C1H1R2CZ01D
	COG (NP0)	50	1.3pF	±.25pF	0.8	490-1375-1-ND	.35	2.03	5.85	490-1375-2-ND	4,000	5.62M	GRM1885C1H1R3CZ01D
	COG (NP0)	50	1.5pF	±.25pF	0.8	490-1376-1-ND	.26	1.53	4.42	490-1376-2-ND	4,000	4.16M	GRM1885C1H1R5CZ01D
	COG (NP0)	50	1.6pF	±.25pF	0.8	490-1377-1-ND	.35	2.03	5.85	490-1377-2-ND	4,000	5.55M	GRM1885C1H1R6CZ01D
	COG (NP0)	50	1.8pF	±.25pF	0.8	490-1378-1-ND	.35	2.03	5.85	490-1378-2-ND	4,000	5.55M	GRM1885C1H1R8CZ01D
	COG (NP0)	50	2.0pF	±.25pF	0.8	490-1379-1-ND	.26	1.53	4.42	490-1379-2-ND	4,000	4.16M	GRM1885C1H2R0CZ01D
	COG (NP0)	50	2.2pF	±.25pF	0.8	490-1380-1-ND	.35	2.03	5.85	490-1380-2-ND	4,000	5.55M	GRM1885C1H2R2CZ01D
	COG (NP0)	50	2.4pF	±.25pF	0.8	490-1381-1-ND	.35	2.03	5.85	490-1381-2-ND	4,000	5.62M	GRM1885C1H2R4CZ01D
	COG (NP0)	50	2.7pF	±.25pF	0.8	490-1382-1-ND	.35	2.03	5.85	490-1382-2-ND	4,000	5.55M	GRM1885C1H2R7CZ01D
	COG (NP0)	50	3.0pF	±.25pF	0.8	490-1383-1-ND	.26	1.53	4.42	490-1383-2-ND	4,000	4.16M	GRM1885C1H3R0CZ01D
	COG (NP0)	50	3.3pF	±.25pF	0.8	490-1384-1-ND	.35	2.03	5.85	490-1384-2-ND	4,000	5.55M	GRM1885C1H3R3CZ01D
	COG (NP0)	50	3.6pF	±.25pF	0.8	490-1385-1-ND	.35	2.03	5.85	490-1385-2-ND	4,000	5.55M	GRM1885C1H3R6CZ01D
	COG (NP0)	50	3.9pF	±.25pF	0.8	490-1386-1-ND	.35	2.03	5.85	490-1386-2-ND	4,000	5.55M	GRM1885C1H3R9CZ01D
	COG (NP0)	50	4.0pF	±.25pF	0.8	490-1387-1-ND	.26	1.53	4.42	490-1387-2-ND	4,000	4.16M	GRM1885C1H4R0CZ01D
	COG (NP0)	50	4.3pF	±.25pF	0.8	490-1388-1-ND	.35	2.03	5.85	490-1388-2-ND	4,000	5.55M	GRM1885C1H4R3CZ01D
	COG (NP0)	50	4.7pF	±.25pF	0.8	490-1389-1-ND	.35	2.03	5.85	490-1389-2-ND	4,000	5.55M	GRM1885C1H4R7CZ01D
	COG (NP0)	50	5.0pF	±.25pF	0.8	490-1390-1-ND	.26	1.53	4.44	490-1390-2-ND	4,000	4.16M	GRM1885C1H5R0CZ01D
	COG (NP0)	50	5.1pF	±.5pF	0.8	490-1391-1-ND	.35	2.03	5.85	490-1391-2-ND	4,000	5.62M	GRM1885C1H5R1DZ01D
	COG (NP0)	50	5.6pF	±.5pF	0.8	490-1392-1-ND	.35	2.03	5.85	490-1392-2-ND	4,000	5.55M	GRM1885C1H5R6DZ01D
	COG (NP0)	50	6.0pF	±.5pF	0.8	490-1393-1-ND	.26	1.53	4.42	490-1393-2-ND	4,000	4.16M	GRM1885C1H6R0DZ01D
	COG (NP0)	50	6.2pF	±.5pF	0.8	490-1394-1-ND	.35	2.03	5.85	490-1394-2-ND	4,000	5.55M	GRM1885C1H6R2DZ01D
	COG (NP0)	50	6.6pF	±.25pF	0.8	490-1395-1-ND	.54	3.20	9.22	490-1395-2-ND	4,000	9.01M	GRM1885C1H6R8CZ01D
	COG (NP0)	50	6.8pF	±.5pF	0.8	490-1396-1-ND	.35	2.03	5.85	490-1396-2-ND	4,000	5.62M	GRM1885C1H6R9DZ01D
	COG (NP0)	50	7.0pF	±.5pF	0.8	490-1397-1-ND	.26	1.53	4.42	490-1397-2-ND	4,000	4.16M	GRM1885C1H7R0DZ01D
	COG (NP0)	50	7.5pF	±.5pF	0.8	490-1398-1-ND	.35	2.03	5.85	490-1398-2-ND	4,000	5.55M	GRM1885C1H7R5DZ01D
	COG (NP0)	50	8.0pF	±.5pF	0.8	490-1399-1-ND	.26	1.53	4.42	490-1399-2-ND	4,000	4.16M	GRM1885C1H8R0DZ01D
	COG (NP0)	50	8.2pF	±.5pF	0.8	490-1400-1-ND	.35	2.03	5.85	490-1400-2-ND	4,000	5.62M	GRM1885C1H8R2DZ01D
	COG (NP0)	50	9.0pF	±.5pF	0.8	490-1401-1-ND	.26	1.53	4.42	490-1401-2-ND	4,000	4.16M	GRM1885C1H9R0DZ01D
	COG (NP0)	50	9.1pF	±.5pF	0.8	490-1402-1-ND	.35	2.03	5.85	490-1402-2-ND	4,000	5.55M	GRM1885C1H9R1DZ01D
	COG (NP0)	50	10pF	±.5%	0.8	490-1403-1-ND	.26	1.53	4.42	490-1403-2-ND	4,000	4.16M	GRM1885C1H10J0A01D
	COG (NP0)	50	11pF	±.5%	0.8	490-1404-1-ND	.37	2.16	6.24	490-1404-2-ND	4,000	5.99M	GRM1885C1H11J0A01D
	COG (NP0)	50	12pF	±.5%	0.8	490-1405-1-ND	.26	1.53	4.42	490-1405-2-ND	4,000	4.16M	GRM1885C1H12J0A01D
	COG (NP0)	50	13pF	±.5%	0.8	490-1406-1-ND	.37	2.16	6.24	490-1406-2-ND	4,000	6.24M	GRM1885C1H13J0A01D
	COG (NP0)	50	15pF	±.5%	0.8	490-1407-1-ND	.26	1.53	4.42	490-1407-2-ND	4,000	4.16M	GRM1885C1H15J0A01D
	COG (NP0)	50	16pF	±.5%	0.8	490-1408-1-ND	.37	2.16	6.24	490-1408-2-ND	4,000	5.99M	GRM1885C1H16J0A01D
	COG (NP0)	50	18pF	±.5%	0.8	490-1409-1-ND	.26	1.53	4.42	490-1409-2-ND	4,000	4.16M	GRM1885C1H18J0A01D
	COG (NP0)	50	20pF	±.5%	0.8	490-1410-1-ND	.33	1.98	5.72	490-1410-2-ND	4,000	5.55M	GRM1885C1H20J0A01D
	COG (NP0)	50	22pF	±.5%	0.8	490-1411-1-ND	.26	1.54	4.44	490-1411-2-ND	4,000	4.16M	GRM1885C1H22J0A01D
	COG (NP0)	50	24pF	±.5%	0.8	490-1412-1-ND	.37	2.16	6.24	490-1412-2-ND	4,000	6.24M	GRM1885C1H24J0A01D
	COG (NP0)	50	27pF	±.5%	0.8	490-1413-1-ND	.26	1.53	4.42	490-1413-2-ND	4,000	4.16M	GRM1885C1H27J0A01D
	COG (NP0)	50	30pF	±.5%	0.8	490-1414-1-ND	.37	2.16	6.24	490-1414-2-ND	4,000	6.24M	GRM1885C1H30J0A01D
	COG (NP0)	50	33pF	±.5%	0.8	490-1415-1-ND	.18	1.08	3.12	490-1415-2-ND	4,000	2.78M	GRM1885C1H33J0A01D
	COG (NP0)	50	36pF	±.5%	0.8	490-1416-1-ND	.37	2.16	6.24	490-1416-2-ND	4,000	6.24M	GRM1885C1H36J0A01D
	COG (NP0)	50	39pF	±.5%	0.8	490-1417-1-ND	.26	1.53	4.42	490-1417-2-ND	4,000	4.16M	GRM1885C1H39J0A01D
	COG (NP0)	50	43pF	±.5%	0.8	490-1418-1-ND	.37	2.16	6.24	490-1418-2-ND	4,000	5.99M	GRM1885C1H43J0A01D
	COG (NP0)	50	47pF	±.5%	0.8	490-1419-1-ND	.18	1.08	3.12	490-1419-2-ND	4,000	2.78M	GRM1885C1H47J0A01D
	COG (NP0)	50	51pF	±.5%	0.8	490-1420-1-ND	.37	2.16	6.24	490-1420-2-ND	4,000	5.99M	GRM1885C1H51J0A01D
	COG (NP0)	50	56pF	±.5%	0.8	490-1421-1-ND	.26	1.53	4.42	490-1421-2-ND	4,000	4.16M	GRM1885C1H56J0A01D
	COG (NP0)	50	62pF	±.5%	0.8	490-1422-1-ND	.37	2.16	6.24	490-1422-2-ND	4,000	6.24M	GRM1885C1H62J0A01D
	COG (NP0)	50	68pF	±.5%	0.8	490-1423-1-ND	.26	1.53	4.42	490-1423-2-ND	4,000	4.16M	GRM1885C1H68J0A01D
	COG (NP0)	50	75pF	±.5%	0.8	490-1424-1-ND	.37	2.16	6.24	490-1424-2-ND	4,000	6.24M	GRM1885C1H75J0A01D
	COG (NP0)	50	82pF	±.5%	0.8	490-1425-1-ND	.26	1.53	4.42	490-1425-2-ND	4,000	4.16M	GRM1885C1H82J0A01D
	COG (NP0)	50	91pF	±.5%	0.8	490-1426-1-ND	.37	2.16	6.24	490-1426-2-ND	4,000	6.24M	GRM1885C1H91J0A01D
	COG (NP0)	50	100pF	±.5%	0.8	490-1427-1-ND	.19	1.15	3.31	490-1427-2-ND	4,000	3.47M	GRM1885C1H101J0A01D
	COG (NP0)	50	110pF	±.5%	0.8	490-1428-1-ND	.53	3.15	9.10	490-1428-2-ND	4,000	9.01M	GRM1885C1H111J0A01D
	COG (NP0)	50	120pF	±.5%	0.8	490-1429-1-ND	.30	1.76	5.07	490-1429-2-ND	4,000	4.85M	GRM1885C1H121J0A01D
	COG (NP0)	50	130pF	±.5%	0.8	490-1430-1-ND	.55	3.29	9.49	490-1430-2-ND	4,000	9.01M	GRM1885C1H131J0A01D
	COG (NP0)	50	150pF	±.5%	0.8	490-1431-1-ND	.30	1.76	5.07	490-1431-2-ND	4,000	4.85M	GRM1885C1H151J0A01D
	COG (NP0)	50	160pF	±.5%	0.8	490-1432-1-ND	.55	3.29	9.49	490-1432-2-ND	4,000	9.01M	GRM1885C1H161J0A01D
	COG (NP0)	50	180pF	±.5%	0.8	490-1433-1-ND	.30	1.76	5.07	490-1433-2-ND	4,000	4.85M	GRM1885C1H181J0A01D
	COG (NP0)	50	200pF	±.5%	0.8	490-1434-1-ND	.56	3.33	9.62	490-1434-2-ND	4,000	9.23M	GRM1885C1H201J0A01D
	COG (NP0)	50	220pF	±.5%	0.8	490-1435-1-ND	.26	1.53	4.42	490-1435-2-ND	4,000	4.16M	GRM1885C1H221J0A01D
	COG (NP0)	50	240pF	±.5%	0.8	490-1436-1-ND	.58	3.42	9.88	490-1436-2-ND	4,000	9.48M	GRM1885C1H241J0A01D
	COG (NP0)	50	270pF	±.5%	0.8	490-1437-1-ND	.30	1.80	5.20	490-1437-2-ND	4,000	4.85M	GRM1885C1H271J0A01D
	COG (NP0)	50	300pF	±.5%	0.8	490-1438-1-ND	.58	3.42	9.88	490-1438-2-ND	4,000	9.48M	GRM1885C1H301J0A01D
	COG (NP0)	50	330pF	±.5%	0.8	490-1439-1-ND	.33	1.94	5.59	490-1439-2-ND	4,000	5.55M	GRM1885C1H331J0A01D
	COG (NP0)	50	360pF	±.5%	0.8	490-1440-1-ND	.60	3.51	10.14	490-1440-2-ND	4,000	9.71M	GRM1885C1H361J0A01D
	COG (NP0)	50	390pF	±.5%	0.8	490-1441-1-ND	.44	2.61	7.54	490-1441-2-ND	4,000	6.93M	GRM1885C1H391J0A01D
	COG												