




# Power Connectors .062" Diameter Connectors



Features: • UL File Number E-29179; CSA File Number LR-19980 • Up to 5 amperes per circuit • 250 Voltage rating • Friction lock • Standard color is natural (Ratings are per circuit and based on fully loaded housings.)




Grid Space	Grid No.	Type	Maximum Amps V.	Dimensions (Inch) A B C D F	Digi-Key Part No.	Pricing 1 10 100	Molex Part No.	
<b>Connector Housings - with Detent Only, Free Hanging</b>								
.145"	1	Plug	5 250	— .750 — —	WM1201-ND	.07 .67 6.10	03-06-2011	
		Recept.	5 250	— .780 — —	WM1200-ND	.08 .76 6.94	03-06-1011	
	2	Plug	5 250	.609 .318 .780 .300 .440	WM1220-ND	.07 .66 6.01	03-06-2023	
		Recept.	5 250	.505 .265 .810 .192 .340	WM1230-ND	.07 .66 6.01	03-06-1023	
	3	Plug	5 250	.754 .318 .750 .300 .590	WM1221-ND	.10 .94 8.59	03-06-2032	
		Recept.	5 250	.650 .265 .780 .192 .484	WM1231-ND	.09 .85 7.73	03-06-1032	
	4	Plug	5 250	.865 .312 .750 .295 .730	WM1222-ND	.14 1.27 11.59	03-06-2042	
		Recept.	5 250	.785 .260 .780 .192 .630	WM1232-ND	.14 1.27 11.59	03-06-1042	
	4a	Plug	5 250	.615 .465 .750 .442 .442	WM1223-ND	.18 1.69 15.46	03-06-2044	
		Recept.	5 250	.506 .400 .750 .339 .339	WM1233-ND	.22 2.11 19.14	03-06-1044	
	5	Plug	5 250	1.044 .318 .750 .310 .890	WM1224-ND	.24 2.30 20.87	03-06-2055	
		Recept.	5 250	.940 .265 .780 .192 .775	WM1234-ND	.23 2.14 19.49	03-06-1056	
	6	Plug	5 250	.615 .607 .750 .600 .450	WM1225-ND	.16 1.51 13.74	03-06-2061	
		Recept.	5 250	.552 .505 .780 .494 .344	WM1235-ND	.24 2.26 20.61	03-06-1062	
	9	Plug	5 250	.752 .615 .750 .590 .590	WM1226-ND	.16 1.51 13.74	03-06-2092	
		Recept.	5 250	.650 .552 .780 .494 .344	WM1236-ND	.24 2.21 20.18	03-06-1092	
	12	Plug	5 250	.903 .614 .750 .590 .740	WM1227-ND	.16 1.51 13.74	03-06-2122	
		Recept.	5 250	.795 .563 .780 .494 .634	WM1237-ND	.24 2.25 20.52	03-06-1122	
	15	Plug	5 250	1.042 .614 .750 .590 .880	WM1228-ND	.20 1.85 16.92	03-06-2152	
		Recept.	5 250	.934 .563 .780 .487 .776	WM1238-ND	.22 2.05 18.72	03-06-1152	
	24	Plug	5 250	1.182 .765 .750 .740 1.040	WM1229-ND	1.05 9.98 90.17	03-06-2242	
		Recept.	5 250	1.182 .765 .750 .740 1.040	WM1239-ND	1.05 9.98 90.17	03-06-2242	
	.145"	2	Plug	5 250	.609 .318 .780 .300 .440	WM1203-ND	.08 .75 6.87	03-06-2024
			Recept.	5 250	.505 .265 .810 .192 .340	WM1202-ND	.09 .85 7.73	03-06-1022
3		Plug	5 250	.754 .318 .750 .300 .590	WM1205-ND	.13 1.19 10.91	03-06-2033	
		Recept.	5 250	.650 .265 .780 .192 .484	WM1204-ND	.16 1.49 13.59	03-06-1038	
4		Plug	5 250	.754 .318 .750 .300 .590	WM1207-ND	.20 1.87 17.09	03-06-2041	
		Recept.	5 250	.785 .260 .780 .192 .630	WM1206-ND	.22 2.11 19.14	03-06-1041	
4a		Plug	5 250	.615 .465 .750 .442 .442	WM1209-ND	.19 1.81 16.49	03-06-2043	
		Recept.	5 250	.506 .400 .750 .339 .339	WM1208-ND	.22 2.11 19.14	03-06-1043	

Grid Space	Grid No.	Type	Maximum Amps V.	Dimensions (Inch) A B C D F	Digi-Key Part No.	Pricing 1 10 100	Molex Part No.
.145"	5	Plug	5 250	1.044 .318 .750 .310 .890	WM1240-ND	24 2.30 20.87	03-06-2054
		Recept.	5 250	.940 .265 .780 .192 .775	WM1241-ND	24 2.30 20.87	03-06-1055
	6	Plug	5 250	.615 .607 .750 .600 .450	WM1211-ND	25 2.36 21.44	03-06-2062
		Recept.	5 250	.552 .505 .780 .494 .344	WM1212-ND	17 1.60 14.60	03-06-1061
	9	Plug	5 250	.752 .615 .750 .590 .590	WM1213-ND	24 2.29 20.87	03-06-2091
		Recept.	5 250	.650 .552 .780 .494 .344	WM1214-ND	26 2.42 22.02	03-06-1091
12	Plug	5 250	.903 .614 .750 .590 .740	WM1215-ND	22 2.02 18.46	03-06-2121	
	Recept.	5 250	.795 .563 .780 .494 .634	WM1216-ND	26 2.48 22.58	03-06-1121	
15	Plug	5 250	1.042 .614 .750 .590 .880	WM1217-ND	33 3.10 28.25	03-06-2151	
	Recept.	5 250	.930 .569 .780 .530 .770	WM1589-ND	33 3.08 28.00	03-06-6155	
24	Plug	5 250	1.182 .765 .750 .740 1.040	WM1219-ND	92 8.65 78.62	03-06-2241	
	Recept.	5 250	1.079 .715 .750 .634 .918	WM1218-ND	88 8.33 75.77	03-06-1241	
.165"	36	Plug	4 —	1.795 .825 .750 1.02 1.622	WM1588-ND	.94 8.84 80.72	03-06-2361
		Recept.	4 —	1.677 .707 .781 .855 1.505	WM1587-ND	1.05 9.92 90.18	03-06-1361

## .062" Terminals

Features: • Use with .062" housings • .008" stock 70/30 brass Temp. Range: -40°C - 105°C High Volt. Test: Withstands 1500V RMS for 60 seconds Current Rating: Amperage rating 5A Storage Temperature Range: -40°C - 125°C Plating: 200-300µ Hot-Tin Dip tin plating




Description	Wire Size	Insulation Dia. (Inch)	Digi-Key Part No.	Pricing 10 100 500	Mfr. Part No.
Male, Crimp Type	18-24	.060/.120	WM1000-ND	.50 4.57 17.51	02-06-2103
Female, Crimp Type	18-24	.060/.120	WM1001-ND	.36 3.32 15.62	02-06-1103
Male, Crimp Type	24-30	.040/.090	WM1002-ND	.38 3.53 16.61	02-06-2132
Female, Crimp Type	24-30	.040/.090	WM1003-ND	.55 5.07 23.85	02-06-1132
Female, Crimp Type	24-30	.040/.090	WM1003TR-ND	230.20/20.000	02-06-1131
Male, PCB Solder-Tail	—	—	WM1004-ND	1.04 9.57 45.02	02-06-6103
Female, PCB Solder-Tail	—	—	WM1005-ND	1.03 9.46 44.51	02-06-7103
Male, Crimp Type	18-24	.060/.120	WM1006-ND†	2.89 26.52 124.77	02-06-6103
Male, Crimp Type	24-30	.040/.090	WM1007-ND†	3.06 28.11 132.25	02-06-6135
Female, Crimp Type	18-24	.060/.120	WM1008-ND†	3.49 32.05 150.78	02-06-5103
Female, Crimp Type	18-24	.060/.120	WM1008TR-ND†	699.06/6.000	02-06-5100
Female, Crimp Type	24-30	.040/.090	WM1009-ND†	3.08 28.28 133.05	02-06-5135
Male, PCB	—	—	WM1010-ND†	5.16 47.35 222.76	02-06-6122
Female, PCB	—	—	WM1011-ND†	3.12 28.38 108.80	02-06-7104
Hand Crimp Tool (Waldom)	18-30	—	WM9900-ND	20.29/1	WHT-1921
Hand Extraction Tool (Waldom)	18-30	—	WM1586-ND	9.14/1	WHT-2023
Universal Crimp Tool	—	—	WM9999-ND	70.79/1	63811-1000
Hand Crimp Tool	24-30	—	WM9021-ND	233.76/1	63819-0800
Production Tool	18-24	—	WM18585-ND	376.05/1	63811-3300
Crimp Tool	18-24	—	WM9025-ND	176.61/1	63819-1300
Extraction Tool	—	—	WM9929-ND	23.60/1	11-03-0002

† 15µ Select Gold Finish † Tape and Reel

## Cable Connector Designer Kit

Contains all parts needed to assemble male and female connectors; totals 86 connectors. All have pin terminal size .062" diameter with crimping tool, pin terminal ejector and case.





WM9979-ND..... 99.36

# MLX™ .084" Power Connectors

Features: • Interchangeable, intermountable and interchangeable with industry standard versions • Cross tested to assure industry compatibility • UL recognized, CSA certified • Positive locks • Fully isolated contacts • Circuit I.D. grooves to reduce assembly errors • Anti-stress positioning tabs to reduce breakage



## Grid Pattern



Pos.	Description	Ampers/Circuit (Max.)*	Voltage Rating (Max.)*	Panel Cutout Dimension (Inch)							Digi-Key Part No.	Pricing				Molex Part No.				
													Fig. 1 - Plug							
2	Plug	13.5	600	.300	.550	—	—	—	—	—	—	WM1242-ND	.10	.97	8.80	33.75	50-84-1020			
3	Plug	13.5	600	.300	.800	—	—	—	—	—	—	WM1244-ND	.12	1.16	10.54	40.41	50-84-1030			
4	Plug	13.5	600	.300	1.050	—	—	—	—	—	—	WM1246-ND	.14	1.32	12.02	46.09	50-84-1040			
6	Plug	11.0	600	.800	.550	—	—	—	—	—	—	WM1248-ND	.14	1.31	11.94	56.16	50-84-1060			
9	Plug	11.0	600	.800	.800	—	—	—	—	—	—	WM1250-ND	.19	1.81	16.45	63.07	50-84-1090			
12	Plug	11.0	600	.800	1.050	—	—	—	—	—	—	WM1252-ND	.29	2.73	24.80	95.08	50-84-1120			
15	Plug	11.0	600	.800	1.300	—	—	—	—	—	—	WM1254-ND	.32	3.04	27.65	105.98	50-84-1150			
													Fig. 2 - Cap							
2	Cap	13.5	600	.300	.550	.340	.095	.250	.530	.565	—	WM1243-ND	.13	1.21	10.97	42.04	50-84-2020			
3	Cap	13.5	600	.300	.800	.340	.095	.250	.530	.815	—	WM1245-ND	.15	1.39	12.63	48.42	50-84-2030			
4	Cap	13.5	600	.300	1.050	.340	.095	.250	.530	1.065	—	WM1247-ND	.15	1.44	13.08	50.15	50-84-2040			
6	Cap	11.0	600	.800	.550	.340	.275	.250	1.030	.565	—	WM1249-ND	.18	1.65	15.04	57.67	50-84-2060			
9	Cap	11.0	600	.800	.800	.480	.275	.250	1.030	.815	—	WM1251-ND	.22	2.10	19.09	73.19	50-84-2090			
12	Cap	11.0	600	.800	1.050	.480	.275	.350	1.030	1.065	—	WM1253-ND	.35	3.30	30.04	115.14	50-84-2120			
15	Cap	11.0	600	.800	1.300	.480	.275	.350	1.030	1.315	—	WM1255-ND	.39	3.69	33.58	128.73	50-84-2150			
													Fig. 3 - Vertical Header							
2	Male	—	—	.300	.550	—	—	—	—	—	—	WM1256-ND	.20	1.89	17.21	65.96	10-84-4020			
2	Female	—	—	.300	.550	—	—	—	—	—	—	WM1263-ND	.19	1.81	16.45	63.06	10-84-4022			
3	Male	—	—	.300	.800	—	—	—	—	—	—	WM1257-ND	.26	2.45	22.31	85.53	10-84-4030			
4	Male	—	—	.300	1.050	—	—	—	—	—	—	WM1258-ND	.33	3.12	28.35	108.68	10-84-4040			
4	Female	—	—	.300	1.050	—	—	—	—	—	—	WM1265-ND	.36	3.41	31.02	118.90	10-84-4042			
6	Male	—	—	.800	.550	—	—	—	—	—	—	WM1259-ND	.50	4.73	43.04	164.99	10-84-4060			
6	Female	—	—	.800	.550	—	—	—	—	—	—	WM1266-ND	.55	5.15	46.79	179.36	10-84-4062			
9	Male	—	—	.800	.800	—	—	—	—	—	—	WM1260-ND	.68	6.38	57.98	222.27	10-84-4090			
9	Female	—	—	.800	.800	—	—	—	—	—	—	WM1267-ND	.74	7.01	63.69	244.16	10-84-4092			
12	Male	—	—	.800	1.050	—	—	—	—											

# molex Power Connectors



## .093" Diameter Connectors



### Features:


- UL File Number E-29179; CSA File Number LR-19980
- Up to 12 amperes per circuit, (ratings are per circuit and based on fully loaded housings)
- 250 Voltage rating for 03-09 series; 600 Voltage rating for 19-09 series
- Friction lock for 03-09 series; Positive lock for 19-09 series

A



### Grid Patterns

(Contacts sold separately)



Grid Space	Grid No.	Type	Maximum Amps V.	Dimensions (Inch)					Digi-Key Part No.	Pricing			Molex Part No.
				A	B	C	D	F		1	10	100	
<b>Connector Housings — with Detent Only, Free Hanging</b>													
.198"	1	Plug	12 5000	—	—	2.250	.437	—	WM1301-ND	.20	1.91	17.38	03-09-2014
	1	Plug	12 250	—	—	1.000	.358	—	WM1303-ND	.13	1.22	10.00	03-09-2011
		Recept.	12 250	—	—	1.000	.234	—	WM1302-ND	.11	1.04	9.00	03-09-1011
	3	Plug	12 250	.933	.375	.970	.340	.770	WM1325-ND	.10	.95	8.67	03-09-2032
		Recept.	12 250	.840	.312	1.015	.236	.670	WM1332-ND	.11	1.01	9.19	03-09-1032
	4	Plug	12 250	1.131	.375	1.000	.338	.971	WM1326-ND	.12	1.09	9.96	03-09-2042
		Recept.	12 250	1.038	.312	1.000	.236	.868	WM1333-ND	.15	1.43	13.05	03-09-1042
	4a	Plug	12 250	.555	.695	1.024	.538	.538	WM1327-ND	.24	2.24	20.44	03-09-2049
		Recept.	12 250	.500	.600	1.000	.434	.434	WM1334-ND	.27	2.49	22.76	03-09-1049
	5	Plug	12 250	—	—	.969	.350	1.170	WM1315-NDΔ	.30	2.79	25.50	03-09-2057
		Recept.	12 250	—	—	1.000	.240	1.070	WM1314-NDΔ	.29	2.69	24.48	03-09-1057
	6	Plug	11 250	1.230	.310	1.105	.240	1.070	WM1592-ND	.27	2.54	23.19	03-09-1054
Recept.		11 250	—	—	—	—	—	—	—	—	—	—	
90	Plug	9 250	.750	.695	1.000	.733	.536	WM1328-ND	.16	1.48	13.48	03-09-2062	
	Recept.	9 250	.718	.600	1.015	.632	.434	WM1335-ND	.15	1.41	12.88	03-09-1064	
12	Plug	9 250	.937	.660	.970	.730	.770	WM1329-ND	.20	1.85	16.92	03-09-2092	
	Recept.	9 250	.828	.725	1.015	.625	.666	WM1336-ND	.20	1.88	17.18	03-09-1094	
248"	Plug	7.5 250	1.155	.760	1.000	.737	.770	WM1330-ND	.23	2.13	19.41	03-09-2121	
	Recept.	7.5 250	1.050	.655	1.015	.633	.871	WM1337-ND	.27	2.50	22.84	03-09-1126	
2	Plug	12 250	1.050	.725	1.020	.690	.870	WM1590-ND	.71	6.68	56.00	03-09-1121	
	Recept.	12 250	.800	.375	1.000	.352	.639	WM1324-ND	.08	.75	6.87	03-09-2022	
2	Plug	12 250	.725	.312	1.030	.250	.536	WM1331-ND	.08	.75	6.87	03-09-1022	
	Recept.	12 250	—	—	—	—	—	—	—	—	—	—	
<b>Connector Housings — with Positive Lock, Free Hanging</b>													
.198"	4§	Plug	9 600	—	—	1.031	.359	1.156	WM1405-ND	.31	2.92	26.54	03-09-2048
	Recept.	9 600	—	—	1.063	.265	1.032	WM1404-ND	.32	3.05	27.76	03-09-1047	
248"	2	Plug	12 600	—	—	1.031	.359	.656	WM1401-ND	.25	2.32	21.06	03-09-2028
	Recept.	12 600	—	—	1.063	.265	.531	WM1400-ND	.23	2.19	19.90	03-09-1028	
<b>Connector Housings — with Mounting Ears and Detent, Panel Mount</b>													
3	Plug	12 250	.933	.375	.970	.340	.770	WM1307-ND	.19	1.79	14.00	03-09-2031	
	Recept.	12 250	.840	.312	1.015	.236	.670	WM1338-ND	.15	1.39	12.71	03-09-1081	
4	Plug	12 250	1.131	.375	.969	.338	.971	WM1309-ND	.30	2.82	22.00	03-09-2041	
	Recept.	12 250	1.038	.312	1.000	.236	.868	WM1308-ND	.29	2.73	21.00	03-09-1041	
4a	Plug	12 250	.555	.695	.969	.538	.538	WM1311-ND	.28	2.64	24.13	03-09-2040	
	Recept.	12 250	.500	.600	1.000	.434	.434	WM1310-ND	.24	2.29	20.87	03-09-1040	
90	Plug	9 250	.750	.695	.969	.733	.536	WM1317-ND	.54	5.08	42.00	03-09-2061	
	Recept.	9 250	.718	.600	1.015	.632	.434	WM1316-ND	.53	4.99	41.00	03-09-1061	
12	Plug	9 250	.937	.660	.970	.730	.770	WM1319-ND	.37	3.48	29.00	03-09-2091	
	Recept.	9 250	.828	.725	1.015	.625	.666	WM1318-ND	.35	3.29	27.00	03-09-1091	
15	Plug	7.5 250	1.155	.760	.969	.737	.975	WM1321-ND	.72	6.77	57.00	03-09-2122	
	Recept.	7.5 250	1.050	.665	1.015	.633	.871	WM1320-ND	.27	2.54	23.19	03-09-1125	
248"	2§	Plug	12 250	.800	.375	.968	.352	.639	WM1305-ND	.09	.85	7.73	03-09-2021
	Recept.	12 250	.725	.312	1.000	.250	.536	WM1304-ND	.08	.75	6.87	03-09-1027	
3	Plug	11 600	1.022	.365	1.100	.350	.862	WM1501-ND	.33	3.11	28.30	19-09-2031	
	Recept.	9 600	1.168	.311	1.140	.250	.760	WM1502-ND	.35	3.33	30.24	19-09-1043	
6	Plug	9 600	1.048	.658	1.100	.640	.886	WM1505-ND	.39	3.63	33.00	19-09-2061	
	Recept.	9 600	.946	.608	1.140	.540	.790	WM1504-ND	.39	3.63	33.00	19-09-1061	
9	Plug	8 600	.948	.850	1.140	.790	.790	WM1506-ND	.56	5.24	47.66	19-09-1091	
	Recept.	6 600	1.300	.910	1.100	.890	1.140	WM1509-ND	.46	4.33	39.50	19-09-2121	
15	Plug	6 600	1.552	.910	1.100	.890	1.388	WM1511-ND	1.05	9.95	90.41	19-09-2151	
	Recept.	6 600	1.422	.850	1.140	.790	1.282	WM1510-ND	1.05	9.95	90.41	19-09-2153	
<b>Housing Positive Lock Panel Mount UL94V-2</b>													
264"	1	Plug	12 600	.485	.394	.320	.320	.320	WM1601-ND	.17	1.61	14.68	19-09-2018
	Recept.	12 600	—	—	.300	.400	—	—	WM1600-ND	.15	1.40	12.70	19-09-1019
2	Plug	12 600	.800	.365	.635	.320	.580	WM1603-ND	.27	2.57	23.44	19-09-2028	
	Recept.	12 600	—	—	.300	.560	—	—	WM1602-ND	.15	1.41	12.88	19-09-1029
3	Plug	11 600	1.022	.365	.862	.320	.848	WM1605-ND	.18	1.69	15.46	19-09-2038	
	Recept.	11 600	—	—	.300	.830	—	—	WM1604-ND	.14	1.32	12.02	19-09-1039
4	Plug	9 600	1.270	.365	1.109	.321	1.110	WM1607-ND	.30	2.79	25.50	19-09-2048	
	Recept.	9 600	—	—	.300	1.090	—	—	WM1606-ND	.19	1.79	16.32	19-09-1049

Grid Space	Grid No.	Type	Maximum Amps V.	Dimensions (Inch)					Digi-Key Part No.	Pricing			Molex Part No.
				A	B	C	D	F		1	10	100	
.264"	6	Plug	9 600	1.048	.658	.888	.604	.850	WM1609-ND	.28	2.63	23.96	19-09-2068
	Recept.	9 600	—	—	.560	.830	—	—	WM1608-ND	.25	2.35	21.47	19-09-1069
	9	Plug	9 600	1.048	.909	.883	.868	.850	WM1611-ND	.46	4.34	39.59	19-09-2098
	Recept.	9 600	—	—	.560	.830	—	—	WM1610-ND	.39	3.62	33.06	19-09-1099
	12	Plug	9 600	1.100	.910	1.140	.668	1.112	WM1613-ND	.65	6.09	55.56	19-09-2128
	Recept.	9 600	—	—	.830	.900	—	—	WM1612-ND	.47	4.43	40.45	19-09-1129
15	Plug	9 600	1.552	.910	1.392	.868	1.380	WM1615-ND	.63	5.94	54.19	19-09-2158	
	Recept.	9 600	—	—	.868	1.380	—	—	WM1614-ND	.46	4.31	39.33	19-09-1159
<b>Housing Positive Lock Panel Mount UL94V-0</b>													
1	Plug	12 600	.485	.394	1.187	.250	.321	—	WM1678-ND	.19	1.78	16.22	19-09-2017
	Recept.	12 600	—	—	1.177	.300	.320	—	WM1670-ND	.15	1.36	12.45	19-09-1016
2	Plug	12 600	.800	.365	1.19	.32	.59	—	WM1679-ND	.35	3.34	30.40	19-09-2027
	Recept.	12 600	—	—	1.18	.30	.56	—	WM1671-ND	.23	2.19	20.01	19-09-1026
3	Plug	11 600	1.02	.394	1.187	.322	.850	—	WM1680-ND	.40	3.74	34.02	19-09-2037
	Recept.	11 600	—	—	1.177	.300	.827	—	WM1672-ND	.41	3.86	35.21	19-09-1036
4	Plug	9 600	—	—	—	—	—	—	WM1681-ND	.42	3.97	36.07	19-09-2047
	Recept.	9 600	—	—	1.177	.30	1.091	—	WM1673-ND	.29	2.76	25.16	19-09-1046
6	Plug	9 600	1.047	.681	1.187	.586	.850	—	WM1682-ND	.49	4.59	41.75	19-09-2067
	Recept.	9 600	—	—	1.177	.563	.827	—	WM1674-ND	.76	7.18	65.52	19-09-1066
9	Plug	9 600	1.048	.909	1.19	.850	.850	—	WM1683-ND	.51	4.85	44.07	19-09-2097
	Recept.	9 600	—	—	1.18	.83	.83	—	WM1675-ND	.52	4.93	45.00	19-09-1096
12	Plug	9 600	1.3	.91	1.19	.868	1.112	—	WM1684-ND	.58	5.47	49.73	19-09-2127
	Recept.	9 600	—	—	1.18	.83	1.09	—	WM1676-ND	.58	5.47	49.73	19-09-1126
15	Plug	9 600	1.552	.91	1.19	.868	1.38	—	WM1685-ND	.74	6.97	63.39	19-09-2157
	Recept.	9 600	—	—	1.18	.83	1.35	—	WM1677-ND	.49	4.64	42.34	19-09-1156
<b>Housing Positive Lock UL94V-2</b>													
.264"													