



Microcontrollers



8-Bit

This XC800 family of 8-bit microcontrollers offer a wide selection of products, combining a high performance 8051 core with on-chip Flash and ROM memory as well as a powerful mix of peripherals such as an enhanced CAPCOM6 (CC6), CAN, LIN and 10 bit ADC.

Based on the 8051 the C505CA enhances the C500 family of 8-bit microcontrollers by providing 32KByte of OTP or 16/32 KByte of ROM, 256 Byte of RAM, 1 KByte of XRAM, Controller Area Network (CAN) Version 2.0B, an asynchronous/synchronous serial interface and highly accurate 10-bit Analog to Digital Converter integrated on chip.

Max. Clock Rate (MHz)	ROM/OTP Flash (Byte)	Data Flash EEPROM (Byte)	RAM (Byte)	I/O Lines	ADC-Inputs/Max. Res. (Bit)	Timers/Counters (16 Bit)	Serial I/O	CAN 2.0B Active	On-Chip Oscillator	On-Chip Voltage Regulator	PWM	Package	Digi-Key Part No.	Price Each		Infineon Part No.
														1	25	
20	32K OTP/ROM	—	1028	34	8/10	3	USART	✓	✓	✓	4-ch	MOFP-44	SAB-C505CA-4EMCAIN-ND	14.92	13.43	SAB-C505CA-4EM CA
20	32K OTP/ROM	—	1028	34	8/10	3	USART	✓	✓	✓	4-ch	MOFP-44	SAF-C505CA-4EMCAIN-ND	15.67	14.10	SAF-C505CA-4EM CA
20	—	—	1028	34	8/10	3	USART	✓	✓	✓	4-ch	MOFP-44	SAF-C505CA-LMCAIN-ND	8.44	7.60	SAF-C505CA-LM CA
10	64K OTP	—	2304	57	8/10	3	USART+SSC	✓	✓	✓	4-ch	MOFP-80	SAF-C515C-8EMCAIN-ND	17.97	15.18	SAF-C515C-8EM CA
26.67	8K Flash	up to 4K	768	27	8/10	3	UART, SSC	—	✓	✓	3+1-ch	TSSOP-38	SAF-XC866-2FRIBCINCT-ND▲	4.07	3.24	SAF-XC866-2FRI BC
26.67	8K Flash	up to 4K	768	27	8/10	3	UART, SSC	—	✓	✓	3+1-ch	TSSOP-38	SAF-XC866-2FRIBCINTR-ND	4002.78/3,000	4.01	SAF-XC866-2FRI BC
26.67	16K Flash	up to 4K	768	27	8/10	3	UART, SSC	—	✓	✓	3+1-ch	TSSOP-38	SAF-XC866-4FRIBCINCT-ND▲	5.04	4.01	SAF-XC866-4FRI BC
26.67	16K Flash	up to 4K	768	27	8/10	3	UART, SSC	—	✓	✓	3+1-ch	TSSOP-38	SAF-XC866-4FRIBCINTR-ND	4963.47/3,000	3.99	SAF-XC866-4FRI BC
20	32K OTP/ROM	—	1028	34	8/10	3	USART	✓	✓	✓	4-ch	MOFP-44	SAK-C505CA-4EMCAINCT-ND▲	15.78	13.81	SAK-C505CA-4EM CA
20	32K OTP/ROM	—	1028	34	8/10	3	USART	✓	✓	✓	4-ch	MOFP-44	SAK-C505CA-4EMCAINTR-ND	6410.95/1,000	3.24	SAK-C505CA-4EM CA
26.67	8K Flash	up to 4K	768	27	8/10	3	UART, SSC	—	✓	✓	3+1-ch	TSSOP-38	SAK-XC866-2FRIBCINCT-ND▲	4.27	3.40	SAK-XC866-2FRI BC
26.67	8K Flash	up to 4K	768	27	8/10	3	UART, SSC	—	✓	✓	3+1-ch	TSSOP-38	SAK-XC866-2FRIBCINTR-ND	4202.94/3,000	4.01	SAK-XC866-2FRI BC
26.67	16K Flash	up to 4K	768	27	8/10	3	UART, SSC	—	✓	✓	3+1-ch	TSSOP-38	SAK-XC866-4FRIBCINCT-ND▲	5.02	3.99	SAK-XC866-4FRI BC
26.67	16K Flash	up to 4K	768	27	8/10	3	UART, SSC	—	✓	✓	3+1-ch	TSSOP-38	SAK-XC866-4FRIBCINTR-ND	4942.28/3,000	3.99	SAK-XC866-4FRI BC
24	32K Flash	up to 8K	1792	48	8/10	4	2xUART, SSC	MultiCAN w/2 Nodes	✓	✓	3+1-ch	TQFP-64	SAK-XC888CM-8FFAABINCT-ND▲	4.28	3.34	SAK-XC888CM-8FFA AB
24	32K Flash	up to 8K	1792	48	8/10	4	2xUART, SSC	MultiCAN w/2 Nodes	✓	✓	3+1-ch	TQFP-64	SAK-XC888CM-8FFAABINTR-ND	6195.27/1,900	3.34	SAK-XC888CM-8FFA AB
24	32K Flash	up to 8K	1792	48	8/10	4	2xUART, SSC	MultiCAN w/2 Nodes	✓	✓	3+1-ch	TQFP-64	SAK-XC888CM-8FFAACINCT-ND▲	8.36	7.17	SAK-XC888CM-8FFA 5V AC
24	32K Flash	up to 8K	1792	48	8/10	4	2xUART, SSC	MultiCAN w/2 Nodes	✓	✓	3+1-ch	TQFP-64	SAK-XC888CM-8FFAACINTR-ND	6035.84/1,900	7.17	SAK-XC888CM-8FFA 5V AC

▲ Cut Tape ◊ Tape and Reel

Starter Kits / Evaluation Boards

B158-H8576-X-0-7600IN-ND	XC866 Easy Kit: Mini Evaluation Kit with XC866	84.51	KIT_XC866_EKIN-ND	XC866/888 CLM Easy Kit: Mini Evaluation Kit	84.51
B158-H8548-X-0-7600IN-ND	XC866 Starter Kit: Full Evaluation Board with XC866	241.71	B158-H8743-X-X-7600IN-ND	XC866/888 CLM Starter Kit: Full Evaluation Board	241.71

16-Bit

Infineon's C166 Family, with pipelined 16-bit core architecture and optimized real-time embedded control peripherals, offers a wide range of performance variations. •C161: Cost optimized CPU and peripheral set control •C164: Lower pin count and price with excellent PWM capabilities and CAN apps •C165: Processor-oriented microcontroller with basic peripheral

set •C167: High-end 16-bit microcontroller with on-chip CAN. The XC164CM series is the new family of enhanced 16-bit microcontroller XC166 which offers impressive DSP performance and advanced interrupt handling combined with a powerful integrated peripheral set, high performance and reliable on-chip Flash memory

Max. CPU Clock (MHz)	Oscillator	3V	ROM/OTP Flash (Byte)	RAM (Byte)	I/O Lines	ADC-Inputs/Max. Res. (Bit)	Timers/Counters (16-Bit)	Serial I/O	Real Time Clock	CAN Interface 2.0B Active	Package	Digi-Key Part No.	Price Each		Infineon Part No.
													1	25	
25	PLL/Prescaler/Direct Input	—	256K Flash	2K	93	12/10	5	ASC+SSC	✓	CAN	TQFP-128	SAB-C161CS-LFCAIN-ND	24.04	20.30	SAB-C161CS-LF CA
25	Prescaler/Direct Input	—	—	2K	63	—	5	ASC+SSC	—	—	MOFP-80	SAB-C1610-LMHAIN-ND§	10.42	9.38	SAB-C1610-LM HA
25	PLL/Prescaler/Direct Input	—	—	2K	76	4/10	5	ASC+SSC	✓	—	TQFP-100	SAB-C161PI-LFCAINCT-ND▲	12.97	11.35	SAB-C161PI-LF CA
25	PLL/Prescaler/Direct Input	—	—	2K	76	4/10	5	ASC+SSC	✓	—	TQFP-100	SAB-C161PI-LFCAINTR-ND	7372.97/1,400	11.35	SAB-C161PI-LF CA
25	PLL/Prescaler/Direct Input	—	—	4K	111	16/10	9	UART+SSC	✓	CAN	MOFP-144	SAB-C167CR-LMHAIN-ND	22.01	18.59	SAB-C167CR-LM HA+
20	PLL/Prescaler/Direct Input	—	—	10K	93	12/10	9	ASC+SSC+IPC+J1850	✓	2 x CAN	TQFP-128	SAF-C161CS-LFCAINCT-ND▲	32.53	30.29	SAF-C161CS-LF CA
20	PLL/Prescaler/Direct Input	—	—	10K	93	12/10	9	ASC+SSC+IPC+J1850	✓	2 x CAN	TQFP-128	SAF-C161CS-LFCAINTR-ND	14301.39/1,000	30.29	SAF-C161CS-LF CA
20	Prescaler/Direct Input	✓	—	1K	63	—	3	ASC+SSC	—	—	MOFP-80	SAF-C161K-LM3VHAINCT-ND▲	14.98	13.11	SAF-C161K-LM 3V HA
20	Prescaler/Direct Input	✓	—	1K	63	—	3	ASC+SSC	—	—	MOFP-80	SAF-C161K-LM3VHAINTR-ND	5290.35/850	13.11	SAF-C161K-LM 3V HA
20	Prescaler/Direct Input	—	—	1K	63	—	3	ASC+SSC	—	—	MOFP-80	SAF-C161K-LMHAIN-ND	10.48	9.44	SAF-C161K-LM HA
25	Prescaler/Direct Input	—	—	2K	63	—	5	ASC+SSC	—	—	MOFP-80	SAF-C1610-L25MHAINCT-ND▲	14.40	12.61	SAF-C1610-L25M HA
25	Prescaler/Direct Input	—	—	2K	63	—	5	ASC+SSC	—	—	MOFP-80	SAF-C1610-L25MHAINTR-ND	5088.19/850	12.61	SAF-C1610-L25M HA
20	Prescaler/Direct Input	✓	—	2K	63	—	5	ASC+SSC	—	—	MOFP-80	SAF-C1610-LM3VHAINCT-ND▲	14.40	12.61	SAF-C1610-LM 3V HA
20	Prescaler/Direct Input	✓	—	2K	63	—	5	ASC+SSC	—	—	MOFP-80	SAF-C1610-LM3VHAINTR-ND	5088.19/850	12.61	SAF-C1610-LM 3V HA
20	Prescaler/Direct Input	—	—	2K	63	—	5	ASC+SSC	—	—	MOFP-80	SAF-C1610-LMHAINCT-ND▲	13.86	12.13	SAF-C1610-LM HA
20	Prescaler/Direct Input	—	—	2K	63	—	5	ASC+SSC	—	—	MOFP-80	SAF-C1610-LMHAINTR-ND	4896.06/850	12.13	SAF-C1610-LM HA
25	PLL/Prescaler/Direct Input	—	—	3K	76	4/10	5	ASC+SSC+IPC	✓	—	TQFP-100	SAF-C161PI-L25FCAINCT-ND▲	14.29	12.51	SAF-C161PI-L25F CA
25	PLL/Prescaler/Direct Input	—	—	3K	76	4/10	5	ASC+SSC+IPC	✓	—	TQFP-100	SAF-C161PI-L25FCAINTR-ND	8128.89/1,400	12.51	SAF-C161PI-L25F CA
25	PLL/Prescaler/Direct Input	—	—	3K	76	4/10	5	ASC+SSC+IPC	✓	—	MOFP-100	SAF-C161PI-L25MCAINCT-ND▲	15.09	13.20	SAF-C161PI-L25M CA
25	PLL/Prescaler/Direct Input	—	—	3K	76	4/10	5	ASC+SSC+IPC	✓	—	MOFP-100	SAF-C161PI-L25MCAINTR-ND	3182.19/500	13.20	SAF-C161PI-L25M CA
20	PLL/Prescaler/Direct Input	✓	—	3K	76	4/10	5	ASC+SSC+IPC	✓	—	TQFP-100	SAF-C161PI-LF3VCAINCT-ND▲	14.29	12.51	SAF-C161PI-LF 3V CA
20	PLL/Prescaler/Direct Input	—	—	3K	76	4/10	5	ASC+SSC+IPC	✓	—	TQFP-100	SAF-C161PI-LF3VCAINTR-ND	8128.89/1,400	12.51	SAF-C161PI-LF 3V CA
20	PLL/Prescaler/Direct Input	—	—	3K	76	4/10	5	ASC+SSC+IPC	✓	—	TQFP-100	SAF-C161PI-LFCAINCT-ND▲	13.61	11.92	SAF-C161PI-LF CA
20	PLL/Prescaler/Direct Input	—	—	3K	76	4/10	5	ASC+SSC+IPC	✓	—	TQFP-100	SAF-C161PI-LFCAINTR-ND	7741.88/1,400	11.92	SAF-C161PI-LF CA
20	PLL/Prescaler/Direct Input	✓	—	3K	76	4/10	5	ASC+SSC+IPC	✓	—	MOFP-100	SAF-C161PI-LM3VCAINCT-ND▲	15.09	13.20	SAF-C161PI-LM 3V CA
20	PLL/Prescaler/Direct Input	✓	—	3K	76	4/10	5	ASC+SSC+IPC	✓	—	MOFP-100	SAF-C161PI-LM3VCAINTR-ND	3182.19/500	13.20	SAF-C161PI-LM 3V CA
20	PLL/Prescaler/Direct Input	—	—	3K	76	4/10	5	ASC+SSC+IPC	✓	—	MOFP-100	SAF-C161PI-LMCAINCT-ND▲	14.37	12.58	SAF-C161PI-LM CA
20	PLL/Prescaler/Direct Input	—	—	3K	76	4/10	5	ASC+SSC+IPC	✓	—	MOFP-100	SAF-C161PI-LMCAINTR-ND	3032.57/500	12.58	SAF-C161PI-LM CA
25	PLL/Prescaler/Direct Input	—	—	2K	63	—	5	ASC+SSC	✓	—	MOFP-80	SAF-C161S-L25MAAINCT-ND▲	7.62	6.53	SAF-C161S-L25M AA
25	PLL/Prescaler/Direct Input	—	—	2K	63	—	5	ASC+SSC	✓	—	MOFP-80	SAF-C161S-L25MAAINTR-ND	2543.76/850	6.53	SAF-C161S-L25M AA
20	PLL/Prescaler/Direct Input	✓	—	2K	63	—	5	ASC+SSC	✓	—	MOFP-80	SAF-C161S-LM3VAAINCT-ND▲	7.62	6.53	SAF-C161S-LM 3V AA
20	PLL/Prescaler/Direct Input	—	—	2K	63	—	5	ASC+SSC	✓	—	MOFP-80	SAF-C161S-LM3VAAINTR-ND	2543.76/850	6.53	SAF-C161S-LM 3V AA
25	PLL/Prescaler/Direct Input	—	64K OTP	4K	59	8/10	5	ASC+SSC	✓	CAN	MOFP-80	SAF-C164CI-8E25MDBIN-ND	19.96	16.86	SAF-C164CI-8E25M DB
20	PLL/Prescaler/Direct Input	—	64K OTP	4K	59	8/10	5	ASC+SSC	✓	CAN	MOFP-80	SAF-C164CI-8EMCBINCT-ND▲	24.44	22.76	SAF-C164CI-8EM CB
20	PLL/Prescaler/Direct Input	—	64K OTP	4K	59	8/10	5	ASC+SSC	✓	CAN	MOFP-80	SAF-C164CI-8EMCBINTR-ND	9311.16/850	22.76	SAF-C164CI-8EM CB
20	PLL/Prescaler/Direct Input	—	64K OTP	4K	59	8/10	5	ASC+SSC	✓	CAN	MOFP-80	SAF-C164CI-8EMDBINCT-ND▲	24.44	22.76	SAF-C164CI-8EM DB
20	PLL/Prescaler/Direct Input	—	64K OTP	4K	59	8/10	5	ASC+SSC	✓	CAN	MOFP-80	SAF-C164CI-8EMDBINTR-ND	9311.16/850	22.76	SAF-C164CI-8EM DB
20	PLL/Prescaler/Direct Input	—	32K OTP	2K	50	8/12	5	ASC+SSC	✓	CAN	TQFP-64	SAF-C164CM-4EFABINCT-ND▲	22.75	19.91	SAF-C164CM-4EF AB
20	PLL/Prescaler/Direct Input	—	32K OTP	2K	50	8/12	5	ASC+SSC	✓	CAN	TQFP-64	SAF-C164CM-4EFABINTR-ND	17559.39/1,900	19.91	SAF-C164CM-4EF AB
25	PLL/Prescaler/Direct Input	—	—	2K	77	—	5	ASC+SSC	—	—	TQFP-100	SAF-C165-L25FAINCT-ND▲	23.17	20.28	SAF-C165-L25F HA
25	PLL/Prescaler/Direct Input	—	—	2K	77	—	5	ASC+SSC	—	—	TQFP-100	SAF-C165-L25FAINTR-ND	13178.32/1,400	20.28	SAF-C165-L25F HA
25	PLL/Prescaler/Direct Input	—	—	3K	72	—	5	ASC+SSC	—	—	MOFP-100	SAF-C165-L25MHAINCT-ND▲	22.70	21.14	SAF-C165-L25M HA

▲ Cut Tape ◊ Tape and Reel § Tray

(Continued)

Max. CPU Clock (MHz)	Oscillator	3V	ROM/OTP/Flash (Byte)	RAM (Byte)	I/O Lines	ADC Inputs/Max. Res. (Bit)	Timers/Counters (16-Bit)	Serial I/O	Real Time Clock	CAN Interface 2.0B Active	Package	Price Each		Infineon Part No.
												1	25	
25	PLL/Prescaler/Direct Input	—	—	3K	72	—	5	ASC+SSC	—	—	MOFP-100	5284.90/500	—	SAF-C165-L25MHAINTR-ND0
20	PLL/Prescaler/Direct Input	✓	—	2K	77	—	5	ASC+SSC	—	—	TOFP-100	23.17	20.28	SAF-C165-LF3VHA
20	PLL/Prescaler/Direct Input	✓	—	2K	77	—	5	ASC+SSC	—	—	TOFP-100	13178.32/1,400	—	SAF-C165-LF3V HA
20	PLL/Prescaler/Direct Input	—	—	2K	77	—	5	ASC+SSC	—	—	TOFP-100	22.53	19.71	SAF-C165-LF HA
20	PLL/Prescaler/Direct Input	—	—	2K	77	—	5	ASC+SSC	—	—	TOFP-100	12810.99/1,400	—	SAF-C165-LF HA
20	PLL/Prescaler/Direct Input	✓	—	2K	77	—	5	ASC+SSC	—	—	MOFP-100	21.93	20.43	SAF-C165-LM3V HA
20	PLL/Prescaler/Direct Input	✓	—	2K	77	—	5	ASC+SSC	—	—	MOFP-100	5105.73/500	—	SAF-C165-LM 3V HA
20	PLL/Prescaler/Direct Input	—	—	3K	72	—	5	ASC+SSC	—	—	MOFP-100	21.54	20.06	SAF-C165-LM HA
20	PLL/Prescaler/Direct Input	—	—	3K	72	—	5	ASC+SSC	—	—	MOFP-100	5013.02/500	—	SAF-C165-LM HA
20	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	TwinCAN	MOFP-64	13.57	11.88	SAF-XC164CM-4F20FAAINTR-ND0
20	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	10476.17/1,900	—	SAF-XC164CM-4F20F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	14.25	12.47	SAF-XC164CM-4F40FAAINTR-ND0
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	10999.97/1,900	—	SAF-XC164CM-4F40F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	14.02	12.27	SAF-XC164CM-8F20F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	10819.22/1,900	—	SAF-XC164CM-8F20F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	14.72	12.88	SAF-XC164CM-8F40F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	11360.05/1,900	—	SAF-XC164CM-8F40F AA
20	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	13.16	11.52	SAF-XC164GM-4F20F AA
20	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	10161.82/1,900	—	SAF-XC164GM-4F20F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	13.82	12.10	SAF-XC164GM-4F40F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	10670.01/1,900	—	SAF-XC164GM-4F40F AA
20	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	13.60	11.90	SAF-XC164GM-8F20F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	10494.64/1,900	—	SAF-XC164GM-8F20F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	14.27	12.50	SAF-XC164GM-8F40F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	11019.34/1,900	—	SAF-XC164GM-8F40F AA
20	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	—	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	12.77	11.18	SAF-XC164KM-4F20F AA
20	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	—	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	9857.15/1,900	—	SAF-XC164KM-4F20F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	—	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	13.41	11.74	SAF-XC164KM-4F40F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	—	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	10349.93/1,900	—	SAF-XC164KM-4F40F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	—	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	13.19	11.54	SAF-XC164KM-8F20F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	—	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	10179.57/1,900	—	SAF-XC164KM-8F20F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	—	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	13.84	12.12	SAF-XC164KM-8F40F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	—	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	10688.85/1,900	—	SAF-XC164KM-8F40F AA
20	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	—	7	2xASC+2xSSC	✓	—	TOFP-64	12.13	10.62	SAF-XC164LM-4F20F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	—	7	2xASC+2xSSC	✓	—	TOFP-64	9364.19/1,900	—	SAF-XC164LM-4F20F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	—	7	2xASC+2xSSC	✓	—	TOFP-64	12.74	11.15	SAF-XC164LM-4F40F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	—	7	2xASC+2xSSC	✓	—	TOFP-64	9832.41/1,900	—	SAF-XC164LM-4F40F AA
20	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	—	7	2xASC+2xSSC	✓	—	TOFP-64	12.53	10.97	SAF-XC164LM-8F20F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	—	7	2xASC+2xSSC	✓	—	TOFP-64	10670.65/1,900	—	SAF-XC164LM-8F20F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	—	7	2xASC+2xSSC	✓	—	TOFP-64	13.16	11.52	SAF-XC164LM-8F40F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	—	7	2xASC+2xSSC	✓	—	TOFP-64	10154.29/1,900	—	SAF-XC164LM-8F40F AA
20	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	12.89	11.29	SAF-XC164SM-4F20F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	9952.19/1,900	—	SAF-XC164SM-4F20F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	13.54	11.85	SAF-XC164SM-4F40F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	10449.99/1,900	—	SAF-XC164SM-4F40F AA
20	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	13.31	11.66	SAF-XC164SM-8F20F AA
20	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	10278.20/1,900	—	SAF-XC164SM-8F20F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	13.98	12.24	SAF-XC164SM-8F40F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	10791.95/1,900	—	SAF-XC164SM-8F40F AA
20	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	12.89	11.29	SAF-XC164TM-4F20F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	9952.19/1,900	—	SAF-XC164TM-4F20F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	13.54	11.85	SAF-XC164TM-4F40F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	10449.99/1,900	—	SAF-XC164TM-4F40F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	13.31	11.66	SAF-XC164TM-8F20F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	10278.20/1,900	—	SAF-XC164TM-8F20F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	13.98	12.24	SAF-XC164TM-8F40F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	—	TOFP-64	10791.95/1,900	—	SAF-XC164TM-8F40F AA
20	PLL/Prescaler/Direct Input	—	10K	93	12/10	9	ASC+SSC+I2C+J1850	2 x CAN	✓	2 x CAN	TOFP-128	33.85	31.52	SAK-C161CS-LF CA
20	PLL/Prescaler/Direct Input	—	10K	93	12/10	9	ASC+SSC+I2C+J1850	2 x CAN	✓	2 x CAN	TOFP-128	14880.10/1,000	—	SAK-C161CS-LF CA
25	PLL/Prescaler/Direct Input	—	64K OTP	4K	59	8/10	5	ASC+SSC	✓	CAN	MOFP-80	20.95	17.70	SAK-C164CI-8E25MDBIN-ND5
20	PLL/Prescaler/Direct Input	—	64K OTP	4K	59	8/10	5	ASC+SSC	✓	CAN	MOFP-80	19.96	16.86	SAK-C164CI-8EMCBIN-ND5
20	PLL/Prescaler/Direct Input	—	64K OTP	4K	59	8/10	5	ASC+SSC	✓	CAN	MOFP-80	19.96	16.86	SAK-C164CI-8EMDBIN-ND5
20	PLL/Prescaler/Direct Input	—	32K OTP	2K	50	8/12	5	ASC+SSC	✓	CAN	TOFP-64	21.99	20.48	SAK-C164CM-4EFABIN-ND0
20	PLL/Prescaler/Direct Input	—	32K OTP	2K	50	8/12	5	ASC+SSC	✓	CAN	TOFP-64	18371.57/1,900	—	SAK-C164CM-4EF AB
25	PLL/Prescaler/Direct Input	—	128K Flash	2K	111	16/10	9	ASC+SSC	—	CAN	MOFP-144	20.01	16.90	SAK-C167CR-LM HA+
40	PLL/Prescaler/Direct Input	—	32K Flash	8K	111	24/10	9	ASC+SSC	✓	CAN	MOFP-144	26.39	22.29	SAK-C167CR-LM40M CA+
25	PLL/Prescaler/Direct Input	—	32K Flash	8K	111	24/10	9	ASC+SSC	✓	CAN	MOFP-144	22.33	18.86	SAK-C167CS-LM CA+
25	PLL/Prescaler/Direct Input	—	128K Flash	2K	111	16/10	9	ASC+SSC	—	CAN	MOFP-144	23.99	20.27	SAK-C167SR-LM HA+
20	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	14.52	12.71	SAK-XC164CM-4F20FAAINTR-ND0
20	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	11209.60/1,900	—	SAK-XC164CM-4F20F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	15.25	13.35	SAK-XC164CM-4F40F AA
40	PLL/Prescaler/Direct Input	—	32K Flash	4K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	11769.98/1,900	—	SAK-XC164CM-4F40F AA
20	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	15.00	13.13	SAK-XC164CM-8F20F AA
20	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	11576.49/1,900	—	SAK-XC164CM-8F20F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14	7	2xASC+2xSSC	✓	TwinCAN	TOFP-64	15.75	13.78	SAK-XC164CM-8F40F AA
40	PLL/Prescaler/Direct Input	—	64K Flash	6K	47	14								

32-Bit

The TriCore™ is the first unified, single-core, 32-bit microcontroller-DSP architecture optimized for real-time embedded systems. The TriCore Instruction Set Architecture (ISA) combines the real-time capability of a microcontroller, the computational power of a DSP, and the high performance/price features of a RISC load/store architecture, in a compact re-programmable core.

C

Max. CPU Clock (MHz)	FPU	MMU	PCP	SRAM (Byte)	ROM/OTP/Flash/eDRAM (Byte)	I/O Lines	CAN	Package	Digi-Key Part No.	Price Each		Infineon Part No.
										1	25	
100	✓	✓	—	144K	—	72	—	LBGA-208	SAF-TC1100-L100EB-GBBINCT-ND▲	25.93	24.15	SAF-TC1100-L100EB-G BB
100	✓	✓	—	144K	—	72	—	LBGA-208	SAF-TC1100-L100EB-GBBINTR-ND◊	11400.21/1,000		SAF-TC1100-L100EB-G BB
150	✓	✓	—	144K	—	72	—	LBGA-208	SAF-TC1100-L150EB-GBBINCT-ND▲	27.75	25.84	SAF-TC1100-L150EB-G BB
150	✓	✓	—	144K	—	72	—	LBGA-208	SAF-TC1100-L150EB-GBBINTR-ND◊	12198.22/1,000		SAF-TC1100-L150EB-G BB
100	✓	✓	—	144K	—	72	MultiCAN	LBGA-208	SAF-TC1115-L100EB-GBBINCT-ND▲	27.74	25.84	SAF-TC1115-L100EB-G BB
100	✓	✓	—	144K	—	72	MultiCAN	LBGA-208	SAF-TC1115-L100EB-GBBINTR-ND◊	12197.66/1,000		SAF-TC1115-L100EB-G BB
150	✓	✓	—	144K	—	72	MultiCAN	LBGA-208	SAF-TC1115-L150EB-GBBINCT-ND▲	30.51	28.41	SAF-TC1115-L150EB-G BB
150	✓	✓	—	144K	—	72	MultiCAN	LBGA-208	SAF-TC1115-L150EB-GBBINTR-ND◊	13412.02/1,000		SAF-TC1115-L150EB-G BB
100	✓	✓	—	144K	—	72	MultiCAN	LBGA-208	SAF-TC1130-L100EB-GBBINCT-ND▲	32.64	30.39	SAF-TC1130-L100EB-G BB
100	✓	✓	—	144K	—	72	MultiCAN	LBGA-208	SAF-TC1130-L100EB-GBBINTR-ND◊	14350.73/1,000		SAF-TC1130-L100EB-G BB
150	✓	✓	—	144K	—	72	MultiCAN	LBGA-208	SAF-TC1130-L150EB-GBBINCT-ND▲	35.89	33.42	SAF-TC1130-L150EB-G BB
150	✓	✓	—	144K	—	72	MultiCAN	LBGA-208	SAF-TC1130-L150EB-GBBINTR-ND◊	15778.91/1,000		SAF-TC1130-L150EB-G BB
66	✓	—	—	48K	1M Flash	81	—	LQFP-176	SAF-TC1161-128F66HLAAIN-ND	22.22	18.77	SAF-TC1161-128F66HL AA
66	✓	—	—	48K	1M Flash	81	MultiCAN	LQFP-176	SAF-TC1162-128F66HLAAIN-ND	23.52	19.87	SAF-TC1162-128F66HL AA
80	✓	—	✓	80K	1.5M Flash	81	—	LQFP-176	SAF-TC1165-192F80HLAAIN-ND	26.92	22.74	SAF-TC1165-192F80HL AA
80	✓	—	✓	80K	1.5M Flash	81	MultiCAN	LQFP-176	SAF-TC1166-192F80HLAAIN-ND	28.23	23.84	SAF-TC1166-192F80HL AA

▲ Cut Tape ◊ Tape and Reel

Starter Kits

B158-H8690-X-0-7600IN-ND Full Starter Kit for TC116X 451.47

B158-H8539-G2-X-7600IN-ND Full Starter Kit for TC176X 591.91

B158-H8537-G2-X-7600IN-ND Full Starter Kit for TC179X 591.91



PK51 Professional Developer's Kit

The PK51 Professional Developer's Kit for the 8051 microcontroller family supports all 8051 derivatives including new devices with extended memory and instruction sets. On-chip peripherals and other key features of the 8051 are easy to access with the PK51 Professional Developer's Kit.

PK51-ND 1946.00

CA51 Compiler Kit

The CA51 Compiler Kit for the 8051 microcontroller family supports all 8051 derivatives including classic devices and IP cores from companies like Analog Devices, Atmel, Cypress Semiconductor, Dallas Semiconductor, Infineon, Intel, NXP, Silicon Labs, STMicroelectronics, Texas Instruments, and Winbond. On Chip peripherals and other key features of the 8051 are easy to access with the CA51 Compiler Kit.

CA51-ND 1197.00

RealView® Microcontroller Development Kit

The RealView Microcontroller Development Kit (MDK) supports ARM7, ARM9, and Cortex-M3 technology-based microcontrollers from Analog Devices, Atmel, Freescale, Luminary, NXP, OKI, Samsung, Sharp, STMicroelectronics, and Texas Instruments.

MDK-ARM-ND 2694.00

RealView® Real-Time Library

The RealView Real-Time Library is a collection of tightly-coupled libraries that are designed to solve the real-time and communication challenges of embedded systems based on ARM powered MCU devices. It also includes several drivers that interface the RTX Real-Time with various communication interfaces.

RTL-ARM-ND 2545.00

MCBXC88x Evaluation Board

The MCBXC88x Evaluation Board introduces you to the Infineon XC88x microcontroller family and allows you to create and test working programs for this 8051-based architecture. The CAN interface, analog input (via potentiometer), and eight LED's (on Port 3) make this board a great starting point for your next 8051 project.

MCBXC88x-ND 90.00

MCBXC167 Evaluation Board

The MCBXC167 Evaluation Board introduces you to the Infineon XC16x microcontroller family and allows you to create and test working programs for this advanced architecture. The board connects to your PC using the serial port (for Flash download) or the OCDs interface (for program debug using Keil ULINK USB-JTAG Adapter and the µVision IDE and Debugger).

MCBXC167-BASIC-ND 90.00

MCBSTR7 Evaluation Board

The MCBSTR7 Evaluation Board introduces you to the STMicroelectronics STR710 ARM family and allows you to create and test working programs for this advanced architecture. The board connects to your PC using the serial port (for Flash download) or the JTAG interface (for program debug using Keil ULINK USB-JTAG Adapter and the µVision IDE and Debugger).

MCBSTR7-ND 112.00

MCBSTR9 Evaluation Board

The MCBSTR9 Evaluation Board introduces you to the STMicroelectronics ARM9 family and allows you to create and test working programs for this advanced architecture. The board connects to your PC using the JTAG interface (for program debug using Keil ULINK USB-JTAG Adapter and the µVision IDE and Debugger). It provides serial (RS-232), CAN, Ethernet, and USB interfaces as well as eight LEDs, analog input (via potentiometer) and several push buttons.

MCBSTR9-ND 150.00

MCBx51 Evaluation Board

The MCBx51 single-board computer is an evaluation board that supports numerous 8051-compatible and 251-compatible devices. The MCBx51 allows you to investigate the capabilities of the 8051 and 251 and create real working programs with the Keil development tools. The MCBx51 works with any 44-pin 8051-compatible or 251-compatible device.

MCBx51-ND 225.00

MCB950 Evaluation Board

The MCB950 Evaluation Board is a versatile, flexible prototype board for the NXP P89LPC952 microcontroller family. It includes the Keil µVision LPC Development Studio which allows you to create and debug programs that program into the on-chip Flash ROM using FlashMagic.

MCB950-ND 75.00

ULINK USB-JTAG Adapter

The ULINK USB Interface Adapter connects your PC's USB port to your target hardware (via JTAG or OCDs) and allows you to debug embedded programs running on target hardware.

ULINK2-ND 225.00

Digi-Reel® Most SMT cutdown parts are available on a Digi-Reel®. For Digi-Reel part number, change 1-ND to 6-ND or CT-ND to DKR-ND. See Digi-Key® Services on page 2 for additional information.

Free shipping on orders over £50! All prices are in British pound sterling and include duties.

694 (UK091) uk.digikey.com — **FREephone: 0-800-587-0991 • 0-800-904-7786** — **FREEFAX: 0-800-587-0992 • 0-800-904-7783**